



COAXIAL

# Termination

**TERM-10W-183N+**

Mini-Circuits

50Ω DC to 18 GHz N-Male

**KEY FEATURES**

- Wideband Operation, DC to 18 GHz
- Input Power Handling, 10 W
- Excellent VSWR, 1.08:1 Typ.
- Rugged Construction

*Generic photo used for illustration purposes only***APPLICATIONS**

- Cellular Communications
- Satellite Communications
- Test & Measurement Systems
- Defense & Radar

**PRODUCT OVERVIEW**

Mini-Circuits' TERM-10W-183N+ is a wideband 50Ω high power termination capable of absorbing signals up to 10 W from DC to 18 GHz. It provides excellent return loss across its entire operating frequency range, effectively dissipating signal power with minimal reflections. This model's N-Type interface allows mating to any N-Female connector. The unit features rugged construction for a long life and comes in a Passivated Stainless-Steel housing.

**ELECTRICAL SPECIFICATIONS<sup>1</sup> AT +25°C**

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range	-	DC	-	18	GHz
VSWR	DC - 10 10 - 18	- -	1.04 1.18	1.35 1.40	:1

1. Specifications are tested to minimum frequency of 0.01 GHz

**ABSOLUTE MAXIMUM RATINGS<sup>2</sup>**

Operating Case Temperature	-45° C to +80° C
Storage Temperature	-45° C to +80° C
Input Power <sup>3</sup>	10 W

2. Permanent damage may occur if any of these limits are exceeded.

3. At +25°C derate linearly to 1 W at 125°C.

 REV. A  
 ECO-027525  
 TERM-10W-183N+  
 MCL NY  
 251015
**Mini-Circuits®**[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 4



COAXIAL







# Termination

TERM-10W-183N+

50Ω DC to 18 GHz N-Male

Mini-Circuits

## TYPICAL PERFORMANCE GRAPHS



Mini-Circuits®



COAXIAL

# Termination


**TERM-10W-183N+**

Mini-Circuits

50Ω DC to 18 GHz N-Male

**CONNECTOR SPECIFICATIONS**

Description	Connector
Connector Type	N-Male
Orientation	Straight

**CASE STYLE DRAWING**

Weight: 65.5 grams MAX

Dimensions are in inches [mm]. Tolerances: 2 Pl.±0.3; 3 Pl. ± .015 inches

**PRODUCT MARKING\*:** TERM-10W-183N+

\*Marking may contain other features or characters for internal lot control.



COAXIAL

# Termination

**TERM-10W-183N+**

50Ω DC to 18 GHz N-Male

**ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD****CLICK HERE**

Performance Data & Graphs	Data Graphs S-Parameter (S1P Files) Data Set (.zip file)
Case Style	LL3725-1
RoHS Status	Compliant
Environmental Ratings	ENV153

**NOTES**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)

**Mini-Circuits®**[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 4 OF 4

**Termination 50 Ω, N-Male****TERM-10W-183N+***Typical Performance Data (+25 °C)*

FREQ. (GHz)	VSWR (:1)
0.01	1.0
0.10	1.0
0.50	1.0
1.00	1.0
1.50	1.0
2.00	1.0
2.50	1.0
3.00	1.0
3.50	1.1
4.00	1.1
4.50	1.1
5.00	1.1
5.50	1.1
6.00	1.1
6.50	1.1
7.00	1.1
7.50	1.1
8.00	1.1
8.50	1.1
9.00	1.1
9.50	1.1
10.00	1.1
10.50	1.1
11.00	1.1
11.50	1.2
12.00	1.2
12.50	1.2
13.00	1.2
13.50	1.2
14.00	1.2
14.50	1.1
15.00	1.1
15.50	1.1
16.00	1.2
16.50	1.3
17.00	1.3
17.50	1.3
18.00	1.2




ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs &amp; shopping online see Mini-Circuits web site

 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
TERM-10W-183N+  
10/28/2025  
Page 1 of 1


*Typical Performance Curves*

# Case Style

LL

## Outline Dimensions

LL3725-1



Weight: 65.5 grams MAX

Dimensions are in inches [mm]. Tolerances: 2 Pl. $\pm$ .03; 3 Pl.  $\pm$  .015 inches

### Notes:

1. Case material: Aluminum Alloy.
2. Finish: Black Anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-45° C to 125° C or -45° C to 80° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-45° C to 125° C or -45° C to 80° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-45° to 125° C 5 Cycles	MIL-STD-202, Method 107, Condition B except -45° C instead of -65° C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I
Connector Durability	500 mating/unmating cycles	MIL-PRF-39012E, PARAGRAPH 4.6.12
Burn-In	5W for 16 hours; 10W for 16 hours	TERM-5W-183N+;TERM-10W-183N+