



LTCC SURFACE MOUNT


# Thru-Line

## TPCV-333+

50Ω DC to 33 GHz

### THE BIG DEAL

- Low Insertion Loss, 0.4 dB Typ.
- Return Loss, 13 dB Typ.
- 1210 Surface Mount Footprint
- Versatile "Place Holder" for Mini-Circuits LTCC Filters
- Power Handling: 6 W



Generic photo used for illustration purposes only

### APPLICATIONS

- Test and Measurement Equipment
- Communication, EW, Radar, and ECM Defense Systems
- 5G MIMO and Back Haul Radio Systems
- Satellite Communications

### FUNCTIONAL DIAGRAM



### PRODUCT OVERVIEW

TPCV-333+ is a miniature low temperature co-fired ceramic (LTCC) 50 Ohm transmission line, with low insertion loss through 33 GHz that supports a variety of applications. This model provides 0.4 dB typical insertion loss over a wide band due to its rugged monolithic construction. Housed in a 1210 ceramic form factor which is ideal for dense signal chain PCB layouts, where it complements MMIC size and performance. The LTCC fabrication process assures minimal RF performance variation while delivering a product that is well suited for environmental extremes of high humidity and temperature.

### KEY FEATURES

Features	Advantages
Footprint Compatible "Thru-Line"	Enables system designers the flexibility to plan to add LTCC filters to the PCB layout at a later stage in the design process, after system test results are available. Compatible with Mini-Circuits low pass filters (LFCV series), with identical case style and pad connections.
LTCC Construction	The use of LTCC technology allows for repeatable performance in a rugged ceramic package, well suited for tough environments such as high humidity and temperature extremes. See Mini-Circuits Environmental Rating ENV06T10 for more information.
Small Size, 1210	1210 package allows for space to be saved in dense circuit board layouts, while also minimizing the effects of parasitics.
Rugged Power Handling, 6 W	Handles up to 6 Watts in a small 1210 package.





### ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC - 19	—	0.3	0.7	dB
		F1-F2	19 - 28	—	0.4	0.9	
		F2-F3	28 - 33	—	0.8	—	
	Return Loss	DC-F1	DC - 19	—	16	—	dB
		F1-F2	19 - 28	—	13	—	
		F2-F3	28 - 33	—	13	—	
Group Delay	DC-F3	DC - 33	—	25	—	psec	

1. Tested on Evaluation Board P/N TB-TPCV-333+

2. Bi-directional RF1 and RF2 ports can be interchanged.


### ABSOLUTE MAXIMUM RATINGS<sup>3</sup>

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power <sup>4</sup>	6 W @ +25°C

3. Permanent damage may occur if any of these limits are exceeded.

4. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1.5 W at +125°C.


### TYPICAL FREQUENCY RESPONSE AT +25°C






### TYPICAL PERFORMANCE GRAPHS


TPCV-333+  
INSERTION LOSS



TPCV-333+  
RETURN LOSS



TPCV-333+  
GROUP DELAY





### FUNCTIONAL DIAGRAM




Figure 1. TPCV-333+ Functional Diagram

### PAD DESCRIPTION

Function	Pad Number	Description
RF1 <sup>2</sup>	1	Connects to RF Input Port
RF2 <sup>2</sup>	2	Connects to RF Output Port
GROUND	3	Connects to Ground on PCB, (See drawing PL-679)

### SUGGESTED PCB LAYOUT (PL-679)




NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4835 Lo Pro) WITH DIELECTRIC THICKNESS .0073±.0007. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
  - DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

Figure 2. Suggested PCB Layout PL-679

### CASE STYLE DRAWING



Weight: .03 grams  
Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005

### PRODUCT MARKING\*: WN

\*Marking may contain other features or characters for internal lot control.



LTCC SURFACE MOUNT

# Thru-Line

## TPCV-333+

Mini-Circuits

50Ω DC to 33 GHz

**ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASH BOARD. [CLICK HERE](#)**

Performance Data and Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	JV1210C-7    Lead Finish: Gold over Nickel Plating.
RoHS Status	Compliant
Tape and Reel	F74
Suggested Layout for PCB Design	PL-679
Evaluation Board	TB-TPCV-333+
	Gerber File
Environmental Rating	ENV06T10

### NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)








Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
0.01	0.00	0.00	0.01	56.14	49.13	47.06	56.95	49.24	47.15
0.10	0.01	0.01	0.02	44.83	42.37	40.00	44.90	42.38	40.04
0.20	0.01	0.02	0.02	40.14	39.75	38.17	40.18	39.67	38.17
0.30	0.01	0.02	0.03	37.76	38.29	37.12	37.53	37.96	36.86
0.40	0.01	0.02	0.03	37.48	37.78	36.58	36.81	37.20	36.09
0.50	0.01	0.02	0.03	37.93	37.81	36.51	37.08	37.18	36.02
0.60	0.01	0.02	0.03	38.07	37.87	36.72	37.83	37.72	36.63
0.70	0.01	0.02	0.03	38.07	37.79	37.07	38.84	38.45	37.59
0.80	0.01	0.02	0.03	38.23	37.78	37.50	40.12	38.99	38.46
0.90	0.01	0.02	0.03	38.01	37.37	37.55	41.12	39.05	38.99
1.00	0.01	0.02	0.03	37.29	36.55	37.10	40.50	38.25	38.70
2.00	0.02	0.03	0.04	29.25	29.49	29.87	29.64	29.79	30.17
3.00	0.02	0.03	0.05	28.43	27.40	25.81	28.87	27.80	26.26
4.00	0.00	0.02	0.04	31.30	29.34	26.00	29.81	28.48	25.63
5.00	0.03	0.05	0.06	26.76	25.52	23.63	26.17	25.34	23.63
6.00	0.07	0.09	0.10	19.86	19.60	18.97	19.97	19.79	19.22
7.00	0.06	0.08	0.10	18.17	18.30	17.69	18.21	18.35	17.75
8.00	0.03	0.05	0.06	24.25	23.73	22.64	24.21	23.53	22.36
9.00	0.03	0.05	0.06	29.16	32.81	39.06	27.18	30.09	32.75
10.00	0.03	0.04	0.06	23.17	24.62	27.55	22.76	24.36	27.06
10.50	0.02	0.04	0.05	25.93	26.49	29.52	25.41	26.12	29.02
11.00	0.01	0.03	0.05	34.25	33.15	36.02	31.78	31.60	34.71
11.50	0.02	0.04	0.06	35.42	40.09	37.75	33.12	37.74	37.45
12.00	0.04	0.06	0.07	26.89	28.14	28.93	26.94	28.93	29.71
12.50	0.05	0.07	0.09	24.66	25.06	25.61	24.79	25.69	26.09
13.00	0.06	0.08	0.10	25.17	24.85	24.87	25.07	25.08	24.85
13.50	0.06	0.08	0.10	29.04	27.52	26.80	28.66	27.33	26.34
14.00	0.04	0.06	0.08	35.31	33.98	32.70	43.68	36.97	33.02
14.50	0.03	0.05	0.08	27.78	28.46	31.57	30.51	32.33	38.25
15.00	0.04	0.06	0.08	22.36	22.73	24.29	23.25	23.89	25.80
15.50	0.07	0.09	0.11	20.04	20.15	21.24	20.30	20.60	21.81
16.00	0.10	0.12	0.14	19.63	19.81	20.30	19.45	19.84	20.46
16.50	0.10	0.13	0.15	21.66	21.61	21.31	21.10	21.28	21.20
17.00	0.08	0.11	0.13	27.18	26.59	24.65	26.45	26.12	24.59
17.50	0.07	0.10	0.12	33.62	34.11	29.76	44.71	41.41	32.47
18.00	0.08	0.10	0.13	26.25	28.43	29.91	27.00	30.49	37.74
18.50	0.09	0.11	0.14	25.35	26.51	28.40	24.63	26.85	31.64
19.00	0.10	0.12	0.14	27.40	27.62	28.69	26.89	28.69	33.42
19.50	0.09	0.11	0.13	30.27	30.65	30.75	29.71	32.03	33.72
20.00	0.09	0.12	0.14	28.90	31.47	32.44	28.52	31.44	31.84
20.50	0.10	0.12	0.15	31.61	34.84	40.93	29.82	32.62	35.36
21.00	0.10	0.12	0.14	36.25	37.53	31.54	45.81	43.65	34.33
21.50	0.09	0.11	0.13	22.80	24.50	22.50	24.66	25.97	23.50
22.00	0.13	0.15	0.18	17.99	19.43	18.89	18.77	19.81	19.12
22.50	0.18	0.21	0.23	16.27	17.56	18.23	16.38	17.29	17.89
23.00	0.21	0.22	0.24	16.67	17.81	20.29	16.36	17.21	19.43
24.00	0.06	0.06	0.06	25.45	25.24	27.26	25.88	25.81	30.68
25.00	0.01	0.03	0.05	22.46	24.02	21.87	26.39	26.46	23.54
26.00	0.11	0.14	0.17	30.06	32.47	25.77	35.84	41.75	28.91
27.00	0.19	0.22	0.24	16.14	16.79	15.86	16.36	16.89	16.18
28.00	0.20	0.22	0.23	13.72	14.07	15.36	13.86	14.14	15.36
29.00	0.15	0.18	0.21	18.23	18.87	22.69	19.10	19.43	23.04
29.50	0.15	0.18	0.22	26.01	26.82	30.60	28.74	30.51	33.28
30.00	0.17	0.20	0.23	26.94	24.32	22.38	28.17	25.84	22.61
30.50	0.17	0.20	0.22	19.79	18.45	18.34	20.48	19.08	18.65
31.00	0.15	0.18	0.20	17.04	16.32	17.18	17.96	16.96	17.70
31.50	0.12	0.15	0.19	16.44	16.31	17.89	17.46	16.96	18.58
32.00	0.11	0.15	0.19	17.36	18.02	19.83	18.70	18.99	21.24
32.50	0.12	0.17	0.21	19.72	21.67	22.85	21.99	24.03	25.74
33.00	0.16	0.20	0.24	24.09	26.53	27.15	29.90	36.50	31.51

*Typical Performance Data*

FREQ.  (GHz)	GROUP DELAY		
	(psec)		
	@-55°C	@+25°C	@+125°C
0.01	17.24	19.33	20.78
0.10	18.53	18.53	18.53
0.50	19.79	19.75	20.38
1.00	19.08	19.38	19.74
2.00	19.71	19.73	20.06
3.00	19.56	19.62	19.88
4.00	19.83	19.98	20.18
5.00	19.17	19.75	19.43
6.00	18.26	18.74	19.07
7.00	19.30	19.46	19.74
8.00	16.43	17.40	13.52
9.00	19.90	19.69	20.44
10.00	18.80	18.55	19.28
11.00	19.33	19.85	18.96
12.00	18.86	20.03	19.12
13.00	21.24	21.07	21.34
14.00	20.01	20.97	20.75
15.00	22.35	21.59	22.18
16.00	20.13	19.36	20.44
17.00	19.36	19.34	19.71
18.00	18.99	21.40	19.84
19.00	21.73	20.23	21.26
20.00	19.37	19.86	19.31
21.00	18.45	19.28	17.52
22.00	22.16	20.37	20.55
23.00	15.93	17.69	17.44
24.00	21.24	20.25	23.16
25.00	24.78	23.74	24.74
26.00	21.89	22.15	21.86
27.00	21.85	20.30	20.65
28.00	17.88	18.76	19.64
28.50	18.04	19.55	19.60
29.00	21.04	22.32	21.86
29.50	22.30	22.14	21.59
30.00	20.83	20.83	20.54
30.50	21.97	20.42	21.68
31.00	21.47	20.29	22.26
31.50	22.06	22.11	21.32
32.00	22.24	22.81	22.39
32.50	21.42	23.03	21.15
33.00	20.96	21.54	21.45

## Typical Performance Curves






# Case Style

# JV

## Outline Dimensions

## JV1210C-7



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT.GRAM
JV1210C-7	.126 (3.20)	.098 (2.50)	.039 (1.00)	.049 (1.25)	.006 (0.15)	.010 (0.25)	.024 (0.60)	.032 (0.81)	.014 (0.36)	.024 (0.61)	.131 (3.33)	.103 (2.63)	.052 (1.31)	.010 (0.25)	0.03

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3Pl.  $\pm .005$

### Notes:

1. Open style, Ceramic base.
2. Termination finish: **as shown below or indicated on Data Sheet.**  
For RoHS Case Styles: Gold plate over Nickel plate. All models, (+) suffix.
3. Pad tolerance is non-cumulative. Minimum spacing between each pad is .004.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F74


## DEVICE ORIENTATION IN T&R



**ILLUSTRATION 1**

### Applicable Case Styles

GE0805C-1  
GE0805C-1AP  
JV1210C-1  
GU2939



**ILLUSTRATION 2**

### Applicable Case Styles

JV1210C  
JV1210C-2  
JV1210C-3  
JV1210C-4  
JV1210C-5  
JV1210C-6  
JV1210C-11

**ILLUSTRATION 3**

### Applicable Case Styles

JC0603C-8  
JC0603C-9  
JV1210C-7  
JV1210C-8  
JV1210C-9  
JV1210C-10  
JV1210C-13  
GE0805C-13  
GE0805C-19  
GE0805C-20

Tape Width, mm	Device Cavity Pitch, mm	Real Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	2000
				4000

Note: Small reel availability varies by model. Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers** NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-003129	NEW RELEASE	JUL 20	DDR	VC
OR1	ECO-019409	JV1210C-13 ADDED	OCT 23	AGS	VC

SUGGESTED MOUNTING CONFIGURATION FOR JV1210C-7, JV1210C-13 CASE STYLE



NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (R04835 Lo Pro) WITH DIELECTRIC THICKNESS  $.0073 \pm .0007$ . COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN DDR	02 JUL 20
TOLERANCES ON:	CHECKED RV	02 JUL 20
2 PL DECIMALS ±	APPROVED RKS	02 JUL 20
3 PL DECIMALS ± .005"		
ANGLES ±		
FRACTIONS ±		

**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235

PL, JV1210C-7, JV1210C-13, TB-LFCV-X+

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-679	OR1
FILE:	98PL679	SCALE:	9:1
		SHEET:	1 OF 1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Test B,B1, 95% Coverage
Thermal Shock	-55° to +125°C, 15 min dwell,250 cycles	MIL-STD-202, Method 107
Bend Test	1mm, deflection for 5 seconds Span of bending: 2.75"	--
High Temp Storage	125°C to 1000 Hrs	---