



THE BIG DEAL

- Low loss, less than 1 dB max at 20 GHz
- Return Loss, 14 dB typical below 20 GHz
- Standard 1812 (4.5mm x 3.2mm) case style
- Suited for very high-volume production



Generic photo used for illustration purposes only

CASE STYLE: NM1812C-3

APPLICATIONS

- Test and Measurement
- EW, Radar and ECM Defense Systems
- 5G MIMO and Back Haul Radio
- Satellite Communications

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

PRODUCT OVERVIEW

The TPHK-3002+ is a 50 Ohm transmission line which can pass signals with low insertion loss typ 1.3 dB up to 30 GHz. This can be used as a place holder in system boards in the absence of LTCC filters. In addition, this low loss device provides excellent matching between devices.

KEY FEATURES

Feature	Advantages
Cost effective	LTCC is scalable technology that is cost effective due to ease of production in high quantities.
Small size (4.5mm x 3.2mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.
Surface Mountable	Suitable for very high volume automated assembly process.

REV. A
ECO-022343
TPHK-3002+
MCL NY
240808



ELECTRICAL SPECIFICATIONS¹ AT 25°C

Parameter	F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	DC-F1	0.1-10	—	0.2	0.5	dB
	F1-F2	10-20	—	0.6	1	
	F2-F3	20-30	—	1.3	2.0	
Return Loss	DC-F1	0.1-10	—	20	—	dB
	F1-F2	10-20	—	14	—	
	F2-F3	20-30	—	7	—	


1. Measured on Mini-Circuits Test Board TB-TPHK-3002C+ with connectors and feed lines de-embedded.

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input	1 W max.

Permanent damage may occur if any of these limits are exceeded

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC







CERAMIC

Thru-Line

TPHK-3002+

50Ω DC to 30 GHz


DEMO BOARD MCL P/N: TB-TPHK-3002C+ SUGGESTED PCB LAYOUT (PL-730)




NOTES:

- PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
- TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



LAYER 3 & PTH




PAD CONNECTIONS

INPUT	1
OUTPUT	2
GROUND	3

PRODUCT MARKING : F446

OUTLINE DRAWING



Weight: .126 grams.

Dimensions are in inches [mm]. Tolerances: 2Pl.±.01; 3Pl. ±.005



CERAMIC



Thru-Line

TPHK-3002+

50Ω DC to 30 GHz

TYPICAL PERFORMANCE DATA AT 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
100	0.02	41.80
1000	0.08	32.12
11000	0.19	30.66
12000	0.26	27.64
13000	0.26	23.70
14000	0.23	19.62
16000	0.39	18.50
18000	0.30	21.34
20000	0.36	23.40
22000	0.46	15.27
24000	0.77	10.07
26000	0.79	10.40
28000	0.50	14.38
30000	0.43	23.85



NOTES



- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html




Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.1	0.02	41.80
0.3	0.04	37.46
0.5	0.05	35.52
0.8	0.06	33.25
1.0	0.08	32.12
1.5	0.10	29.70
2.0	0.11	28.53
2.5	0.11	28.64
3.0	0.10	30.10
3.5	0.10	31.98
4.0	0.10	31.33
4.5	0.12	28.62
5.0	0.14	25.77
5.5	0.16	24.09
6.0	0.16	23.30
6.5	0.16	23.31
7.0	0.17	24.03
7.5	0.24	24.42
8.0	0.22	25.74
8.5	0.21	26.94
9.0	0.20	28.53
9.5	0.18	31.85
10.0	0.16	37.97
10.5	0.17	35.44
11.0	0.19	30.66
11.5	0.23	28.98
12.0	0.26	27.64
12.5	0.28	25.72
13.0	0.26	23.70
13.5	0.25	21.48
14.0	0.23	19.62
14.5	0.25	18.27
15.0	0.30	17.74
15.5	0.36	17.77
16.0	0.39	18.50
16.5	0.39	19.04
17.0	0.36	19.50
17.5	0.33	20.11
18.0	0.30	21.34
18.5	0.29	24.38
19.0	0.30	31.87
19.5	0.32	31.84
20.0	0.36	23.40
20.5	0.41	20.05
21.0	0.45	18.11
21.5	0.46	16.62
22.0	0.46	15.27
22.5	0.50	13.65
23.0	0.58	12.05
23.5	0.68	10.87
24.0	0.77	10.07
24.5	0.81	9.86
25.0	0.82	9.92
25.5	0.81	10.16
26.0	0.79	10.40
26.5	0.74	10.79
27.0	0.68	11.30
27.5	0.59	12.40
28.0	0.50	14.38
28.5	0.43	17.85
29.0	0.39	24.32
29.5	0.39	33.10
30.0	0.43	23.85

Typical Performance Curves





Weight: .126 grams.

Dimensions are in inches [mm]. Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$ Inches

Notes:

1. Case material: Ceramic.
2. Termination Finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin Plate over Nickel plate. All models, (+) suffix.

Mini-Circuits[®]
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-013254	NEW RELEASE	05/16/22	ITG	IL
A	ECO-015587	UPDATED STACK-UP DIAGRAM	11/01/22	ITG	IL
B	ECO-020890	ADDED DIMENSIONS	02/16/24	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR
NM1812C-3 CASE STYLE



STACK-UP DIAGRAM




- TOTAL FINISHED THICKNESS 0.0228±.004.
- B-VIA PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 2.
- PTH PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 4.
- INDICATED PLUGGED PTH'S ARE PLUGGED WITH EPOXY AND CAPPED WITH COPPER FROM TOP SIDE.
- LAYER 4 IS CONTINUOUS GROUND PLANE.

NOTES:

- PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
- TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
	DRAWN	ITG	05/16/22
	CHECKED	GF	05/16/22
	APPROVED	IL	05/16/22

DIMENSIONS ARE IN INCHES
TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005
ANGLES ±
FRACTIONS ±




Mini-Circuits[®] 13 Neptune Avenue
Brooklyn NY 11235

PL, NM1812C-3, TB-1239


Mini-Circuits[®]
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-730	B
FILE:	98PL730	SCALE: 8:1	SHEET: 1 OF 2

LAYER 2, B-VIA & PTH



LAYER 3 & PTH



 Mini-Circuits

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



ALL DIMENSIONS ARE IN INCHES EXCEPT OTHERWISE SPECIFIED

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-730	REV: B
-----------	---------------------	--------------------------	-----------


ASHEETA2.DWG REV:A DATE: 01/12/94

FILE: 98PL730	SCALE: 8:1	SHEET: 2 OF 2
------------------	---------------	------------------

Evaluation Board and Circuit




Schematic Diagram



STACK-UP DIAGRAM

Notes:

1. 2.92 mm Female End Launch Connector.
2. PCB Material: Megtron 6 R5775(N).
Dielectric Constant=3.6.
3. Total finished thickness .023".

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Cycling	-55 to 125°C, 100 cycles, Dwell Time 15 minutes.	MIL-STD-202, Method 107, Condition A-3
Mechanical Shock	50g, 11ms half-sine, 18 shocks applied each to 3 axes	MIL-STD-202 Method 213, Condition A
Vibration	10-2000Hz sine, 20g, 12 cycles applied each to 3 axes	MIL-STD-202, Method 204, Condition D
Constant Acceleration	30Kg, Y1 Direction	MIL-STD-883, Method 2001, Condition E
Humidity	85°C, 90-95% Relative Humidity, 250hours	
Solderability	10X / 30X Magnification	J-STD-002C Test S, J-STD-002C Test S1
High Temp Storage	125°C, 250 hours	