


Surface Mount RF Transformer

75Ω 1 to 400 MHz

TRS1.33-1T-75+



Generic photo used for illustration purposes only

CASE STYLE: AT577

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.75W
DC Current	300mA

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

PRIMARY DOT	1
PRIMARY	3
SECONDARY DOT	6
SECONDARY	4
SECONDARY CT	5
NOT USED	2

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.200	.200	.200	.075	.050	.025
5.08	5.08	5.08	1.91	1.27	0.64
G	H	J	K	wt	
.026	.070	.220	.035	grams	
0.66	1.78	5.59	0.89	0.15	

Config. A



Features

- wideband, 1 to 400 MHz
- good return loss
- excellent amplitude unbalance and phase unbalance
- DC isolated

Applications

- impedance matching
- balanced to unbalance transformer
- push-pull amplifiers
- CATV

Electrical Specifications at 25°C


Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Impedance Ratio (secondary/primary)			1.33		Ohm
Frequency Range		1	—	400	MHz
Insertion Loss*	1 - 400	—	0.6	1.2	dB
	5 - 200	—	0.4	0.9	
Amplitude Unbalance	1 - 400	—	1.10	2.0	dB
	5 - 200	—	0.5	0.9	
Phase Unbalance	1 - 400	—	3	8	Degree
	5 - 200	—	2	7	

* Insertion Loss is referenced to mid-band loss, 0.4 dB.


Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (Deg.)
1.00	0.68	21.22	0.03	0.01
5.00	0.40	29.54	0.03	0.09
10.00	0.37	33.00	0.03	0.17
50.00	0.38	33.93	0.01	0.68
100.00	0.40	30.23	0.09	1.27
150.00	0.42	27.24	0.22	1.86
200.00	0.45	25.42	0.37	2.23
300.00	0.51	22.48	0.80	2.91
350.00	0.55	21.37	1.08	3.16
400.00	0.60	20.37	1.37	3.35

TRS1.33-1T-75+
INSERTION LOSS



TRS1.33-1T-75+
INPUT RETURN LOSS



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



RF Transformer


TRS1.33-1T-75+

Typical Performance Data


FREQUENCY MHz	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
1.0	0.68	21.22	0.03	0.01
3.0	0.47	26.74	0.03	0.03
5.0	0.40	29.54	0.03	0.09
7.0	0.38	31.32	0.04	0.11
9.0	0.37	32.52	0.03	0.15
10.0	0.37	33.00	0.03	0.17
30.0	0.36	35.17	0.02	0.44
50.0	0.38	33.93	0.01	0.68
70.0	0.39	32.43	0.03	0.93
90.0	0.40	30.90	0.07	1.17
100.0	0.40	30.23	0.09	1.27
125.0	0.42	28.64	0.14	1.54
150.0	0.42	27.24	0.22	1.86
175.0	0.44	26.30	0.29	2.01
200.0	0.45	25.42	0.37	2.23
225.0	0.47	24.56	0.46	2.40
250.0	0.48	23.82	0.57	2.59
275.0	0.50	23.12	0.68	2.72
300.0	0.51	22.48	0.80	2.91
325.0	0.53	21.92	0.93	3.04
350.0	0.55	21.37	1.08	3.16
375.0	0.58	20.81	1.22	3.21
400.0	0.60	20.37	1.37	3.35

Typical Performance Data


Average Insertion Loss




Input Return Loss



Amplitude Unbalance





Phase Unbalance




Outline Dimensions

AT577



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
AT577	.200 (5.08)	.200 (5.08)	.200 (5.08)	.075 (1.91)	.050 (1.27)	.025 (0.64)	.026 (0.66)	.070 (1.78)	.220 (5.59)	.035 (0.89)	-- --	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish:
For RoHS Case Style: 2-10 μ inch (.05-.25 microns) Gold over 100-300 μ inch (2.54-7.62 microns) Nickel plate.
For RoHS-5 Case Style: Tin-Lead plate



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F73

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		13	Standard	1000
		2000		

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits[®]

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT




TB-575+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215