



COAXIAL

# Fixed Attenuator

UNAT-A-SERIES

Mini-Circuits

50Ω Up to 2W DC to 6000 MHz

## THE BIG DEAL

- Wideband coverage, DC to 6000 MHz
- Up to 2 Watt rating
- Rugged unibody construction
- Excellent VSWR
- Excellent flatness



Generic photo used for illustration purposes only

## APPLICATIONS

- Signal level adjustment
- Impedance matching

|            |               |
|------------|---------------|
| Model No.  | UNAT-A-SERIES |
| Case Style | FF779         |
| Connectors | N-Type        |

**+RoHS Compliant**  
 The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## PRODUCT OVERVIEW

Mini-Circuits' UNAT-A series are fixed attenuators from DC to 6000 MHz frequency range with excellent flatness in attenuation. UNAT-A series is available with nominal attenuation of 1 to 30 dB. This attenuator series support testing and measurement application. Precise performance, excellent VSWR and rugged unibody construction makes this model ideal solution for systems requiring precise attenuation across very wide frequency range.

## KEY FEATURES

| Feature             | Advantages                                      |
|---------------------|---|
| Rugged construction | Excellent durability for a long lifetime of use |
| Up to 2 Watt rating | Good power handling                             |
| Excellent VSWR      | Well matched for 50 Ω systems                   |
| Flat attenuation    | Good performance over the band                  |

REV. B  
 ECO-019296  
 UNAT-10A+  
 EDU4155  
 URJ  
 230923





COAXIAL

# Fixed Attenuator


UNAT-10A+

### MAXIMUM RATINGS

|                       |                |
|-----------------------|----------------|
| Operating Temperature | -45°C to 100°C |
| Storage Temperature   | -55°C to 100°C |

Permanent damage may occur if any of these limits are exceeded.

### OUTLINE DRAWING



### OUTLINE DIMENSIONS (Inch/mm)

| A  | B     | C  | D     | E     | Wt.   |
|----|-------|----|-------|-------|-------|
| -- | .71   | -- | 2.11  | .718  | grams |
| -- | 18.03 | -- | 53.59 | 18.24 | 72.5  |

Note: Please refer to case style drawing for details



### ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter                                     | Condition (MHz) | Min. | Typ.     | Max. | Unit |
|---|-----------------|------|----------|------|------|
| Frequency Range                               |                 | DC   | -        | 6000 | MHz  |
| Attenuation <sup>1</sup> nominal <sup>3</sup> | 10              | -    | 10 ± 0.3 | -    | dB   |
| Attenuation Flatness <sup>2</sup>             | DC - 3000       | -    | 0.20     | -    | dB   |
|   | 3000 - 4500     | -    | 0.15     | -    |      |
|   | 4500 - 6000     | -    | 0.20     | -    |      |
|   | DC - 6000       | -    | 0.40     | -    |      |
| VSWR  | DC - 3000       | -    | 1.2      | 1.6  | :1   |
|   | 3000 - 4500     | -    | 1.2      | 1.6  |      |
|   | 4500 - 6000     | -    | 1.3      | -    |      |
| Input Power <sup>4</sup>                      |                 | -    | -        | 1.7  | W    |

1. Attenuation varies by 0.3 dB max. over temperature.
2. Flatness = variation over band divided by 2.
3. Nominal attenuation at 10 MHz
4. RF power at 25°C is 1.7W; Derate linearly to 1.0W at 85°C

### TYPICAL PERFORMANCE DATA

| Frequency (MHz) | Attenuation (dB) | VSWR (:1) |
|-----------------|------------------|-----------|
| 10              | 9.95             | 1.12      |
| 100             | 9.97             | 1.11      |
| 500             | 10.02            | 1.12      |
| 900             | 10.05            | 1.12      |
| 1000            | 10.06            | 1.12      |
| 1400            | 10.09            | 1.13      |
| 1500            | 10.10            | 1.13      |
| 2000            | 10.14            | 1.14      |
| 2500            | 10.18            | 1.14      |
| 2800            | 10.20            | 1.14      |
| 3000            | 10.21            | 1.14      |
| 4000            | 10.30            | 1.13      |
| 4500            | 10.35            | 1.12      |
| 5000            | 10.39            | 1.12      |
| 6000            | 10.48            | 1.15      |



- NOTES
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  - Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)





# Coaxial Fixed Attenuator

# UNAT-10A+

## Typical Performance Data

| FREQ. | ATTENUATION | VSWR |
|-------|-------------|------|
| (MHz) | (dB)        | (:1) |
| 10    | 9.95        | 1.12 |
| 20    | 9.95        | 1.12 |
| 50    | 9.96        | 1.12 |
| 100   | 9.97        | 1.11 |
| 200   | 9.99        | 1.11 |
| 300   | 10.00       | 1.11 |
| 400   | 10.01       | 1.11 |
| 500   | 10.02       | 1.12 |
| 600   | 10.02       | 1.12 |
| 700   | 10.03       | 1.12 |
| 800   | 10.05       | 1.12 |
| 900   | 10.05       | 1.12 |
| 1000  | 10.06       | 1.12 |
| 1100  | 10.07       | 1.12 |
| 1200  | 10.08       | 1.12 |
| 1300  | 10.08       | 1.13 |
| 1400  | 10.09       | 1.13 |
| 1500  | 10.10       | 1.13 |
| 1600  | 10.11       | 1.13 |
| 1700  | 10.12       | 1.13 |
| 1800  | 10.13       | 1.13 |
| 1900  | 10.13       | 1.14 |
| 2000  | 10.14       | 1.14 |
| 2100  | 10.15       | 1.14 |
| 2200  | 10.16       | 1.14 |
| 2300  | 10.16       | 1.14 |
| 2400  | 10.17       | 1.14 |
| 2500  | 10.18       | 1.14 |
| 2600  | 10.19       | 1.14 |
| 2700  | 10.19       | 1.14 |
| 2800  | 10.20       | 1.14 |
| 2900  | 10.21       | 1.14 |
| 3000  | 10.21       | 1.14 |
| 3100  | 10.23       | 1.14 |
| 3200  | 10.23       | 1.14 |
| 3300  | 10.24       | 1.14 |
| 3400  | 10.25       | 1.14 |
| 3500  | 10.26       | 1.14 |
| 3600  | 10.26       | 1.13 |
| 3700  | 10.27       | 1.13 |
| 3800  | 10.28       | 1.13 |
| 3900  | 10.29       | 1.13 |
| 4000  | 10.30       | 1.13 |
| 4100  | 10.31       | 1.13 |
| 4200  | 10.32       | 1.12 |
| 4300  | 10.33       | 1.12 |
| 4400  | 10.34       | 1.12 |
| 4500  | 10.35       | 1.12 |
| 4600  | 10.35       | 1.12 |
| 4700  | 10.36       | 1.12 |
| 4800  | 10.37       | 1.12 |
| 4900  | 10.38       | 1.12 |
| 5000  | 10.39       | 1.12 |
| 5100  | 10.40       | 1.12 |
| 5200  | 10.41       | 1.12 |
| 5300  | 10.42       | 1.12 |
| 5400  | 10.43       | 1.13 |
| 5500  | 10.44       | 1.13 |
| 5800  | 10.46       | 1.14 |
| 6000  | 10.48       | 1.15 |

## Typical Performance Curves




# Case Style

# FF

## Outline Dimensions

### FF779



| CASE #. | A  | B              | C  | D               | E               | WT GRAMS |
|---------|----|----------------|----|-----------------|-----------------|----------|
| FF779   | -- | .71<br>(18.03) | -- | 2.11<br>(53.59) | .718<br>(18.24) | 72.5     |

Dimensions are in inches (mm). Tolerances: 2Pl. +.05/-.04; 3Pl. ± .030

### Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.

 **Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

FF779 Rev.: AR (13/AUG/21) ECO-009237 File: FF779

This document and its contents are the property of Mini-Circuits.

Sheet 1 of 1



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition  | Reference/Spec                       |
|----------------------------|--|--------------------------------------|
| Operating Temperature      | -45° to 100° C<br>Ambient Environment  | Individual Model Data Sheet          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment  | Individual Model Data Sheet          |
| Barometric Pressure        | 100,000 Feet   | MIL-STD-202, Method 105, Condition D |
| Humidity                   | 90% RH, 65°C<br>Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103              |
| Thermal Shock              | -65° to 125°C, 5 cycles  | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)    | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock           | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)                          | MIL-STD-202, Method 213, Condition I |