

# Coaxial Low Pass Filter

## VLFG-1800+

50Ω DC to 1800 MHz



Generic photo used for illustration purposes only  
CASE STYLE: FF704

### The Big Deal

- Excellent power handling, 5.5W
- Temperature stable
- Rugged unibody construction
- Good rejection, 42 dB typical

### Product Overview

VLFG-1800+ is a 50Ω low pass filter built in rugged unibody construction. Covering DC-1800 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. VLFG-1800+ offer low insertion loss, and excellent power handling capability. It handles up to 5.5W RF input power and provides a wide operating temperature range from -55°C to 125°C.

### Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
5.5W Power handling	Supports a range of system power requirements.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Low Pass Filter

## VLFG-1800+

50Ω DC to 1800 MHz



Generic photo used for illustration purposes only  
CASE STYLE: FF704

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Features

- Low loss, 1.3 dB typical
- Good rejection 42 dB typical
- Excellent power handling, 5.5W
- Temperature stable
- Connectorized package
- Rugged unibody construction

### Applications


- Military radar applications
- Test and measurement
- Telecommunication and broadband wireless applications

### Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Insertion Loss	DC-F1	DC - 1800	—	1.3	2.2	dB
	Freq. Cut-Off	F2*	2030	—	3.0	—	dB
	Return Loss	DC-F1	DC - 1800	—	18	—	dB
Stop Band	Rejection Loss	F3-F4	2450 - 2900	20	40	—	dB
		F4-F5	2900 - 7000	33	42	—	dB
		F5-F6	7000 - 10000	—	35	—	dB

In Application where DC voltage is present at either input or output port, DC blocks are required.  
\* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

### Functional Schematic



### Maximum Ratings





Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	5.5W max. @25°C

\*Passband rating, derate linearly to 1W at 125°C ambient  
Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.05	41.30
100	0.12	32.85
500	0.30	24.65
1000	0.53	18.60
1400	0.73	20.50
1500	0.80	23.69
1800	1.27	23.19
2030	2.91	14.36
2050	3.39	12.12
2300	24.25	1.59
2350	31.37	1.33
2450	47.13	1.02
2900	64.37	0.58
3000	58.63	0.55
4000	52.95	0.45
5500	48.33	0.43
6000	47.10	0.43
7000	43.68	0.44
8500	35.11	0.45
10000	34.91	0.43

### Typical Frequency Response



### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



**Coaxial Connections**

PORT - 1	SMA-Male
PORT - 2	SMA-Female

**Outline Drawing**



**Outline Dimensions ( inch )**

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10

Note: Please refer to case style drawing for details

**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)








## Typical Performance Data

FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+100°C	@-55°C	@+25°C	@+100°C	@-55°C	@+25°C	@+100°C
10	0.05	0.05	0.07	44.60	41.30	40.38	44.22	42.50	41.26
50	0.08	0.09	0.11	40.48	36.46	33.61	39.42	35.81	33.20
100	0.10	0.12	0.14	34.86	32.85	30.89	33.61	31.84	30.40
250	0.17	0.20	0.22	24.91	28.83	33.37	23.80	26.47	29.19
400	0.21	0.26	0.29	25.73	26.22	29.46	23.46	23.35	24.59
550	0.25	0.32	0.37	23.46	23.83	25.28	21.32	21.12	21.64
700	0.30	0.39	0.44	21.11	21.64	22.35	19.62	19.55	19.68
1000	0.42	0.53	0.62	17.84	18.60	18.19	17.55	18.00	17.40
1100	0.45	0.58	0.67	17.82	18.20	17.71	17.93	18.03	17.36
1150	0.47	0.60	0.70	18.11	18.18	17.70	18.42	18.22	17.56
1160	0.47	0.61	0.70	18.18	18.18	17.73	18.51	18.26	17.62
1170	0.47	0.61	0.71	18.23	18.19	17.76	18.59	18.30	17.66
1200	0.48	0.62	0.73	18.29	18.24	17.77	18.79	18.48	17.83
1300	0.52	0.67	0.78	18.90	18.91	18.69	19.70	19.52	19.16
1400	0.56	0.73	0.84	20.37	20.50	20.84	21.48	21.44	21.70
1500	0.62	0.80	0.92	23.41	23.69	25.17	24.86	24.61	25.89
1600	0.69	0.90	1.04	29.19	30.81	36.78	29.14	28.33	28.47
1650	0.74	0.96	1.13	34.74	36.24	34.32	29.32	27.59	25.82
1700	0.81	1.05	1.23	33.96	31.16	27.91	27.36	25.20	23.18
1800	0.99	1.27	1.51	24.57	23.19	21.81	22.36	20.72	19.32
1850	1.11	1.43	1.69	22.64	21.69	21.18	20.73	19.27	18.29
1900	1.26	1.63	1.94	21.43	21.09	21.18	19.31	18.00	17.18
2000	1.80	2.41	2.97	19.68	17.79	16.51	15.55	13.62	12.47
2030	2.14	2.91	3.65	16.61	14.36	12.79	13.37	11.41	10.22
2100	3.80	5.32	6.74	8.92	7.38	6.42	7.77	6.47	5.76
2300	20.49	24.25	27.39	1.49	1.59	1.70	1.90	2.12	2.28
2450	44.90	47.13	45.17	0.85	1.02	1.16	1.38	1.65	1.80
2500	46.84	44.39	43.52	0.75	0.92	1.06	1.28	1.54	1.68
2900	66.74	64.37	61.62	0.39	0.58	0.72	0.76	0.95	1.03
3000	60.01	58.63	57.97	0.37	0.55	0.70	0.68	0.86	0.93
3800	56.53	55.73	55.04	0.26	0.46	0.61	0.37	0.51	0.56
3900	54.56	54.05	53.65	0.28	0.45	0.61	0.34	0.49	0.53
4000	53.34	52.95	52.63	0.28	0.45	0.60	0.32	0.47	0.52
4100	52.41	52.07	51.90	0.27	0.45	0.57	0.30	0.46	0.50
4200	51.74	51.47	51.30	0.27	0.44	0.55	0.29	0.44	0.50
4300	51.20	51.00	50.82	0.28	0.44	0.54	0.27	0.43	0.49
4400	50.76	50.54	50.47	0.29	0.44	0.55	0.25	0.42	0.49
4500	50.46	50.31	50.16	0.29	0.44	0.54	0.24	0.41	0.48
4600	50.19	50.00	49.96	0.27	0.43	0.51	0.23	0.40	0.48
4700	49.95	49.81	49.73	0.26	0.43	0.51	0.22	0.39	0.48
4800	49.74	49.62	49.51	0.27	0.43	0.52	0.20	0.39	0.48
4900	49.72	49.45	49.26	0.26	0.43	0.54	0.19	0.39	0.49
5000	49.48	49.33	49.10	0.23	0.43	0.55	0.19	0.38	0.49
5100	49.26	49.14	48.97	0.21	0.43	0.56	0.18	0.38	0.49
5200	49.16	48.93	48.77	0.21	0.42	0.57	0.17	0.38	0.50
6000	46.97	47.10	47.05	0.13	0.43	0.74	0.15	0.40	0.56
6600	44.81	45.14	45.35	0.16	0.42	0.72	0.18	0.43	0.60
6850	44.02	44.25	44.43	0.18	0.43	0.69	0.19	0.44	0.61
7000	43.55	43.68	43.88	0.19	0.44	0.68	0.19	0.44	0.61
7150	43.01	43.12	43.29	0.20	0.45	0.69	0.21	0.45	0.62
7300	42.53	42.54	42.59	0.21	0.44	0.67	0.22	0.46	0.62
7450	42.00	41.97	42.03	0.21	0.44	0.65	0.22	0.47	0.62
7600	41.43	41.33	41.38	0.20	0.44	0.63	0.23	0.47	0.61
7750	40.76	40.70	40.72	0.20	0.45	0.63	0.24	0.47	0.60
7900	40.10	40.00	39.97	0.19	0.45	0.66	0.25	0.48	0.60
8000	39.60	39.49	39.50	0.18	0.45	0.64	0.26	0.48	0.60
8200	38.46	38.37	38.23	0.18	0.44	0.67	0.27	0.50	0.60
9000	40.11	39.57	39.54	0.08	0.44	0.75	0.27	0.50	0.53
9300	37.73	37.63	37.77	0.07	0.43	0.82	0.22	0.47	0.52
10000	35.40	34.91	34.81	0.13	0.43	0.74	0.17	0.47	0.55

## Typical Performance Data

FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-55°C	@+25°C	@+100°C
10	0.47	0.49	0.48
30	0.47	0.48	0.47
70	0.46	0.46	0.45
110	0.45	0.44	0.44
150	0.45	0.44	0.43
190	0.45	0.44	0.43
230	0.45	0.44	0.43
270	0.45	0.44	0.44
310	0.45	0.44	0.44
350	0.45	0.44	0.44
390	0.46	0.44	0.44
430	0.46	0.45	0.44
470	0.46	0.45	0.44
510	0.46	0.45	0.44
550	0.46	0.45	0.45
590	0.47	0.46	0.45
630	0.47	0.46	0.45
670	0.47	0.46	0.45
710	0.47	0.46	0.46
750	0.48	0.47	0.46
800	0.48	0.47	0.47
1000	0.51	0.50	0.49
1010	0.51	0.50	0.49
1020	0.51	0.50	0.50
1030	0.51	0.50	0.50
1070	0.52	0.51	0.50
1110	0.53	0.52	0.51
1150	0.54	0.53	0.52
1190	0.55	0.54	0.53
1230	0.56	0.55	0.54
1270	0.57	0.56	0.55
1310	0.58	0.57	0.57
1350	0.59	0.59	0.58
1380	0.60	0.60	0.59
1390	0.60	0.60	0.60
1400	0.61	0.60	0.60
1450	0.63	0.63	0.63
1500	0.65	0.65	0.65
1600	0.71	0.71	0.71
1700	0.78	0.79	0.80
1800	0.88	0.90	0.92

## Typical Performance Curves




# Case Style

# FF

## FF704

### Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

#### Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, Except +100°C