

Coaxial High Pass Filter

VHFG-2100+

50Ω 2200 to 6000 MHz



Generic photo used for illustration purposes only
CASE STYLE: FF704

The Big Deal

- Excellent power handling, 4W
- Temperature stable
- Rugged unibody construction
- Good rejection, 47 dB typical

Product Overview

VHFG-2100+ is a 50Ω high pass filter built in rugged unibody construction. Covering 2200-6000 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. VHFG-2100+ offer low insertion loss, and excellent power handling capability. It handles up to 4W RF input power and provides a wide operating temperature range from -55°C to 125°C.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
4W Power handling	Supports a range of system power requirements.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



High Pass Filter

VHFG-2100+

50Ω 2200 to 6000 MHz



Generic photo used for illustration purposes only
CASE STYLE: FF704

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Features

- Temperature stable
- Excellent power handling, 4W
- Connectorized package
- Rugged unibody construction

Applications


- Transmitters / Receivers
- Global positioning system(GPS)
- Satellite broadcast applications
- Wireless local area Network

Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	DC - 1050	40	47	-	dB
		DC-F2	DC - 1320	22	32	-	dB
	Freq. Cut-Off	F3*	2100	-	3.0	-	dB
Pass Band	Insertion Loss	F4-F7	2200 - 6000	-	2.0	-	dB
		F5-F6	2500 - 5000	-	1.0	1.8	dB
	Return Loss	F5-F6	2500 - 5000	-	15	-	dB

In Applications where DC voltage is present at either input or output ports, DC blocks are required.
* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

Functional Schematic



Maximum Ratings





Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	4W max. @25°C

*Passband rating, derate linearly to 0.8W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	92.86	0.12
250	78.78	0.26
700	74.96	0.41
950	57.60	0.46
1050	49.26	0.48
1320	33.16	0.57
1380	30.17	0.60
1600	20.03	0.79
1700	15.71	1.01
1900	7.83	2.37
2050	3.61	5.72
2100	2.73	7.61
2200	1.67	12.77
2300	1.20	19.99
2500	0.89	27.56
3000	0.65	30.16
4000	0.52	29.12
5000	0.62	15.90
5600	0.88	11.13
6000	1.13	9.01

Typical Frequency Response



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch)

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	76.85	72.91	69.07	0.14	0.16	0.21	0.12	0.16	0.20
100	76.06	89.35	76.41	0.16	0.20	0.25	0.15	0.19	0.25
200	82.21	74.63	76.50	0.19	0.23	0.29	0.18	0.24	0.30
300	71.43	71.80	71.48	0.21	0.26	0.32	0.20	0.26	0.33
400	67.64	67.67	67.65	0.21	0.27	0.34	0.21	0.28	0.36
500	64.60	64.78	64.27	0.22	0.29	0.37	0.23	0.31	0.39
600	62.50	62.37	62.35	0.24	0.31	0.39	0.24	0.32	0.41
700	61.62	61.71	61.73	0.27	0.34	0.43	0.26	0.35	0.44
800	63.17	63.87	64.40	0.27	0.35	0.45	0.28	0.37	0.47
900	74.90	74.50	71.06	0.29	0.37	0.47	0.29	0.39	0.49
1000	57.88	56.49	54.75	0.31	0.40	0.51	0.31	0.41	0.53
1050	52.49	51.36	50.01	0.31	0.41	0.52	0.32	0.42	0.54
1200	41.31	40.50	39.48	0.33	0.43	0.56	0.34	0.46	0.59
1320	34.55	33.80	32.85	0.37	0.49	0.62	0.37	0.50	0.64
1430	29.09	28.37	27.44	0.41	0.53	0.69	0.41	0.55	0.72
1500	25.84	25.13	24.20	0.44	0.57	0.75	0.44	0.60	0.78
1620	20.57	19.86	18.92	0.53	0.69	0.91	0.55	0.74	0.97
1700	17.19	16.47	15.54	0.64	0.84	1.10	0.67	0.89	1.18
1800	13.13	12.43	11.53	0.90	1.17	1.54	0.97	1.26	1.67
1900	9.30	8.66	7.87	1.46	1.85	2.43	1.55	1.99	2.63
2000	5.95	5.46	4.90	2.63	3.27	4.20	2.78	3.48	4.51
2100	3.42	3.15	2.90	4.88	5.88	7.24	5.14	6.25	7.80
2200	1.89	1.84	1.82	8.52	9.88	11.63	9.09	10.69	12.82
2300	1.16	1.23	1.33	13.43	15.03	16.87	14.81	17.00	19.67
2400	0.85	0.96	1.11	18.79	20.04	21.22	22.52	24.83	26.12
2470	0.74	0.87	1.02	21.20	21.73	22.38	26.32	26.23	25.73
2500	0.71	0.84	0.99	21.73	22.00	22.56	26.17	25.47	25.00
2700	0.58	0.71	0.85	21.97	22.36	23.47	22.43	22.62	23.58
2800	0.53	0.65	0.79	22.63	23.28	24.65	22.42	23.00	24.38
2900	0.49	0.61	0.75	23.83	24.66	26.11	23.11	23.94	25.67
2960	0.47	0.59	0.73	24.85	25.76	27.09	23.75	24.72	26.60
3100	0.42	0.54	0.68	27.24	27.81	28.23	25.44	26.54	28.37
3200	0.40	0.52	0.66	28.74	28.58	28.19	26.36	27.29	28.76
3300	0.38	0.50	0.64	29.48	28.47	27.62	26.85	27.41	28.43
3400	0.36	0.48	0.62	29.67	28.09	27.16	27.51	27.74	28.48
3500	0.34	0.46	0.61	29.66	27.78	26.95	27.69	27.69	28.44
3600	0.33	0.45	0.59	29.67	27.71	27.02	28.28	28.14	28.98
3700	0.32	0.44	0.58	30.11	28.14	27.57	29.23	29.02	29.91
3800	0.31	0.43	0.57	30.47	28.63	28.21	30.25	30.39	31.90
3900	0.29	0.42	0.56	31.34	29.76	29.43	31.97	32.57	34.96
4000	0.29	0.41	0.56	31.34	30.36	30.13	33.15	35.45	42.34
4100	0.28	0.40	0.55	30.83	30.50	30.28	33.29	37.07	45.27
4200	0.28	0.40	0.55	28.83	29.03	28.80	31.18	33.75	34.60
4250	0.28	0.40	0.55	27.85	28.12	27.86	29.94	31.78	31.96
4450	0.28	0.40	0.55	23.64	23.85	23.70	24.64	25.16	24.97
4500	0.28	0.40	0.55	22.62	22.81	22.64	23.47	23.84	23.62
4600	0.29	0.41	0.56	21.12	21.18	21.10	21.61	21.77	21.64
4700	0.29	0.42	0.58	19.59	19.61	19.54	19.95	20.04	19.91
4750	0.30	0.43	0.59	18.83	18.84	18.77	19.10	19.15	19.04
4900	0.33	0.46	0.62	16.98	16.92	16.91	17.14	17.12	17.06
5000	0.35	0.48	0.65	15.92	15.86	15.85	16.02	15.98	15.94
5100	0.38	0.52	0.68	14.95	14.85	14.87	15.04	14.96	14.95
5310	0.45	0.59	0.76	13.26	13.14	13.17	13.30	13.19	13.19
5300	0.44	0.58	0.75	13.34	13.20	13.26	13.39	13.27	13.29
5400	0.48	0.63	0.79	12.63	12.51	12.57	12.61	12.50	12.53
5500	0.52	0.67	0.84	11.93	11.82	11.87	11.95	11.85	11.87
5650	0.59	0.75	0.93	11.05	10.94	11.01	11.03	10.93	10.97
5700	0.61	0.77	0.96	10.76	10.66	10.73	10.72	10.63	10.67
5800	0.66	0.83	1.02	10.25	10.15	10.22	10.19	10.11	10.14
6000	0.77	0.94	1.14	9.30	9.20	9.27	9.28	9.20	9.24

* Temperature test data was based on the underlying chip








Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-55°C	@+25°C	@+125°C
2000	0.63	0.65	0.67
2100	0.68	0.68	0.67
2200	0.65	0.63	0.60
2300	0.56	0.53	0.51
2400	0.46	0.44	0.42
2500	0.39	0.38	0.36
2600	0.34	0.33	0.32
2700	0.30	0.29	0.29
2800	0.27	0.27	0.26
2900	0.25	0.24	0.24
3000	0.23	0.22	0.22
3100	0.21	0.21	0.21
3200	0.20	0.20	0.19
3300	0.19	0.18	0.18
3400	0.18	0.17	0.17
3500	0.17	0.16	0.16
3600	0.16	0.16	0.16
3700	0.15	0.15	0.15
3800	0.14	0.14	0.14
3900	0.14	0.14	0.14
4000	0.13	0.13	0.13
4100	0.13	0.13	0.13
4200	0.13	0.12	0.12
4300	0.12	0.12	0.12
4400	0.12	0.12	0.12
4500	0.12	0.11	0.12
4600	0.11	0.11	0.11
4700	0.11	0.11	0.11
4800	0.11	0.11	0.11
4900	0.10	0.10	0.11
5000	0.10	0.10	0.10
5100	0.10	0.10	0.10
5200	0.10	0.10	0.10
5300	0.10	0.09	0.10
5400	0.09	0.09	0.10
5500	0.09	0.09	0.09
5600	0.09	0.09	0.09
5700	0.09	0.09	0.09
5800	0.09	0.09	0.09
5900	0.09	0.09	0.09
6000	0.09	0.08	0.09

* Temperature test data was based on the underlying chip

Typical Performance Curves




* Temperature test data was based on the underlying chip

Case Style

FF

FF704

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.

Mini-Circuits[®]
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Thermal Shock	-55° to 125°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, Except +125°C