

Low Pass Filter

50Ω

*DC to 7200 MHz

VLF-7200+

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	8W at 25°C
DC Current Input to Output	0.5A max. at 25°C

*Passband rating, derate linearly to 3 W at 100°C ambient
Permanent damage may occur if any of these limits are exceeded.

Features

- Rugged uni-body construction, small size
- 7 sections
- Excellent power handling, 8W
- Temperature stable
- Low cost
- Protected by US Patent 6,943,646

Applications

- Harmonic rejection
- Transmitters/receivers
- Lab use




CASE STYLE: FF704

Connectors	Model
SMA	VLF-7200+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Low Pass Filter Electrical Specifications (T_{AMB} = 25°C)


PASSBAND (MHz)	fco, MHz Nom.	STOP BAND (MHz) (loss, dB)			VSWR (:1)		NO. OF SECTIONS
		F 20 Min.	30 Typ.	FR 20 Typ.	Stopband Typ.	Passband Typ.	
*DC - 7200 (loss < 2 dB) Max.	(loss 3 dB) Typ. 8150	9500	8850 - 9600	12300	17	1.3	7

* Not for use with DC voltage at input and output ports

Typical frequency response



Electrical schematic




Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
40	0.06	1.04
500	0.09	1.04
2000	0.25	1.24
3600	0.45	1.46
6000	0.53	1.22
7200	0.89	1.42
8000	2.15	1.55
8150	3.48	2.07
8320	7.22	4.05
8500	14.32	8.08
8730	28.60	12.99
8850	38.88	15.13
9500	33.12	21.73
9600	34.36	22.29
10500	52.18	32.79
12300	36.42	56.04
15000	24.94	34.07


Outline Dimensions (inch/mm)

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10

VLF-7200+
INSERTION LOSS



VLF-7200+
VSWR



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Low Pass Filter

VLF-7200+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
40	0.06	0.05	0.07	46.20	41.35	37.60	45.99	39.51	36.04
50	0.00	0.03	0.02	49.53	42.00	37.32	48.05	41.19	37.05
100	0.01	0.03	0.03	42.54	46.42	40.03	41.07	44.01	39.40
200	0.02	0.05	0.04	47.66	40.50	38.95	41.34	40.15	39.17
300	0.02	0.06	0.06	40.76	36.30	30.90	41.82	36.56	30.86
400	0.04	0.08	0.08	37.50	33.57	28.57	42.20	33.65	28.20
500	0.06	0.10	0.10	32.41	31.53	28.25	33.53	31.85	28.03
1000	0.09	0.14	0.16	25.27	24.77	24.43	25.90	25.20	24.77
1500	0.12	0.19	0.22	21.37	21.03	20.89	21.66	21.33	21.37
2000	0.16	0.25	0.29	17.92	17.75	17.64	18.09	17.96	17.94
2500	0.24	0.33	0.37	15.57	15.76	16.08	15.53	15.78	16.16
3000	0.28	0.40	0.43	14.57	14.69	15.24	14.58	14.68	15.25
3450	0.33	0.45	0.50	13.78	14.01	14.12	13.72	14.02	14.14
4000	0.33	0.50	0.59	14.29	13.83	13.29	14.31	13.89	13.35
4500	0.33	0.50	0.59	15.01	14.64	14.29	15.15	14.76	14.34
5000	0.33	0.48	0.56	16.00	16.35	16.36	16.27	16.53	16.36
5500	0.31	0.48	0.56	19.39	19.62	19.85	19.69	19.65	19.52
6000	0.32	0.49	0.58	22.37	24.75	27.20	21.86	24.52	26.67
6700	0.39	0.60	0.72	45.10	34.28	29.32	36.71	30.95	26.93
7000	0.49	0.71	0.84	24.19	25.69	24.91	25.08	24.97	22.85
7200	0.58	0.80	0.93	19.17	21.14	21.91	19.85	21.04	20.56
7500	0.84	1.08	1.21	14.53	15.67	16.58	15.40	16.35	16.91
8000	1.97	2.47	2.79	8.41	8.11	7.93	10.52	11.00	11.30
8150	3.23	4.01	4.58	5.63	5.24	4.91	7.70	7.86	7.66
8200	3.93	4.91	5.62	4.71	4.32	4.02	6.69	6.63	6.38
8400	8.78	10.79	12.01	1.99	1.81	1.71	3.27	3.08	2.99
8500	12.64	15.04	16.51	1.29	1.26	1.22	2.23	2.21	2.23
8600	17.41	20.18	21.91	0.93	0.99	0.99	1.64	1.75	1.81
8700	23.27	26.52	28.69	0.70	0.85	0.88	1.21	1.40	1.51
8750	26.80	30.42	32.90	0.64	0.78	0.81	1.12	1.33	1.44
8850	36.14	39.58	40.23	0.55	0.71	0.75	0.92	1.16	1.30
9000	36.65	35.31	34.90	0.45	0.63	0.69	0.77	1.05	1.21
9500	34.14	34.46	34.78	0.26	0.51	0.68	0.54	0.80	1.00
9550	34.65	35.03	35.37	0.25	0.51	0.70	0.54	0.81	1.01
9600	35.26	35.68	36.04	0.25	0.53	0.72	0.49	0.74	0.95
10000	41.16	41.89	42.47	0.19	0.46	0.70	0.41	0.65	0.82
11000	46.12	46.57	47.62	0.19	0.40	0.59	0.20	0.40	0.48
12300	34.47	34.86	35.93	0.02	0.25	0.37	0.00	0.25	0.37
14000	29.53	26.64	26.86	0.11	0.31	0.32	0.02	0.30	0.42
16000	20.96	22.26	21.65	0.18	0.29	0.42	0.05	0.44	0.84
18000	17.59	16.25	16.11	0.13	0.59	0.83	0.39	0.72	1.01
20000	9.76	10.92	11.00	1.67	1.53	1.63	1.25	1.66	2.11

REV. X1
VLF-7200+
071009
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial Low Pass Filter


Typical Performance Curves

VLF-7200+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1
VLF-7200+
071009
Page 1 of 1

Mini-Circuits®


IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I