



(LTCC) COAXIAL

Low Pass Filter

VLFG-2275+

50Ω DC to 2275 MHz SMA Male/Female

KEY FEATURES

- Low Insertion Loss, 1.2 dB Typ.
- Return Loss, 15 dB Typ.
- Stop Band Rejection, 45 dB Typ.
- Rugged unibody construction.
- Power Handling: 4.5 Watts

APPLICATIONS

- ISM Applications
- Communications, Radar, and Defense Systems
- Test and Measurement Equipment
- LTE & 5G MIMO Infrastructure


PRODUCT OVERVIEW

VLFG-2275+ is a Low Pass filter with DC to 2275 MHz passband supporting a variety of applications. This model provides 1.2 dB typical insertion loss over a wide band due to its rugged unibody construction. VLFG-2275+ offers low insertion loss, and excellent power handling capability. It handles up to 4.5W RF input power and provides a wide operating temperature range from -55°C to 125°C.



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM



ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units	
Pass Band	Insertion Loss	DC-F1	DC- 2275	—	1.2	2.0	dB
	Freq. Cut-Off ³	Fc ³	2700	—	3	—	dB
	Return Loss	DC-F1	DC - 2275	—	15	—	dB
Stop Band	Rejection	F2-F3	3300 - 4000	20	40	—	dB
		F3-F4	4000 - 7000	32	45	—	
		F4-F5	7000 - 10000	—	25	—	

1. This filter is bi-directional, RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

2. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

3. Typical variation ± 5%


ABSOLUTE MAXIMUM RATINGS⁴

Parameter	Ratings
Operating Temperature	-55 °C to +125 °C
Storage Temperature	-55 °C to +125 °C
Input Power ⁵	4.5 W @25°C

4. Permanent damage may occur if any of these limits are exceeded.

5. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C





(LTCC) COAXIAL





Low Pass Filter

VLFG-2275+

Mini-Circuits

50Ω DC to 2275 MHz SMA Male/Female

TYPICAL PERFORMANCE GRAPHS AT +25°C





(LTCC) COAXIAL

Low Pass Filter

VLFG-2275+


Mini-Circuits

50Ω DC to 2275 MHz SMA Male/Female

CONNECTOR DESCRIPTION

Function	Functionality	Connector
RF1 ¹	Port-1	SMA MALE
RF2 ¹	Port-2	SMA FEMALE

CASE STYLE DRAWING



Unit weight: 10.0grams

Dimensions are in inches (mm). Tolerances: 2 Pl. ±.04"; 3 Pl. ±.30"

PRODUCT MARKING*: VLFG-2275+

*Marking may contain other features or characters for internal lot control.



(LTCC) COAXIAL

Low Pass Filter

VLFG-2275+

50Ω DC to 2275 MHz SMA Male/Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (SXP Files) Data Set (.zip file)
Case Style	FF704
RoHS Status	Compliant
Environmental Ratings	ENV123

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html







Coaxial Low Pass Filter

VLFG-2275+

Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
10	0.05	43.22	44.58	10	0.38
20	0.05	42.04	42.71	30	0.38
40	0.07	40.15	39.51	90	0.37
100	0.11	36.02	34.97	100	0.37
120	0.12	35.42	34.02	150	0.37
200	0.15	33.56	31.31	200	0.37
300	0.18	32.52	29.09	250	0.37
400	0.21	31.61	27.25	300	0.37
500	0.24	30.57	25.75	350	0.37
600	0.26	29.14	24.42	400	0.37
700	0.29	27.51	23.28	450	0.37
850	0.33	25.05	21.84	500	0.37
900	0.35	24.32	21.46	550	0.37
1000	0.38	23.02	20.76	600	0.37
1100	0.41	21.96	20.20	650	0.38
1200	0.44	21.17	19.84	700	0.38
1300	0.47	20.64	19.69	800	0.38
1400	0.50	20.40	19.78	850	0.38
1500	0.53	20.49	20.22	900	0.39
1600	0.56	20.98	21.09	950	0.39
1700	0.59	21.88	22.51	1000	0.39
1800	0.62	23.26	24.90	1030	0.39
1900	0.67	24.79	28.36	1060	0.39
2000	0.74	25.18	29.30	1090	0.40
2100	0.81	23.38	25.13	1100	0.40
2275	1.01	19.26	19.10	1130	0.40
2300	1.04	18.84	18.55	1150	0.40
2400	1.20	17.81	17.02	1170	0.40
2500	1.40	18.19	16.39	1190	0.40
2600	1.69	20.53	15.93	1200	0.40
2700	2.32	16.70	12.88	1250	0.41
2800	4.04	8.53	7.90	1270	0.41
2900	8.08	3.89	4.61	1290	0.41
3000	14.67	1.99	3.33	1300	0.41
3300	47.94	0.85	2.01	1320	0.41
3500	62.79	0.69	1.43	1340	0.41
3700	56.22	0.61	1.07	1360	0.42
3900	54.59	0.56	0.84	1380	0.42
4000	56.29	0.55	0.76	1400	0.42
4100	59.81	0.54	0.70	1420	0.42
4300	66.60	0.52	0.60	1440	0.42
4500	55.24	0.51	0.52	1460	0.43
4700	50.78	0.50	0.46	1480	0.43
5000	47.37	0.49	0.40	1500	0.43
5100	46.70	0.48	0.39	1550	0.44
5300	45.65	0.48	0.36	1600	0.44
5500	44.95	0.48	0.34	1650	0.45
5700	44.44	0.48	0.33	1700	0.46
5900	44.03	0.47	0.31	1750	0.47
6100	43.71	0.47	0.31	1800	0.48
6300	43.44	0.47	0.30	1850	0.49
6500	43.17	0.47	0.31	1900	0.50
7000	42.52	0.46	0.31	1950	0.51
7500	41.75	0.45	0.34	2000	0.52
8000	40.78	0.44	0.38	2020	0.53
8500	39.60	0.42	0.43	2050	0.54
9000	38.29	0.39	0.48	2100	0.56
9300	37.49	0.38	0.51	2150	0.57
9600	36.74	0.38	0.55	2200	0.59
10000	36.45	0.37	0.77	2275	0.63

Typical Performance Curves




Case Style

FF

FF704

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Thermal Shock	-55° to 125°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, Except +125°C