

Instrumentation Test Cable

VNAC-2R1-K+

50Ω 25 inches DC to 40 GHz Low Loss



CASE STYLE: NE1922-2.1

The Big Deal

- Ultra-wideband operation, DC to 40 GHz
- Rugged 2.92mm-female connector for direct interface with VNA
- Rugged construction, crush and torque resistant

Product Overview

Mini-Circuits’ VNAC-2R1-K+ is an ultra-wideband precision instrumentation cable specially designed for use with VNA equipment in test environments. The cable provides excellent VSWR and very low insertion loss over the entire frequency range. Passivated stainless steel rugged 2.92mm (F) connector interfaces directly with the ports of the VNA*, and a rugged crush and torque resistant outer sheath protects the cable from damage in demanding lab settings.

Feature	Advantages
DC-40 GHz operation designed for use with Vector Network Analyzers (VNA)	Covers a wide range of test applications; rugged 2.92mm connector interfaces directly with VNA without the need for an adapter for improved VSWR performance.
Rugged cable-connector interface	Chrome plated metal back shell maintains integrity of the cable-connector interface improving the reliability and extending life of use.
Extra rugged yet flexible armored cable construction.	100% coverage, non-interleaved, stainless steel spiral sheath provides crush resistance and captured, opposing force steel braid provides torque resistance. PET monofilament yarn outer cover eliminates conductivity and allows easy handling.
25” length	Standard VNA cable length makes VNAC-2R1-K+ a high performing, cost-effective replacement for expensive OEM cables.

*Compatible with 2.92mm-female connector or customer VNA equipment.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit’s applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, “Standard Terms”); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits’ website at www.minicircuits.com/MCLStore/terms.jsp

Instrumentation Test Cable

50Ω 25 Inches DC to 40 GHz Low Loss

VNAC-2R1-K+



Maximum Ratings

Operating Temperature +18°C to +30°C

Storage Temperature -40°C to +70°C

Power Handling at 25°C, Sea level 10W

Permanent damage may occur if any of these limits are exceeded.

Features

- extremely low insertion loss
- extra rugged construction includes protective shield and strain relief for longer life
- stainless steel 40 GHz connector for long mating-cycle life
- double shield cable for excellent shielding effectiveness

Applications

- military and defense applications
- research & development labs


CASE STYLE: NE1922-2.1

Conn1	Conn2	Model
2.92 mm Male	2.92mm Rugged Female	VNAC-2R1-K+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Outline Drawing



Outline Dimensions (inch mm)

	A	B	C	D	F	T		
Feet							Inches	mm
Meters	0.62	0.312	0.86	0.750				grams
	15.75	7.92	21.84	19.05			+50/-0	+12.7/-0
								182

Cable Construction



Product Guarantee

Mini-Circuits® will repair or replace your test cable at its option if the connector attachment fails within six months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Electrical Specifications at 25°C

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		40	GHz
Length			2.08		FT
Insertion Loss	DC - 6	—	0.79	0.97	dB
	6-18	—	1.44	1.60	
	18-26.5	—	1.81	2.03	
	26.5-40	—	2.25	2.43	
Return Loss	DC - 6	15.5	27.1	—	dB
	6-18	15.5	22.6	—	
	18-26.5	15.5	20.8	—	
	26.5-40	15.5	18.1	—	

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	
		2.92 mm Male	2.92 mm Fem
50	0.05	40.79	38.62
1000	0.27	45.25	39.44
3500	0.52	38.21	35.13
6000	0.69	33.27	30.46
10000	0.95	30.50	30.19
14000	1.12	35.37	35.50
18000	1.30	26.68	27.64
22000	1.49	31.15	34.78
26500	1.64	39.25	26.94
30000	1.84	22.33	24.83
32000	1.87	22.32	28.08
34000	1.90	26.50	28.85
36000	1.97	26.68	30.37
38000	2.21	21.84	29.34
40000	2.17	20.66	20.97






Instrumentation Test Cable

Typical Performance Data


FREQUENCY	INSERTION LOSS	2.92mm MALE RETURN LOSS	2.92mm FEMALE Ruggedized RETURN LOSS
(MHz)	(dB)	(dB)	(dB)
50	0.05	40.8	38.6
100	0.08	40.1	39.3
500	0.19	49.2	41.4
1000	0.27	45.2	39.4
2000	0.39	37.1	37.6
3000	0.48	39.8	37.7
4000	0.55	38.4	34.9
5000	0.63	36.9	32.3
6000	0.69	33.3	30.5
7000	0.76	32.3	29.0
8000	0.81	30.4	28.1
9000	0.86	31.9	32.0
10000	0.95	30.5	30.2
11000	0.99	30.7	31.0
12000	1.03	30.8	33.0
13000	1.07	33.7	37.1
14000	1.12	35.4	35.5
15000	1.16	31.7	36.3
16000	1.18	30.8	36.9
17000	1.25	26.3	30.0
18000	1.30	26.7	27.6
19000	1.32	27.6	26.8
20000	1.32	25.5	26.8
21000	1.39	26.6	31.3
22000	1.49	31.1	34.8
23000	1.51	34.2	30.7
24000	1.54	28.2	30.6
25000	1.58	30.7	30.7
26000	1.62	31.2	27.6
27000	1.65	33.9	25.0
28000	1.74	26.6	24.4
29000	1.82	23.3	26.2
30000	1.84	22.3	24.8
31000	1.86	21.4	26.4
32000	1.87	22.3	28.1
33000	1.90	24.4	27.1
34000	1.90	26.5	28.9
35000	1.94	33.1	30.4
36000	1.97	26.7	30.4
37000	2.06	22.6	34.1
38000	2.21	21.8	29.3
39000	2.23	21.8	28.2
40000	2.17	20.7	21.0

Instrumentation Test Cable

Typical Performance Curves



Outline Dimensions



NA1922 SERIES

2.92mm MALE (CONN-1)

2.92mm RUGGED FEMALE (CONN-2)

CASE STYLE #	A		B	C	D	E	F	T		WEIGHT GRAMS
	FEET	METERS						INCH	MM	
NE1922-2.1	2.08	.63	.62 (15.75)	.312 (7.92)	.86 (21.84)	-	.750 (19.05)	+.50/-0	+12.7/-0	182.0
NE1922-3	3.00	.91						+.72/-0	+18.29/-0	210.0

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Note:

- VNA 26.5 and 40 GHz Coaxial Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	+18°C to 30°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-40° to 70° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-40°C to 70°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except- 30 minute dwell instead of 1 hour