

MMIC

# REFLECTIONLESS FILTER DICE

50Ω DC to 21 GHz

## The Big Deal

- Patented design eliminates in band spurs
- Pass band cut-off up to 21 GHz
- Stop band up to 35 GHz
- Excellent repeatability through IPD\* process
- Unpackaged Die Form



**X-Series**

Available in Low Pass, High Pass and Band Pass designs

## Product Overview

Mini-Circuits' X-Series reflectionless filters employ a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level which interact with neighboring components and often result in intermodulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolators, isolation amplifiers or attenuators.

### Key Features

Easy integration with sensitive reflective components, e.g. mixers, multipliers

Enables stable integration of wideband amplifiers

Cascadable

Excellent power handling in a tiny surface mount device

Excellent repeatability of RF performance

Excellent stability over temperature

Operating Temperature up to 105°C

Unpackaged Die form

### Advantages

Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.

Because reflectionless filters maintain good impedance in the stop band; they can be integrated with high gain, wideband amplifiers without the risk of creating instabilities in these out of band regions.

Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect pass band signals.

High power handling extends the usability of these filters to the transmit path for inter-stage filtering.

Through semiconductor IPD process, X-series filters are inherently repeatable for large volume production.

With  $\pm 0.3$  dB variation over temperature ideal for use in wide temperature range applications without the need for additional temperature compensation.

Suitable for operation close to high power components

Enables direct integration into customer hybrids

\*IPD – Integrated Passive Device, is a GaAs semiconductor process




# Reflectionless High Pass Filter Die

## XHF-252-D+

50Ω      2460 to 10400 MHz

### Features

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Protected by US Patent No. 8,392,495



### Applications

- Wi-Fi
- WiMax
- Microwave Radio
- Military & Space

#### +RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

### General Description

Mini-Circuits' XHF-252-D+ reflectionless filter die employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

### Simplified Schematic



Pad	Description
RF-IN	RF Input Pad
RF-OUT	RF Output Pad
Ground	Ground Bonding Pad

Electrical Specifications<sup>1</sup> at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection	DC-F1	DC-1520		14	dB
	Frequency Cut-off	F2	2030		3.0	dB
	VSWR	DC - F1	DC-1520		1.2	:1
Pass Band	Insertion Loss	F3-F5	2460 -10400		1.0	dB
	VSWR	F3-F4	2460 - 3700		1.5	:1
		F4-F5	3700 - 10400		1.7	:1

<sup>1</sup> Measured on Mini-Circuits Characterization test board. Die packaged in 3mm x 3mm, 12-lead MCLP package and soldered on TB-844-252H+

Absolute Maximum Ratings<sup>1,4</sup>


Parameter	Ratings
Operating Temperature	-55°C to +105°C
RF Power Input, Passband (F3-F5) <sup>2</sup>	2W at 25°C
RF Power Input, Stopband (DC-F3) <sup>3</sup>	0.5W at 25°C

<sup>2</sup> Passband rating derates linearly to 1W at 105°C ambient

<sup>3</sup> Stopband rating derates linearly to 0.25W at 105°C ambient



<sup>4</sup> Permanent damage may occur if any of these limits are exceeded.

Specification Definition



Typical Performance Data at 25°C<sup>1</sup>

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	38.00	1.04
50	32.70	1.05
100	27.74	1.05
200	22.16	1.06
300	19.04	1.08
500	15.66	1.13
1000	16.11	1.25
1520	13.92	1.27
2030	2.86	1.15
2460	0.95	1.04
3000	0.46	1.24
3700	0.42	1.52
4400	0.48	1.69
5100	0.48	1.70
6000	0.40	1.57
7000	0.30	1.36
8000	0.20	1.23
9000	0.14	1.22
10000	0.20	1.42
10400	0.32	1.59



**Die Layout**




Fig 1. Die Layout

**Bonding Pad Position**  
(Dimensions in  $\mu\text{m}$ , Typical)




Fig 2. Bonding Pad Positions


**Critical Dimensions**

Parameter	Values
Die Thickness, $\mu\text{m}$	100
Die Width, $\mu\text{m}$	1000
Die Length, $\mu\text{m}$	850
Bond Pad Size (Ground pad), $\mu\text{m}$	75 x 75

## Assembly and Handling Procedure

1. Storage  
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD  
MMIC Gallium Arsenide (GaAs) filter dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach  
The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030Hk-PT/H579/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
4. Wire Bonding  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

## Assembly Diagram



## Recommended Wire Length, Typical

Wire	Wire Length (mm)	Wire Loop Height (mm)
All wires	1.0	0.15

Note: Use double bond wire at RF IN & RF OUT

Additional Detailed Technical Information	
<i>additional information is available on our dash board.</i>	
<b>Performance Data</b>	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)
<b>Case Style</b>	Die
<b>Die Ordering and packaging information</b>	Quantity, Package                      Model No. Small, Gel - Pak: 10,50,100 KGD*    XHF-252-DG+ Medium†, Partial wafer: KGD* <5K    XHF-252-DP+
	†Available upon request contact sales representative  Refer to <a href="#">AN-60-067</a>
<b>Environmental Ratings</b>	ENV-80

\*Known Good Dice ("KGD") means that the dice are taken from PCM good wafer and visually inspected according to Mini-Circuits inspection criteria. While this is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

## ESD Rating\*\*

Human Body Model (HBM): Class 2 (2000 to <4000V) in accordance with ANSI/ESD STM 5.1 - 2001

\*\* Tested in industry standard MCLP 3x3mm 12 lead package.

### Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS					GROUP DELAY				
	(dB)					(nsec)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
10	40.40	40.01	39.14	37.45	37.45	-3.06	-3.52	-2.26	-3.60	-1.77
50	33.24	33.36	32.67	32.28	32.28	-1.63	-1.91	-1.44	-1.98	-1.19
100	27.81	27.77	27.72	27.68	27.52	-0.13	-0.11	-0.22	-0.27	-0.28
200	22.19	22.21	22.23	22.19	22.22	0.29	0.27	0.23	0.23	0.21
400	17.05	17.08	17.13	17.13	17.17	0.35	0.34	0.34	0.32	0.33
600	14.88	14.90	14.98	15.02	15.04	0.36	0.35	0.34	0.34	0.34
800	14.44	14.48	14.58	14.68	14.71	0.36	0.36	0.35	0.34	0.34
1000	16.01	16.07	16.26	16.40	16.44	0.35	0.35	0.33	0.32	0.32
1100	18.15	18.21	18.52	18.69	18.76	0.33	0.32	0.29	0.26	0.24
1200	22.45	22.55	23.01	23.31	23.39	0.15	0.12	-0.02	-0.15	-0.20
1300	35.59	35.37	33.88	32.22	31.78	-3.08	-3.04	-2.78	-2.55	-2.46
1400	22.70	22.54	21.90	21.35	21.17	-0.25	-0.24	-0.25	-0.23	-0.24
1500	15.43	15.37	15.15	14.93	14.89	0.36	0.36	0.33	0.31	0.30
1520	14.41	14.38	14.19	14.00	13.95	0.39	0.38	0.35	0.34	0.33
1600	11.12	11.10	11.02	10.93	10.90	0.44	0.43	0.42	0.40	0.40
1700	8.12	8.13	8.14	8.11	8.11	0.46	0.46	0.44	0.44	0.43
1800	5.95	5.96	6.02	6.05	6.06	0.47	0.46	0.45	0.44	0.44
1900	4.38	4.40	4.50	4.56	4.58	0.45	0.45	0.44	0.43	0.43
2000	3.25	3.28	3.40	3.48	3.51	0.43	0.43	0.42	0.42	0.41
2030	2.98	3.01	3.14	3.22	3.25	0.43	0.42	0.41	0.41	0.41
2100	2.45	2.49	2.63	2.71	2.74	0.41	0.41	0.40	0.39	0.39
2200	1.89	1.93	2.08	2.17	2.20	0.38	0.38	0.37	0.37	0.37
2300	1.49	1.53	1.69	1.78	1.81	0.36	0.36	0.35	0.35	0.34
2400	1.21	1.26	1.42	1.51	1.54	0.34	0.34	0.33	0.33	0.33
2460	1.08	1.13	1.29	1.38	1.42	0.33	0.33	0.32	0.32	0.31
2500	1.02	1.06	1.22	1.32	1.35	0.32	0.32	0.31	0.31	0.31
2600	0.88	0.92	1.08	1.18	1.21	0.31	0.31	0.30	0.30	0.29
2700	0.77	0.81	0.98	1.07	1.11	0.29	0.29	0.28	0.28	0.28
2800	0.71	0.75	0.92	1.01	1.05	0.28	0.28	0.27	0.27	0.27
2900	0.67	0.71	0.88	0.97	1.00	0.27	0.27	0.26	0.26	0.26
3000	0.64	0.68	0.84	0.94	0.97	0.26	0.26	0.25	0.25	0.25
3100	0.62	0.66	0.83	0.92	0.96	0.25	0.25	0.25	0.25	0.25
3200	0.61	0.66	0.83	0.91	0.94	0.25	0.25	0.24	0.24	0.24
3300	0.62	0.66	0.83	0.91	0.94	0.24	0.24	0.24	0.24	0.23
3400	0.63	0.67	0.84	0.92	0.95	0.24	0.24	0.23	0.23	0.23
3500	0.64	0.68	0.85	0.93	0.96	0.23	0.23	0.23	0.23	0.23
3600	0.65	0.70	0.86	0.94	0.97	0.23	0.23	0.22	0.22	0.22
3700	0.67	0.71	0.87	0.95	0.98	0.22	0.23	0.22	0.22	0.22
3800	0.69	0.74	0.89	0.98	1.00	0.22	0.22	0.22	0.22	0.22
3900	0.71	0.75	0.91	0.98	1.01	0.22	0.22	0.21	0.21	0.21
4000	0.73	0.77	0.93	1.01	1.05	0.22	0.22	0.21	0.21	0.21
4200	0.75	0.80	0.95	1.04	1.08	0.21	0.21	0.21	0.21	0.21
4400	0.75	0.80	0.97	1.06	1.10	0.21	0.21	0.20	0.20	0.20
4600	0.77	0.82	1.00	1.10	1.14	0.21	0.21	0.20	0.20	0.20
4800	0.78	0.82	1.01	1.12	1.16	0.20	0.20	0.20	0.20	0.20
5000	0.77	0.82	1.01	1.14	1.18	0.20	0.20	0.20	0.20	0.20
5200	0.76	0.81	1.01	1.14	1.20	0.20	0.20	0.20	0.19	0.19
5400	0.74	0.79	1.00	1.14	1.20	0.20	0.20	0.19	0.20	0.19
5600	0.70	0.76	0.98	1.14	1.19	0.20	0.20	0.19	0.19	0.19
5800	0.69	0.74	0.97	1.13	1.19	0.20	0.20	0.20	0.19	0.19
6000	0.67	0.73	0.97	1.13	1.19	0.20	0.20	0.19	0.19	0.19
6200	0.65	0.70	0.94	1.10	1.16	0.20	0.20	0.19	0.19	0.19
6400	0.64	0.69	0.93	1.09	1.15	0.20	0.20	0.20	0.19	0.19
6600	0.63	0.68	0.93	1.08	1.14	0.20	0.20	0.19	0.19	0.19
6800	0.62	0.68	0.92	1.07	1.12	0.20	0.20	0.19	0.19	0.19
7000	0.62	0.68	0.91	1.06	1.11	0.20	0.20	0.19	0.19	0.19
7200	0.63	0.69	0.92	1.06	1.09	0.20	0.20	0.19	0.19	0.19
7400	0.61	0.67	0.92	1.05	1.09	0.20	0.20	0.19	0.19	0.19
7600	0.59	0.65	0.90	1.04	1.09	0.20	0.20	0.19	0.19	0.19
7800	0.58	0.65	0.90	1.05	1.10	0.20	0.20	0.19	0.19	0.19
8000	0.59	0.65	0.90	1.06	1.11	0.20	0.20	0.19	0.19	0.19
8200	0.59	0.65	0.91	1.07	1.13	0.20	0.20	0.19	0.19	0.19
8400	0.59	0.65	0.92	1.09	1.15	0.20	0.20	0.19	0.19	0.19
8600	0.59	0.66	0.94	1.11	1.17	0.20	0.20	0.19	0.19	0.19
8800	0.60	0.67	0.96	1.13	1.20	0.20	0.20	0.19	0.19	0.19
9000	0.60	0.67	0.97	1.15	1.23	0.20	0.20	0.19	0.19	0.19
9200	0.61	0.69	1.00	1.19	1.27	0.20	0.20	0.19	0.19	0.19
9400	0.63	0.70	1.03	1.23	1.31	0.20	0.20	0.19	0.19	0.19
9600	0.64	0.72	1.07	1.27	1.35	0.20	0.20	0.19	0.19	0.19
9800	0.68	0.75	1.11	1.32	1.42	0.20	0.20	0.19	0.19	0.19
10000	0.72	0.80	1.16	1.38	1.47	0.20	0.20	0.20	0.19	0.19
10400	0.89	0.95	1.31	1.55	1.64	0.20	0.20	0.19	0.19	0.19
10500	0.93	1.00	1.35	1.59	1.68	0.20	0.20	0.19	0.19	0.19
11000	1.29	1.35	1.65	1.89	1.96	0.20	0.20	0.19	0.19	0.19
11500	1.76	1.82	2.06	2.28	2.34	0.19	0.19	0.19	0.19	0.19
12000	2.23	2.29	2.56	2.78	2.84	0.19	0.19	0.19	0.19	0.19











Typical Performance Data

FREQ.  (MHz)	INPUT RETURN LOSS					OUTPUT RETURN LOSS				
	(dB)					(dB)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
10	34.79	34.91	32.47	30.60	30.48	35.21	34.71	33.08	30.67	31.05
50	35.25	34.63	33.20	31.41	30.98	33.97	33.48	32.42	31.42	31.23
100	32.92	32.83	32.09	31.01	30.53	32.28	32.09	32.20	31.93	31.71
200	31.05	30.89	30.09	29.31	28.99	31.33	31.14	30.30	29.49	29.13
400	26.49	26.42	26.12	25.72	25.62	27.13	26.93	26.34	26.09	25.85
600	23.56	23.53	23.20	23.03	22.96	24.03	23.92	23.49	23.19	23.07
800	21.24	21.23	20.99	20.90	20.87	21.57	21.53	21.18	20.80	20.63
1000	19.35	19.38	19.20	19.08	19.06	19.56	19.54	19.31	19.18	19.10
1100	18.65	18.65	18.57	18.48	18.44	18.76	18.78	18.60	18.42	18.35
1200	18.13	18.12	18.08	18.00	17.95	18.08	18.12	18.08	18.01	17.98
1300	17.81	17.82	17.84	17.76	17.73	17.72	17.77	17.83	17.79	17.74
1400	17.82	17.85	17.95	17.86	17.82	17.61	17.67	17.84	17.83	17.79
1500	18.24	18.29	18.45	18.36	18.32	17.97	18.03	18.25	18.29	18.32
1520	18.35	18.42	18.57	18.47	18.44	18.04	18.15	18.36	18.42	18.46
1600	19.02	19.08	19.26	19.15	19.10	18.54	18.63	18.98	19.01	19.02
1700	20.12	20.16	20.31	20.19	20.13	19.42	19.52	20.00	20.02	20.01
1800	21.10	21.14	21.40	21.24	21.22	20.38	20.50	21.01	21.08	21.11
1900	21.70	21.76	22.22	22.14	22.12	21.11	21.20	21.91	22.03	22.02
2000	22.23	22.33	22.98	23.08	23.07	21.66	21.84	22.73	22.94	22.96
2030	22.41	22.55	23.29	23.41	23.39	21.97	22.13	23.12	23.39	23.41
2100	23.19	23.37	24.28	24.46	24.46	22.64	22.87	23.98	24.34	24.41
2200	24.60	24.84	26.05	26.28	26.31	24.11	24.30	25.67	26.22	26.13
2300	27.14	27.43	28.89	28.77	28.62	26.26	26.55	28.05	28.51	28.43
2400	31.51	31.81	32.62	31.15	30.27	29.22	29.56	30.37	29.96	29.72
2460	35.58	35.66	33.90	31.09	30.33	30.76	31.00	31.04	29.96	29.49
2500	38.27	37.61	33.12	30.40	29.70	31.22	31.17	30.54	29.23	28.65
2600	33.74	32.84	29.47	27.74	27.23	29.93	29.58	28.34	27.12	26.74
2700	28.15	27.77	26.10	25.17	24.93	26.65	26.38	25.49	24.68	24.41
2800	24.50	24.28	23.25	22.76	22.60	23.77	23.63	22.96	22.96	22.27
2900	22.14	21.99	21.27	20.99	20.90	21.66	21.50	21.09	20.79	20.67
3000	20.20	20.14	19.70	19.56	19.57	19.91	19.83	19.61	19.44	19.42
3100	18.69	18.63	18.37	18.35	18.35	18.46	18.42	18.36	18.28	18.27
3200	17.57	17.53	17.31	17.37	17.42	17.33	17.32	17.25	17.29	17.34
3300	16.61	16.57	16.45	16.56	16.65	16.38	16.39	16.43	16.52	16.59
3400	15.65	15.62	15.62	15.75	15.84	15.51	15.52	15.63	15.75	15.84
3500	14.95	14.95	14.99	15.15	15.23	14.82	14.84	15.01	15.17	15.25
3600	14.35	14.36	14.41	14.58	14.68	14.19	14.23	14.42	14.60	14.70
3700	13.79	13.80	13.93	14.10	14.19	13.63	13.65	13.92	14.14	14.22
3800	13.28	13.29	13.46	13.68	13.79	13.11	13.15	13.47	13.72	13.84
3900	12.88	12.89	13.12	13.33	13.44	12.70	12.76	13.10	13.33	13.46
4000	12.56	12.57	12.79	12.95	13.05	12.38	12.42	12.78	12.99	13.09
4200	12.04	12.06	12.28	12.42	12.50	11.87	11.94	12.28	12.45	12.53
4400	11.82	11.83	11.99	12.04	12.12	11.65	11.70	11.97	12.06	12.13
4600	11.62	11.64	11.76	11.76	11.81	11.46	11.49	11.74	11.77	11.82
4800	11.55	11.56	11.68	11.62	11.65	11.38	11.42	11.64	11.61	11.63
5000	11.65	11.67	11.69	11.54	11.53	11.53	11.56	11.67	11.54	11.54
5200	11.80	11.82	11.80	11.58	11.55	11.68	11.73	11.79	11.60	11.55
5400	12.10	12.13	12.03	11.75	11.67	11.95	12.01	11.97	11.69	11.61
5600	12.50	12.52	12.33	11.98	11.86	12.42	12.45	12.29	11.94	11.83
5800	12.93	12.97	12.71	12.30	12.16	12.72	12.77	12.60	12.17	12.02
6000	13.34	13.39	13.12	12.70	12.55	13.10	13.17	12.98	12.58	12.40
6200	13.91	13.95	13.69	13.21	13.03	13.60	13.70	13.53	13.07	12.87
6400	14.43	14.48	14.24	13.82	13.64	14.05	14.14	14.08	13.68	13.49
6600	14.95	15.01	14.92	14.53	14.40	14.42	14.56	14.69	14.34	14.19
6800	15.41	15.51	15.59	15.34	15.24	14.82	15.02	15.35	15.16	15.07
7000	15.89	16.00	16.29	16.18	16.18	15.24	15.46	16.05	16.02	16.03
7200	16.26	16.39	16.98	17.11	17.18	15.61	15.83	16.73	16.93	17.07
7400	16.76	16.83	17.51	17.97	18.12	16.04	16.22	17.26	17.75	18.08
7600	17.53	17.56	18.21	18.83	19.10	16.67	16.80	17.88	18.72	19.11
7800	18.20	18.20	18.89	19.67	20.00	17.43	17.51	18.63	19.61	20.09
8000	18.59	18.56	19.37	20.27	20.60	17.90	17.98	19.21	20.41	21.04
8200	19.06	19.00	19.79	20.54	20.79	18.43	18.52	19.67	20.85	21.33
8400	19.56	19.47	20.02	20.50	20.68	19.22	19.23	20.07	20.84	21.25
8600	20.01	19.86	20.16	20.48	20.54	19.71	19.67	20.25	21.00	21.29
8800	20.33	20.11	20.02	19.96	19.88	20.23	20.11	20.18	20.37	20.42
9000	20.94	20.57	19.69	19.26	19.01	21.10	20.82	19.96	19.64	19.45
9200	20.98	20.53	19.09	18.39	18.04	21.36	20.95	19.52	18.87	18.56
9400	20.70	20.16	18.29	17.47	17.08	21.34	20.76	18.72	17.92	17.56
9600	19.84	19.33	17.32	16.43	16.02	20.65	20.09	17.89	16.91	16.51
9800	18.36	17.99	16.27	15.46	15.06	18.92	18.56	16.75	15.91	15.59
10000	16.62	16.40	15.12	14.43	14.12	17.22	16.93	15.70	14.95	14.67
10400	13.40	13.38	12.95	12.46	12.32	13.69	13.72	13.46	12.97	12.77
10500	12.67	12.70	12.45	12.03	11.94	12.95	12.99	12.97	12.59	12.40
11000	9.47	9.60	10.01	9.97	10.03	9.71	9.83	10.58	10.65	10.66
11500	7.43	7.55	8.13	8.30	8.44	7.61	7.72	8.64	8.96	9.12
12000	6.20	6.29	6.71	6.94	7.07	6.47	6.49	7.19	7.50	7.63





## Typical Performance Curves



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	