

NEW!
Two & Three
Section Models


MMIC

REFLECTIONLESS FILTERS DICE

50Ω DC to 21 GHz

The Big Deal

- High Stopband rejection, up to 50 dB
- Patented design terminates stopband signals
- Pass band cut-off up to 11 GHz
- Stop band up to 26 GHz
- Excellent repeatability through IPD* process



X-Series

Available in Low Pass
and High Pass designs

Product Overview

Mini-Circuits' **X-Series** of reflectionless filters now includes 2- and 3-section models, giving you ultra-high rejection in the stopband – up to 50 dB! Reflectionless filters employ a patented filter topology which absorbs and terminates stopband signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stopband, sending signals back to the source at 100% power. These reflections interact with neighboring components and often result in intermodulation and other interferences. By eliminating stopband reflections, reflectionless filters can readily be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

Key Features	Advantages
Easy integration with sensitive reflective components, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
High stopband rejection, up to 50 dB	Ideal for applications where suppression of strong spurious signals and intermodulation products is needed.
Enables stable integration of wideband amplifiers	Because reflectionless filters maintain good impedance in the stopband; they can be integrated with high gain, wideband amplifiers without the risk of creating instabilities in these out of band regions.
Cascadable	Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect passband signals. Low & highpass filters can be cascaded to realize bandpass filters.
Excellent power handling in a tiny surface mount device up to 7W in passband	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.
Excellent repeatability of RF performance	Through semiconductor IPD process, X-series filters are inherently repeatable for large volume production.
Excellent stability over temperature	With ± 0.3 dB variation over temperature ideal for use in wide temperature range applications without the need for additional temperature compensation.
Operating temperature up to 105°C	Suitable for operation close to high power components.

*IPD – Integrated Passive Device, is a GaAs semiconductor process



Reflectionless Low Pass Filter Die

XLF-112H-D+

50Ω DC to 1050 MHz

Features

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent stopband rejection, 39 dB typ.
- Temperature stable, up to 105°C
- Protected by US Patents 8,392,495; 9,705,467, additional patent pending
- Protected by China Patent 201080014266.1
- Protected by Taiwan Patent I581494


Applications

- Mobile
- ISM Applications
- TV broadcasting
- UHF radar

General Description

Mini-Circuits' XLF-112H-D+ three-section reflectionless filter Die employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

Simplified Schematic and Pad description



Pad#	Description
2	RF-IN
5	RF-OUT
1,3,4,6	Ground
Die bottom	Ground

Note: 1. Bond Pad material - Gold
2. Bottom of Die - Gold plated




+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

Bonding Pad Position



Dimensions in μm, Typical

L1	L2	L3	H1	H2	H3	H4	Thickness	Bond pad size
180	1820	2000	594	694	794	1420	100	78 x 78

Electrical Specifications¹ at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC - F1	DC - 1050	—	1.9	—	dB
	Frequency Cut-off	F2	1200	—	3.0	—	
	VSWR	DC - F1	DC - 1050	—	1.3	—	:1
Stop Band	Rejection	F3 - F3'	2000 - 2200	—	17	—	
		F3' - F4	2200 - 10000	—	36	—	dB
		F4 - F5	10000 - 19000	—	39	—	
	VSWR	F3 - F3'	2000 - 2200	—	1.2	—	
		F3' - F4	2200 - 10000	—	1.3	—	:1
		F4 - F5	10000 - 19000	—	2.1	—	

¹ Measured on Mini-Circuits Characterization Test Board . Die packaged in 4x4mm, 24-lead MCLP package and soldered on TB-952-112H+.

Absolute Maximum Ratings⁴


Parameter	Ratings
Operating Temperature	-55°C to +105°C
RF Power Input, Passband (DC-F1) ²	7.9W at 25°C
RF Power Input, Stopband (F2-F5) ³	1.58W at 25°C

² Passband rating derates linearly to 3.9W at 105°C ambient

³ Stopband rating derates linearly to 0.75W at 105°C ambient


⁴ Permanent damage may occur if any of these limits are exceeded.

SPECIFICATION DEFINITION




Typical Performance Data at 25°C¹

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	1.47	1.23
100	1.49	1.24
500	1.83	1.35
1050	2.64	1.23
1200	2.98	1.15
1500	4.25	1.20
2000	17.81	1.22
2200	41.34	1.27
2500	40.58	1.50
4000	39.65	1.20
6000	55.66	1.19
8000	41.20	1.53
9000	40.21	1.66
10000	40.62	1.76
11000	41.67	1.88
12000	43.14	2.08
15000	54.22	1.76
18000	51.84	2.06
19000	51.28	2.25



Assembly Diagram



Note: Ground bond wires are optional.

Assembly and Handling Procedure

- 1. Storage**
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
- 2. ESD**
MMIC Gallium Arsenide (GaAs) filter dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
- 3. Die Attach**
The Die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030Hk-PT/H579/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total Die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic Die pick up tools only.
- 4. Wire Bonding**
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the Die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

Additional Detailed Technical Information <i>additional information is available on our dash board.</i>											
Performance Data	Data Table										
	Swept Graphs										
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)										
Case Style	Die										
Die Ordering and packaging information	<table> <tr> <td>Quantity, Package</td> <td>Model No.</td> </tr> <tr> <td>Small, Gel - Pak: 5,10,50,100 KGD*</td> <td>XLF-112H-DG+</td> </tr> <tr> <td>Medium†, Partial wafer: KGD*<450</td> <td>XLF-112H-DP+</td> </tr> <tr> <td colspan="2">†Available upon request contact sales representative</td> </tr> <tr> <td colspan="2">Refer to AN-60-067</td> </tr> </table>	Quantity, Package	Model No.	Small, Gel - Pak: 5,10,50,100 KGD*	XLF-112H-DG+	Medium†, Partial wafer: KGD*<450	XLF-112H-DP+	†Available upon request contact sales representative		Refer to AN-60-067	
Quantity, Package	Model No.										
Small, Gel - Pak: 5,10,50,100 KGD*	XLF-112H-DG+										
Medium†, Partial wafer: KGD*<450	XLF-112H-DP+										
†Available upon request contact sales representative											
Refer to AN-60-067											
Environmental Ratings	ENV-80										

*Known Good Dice ("KGD") means that the dice are taken from PCM good wafer and visually inspected in question have been subjected to Mini-Circuits while this is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

ESD Rating**

Human Body Model (HBM): Class 1A (250V) in accordance with ANSI/ESD STM 5.1 - 2001

** Tested in industry standard MCLP 4x4mm 24 lead package.

Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, Die preparation, Die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.

MMIC Reflectionless Low Pass Filter Die **XLF-112H-D+**

Typical Performance Data

Test Condition @ Temperature = +25°C

FREQ.	INSERTION LOSS	INPUT RETURN LOSS	OUTPUT RETURN LOSS
(MHz)	(dB)	(dB)	(dB)
10	1.47	19.60	19.63
50	1.48	19.52	19.77
100	1.49	19.43	19.44
300	1.62	17.93	17.90
400	1.71	17.18	17.17
500	1.83	16.64	16.63
700	2.09	16.40	16.32
1000	2.55	18.92	18.67
1050	2.64	19.83	19.58
1200	2.98	23.56	23.04
1500	4.25	21.01	20.96
2200	41.34	18.85	18.62
2500	40.58	14.10	14.00
3000	52.89	15.16	15.40
3500	36.27	18.53	19.25
4000	39.63	20.80	22.55
4500	53.97	24.57	27.23
5000	63.49	33.08	34.64
5500	60.33	31.28	26.64
6000	55.52	23.07	21.21
6500	49.50	19.00	17.88
7000	45.18	16.43	15.84
7500	42.68	14.70	14.54
8000	41.17	13.53	13.67
8500	40.44	12.75	13.08
9000	40.18	12.09	12.64
9500	40.30	11.65	12.40
10000	40.62	11.20	12.26
10500	41.05	10.79	12.00
11000	41.62	10.30	11.57
11500	42.35	9.74	10.90
12000	43.14	9.09	10.11
12500	44.05	8.48	9.35
13000	45.23	7.86	8.70
13500	47.36	7.48	8.15
14000	64.08	7.38	7.99
14500	51.44	9.92	10.38
15000	54.17	11.20	11.89
15500	54.86	10.28	10.66
16000	53.16	10.03	10.17
16500	52.57	10.07	9.95
17000	52.29	9.87	9.83
17500	51.70	9.64	9.62
18000	51.75	9.19	9.27
18500	51.73	8.82	8.73
19000	51.28	8.30	8.46
19500	50.83	7.99	8.05
20000	50.19	7.66	7.67
20500	48.81	7.52	7.35
21000	47.37	7.08	7.13
21500	45.72	7.00	6.98
22000	44.99	6.54	6.95
22500	43.74	6.40	6.88
23000	42.61	6.04	6.80
23500	41.84	5.79	6.54
24000	41.15	5.52	6.15
24500	40.42	5.28	5.65
25000	39.96	5.08	5.21
25500	40.24	4.98	4.90
26000	41.18	4.94	4.73

Note: "Test data of Die packaged in industry standard 4x4mm, 24-lead MCLP package"



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site






The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
XLF-112H-D+
11/10/2017
Page 1 of 1

Typical Performance Curves



Note: "Test data of Die packaged in industry standard 4x4mm, 24-lead MCLP package"



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	