



MMIC REFLECTIONLESS

Low Pass Filter


XLF-861+

Mini-Circuits

50Ω DC to 860 MHz

THE BIG DEAL

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Temperature sData, up to +105°C
- Small size, 3 x 3 mm
- Protected by US Patent No. 8,392,495



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Harmonics Rejection
- Wideband Matching
- Transmitters / Receivers

PRODUCT OVERVIEW

Mini-Circuits' XLF-861+ reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

KEY FEATURES

| Features | Advantages |
|---|--|
| Reflectionless Technology | Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space. |
| 50Ω Match in Stopband | Reflectionless filters maintain good impedance matching in the stopband, allowing for integration with high gain, wideband amplifiers without the risk of creating out-of-band instabilities. |
| Excellent RF Performance Repeatability | Fabricated on a GaAs process, X-series filters are inherently repeaData for large-volume production. |
| Excellent Stability over temperature | With ±0.3 dB variation over temperature, is ideal for use in wide temperature range applications without the need for additional temperature compensation. |
| Excellent Power Handling in a Compact Package | High power handling extends the usability of these filters to the transmit path for inter-stage filtering. |





ELECTRICAL SPECIFICATIONS¹ AT +25°C

| Parameter | F# | Frequency (MHz) | Min. | Typ. | Max. | Unit | |
|-----------|-------------------|-----------------|--------------|------|------|------|----|
| Pass Band | Insertion Loss | DC - F1 | DC - 860 | — | 1.4 | 1.8 | dB |
| | Frequency Cut-off | F2 | 1150 | — | 3.0 | — | dB |
| | VSWR | DC - F1 | DC - 860 | — | 1.2 | — | :1 |
| Stop Band | Rejection | F3 - F4 | 1700 - 7500 | 12 | 15 | — | dB |
| | | F4 - F5 | 7500 - 25000 | — | 24 | — | dB |
| | VSWR | F3 - F4 | 1700 - 7500 | — | 1.2 | — | :1 |
| | | F4 - F5 | 7500 - 25000 | — | 2.3 | — | :1 |

1. Measured on Mini-Circuits Characterization Test Board TB-844-861+.

ABSOLUTE MAXIMUM RATINGS²


| Parameter | Ratings |
|---|-----------------|
| Operating Temperature | -55°C to +105°C |
| Storage Temperature | -65°C to +150°C |
| RF Power Input, Passband (DC-F1) ³ | 2 W at +25°C |
| RF Power Input, Stopband (F2-F5) ⁴ | 0.2 W at +25°C |

2. Permanent damage may occur if any of these limits are exceeded.

3. Passband rating derates linearly to 1 W at +105°C ambient



4. Stopband rating derates linearly to 0.1 W at +105°C ambient

SPECIFICATION DEFINITION






SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



| Function | Pad Number | Description |
|---------------------|-----------------|------------------------|
| RF-IN | 2 | RF Input Pad |
| RF-OUT | 8 | RF Output Pad |
| GND | 1,3,7,9, Paddle | Connected to ground |
| NC (GND Externally) | 4,5,6,10,11,12 | No internal connection |

PRODUCT MARKING





Marking may contain other features or characters for internal lot control



TYPICAL PERFORMANCE DATA AT +25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 10 | 0.67 | 1.02 |
| 100 | 0.65 | 1.06 |
| 200 | 0.67 | 1.09 |
| 400 | 0.76 | 1.18 |
| 860 | 1.38 | 1.30 |
| 1150 | 2.97 | 1.21 |
| 1700 | 15.26 | 1.22 |
| 2500 | 16.70 | 1.11 |
| 4000 | 15.03 | 1.02 |
| 5500 | 16.44 | 1.11 |
| 7500 | 16.09 | 1.26 |
| 9000 | 12.17 | 1.48 |
| 11000 | 26.57 | 1.17 |
| 13000 | 27.34 | 1.48 |
| 15000 | 25.78 | 1.52 |
| 17000 | 23.91 | 1.32 |
| 19000 | 22.50 | 1.86 |
| 21000 | 23.63 | 3.26 |
| 23000 | 24.92 | 4.53 |
| 25000 | 27.04 | 6.16 |





MMIC REFLECTIONLESS

Low Pass Filter

XLF-861+

Mini-Circuits

50Ω DC to 860 MHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. TO ACCESS [CLICK HERE](#)

| | |
|--|---|
| Performance Data & Graphs | Data Graphs S-Parameter (S2P Files) Data Set (.zip file) |
| Case Style | DQ1225 Plastic package, exposed paddle lead finish: matte-tin |
| Tape & Reel Standard quantities available on reel | F66 7" reels with 20, 50, 100, 200, 500, 1000, 2000, 3000 devices |
| Suggested Layout for PCB Design | PL-451 |
| Evaluation Board | TB-844-861+ (without connectors) TB-844-861C+ (with connectors) B20-118-F1+ Connector sold separately |
| Environmental Ratings | ENV82 |

ESD RATING

Human body model (HBM): Class 1A (250 to <500 V) in accordance with ANSI/ESD 5.1-2001


MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D



REFLECTIONLESS FILTER APPLICATION NOTE

Application Circuit Example: Pairing mixers with reflectionless filters to improve system dynamic range



Test block diagram: IF output reflection spectrum with single input frequency




Figure 1. IF output reflection spectrum without filter





Figure 2. IF output reflection spectrum with conventional filter



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Typical Performance Data

| FREQ. (MHz) | INSERTION LOSS | | | | | GROUP DELAY | | | | |
|--------------------|----------------|--------|--------|--------|---------|-------------|--------|--------|--------|---------|
| | (dB) | | | | | (nsec) | | | | |
| | @-55°C | @-40°C | @+25°C | @+85°C | @+105°C | @-55°C | @-40°C | @+25°C | @+85°C | @+105°C |
| 10 | 0.54 | 0.57 | 0.68 | 0.73 | 0.77 | 0.18 | 0.21 | 0.21 | 0.21 | 0.18 |
| 50 | 0.54 | 0.56 | 0.65 | 0.72 | 0.75 | 0.19 | 0.21 | 0.20 | 0.21 | 0.19 |
| 100 | 0.52 | 0.55 | 0.64 | 0.72 | 0.74 | 0.20 | 0.20 | 0.20 | 0.20 | 0.20 |
| 120 | 0.53 | 0.55 | 0.65 | 0.72 | 0.75 | 0.20 | 0.20 | 0.20 | 0.20 | 0.20 |
| 140 | 0.53 | 0.55 | 0.65 | 0.73 | 0.75 | 0.20 | 0.20 | 0.20 | 0.20 | 0.20 |
| 160 | 0.54 | 0.56 | 0.66 | 0.74 | 0.76 | 0.20 | 0.20 | 0.20 | 0.20 | 0.20 |
| 180 | 0.53 | 0.56 | 0.66 | 0.73 | 0.77 | 0.20 | 0.20 | 0.20 | 0.20 | 0.20 |
| 200 | 0.54 | 0.56 | 0.66 | 0.75 | 0.77 | 0.20 | 0.20 | 0.20 | 0.20 | 0.20 |
| 250 | 0.55 | 0.58 | 0.69 | 0.77 | 0.80 | 0.20 | 0.20 | 0.20 | 0.20 | 0.20 |
| 300 | 0.56 | 0.59 | 0.71 | 0.79 | 0.82 | 0.20 | 0.20 | 0.20 | 0.20 | 0.20 |
| 350 | 0.58 | 0.61 | 0.73 | 0.81 | 0.85 | 0.20 | 0.21 | 0.20 | 0.20 | 0.20 |
| 400 | 0.59 | 0.62 | 0.74 | 0.83 | 0.87 | 0.21 | 0.21 | 0.21 | 0.21 | 0.21 |
| 450 | 0.61 | 0.66 | 0.78 | 0.88 | 0.90 | 0.21 | 0.21 | 0.21 | 0.21 | 0.21 |
| 500 | 0.64 | 0.68 | 0.81 | 0.91 | 0.95 | 0.22 | 0.22 | 0.21 | 0.21 | 0.21 |
| 550 | 0.68 | 0.71 | 0.86 | 0.96 | 1.00 | 0.22 | 0.22 | 0.22 | 0.22 | 0.22 |
| 600 | 0.72 | 0.76 | 0.91 | 1.01 | 1.05 | 0.23 | 0.23 | 0.22 | 0.22 | 0.22 |
| 650 | 0.77 | 0.81 | 0.97 | 1.08 | 1.12 | 0.23 | 0.24 | 0.23 | 0.23 | 0.23 |
| 700 | 0.83 | 0.87 | 1.04 | 1.16 | 1.20 | 0.24 | 0.24 | 0.24 | 0.24 | 0.24 |
| 750 | 0.89 | 0.94 | 1.12 | 1.24 | 1.29 | 0.25 | 0.25 | 0.25 | 0.25 | 0.25 |
| 800 | 0.98 | 1.03 | 1.22 | 1.35 | 1.40 | 0.26 | 0.26 | 0.26 | 0.26 | 0.26 |
| 850 | 1.09 | 1.13 | 1.33 | 1.48 | 1.53 | 0.27 | 0.27 | 0.27 | 0.27 | 0.27 |
| 860 | 1.11 | 1.16 | 1.37 | 1.51 | 1.56 | 0.27 | 0.27 | 0.27 | 0.27 | 0.27 |
| 880 | 1.17 | 1.22 | 1.43 | 1.57 | 1.62 | 0.28 | 0.28 | 0.27 | 0.27 | 0.27 |
| 900 | 1.22 | 1.27 | 1.48 | 1.63 | 1.69 | 0.29 | 0.28 | 0.28 | 0.28 | 0.28 |
| 920 | 1.28 | 1.33 | 1.55 | 1.71 | 1.76 | 0.29 | 0.29 | 0.28 | 0.28 | 0.28 |
| 940 | 1.34 | 1.40 | 1.62 | 1.79 | 1.84 | 0.29 | 0.29 | 0.29 | 0.29 | 0.29 |
| 960 | 1.41 | 1.47 | 1.70 | 1.87 | 1.93 | 0.30 | 0.30 | 0.29 | 0.29 | 0.29 |
| 980 | 1.50 | 1.56 | 1.80 | 1.97 | 2.03 | 0.30 | 0.30 | 0.30 | 0.30 | 0.30 |
| 1000 | 1.58 | 1.64 | 1.89 | 2.06 | 2.13 | 0.31 | 0.31 | 0.31 | 0.30 | 0.30 |
| 1050 | 1.84 | 1.90 | 2.16 | 2.36 | 2.42 | 0.32 | 0.32 | 0.31 | 0.31 | 0.31 |
| 1100 | 2.16 | 2.22 | 2.51 | 2.72 | 2.79 | 0.34 | 0.33 | 0.33 | 0.32 | 0.32 |
| 1150 | 2.54 | 2.62 | 2.93 | 3.15 | 3.23 | 0.34 | 0.34 | 0.33 | 0.33 | 0.33 |
| 1200 | 3.02 | 3.10 | 3.43 | 3.68 | 3.76 | 0.35 | 0.35 | 0.34 | 0.34 | 0.33 |
| 1300 | 4.28 | 4.37 | 4.75 | 5.02 | 5.12 | 0.35 | 0.35 | 0.34 | 0.33 | 0.33 |
| 1400 | 6.03 | 6.13 | 6.53 | 6.85 | 6.95 | 0.33 | 0.33 | 0.31 | 0.30 | 0.29 |
| 1500 | 8.27 | 8.38 | 8.83 | 9.16 | 9.26 | 0.28 | 0.28 | 0.25 | 0.24 | 0.23 |
| 1600 | 11.07 | 11.19 | 11.65 | 11.99 | 12.10 | 0.20 | 0.20 | 0.17 | 0.15 | 0.14 |
| 1700 | 14.51 | 14.62 | 15.09 | 15.42 | 15.53 | 0.08 | 0.07 | 0.03 | -0.01 | -0.02 |
| 1800 | 18.76 | 18.86 | 19.29 | 19.54 | 19.58 | -0.18 | -0.20 | -0.26 | -0.32 | -0.33 |
| 1900 | 23.76 | 23.80 | 23.73 | 23.54 | 23.45 | -0.81 | -0.82 | -0.85 | -0.83 | -0.83 |
| 2000 | 26.00 | 25.80 | 24.92 | 24.21 | 23.97 | -1.16 | -1.11 | -0.96 | -0.85 | -0.81 |
| 2500 | 16.68 | 16.68 | 16.70 | 16.62 | 16.61 | 0.07 | 0.07 | 0.06 | 0.05 | 0.05 |
| 3000 | 14.78 | 14.81 | 14.93 | 14.97 | 14.97 | 0.08 | 0.08 | 0.07 | 0.07 | 0.07 |
| 3500 | 14.51 | 14.55 | 14.71 | 14.78 | 14.78 | 0.07 | 0.07 | 0.07 | 0.06 | 0.06 |
| 4000 | 14.74 | 14.80 | 14.99 | 15.05 | 15.08 | 0.07 | 0.07 | 0.06 | 0.06 | 0.06 |
| 4500 | 15.17 | 15.21 | 15.42 | 15.51 | 15.56 | 0.06 | 0.07 | 0.05 | 0.06 | 0.06 |
| 5000 | 15.62 | 15.68 | 15.90 | 15.99 | 16.06 | 0.06 | 0.06 | 0.05 | 0.06 | 0.05 |
| 5500 | 16.06 | 16.11 | 16.33 | 16.47 | 16.51 | 0.06 | 0.05 | 0.05 | 0.05 | 0.05 |
| 6000 | 16.38 | 16.47 | 16.69 | 16.80 | 16.86 | 0.05 | 0.06 | 0.05 | 0.06 | 0.05 |
| 6500 | 16.54 | 16.59 | 16.86 | 16.95 | 16.98 | 0.06 | 0.06 | 0.05 | 0.06 | 0.06 |
| 7000 | 16.42 | 16.46 | 16.66 | 16.74 | 16.77 | 0.07 | 0.06 | 0.06 | 0.06 | 0.06 |
| 7500 | 15.72 | 15.78 | 15.92 | 15.94 | 15.96 | 0.07 | 0.07 | 0.07 | 0.08 | 0.08 |
| 8000 | 14.12 | 14.15 | 14.26 | 14.20 | 14.19 | 0.11 | 0.11 | 0.12 | 0.13 | 0.13 |
| 8500 | 11.15 | 11.19 | 11.41 | 11.54 | 11.62 | 0.25 | 0.25 | 0.27 | 0.29 | 0.30 |
| 9000 | 10.73 | 10.99 | 12.19 | 13.20 | 13.54 | 0.36 | 0.35 | 0.31 | 0.28 | 0.27 |
| 10000 | 21.05 | 21.23 | 22.11 | 22.76 | 22.95 | 0.08 | 0.07 | 0.06 | 0.05 | 0.07 |
| 11000 | 25.85 | 25.97 | 26.52 | 26.84 | 27.00 | 0.04 | 0.03 | 0.03 | 0.03 | 0.02 |
| 12000 | 27.09 | 27.22 | 27.70 | 27.92 | 28.00 | 0.04 | 0.05 | 0.03 | 0.04 | 0.03 |
| 13000 | 26.82 | 26.95 | 27.41 | 27.64 | 27.76 | 0.03 | 0.04 | 0.03 | 0.02 | 0.03 |
| 14000 | 26.17 | 26.33 | 26.62 | 26.84 | 26.83 | 0.04 | 0.05 | 0.03 | 0.04 | 0.04 |
| 15000 | 25.31 | 25.37 | 25.61 | 25.69 | 25.76 | 0.04 | 0.04 | 0.04 | 0.03 | 0.04 |
| 16000 | 24.18 | 24.25 | 24.54 | 24.70 | 24.76 | 0.04 | 0.04 | 0.05 | 0.04 | 0.04 |
| 17000 | 23.07 | 23.20 | 23.65 | 23.90 | 23.96 | 0.05 | 0.04 | 0.05 | 0.04 | 0.05 |
| 18000 | 22.58 | 22.68 | 23.02 | 23.28 | 23.34 | 0.05 | 0.05 | 0.06 | 0.04 | 0.05 |
| 19000 | 22.34 | 22.45 | 22.96 | 23.41 | 23.36 | 0.05 | 0.06 | 0.04 | 0.05 | 0.05 |
| 20000 | 22.53 | 22.68 | 23.70 | 24.29 | 24.50 | 0.06 | 0.06 | 0.04 | 0.04 | 0.04 |
| 21000 | 24.10 | 23.98 | 23.64 | 24.31 | 24.63 | -0.04 | -0.03 | 0.05 | 0.04 | 0.03 |
| 22000 | 24.42 | 24.51 | 24.32 | 24.55 | 24.66 | 0.00 | -0.01 | 0.03 | 0.04 | 0.04 |
| 23000 | 24.59 | 24.72 | 24.98 | 24.97 | 24.87 | 0.02 | 0.02 | 0.04 | 0.04 | 0.04 |
| 24000 | 23.69 | 23.94 | 25.44 | 25.89 | 26.00 | 0.06 | 0.07 | 0.03 | 0.02 | 0.02 |
| 25000 | 25.33 | 25.41 | 26.04 | 26.72 | 27.11 | 0.03 | 0.04 | 0.02 | 0.01 | -0.01 |
| 26000 | 27.27 | 27.19 | 26.68 | 27.04 | 27.23 | -0.03 | -0.01 | 0.01 | 0.01 | 0.03 |
| 27000 | 26.60 | 26.68 | 27.04 | 26.73 | 26.70 | 0.00 | 0.00 | -0.02 | 0.02 | 0.02 |
| 28000 | 22.69 | 22.69 | 23.24 | 23.81 | 24.20 | 0.11 | 0.10 | 0.16 | 0.17 | 0.21 |
| 29000 | 20.52 | 21.00 | 23.81 | 28.14 | 29.52 | 0.31 | 0.32 | 0.39 | 0.41 | 0.54 |
| 30000 | 23.90 | 24.20 | 24.34 | 24.09 | 24.17 | 0.35 | 0.36 | 0.31 | 0.26 | 0.23 |











Typical Performance Data


| FREQ. (MHz) | INPUT RETURN LOSS | | | | | OUTPUT RETURN LOSS | | | | |
|--------------------|-------------------|--------|--------|--------|---------|--------------------|--------|--------|--------|---------|
| | (dB) | | | | | (dB) | | | | |
| | @-55°C | @-40°C | @+25°C | @+85°C | @+105°C | @-55°C | @-40°C | @+25°C | @+85°C | @+105°C |
| 10 | 42.30 | 43.31 | 39.73 | 34.87 | 33.33 | 36.92 | 37.77 | 34.87 | 32.04 | 30.84 |
| 50 | 35.29 | 35.29 | 33.16 | 30.71 | 30.11 | 35.47 | 35.70 | 33.77 | 31.94 | 31.42 |
| 100 | 32.38 | 32.40 | 30.87 | 29.09 | 28.54 | 32.47 | 32.41 | 32.00 | 30.86 | 30.44 |
| 120 | 32.01 | 31.86 | 30.14 | 28.54 | 27.96 | 31.79 | 31.74 | 30.59 | 29.79 | 29.51 |
| 140 | 30.96 | 30.61 | 29.12 | 27.75 | 27.17 | 31.44 | 31.21 | 29.87 | 29.00 | 28.46 |
| 160 | 30.16 | 29.73 | 28.26 | 27.16 | 26.64 | 30.59 | 30.17 | 28.82 | 27.74 | 27.38 |
| 180 | 29.40 | 29.14 | 27.72 | 26.61 | 26.23 | 29.57 | 29.02 | 27.55 | 26.57 | 26.12 |
| 200 | 28.22 | 27.92 | 26.77 | 25.89 | 25.47 | 28.70 | 28.43 | 26.97 | 25.89 | 25.46 |
| 250 | 26.09 | 26.03 | 25.03 | 24.52 | 24.30 | 26.26 | 26.14 | 25.26 | 24.49 | 24.25 |
| 300 | 24.70 | 24.56 | 23.84 | 23.45 | 23.34 | 24.35 | 24.24 | 23.71 | 23.16 | 23.09 |
| 350 | 23.30 | 23.22 | 22.49 | 22.17 | 22.03 | 23.31 | 23.18 | 22.64 | 22.21 | 22.17 |
| 400 | 22.17 | 22.11 | 21.49 | 21.19 | 21.00 | 22.32 | 22.19 | 21.63 | 21.22 | 21.08 |
| 450 | 21.16 | 21.07 | 20.67 | 20.38 | 20.21 | 21.39 | 21.34 | 20.84 | 20.38 | 20.20 |
| 500 | 20.42 | 20.37 | 19.91 | 19.72 | 19.62 | 20.68 | 20.58 | 20.18 | 19.75 | 19.59 |
| 550 | 19.97 | 19.90 | 19.38 | 19.25 | 19.21 | 19.92 | 19.80 | 19.40 | 19.09 | 19.02 |
| 600 | 19.46 | 19.39 | 18.88 | 18.75 | 18.71 | 19.48 | 19.42 | 18.91 | 18.72 | 18.67 |
| 650 | 18.88 | 18.84 | 18.45 | 18.28 | 18.25 | 18.97 | 18.93 | 18.48 | 18.28 | 18.23 |
| 700 | 18.48 | 18.45 | 18.18 | 17.97 | 17.95 | 18.57 | 18.49 | 18.18 | 17.94 | 17.86 |
| 750 | 18.22 | 18.20 | 17.99 | 17.85 | 17.78 | 18.20 | 18.20 | 17.97 | 17.73 | 17.63 |
| 800 | 18.00 | 17.99 | 17.85 | 17.72 | 17.69 | 17.96 | 17.94 | 17.78 | 17.60 | 17.53 |
| 850 | 17.96 | 17.96 | 17.86 | 17.76 | 17.76 | 17.90 | 17.91 | 17.78 | 17.67 | 17.63 |
| 860 | 17.93 | 17.93 | 17.84 | 17.74 | 17.77 | 17.88 | 17.91 | 17.79 | 17.68 | 17.64 |
| 880 | 17.96 | 17.95 | 17.88 | 17.80 | 17.78 | 17.94 | 17.97 | 17.87 | 17.80 | 17.73 |
| 900 | 18.02 | 18.00 | 17.96 | 17.86 | 17.87 | 17.95 | 17.97 | 17.91 | 17.84 | 17.78 |
| 920 | 18.09 | 18.09 | 18.06 | 17.95 | 17.95 | 18.05 | 18.06 | 18.00 | 17.93 | 17.90 |
| 940 | 18.16 | 18.17 | 18.14 | 18.04 | 18.03 | 18.17 | 18.17 | 18.13 | 18.07 | 18.03 |
| 960 | 18.31 | 18.31 | 18.30 | 18.17 | 18.17 | 18.24 | 18.29 | 18.24 | 18.16 | 18.13 |
| 980 | 18.42 | 18.43 | 18.44 | 18.32 | 18.30 | 18.39 | 18.42 | 18.39 | 18.32 | 18.25 |
| 1000 | 18.53 | 18.56 | 18.57 | 18.45 | 18.43 | 18.57 | 18.62 | 18.59 | 18.50 | 18.43 |
| 1050 | 19.04 | 19.09 | 19.14 | 19.04 | 19.03 | 19.03 | 19.12 | 19.15 | 19.06 | 18.98 |
| 1100 | 19.82 | 19.87 | 19.97 | 19.86 | 19.83 | 19.87 | 19.92 | 19.94 | 19.84 | 19.88 |
| 1150 | 20.71 | 20.72 | 20.83 | 20.72 | 20.69 | 20.84 | 20.88 | 21.02 | 20.90 | 20.87 |
| 1200 | 21.80 | 21.82 | 21.88 | 21.70 | 21.63 | 21.93 | 21.95 | 22.02 | 21.87 | 21.79 |
| 1300 | 23.57 | 23.52 | 23.37 | 23.04 | 22.94 | 23.78 | 23.79 | 23.60 | 23.29 | 23.11 |
| 1400 | 22.97 | 22.98 | 22.86 | 22.62 | 22.54 | 23.25 | 23.22 | 23.03 | 22.87 | 22.74 |
| 1500 | 21.29 | 21.30 | 21.43 | 21.35 | 21.30 | 21.43 | 21.50 | 21.50 | 21.52 | 21.53 |
| 1600 | 20.06 | 20.13 | 20.43 | 20.45 | 20.45 | 20.08 | 20.15 | 20.48 | 20.56 | 20.54 |
| 1700 | 19.49 | 19.59 | 19.96 | 20.04 | 20.04 | 19.52 | 19.62 | 20.06 | 20.17 | 20.21 |
| 1800 | 19.47 | 19.57 | 19.97 | 20.06 | 20.05 | 19.54 | 19.62 | 20.14 | 20.22 | 20.24 |
| 1900 | 19.82 | 19.94 | 20.36 | 20.45 | 20.44 | 19.76 | 19.90 | 20.49 | 20.63 | 20.60 |
| 2000 | 20.48 | 20.55 | 20.93 | 21.05 | 21.06 | 20.35 | 20.50 | 21.09 | 21.19 | 21.24 |
| 2500 | 26.23 | 26.30 | 26.27 | 26.40 | 26.32 | 25.62 | 25.75 | 26.28 | 26.42 | 26.31 |
| 3000 | 34.87 | 35.73 | 37.47 | 37.04 | 36.50 | 34.99 | 35.42 | 37.20 | 36.82 | 36.38 |
| 3500 | 33.65 | 34.32 | 38.34 | 44.87 | 47.69 | 37.05 | 37.77 | 40.17 | 44.69 | 46.43 |
| 4000 | 30.03 | 30.37 | 32.13 | 34.59 | 35.21 | 29.35 | 29.95 | 32.93 | 35.83 | 36.81 |
| 4500 | 28.45 | 28.77 | 29.83 | 30.56 | 30.74 | 27.56 | 27.88 | 30.36 | 31.24 | 31.32 |
| 5000 | 27.94 | 27.92 | 27.85 | 27.67 | 27.54 | 27.96 | 27.99 | 27.62 | 26.57 | 26.57 |
| 5500 | 26.52 | 26.39 | 25.61 | 24.98 | 24.85 | 27.86 | 27.55 | 24.72 | 23.43 | 22.91 |
| 6000 | 24.00 | 23.98 | 23.47 | 22.83 | 22.71 | 24.05 | 23.85 | 22.20 | 21.24 | 20.94 |
| 6500 | 22.38 | 22.34 | 21.82 | 21.54 | 21.55 | 20.36 | 20.40 | 20.47 | 20.11 | 20.07 |
| 7000 | 21.12 | 21.06 | 20.72 | 20.72 | 20.81 | 17.77 | 17.92 | 19.30 | 19.66 | 19.99 |
| 7500 | 20.27 | 20.23 | 20.15 | 20.10 | 20.19 | 17.10 | 17.23 | 18.59 | 19.23 | 19.55 |
| 8000 | 18.99 | 18.97 | 18.87 | 18.63 | 18.54 | 17.45 | 17.50 | 17.83 | 17.76 | 17.75 |
| 8500 | 14.95 | 14.92 | 15.00 | 14.86 | 14.78 | 16.16 | 16.08 | 15.34 | 14.95 | 14.72 |
| 9000 | 12.39 | 12.62 | 13.54 | 14.54 | 14.89 | 12.32 | 12.66 | 14.69 | 16.15 | 16.76 |
| 10000 | 24.00 | 24.36 | 25.88 | 27.75 | 28.95 | 27.52 | 27.61 | 27.55 | 28.49 | 28.81 |
| 11000 | 27.19 | 26.91 | 25.48 | 24.07 | 23.40 | 19.66 | 19.94 | 22.63 | 23.32 | 23.66 |
| 12000 | 18.37 | 18.21 | 17.52 | 16.78 | 16.47 | 16.79 | 16.65 | 16.23 | 15.94 | 15.91 |
| 13000 | 15.18 | 15.11 | 14.83 | 14.34 | 14.22 | 16.05 | 15.75 | 13.60 | 12.60 | 12.18 |
| 14000 | 13.88 | 13.89 | 13.92 | 13.83 | 13.86 | 11.76 | 11.94 | 12.52 | 12.04 | 11.74 |
| 15000 | 13.83 | 13.91 | 14.25 | 14.44 | 14.59 | 10.06 | 10.31 | 12.73 | 13.80 | 14.32 |
| 16000 | 15.10 | 15.21 | 15.65 | 16.07 | 16.26 | 12.89 | 13.02 | 14.34 | 15.61 | 16.42 |
| 17000 | 16.23 | 16.37 | 17.03 | 17.28 | 17.31 | 22.74 | 22.76 | 18.32 | 16.69 | 15.77 |
| 18000 | 13.78 | 13.76 | 13.78 | 13.56 | 13.36 | 12.04 | 12.45 | 17.49 | 19.78 | 20.45 |
| 19000 | 9.38 | 9.33 | 9.12 | 8.82 | 8.75 | 11.32 | 11.31 | 11.42 | 11.58 | 11.85 |
| 20000 | 6.16 | 6.17 | 6.11 | 5.99 | 6.00 | 9.82 | 9.70 | 7.64 | 6.75 | 6.37 |
| 21000 | 4.38 | 4.57 | 5.58 | 5.07 | 5.09 | 4.49 | 4.72 | 5.63 | 5.19 | 4.83 |
| 22000 | 4.27 | 4.29 | 4.17 | 4.02 | 4.06 | 2.27 | 2.48 | 4.56 | 5.52 | 5.68 |
| 23000 | 3.13 | 3.19 | 3.43 | 3.61 | 3.71 | 2.66 | 2.77 | 3.96 | 5.24 | 6.04 |
| 24000 | 2.69 | 2.78 | 3.05 | 3.40 | 3.54 | 4.55 | 4.59 | 3.60 | 3.55 | 3.54 |
| 25000 | 2.18 | 2.26 | 2.69 | 2.97 | 3.06 | 1.71 | 1.97 | 3.15 | 3.08 | 2.88 |
| 26000 | 1.85 | 1.95 | 2.44 | 2.62 | 2.70 | 0.53 | 0.74 | 2.81 | 3.87 | 4.07 |
| 27000 | 1.99 | 2.10 | 2.53 | 2.86 | 3.02 | 1.51 | 1.67 | 2.87 | 4.18 | 4.94 |
| 28000 | 2.78 | 2.97 | 3.66 | 4.31 | 4.49 | 4.14 | 4.47 | 4.14 | 3.95 | 3.84 |
| 29000 | 4.02 | 4.07 | 4.45 | 4.49 | 4.44 | 2.43 | 2.74 | 5.02 | 4.51 | 3.93 |
| 30000 | 3.36 | 3.43 | 4.10 | 4.30 | 4.33 | 1.37 | 1.59 | 4.18 | 5.99 | 6.23 |




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN $\pm .002$

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

1. Case material: Plastic.
2. Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F66



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel see note | |
|----------------|-------------------------|-------------------|------------------------------|------------------|
| 8 | 4 | 7 | Small quantity standard | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | 7 | Standard | 1000, 2000, 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|-------------|----------|-----|------|
| OR | M152656 | NEW RELEASE | 09/11/15 | ITG | MY |
| | | | | | |
| | | | | | |

SUGGESTED MOUNTING CONFIGURATION
FOR DQ1225 CASE STYLE, "12FL02" PIN CODE



NOTES:

- TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.0066 \pm .0007$ ". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

| UNLESS OTHERWISE SPECIFIED | INITIALS | | DATE |
|--|----------|-----|----------|
| DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ± | DRAWN | ITG | 09/10/15 |
| | CHECKED | GF | 09/11/15 |
| | APPROVED | MY | 09/11/15 |

Mini-Circuits[®] 13 Neptune Avenue
Brooklyn NY 11235


PL, 12FL02, DQ1225, TB-844+

Mini-Circuits[®]
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


| | | | |
|------------------|---------------------|--------------------------|------------|
| SIZE A | CODE IDENT 15542 | DRAWING NO: 98-PL-451 | REV: OR |
| FILE: 98PL451 | SCALE: 16:1 | SHEET: 1 OF 1 | |

Evaluation Board and Circuit

To be used with Mini-Circuits 50 Ohm 2.92 connectors B20-118-F1+.
Connectors are sold separately.




TB-844-861+





Schematic Diagram

Note:

PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm 2.92 mm Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|---|
| Operating Temperature | -55° to 105°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -65° to 150° C Ambient Environment | Individual Model Data Sheet |
| Autoclave | 15 psig, 100% RH, 121°C, 96 hours | JESD22-A102-C, Condition C |
| Temperature Cycling | -65° to 150°C, 100 cycles | JESD22-A104 |
| Temperature Humidity | 85°C/ 85% RH, 168 hours | JESD22-113 |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1 |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS) | J-STD-020C |
| Solderability | 10X magnification, 95% coverage | JESD22-B102, Method 1: Dip and Look Test |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |