



MMIC REFLECTIONLESS

Low Pass Filter

XLF-732+

Mini-Circuits

50Ω DC to 7300 MHz

THE BIG DEAL

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Temperature sData, up to +105°C
- Small size, 3 x 3 mm
- Protected by US Patent No. 8,392,495

*Generic photo used for illustration purposes only*

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Harmonics Rejection
- Wideband Matching
- Transmitters / Receivers

PRODUCT OVERVIEW

Mini-Circuits' XLF-732+ reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

KEY FEATURES

Features	Advantages
Reflectionless Technology	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
50Ω Match in Stopband	Reflectionless filters maintain good impedance matching in the stopband, allowing for integration with high gain, wideband amplifiers without the risk of creating out-of-band instabilities.
Excellent RF Performance Repeatability	Fabricated on a GaAs process, X-series filters are inherently repeatable for large-volume production.
Excellent Stability over temperature	With ±0.3 dB variation over temperature, is ideal for use in wide temperature range applications without the need for additional temperature compensation.
Excellent Power Handling in a Compact Package	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.

REV. B
ECO-020994
XLF-732+
MCL NY
240226



MMIC REFLECTIONLESS

Low Pass Filter

XLF-732+

50Ω DC to 7300 MHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC - F1	DC - 7300	—	1.1	1.5
	Frequency Cut-off	F2	9800	—	3.0	—
	VSWR	DC - F1	DC - 7300	—	1.2	—
Stop Band	Rejection	F3 - F5	14300 - 34000	13	16	—
	VSWR	F3 - F4	14300 - 25000	—	2.5	—
		F4 - F5	25000 - 34000	—	3.0	—

1. Measured on Mini-Circuits Characterization Test Board TB-844-732+

ABSOLUTE MAXIMUM RATINGS²


Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-65°C to +150°C
RF Power Input, Passband (DC-F1) ³	2 W at +25°C
RF Power Input, Stopband (F2-F5) ⁴	0.2 W at +25°C

2. Permanent damage may occur if any of these limits are exceeded.

3. Passband rating derates linearly to 1 W at 105°C ambient

4. Stopband rating derates linearly to 0.1 W at 105°C ambient

SPECIFICATION DEFINITION







MMIC REFLECTIONLESS Low Pass Filter

XLF-732+

Mini-Circuits


50Ω DC to 7300 MHz

SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	2	RF Input Pad
RF-OUT	8	RF Output Pad
GND	1,3,7,9, Paddle	Connected to ground
NC (GND Externally)	4,5,6,10,11,12	No internal connection

PRODUCT MARKING



Marking may contain other features or characters for internal lot control

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 3 OF 6



MMIC REFLECTIONLESS



Low Pass Filter

XLF-732+

50Ω DC to 7300 MHz

TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.40	1.03
100	0.38	1.02
200	0.39	1.04
400	0.40	1.09
800	0.44	1.17
1600	0.52	1.28
3200	0.57	1.21
5000	0.69	1.19
7300	1.09	1.10
9800	2.97	1.51
12000	7.38	1.51
14300	15.66	1.50
17000	26.40	1.94
19500	22.31	3.14
22000	20.23	3.22
25000	18.17	2.38
27000	17.64	1.82
29500	17.81	2.15
32000	20.13	4.24
34000	21.50	6.90





MMIC REFLECTIONLESS

Low Pass Filter

XLF-732+

Mini-Circuits

50Ω DC to 7300 MHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500 ,1000, 2000, 3000 devices
Suggested Layout for PCB Design	PL-451
Evaluation Board	TB-844-732+ (without connectors) TB-844-732C+ (with connectors) B20-118-F1+ Connector sold separately
Environmental Ratings	ENV82

ESD RATING

Human body model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD 5.1-2001

MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

Mini-Circuits®




MMIC REFLECTIONLESS Low Pass Filter

XLF-732+

50Ω DC to 7300 MHz

REFLECTIONLESS FILTER APPLICATION NOTE

Application Circuit Example: Pairing mixers with reflectionless filters to improve system dynamic range



Test block diagram: IF output reflection spectrum with single input frequency




Figure 1. IF output reflection spectrum without filter





Figure 2. IF output reflection spectrum with conventional filter

An application circuit was assembled to measure the IF reflection spectrum at the output of a mixer when the mixer was paired with a conventional filter versus a reflectionless filter.

While the conventional filter reduces the reflections present when the mixer is used alone (no filter), the reflectionless filter virtually eliminates those reflections altogether.

The reflected signal at marker 1 in the figures above exhibits a reduction of more than 20 dB from -28.7 dBm to -50.3 dBm when the reflectionless filter is used as compared to the conventional filter, thus eliminating unwanted spurious mixing products and improving system dynamic range.

For more information, refer to application note [AN-75-007](#).



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits®

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)					GROUP DELAY (nsec)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
	0.38	0.36	0.40	0.43	0.45	0.12	0.13	0.13	0.13	0.15
50	0.34	0.35	0.38	0.40	0.43	0.08	0.09	0.09	0.09	0.10
100	0.34	0.35	0.39	0.41	0.43	0.05	0.06	0.05	0.06	0.06
200	0.34	0.36	0.40	0.43	0.44	0.05	0.05	0.05	0.05	0.05
300	0.35	0.36	0.40	0.44	0.46	0.05	0.05	0.05	0.05	0.05
400	0.34	0.36	0.41	0.45	0.46	0.05	0.05	0.05	0.05	0.05
500	0.35	0.37	0.42	0.46	0.48	0.05	0.05	0.04	0.05	0.05
600	0.35	0.37	0.43	0.48	0.50	0.05	0.05	0.05	0.05	0.05
700	0.35	0.37	0.44	0.49	0.51	0.05	0.05	0.04	0.05	0.05
800	0.36	0.37	0.44	0.49	0.51	0.05	0.05	0.05	0.05	0.05
900	0.37	0.38	0.45	0.50	0.53	0.05	0.05	0.04	0.05	0.05
1000	0.37	0.39	0.46	0.52	0.53	0.05	0.05	0.05	0.05	0.05
1200	0.39	0.41	0.48	0.55	0.56	0.05	0.05	0.04	0.05	0.05
1400	0.40	0.43	0.51	0.57	0.59	0.05	0.05	0.05	0.05	0.05
1600	0.43	0.45	0.52	0.59	0.61	0.05	0.05	0.04	0.05	0.05
1800	0.44	0.46	0.54	0.60	0.62	0.04	0.05	0.04	0.05	0.05
2000	0.44	0.47	0.55	0.61	0.63	0.05	0.05	0.04	0.05	0.05
2500	0.45	0.48	0.57	0.64	0.66	0.05	0.05	0.04	0.05	0.05
3000	0.45	0.48	0.58	0.65	0.68	0.05	0.05	0.04	0.05	0.05
3500	0.46	0.49	0.60	0.68	0.71	0.05	0.05	0.05	0.05	0.05
4000	0.48	0.52	0.63	0.73	0.76	0.05	0.05	0.05	0.05	0.05
4500	0.51	0.55	0.68	0.78	0.82	0.05	0.05	0.05	0.05	0.05
5000	0.56	0.59	0.73	0.84	0.88	0.05	0.05	0.05	0.05	0.05
5500	0.59	0.63	0.78	0.89	0.94	0.05	0.05	0.05	0.05	0.05
6000	0.64	0.68	0.85	0.97	1.02	0.05	0.05	0.05	0.05	0.05
6500	0.69	0.74	0.92	1.05	1.10	0.06	0.05	0.05	0.06	0.06
7000	0.78	0.84	1.02	1.18	1.23	0.06	0.06	0.05	0.06	0.06
7300	0.85	0.90	1.11	1.27	1.32	0.06	0.06	0.05	0.06	0.06
7500	0.91	0.96	1.17	1.33	1.40	0.06	0.06	0.06	0.06	0.06
7800	1.01	1.07	1.29	1.47	1.53	0.06	0.06	0.06	0.06	0.06
8000	1.08	1.15	1.38	1.56	1.63	0.06	0.06	0.06	0.06	0.06
8200	1.18	1.24	1.48	1.68	1.75	0.06	0.06	0.06	0.06	0.06
8400	1.29	1.35	1.60	1.80	1.88	0.06	0.06	0.06	0.06	0.06
8600	1.42	1.49	1.74	1.95	2.03	0.06	0.06	0.06	0.06	0.06
8800	1.56	1.64	1.89	2.11	2.19	0.06	0.07	0.06	0.06	0.07
9000	1.73	1.80	2.07	2.29	2.37	0.06	0.07	0.06	0.06	0.07
9200	1.91	1.98	2.27	2.49	2.58	0.06	0.06	0.06	0.06	0.07
9400	2.10	2.18	2.48	2.72	2.79	0.07	0.07	0.06	0.07	0.07
9600	2.31	2.39	2.71	2.95	3.03	0.07	0.07	0.06	0.06	0.07
9800	2.54	2.63	2.96	3.22	3.30	0.07	0.07	0.07	0.07	0.07
10000	2.79	2.89	3.24	3.50	3.59	0.07	0.07	0.06	0.07	0.07
10200	3.07	3.17	3.52	3.81	3.89	0.07	0.07	0.06	0.07	0.07
10400	3.37	3.47	3.84	4.13	4.23	0.07	0.07	0.06	0.07	0.07
10600	3.70	3.79	4.17	4.48	4.58	0.07	0.07	0.06	0.07	0.07
10800	4.04	4.14	4.54	4.86	4.96	0.07	0.07	0.06	0.07	0.07
11000	4.42	4.53	4.92	5.26	5.37	0.07	0.07	0.06	0.06	0.07
12000	6.78	6.91	7.34	7.73	7.86	0.06	0.06	0.06	0.06	0.06
13000	9.92	10.03	10.46	10.88	11.02	0.05	0.05	0.05	0.05	0.05
14000	13.67	13.80	14.31	14.74	14.87	0.04	0.04	0.04	0.04	0.04
14300	14.97	15.12	15.64	16.07	16.23	0.03	0.04	0.03	0.03	0.03
15000	18.46	18.60	19.18	19.62	19.76	0.02	0.01	0.01	0.00	0.00
16000	24.49	24.60	24.85	25.02	25.03	-0.06	-0.07	-0.08	-0.08	-0.08
17000	26.89	26.87	26.40	26.02	25.89	-0.10	-0.10	-0.08	-0.07	-0.06
18000	24.17	24.15	24.04	23.87	23.82	0.01	-0.01	-0.01	0.00	0.00
19000	22.45	22.51	22.53	22.50	22.55	0.02	0.02	0.01	0.02	0.01
20000	21.57	21.66	21.63	21.74	21.79	0.01	0.02	0.02	0.01	0.02
21000	20.89	20.97	21.17	21.22	21.24	0.03	0.02	0.00	0.01	0.01
22000	19.90	19.99	20.10	20.14	20.12	0.03	0.02	0.02	0.03	0.02
23000	19.04	19.10	19.25	19.31	19.28	0.04	0.03	0.03	0.03	0.03
24000	18.35	18.39	18.53	18.65	18.67	0.03	0.03	0.03	0.03	0.04
25000	17.70	17.77	18.04	18.19	18.25	0.04	0.04	0.03	0.03	0.04
26000	17.09	17.21	17.59	17.86	17.96	0.04	0.05	0.04	0.04	0.04
27000	16.74	16.81	17.32	17.70	17.81	0.06	0.05	0.05	0.03	0.05
28000	16.63	16.76	17.23	17.59	17.72	0.04	0.04	0.05	0.04	0.05
29000	16.85	17.03	17.42	17.82	17.97	0.05	0.05	0.05	0.05	0.05
30000	17.29	17.46	18.02	18.34	18.39	0.05	0.04	0.04	0.04	0.04
31000	18.07	18.25	18.85	19.05	19.11	0.04	0.04	0.02	0.04	0.03
32000	19.14	19.32	19.60	19.92	20.02	0.03	0.03	0.03	0.04	0.04
33000	20.21	20.26	20.41	20.99	21.12	0.03	0.03	0.02	0.03	0.03
34000	21.16	21.26	21.30	21.62	21.89	-0.02	-0.01	0.00	0.01	0.00
35000	20.82	20.93	21.10	21.52	21.69	0.03	0.04	0.04	0.01	0.02
36000	20.85	20.81	20.94	21.13	21.00	0.00	0.01	0.03	0.00	0.03
37000	19.12	19.10	19.17	19.28	19.22	0.02	0.03	0.00	0.02	0.02
38000	17.01	17.03	16.89	16.73	16.69	0.02	0.03	0.02	0.04	0.05
39000	13.16	13.18	13.37	13.29	13.25	0.08	0.08	0.09	0.09	0.10
40000	10.44	10.55	11.03	11.43	11.63	0.10	0.15	0.10	0.10	0.12


Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine

Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



Typical Performance Data


FREQ. (MHz)	INPUT RETURN LOSS (dB)					OUTPUT RETURN LOSS (dB)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
	32.04	32.18	34.66	34.28	34.44	37.29	38.03	39.87	40.40	43.91
50	36.77	37.38	39.50	43.25	44.30	36.43	36.67	39.70	42.32	43.60
100	34.97	35.32	37.93	39.48	40.50	35.79	36.45	39.47	41.71	42.09
200	34.56	34.46	34.57	34.90	34.88	34.54	34.58	34.15	34.70	34.57
300	31.46	31.55	30.73	30.64	30.78	31.89	31.91	31.04	31.13	31.14
400	28.97	28.95	28.42	28.63	28.74	28.58	28.62	28.14	28.35	28.27
500	27.43	27.25	26.31	26.55	26.57	27.41	27.19	26.42	26.55	26.59
600	26.11	25.91	24.77	24.82	24.88	26.10	25.90	24.78	24.80	24.87
700	24.88	24.65	23.71	23.64	23.68	24.65	24.44	23.54	23.43	23.47
800	23.49	23.30	22.55	22.51	22.51	23.45	23.29	22.57	22.49	22.52
900	22.53	22.46	21.91	21.81	21.84	22.44	22.37	21.86	21.78	21.78
1000	21.53	21.45	21.12	20.94	20.95	21.47	21.39	21.09	20.92	20.92
1200	20.30	20.28	20.04	19.87	19.83	20.21	20.21	19.93	19.79	19.75
1400	19.60	19.58	19.25	19.06	19.04	19.59	19.56	19.28	19.09	19.08
1600	18.70	18.73	18.81	18.64	18.62	18.75	18.76	18.83	18.66	18.62
1800	18.23	18.29	18.55	18.42	18.37	18.21	18.26	18.55	18.42	18.41
2000	18.28	18.32	18.49	18.46	18.45	18.24	18.28	18.47	18.50	18.47
2500	18.76	18.80	19.09	19.22	19.26	18.75	18.79	19.06	19.27	19.30
3000	20.34	20.29	20.01	20.12	20.16	20.34	20.30	19.97	20.14	20.19
3500	20.76	20.76	20.96	20.85	20.87	20.81	20.86	20.96	20.85	20.82
4000	20.90	20.89	20.96	20.63	20.65	21.00	20.96	21.02	20.67	20.69
4500	20.21	20.17	20.23	19.51	19.44	20.24	20.21	20.26	19.57	19.50
5000	19.21	19.25	19.65	19.14	19.09	19.41	19.44	19.83	19.28	19.20
5500	19.19	19.26	19.73	19.81	19.75	19.33	19.43	19.82	19.89	19.87
6000	19.76	19.86	20.25	20.73	20.84	19.79	19.90	20.28	20.80	20.95
6500	21.08	21.16	21.47	22.13	22.34	21.09	21.20	21.53	22.19	22.42
7000	22.35	22.49	23.21	23.71	23.45	22.35	22.49	23.18	23.78	23.65
7300	23.40	23.48	23.77	24.05	23.68	23.31	23.37	23.77	24.13	23.91
7500	23.79	23.83	23.64	23.56	23.18	23.83	23.95	23.98	23.89	23.57
7800	22.96	22.96	22.80	22.20	21.70	23.13	23.20	23.14	22.44	21.98
8000	22.30	22.31	21.89	21.13	20.67	22.47	22.50	22.37	21.51	21.02
8200	20.86	20.88	20.71	19.91	19.47	21.10	21.17	21.34	20.46	20.04
8400	19.92	19.97	19.63	18.94	18.59	20.03	20.12	20.25	19.56	19.15
8600	18.26	18.37	18.34	17.92	17.63	18.55	18.67	19.06	18.60	18.25
8800	17.12	17.23	17.26	17.09	16.92	17.54	17.64	18.05	17.90	17.65
9000	16.20	16.28	16.21	16.26	16.22	16.79	16.88	17.07	17.16	17.08
9200	15.50	15.53	15.35	15.56	15.62	16.13	16.20	16.23	16.50	16.55
9400	14.90	14.92	14.69	14.96	15.08	15.67	15.69	15.59	15.90	16.03
9600	14.53	14.54	14.20	14.46	14.56	15.37	15.37	15.13	15.44	15.57
9800	14.12	14.11	13.79	14.01	14.13	15.14	15.13	14.82	15.10	15.27
10000	13.82	13.81	13.55	13.73	13.88	14.95	14.93	14.69	14.90	15.04
10200	13.61	13.60	13.39	13.53	13.65	14.94	14.92	14.68	14.86	15.03
10400	13.51	13.51	13.39	13.48	13.59	14.98	14.98	14.81	14.98	15.12
10600	13.39	13.39	13.43	13.42	13.48	15.12	15.08	14.98	15.09	15.19
10800	13.45	13.46	13.57	13.51	13.52	15.27	15.28	15.17	15.21	15.25
11000	13.33	13.37	13.65	13.56	13.53	15.37	15.36	15.35	15.30	15.28
12000	12.58	12.69	13.18	13.16	13.18	14.27	14.29	14.43	14.14	13.99
13000	11.58	11.71	12.60	12.89	13.06	12.23	12.36	13.09	13.24	13.22
14000	11.78	11.98	13.02	14.00	14.48	12.63	12.81	13.32	14.13	14.56
14300	12.05	12.24	13.30	14.27	14.69	12.93	13.09	13.58	14.58	15.06
15000	12.81	12.96	13.80	14.38	14.52	13.04	13.21	13.91	14.68	14.93
16000	12.94	13.05	13.19	13.37	13.30	12.25	12.41	13.41	13.54	13.47
17000	10.64	10.71	10.51	10.65	10.64	10.76	10.85	11.10	11.31	11.38
18000	8.03	8.09	7.98	8.12	8.16	8.80	8.82	8.70	8.90	8.98
19000	5.98	6.06	6.26	6.39	6.44	6.78	6.85	7.01	7.11	7.11
20000	4.96	5.05	5.39	5.65	5.74	5.64	5.74	6.14	6.29	6.27
21000	4.54	4.64	5.03	5.39	5.57	5.47	5.56	5.93	6.24	6.34
22000	4.76	4.87	5.43	5.82	6.04	5.99	6.07	6.25	6.80	7.05
23000	5.21	5.34	6.02	6.47	6.74	6.45	6.56	6.90	7.48	7.74
24000	5.95	6.08	6.89	7.48	7.79	6.82	6.97	7.67	8.12	8.28
25000	6.94	7.09	7.93	8.47	8.71	7.55	7.69	8.39	8.78	8.92
26000	8.64	8.73	9.32	9.56	9.58	8.94	9.01	9.28	9.65	9.81
27000	11.24	11.28	10.96	10.86	10.70	10.52	10.58	10.40	10.57	10.62
28000	13.24	13.20	11.94	11.88	11.71	10.51	10.64	11.23	10.93	10.66
29000	10.67	10.69	10.16	10.00	9.87	9.27	9.35	9.96	9.74	9.61
30000	7.51	7.54	7.53	7.58	7.61	8.29	8.28	7.97	8.42	8.69
31000	5.17	5.26	5.35	5.72	5.95	6.15	6.18	6.02	6.53	6.75
32000	3.46	3.56	3.96	4.39	4.62	4.34	4.43	4.79	5.04	5.07
33000	2.21	2.34	2.90	3.13	3.23	2.98	3.09	3.59	3.66	3.63
34000	1.58	1.68	2.22	2.38	2.45	2.56	2.65	3.02	3.17	3.23
35000	1.26	1.36	1.88	2.03	2.11	2.55	2.59	2.68	2.89	3.01
36000	1.26	1.36	1.83	2.17	2.37	2.50	2.59	2.67	3.06	3.25
37000	1.54	1.68	2.32	2.88	3.11	2.35	2.50	3.13	3.40	3.44
38000	2.35	2.55	3.63	4.15	4.34	3.04	3.23	4.26	4.62	4.73
39000	4.39	4.60	5.74	6.52	6.81	5.33	5.55	6.54	7.67	8.36
40000	7.88	8.11	7.79	8.33	8.37	7.29	7.53	8.39	8.67	8.51


Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED


MMIC Reflectionless Low Pass Filter

XLF-732+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

minicircuits.com


IF/RF MICROWAVE COMPONENTS

Case Style


DQ

DQ1225

Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN $\pm .002$

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

1. Case material: Plastic.
2. Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix.
See Data sheet.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F66

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M152656	NEW RELEASE	09/11/15	ITG	MY

SUGGESTED MOUNTING CONFIGURATION
FOR DQ1225 CASE STYLE, "12FL02" PIN CODE

NOTES:

1. TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.0066\pm.0007$ ". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS \pm 3 PL DECIMALS $\pm .005$ ANGLES \pm FRACTIONS \pm

INITIALS

DATE

DRAWN

ITG

09/10/15

CHECKED

GF

09/11/15

APPROVED

MY

09/11/15



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 12FL02, DQ1225, TB-844+


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-451	OR
FILE:	98PL451	SCALE: 16:1	SHEET: 1 OF 1

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEET1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit

To be used with Mini-Circuits 50 Ohm 2.92 connectors B20-118-F1+.
Connectors are sold separately.



TB-844-732+




Schematic Diagram

Note:


PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**

Evaluation Board and Circuit



TB-844-732C+



Schematic Diagram

Notes:

1. 50 Ohm 2.92 mm Female connectors.
2. PCB Material: RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020C
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215