


**MMIC**

# **REFLECTIONLESS FILTER DICE**

**50Ω DC to 21 GHz**



## **X-Series**

*Available in Low Pass, High Pass and Band Pass designs*

### **The Big Deal**

- Patented design eliminates in band spurs
- Pass band cut-off up to 21 GHz
- Stop band up to 35 GHz
- Excellent repeatability through IPD\* process
- Unpackaged Die Form

### **Product Overview**

Mini-Circuits' X-Series reflectionless filters employ a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level which interact with neighboring components and often result in intermodulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolators, isolation amplifiers or attenuators.

<b>Key Features</b>	<b>Advantages</b>
Easy integration with sensitive reflective components, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
Enables stable integration of wideband amplifiers	Because reflectionless filters maintain good impedance in the stop band; they can be integrated with high gain, wideband amplifiers without the risk of creating instabilities in these out of band regions.
Cascadable	Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect pass band signals.
Excellent power handling in a tiny surface mount device	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.
Excellent repeatability of RF performance	Through semiconductor IPD process, X-series filters are inherently repeatable for large volume production.
Excellent stability over temperature	With ±0.3 dB variation over temperature ideal for use in wide temperature range applications without the need for additional temperature compensation.
Operating Temperature up to 105°C	Suitable for operation close to high power components
Unpackaged Die form	Enables direct integration into customer hybrids

\*IPD – Integrated Passive Device, is a GaAs semiconductor process



# Reflectionless Low Pass Filter Die

XLF-982-D+

50Ω DC to 9800 MHz

## Features

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Protected by US Patent No. 8,392,495



## Applications

- Harmonics Rejection
- Wideband Matching
- Transmitters / Receivers

### +RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

*Ordering Information: Refer to Last Page*

## General Description

Mini-Circuits' XLF-982-D+ reflectionless filter die employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

## Simplified Schematic



Pad	Description
RF-IN	RF Input Pad
RF-OUT	RF Output Pad
Ground	Ground Bonding Pad

 Mini-Circuits®


[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR  
M152659  
XLF-982-D+  
RS/CP  
180124  
Page 2 of 6

**Electrical Specifications<sup>1</sup> at 25°C**

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC - F1	DC - 9800	1.4		dB
	Frequency Cut-off	F2	13100	3.0		dB
	VSWR	DC - F1	DC - 9800	1.2		:1
Stop Band	Rejection	F3 - F4	19000 - 22000	15		dB
		F4 - F5	22000 - 32500	20		dB
	VSWR	F3 - F4	19000 - 22000	3.4		:1
		F4 - F5	22000 - 32500	3.0		:1

<sup>1</sup> Measured on Mini-Circuits Characterization test board. Die packaged in 3mm x 3mm, 12-lead MCLP package and soldered on TB-844-982+

**Specification Definition****Absolute Maximum Ratings<sup>1,4</sup>**

Parameter	Ratings
Operating Temperature	-55°C to +105°C
RF Power Input, Passband (DC-F1) <sup>2</sup>	2W at 25°C
RF Power Input, Stopband (F2-F5) <sup>3</sup>	0.2W at 25°C


<sup>2</sup> Passband rating derates linearly to 1W at 105°C ambient

<sup>3</sup> Stopband rating derates linearly to 0.1mW at 105°C ambient

<sup>4</sup> Permanent damage may occur if any of these limits are exceeded.

**Typical Performance Data at 25°C<sup>1</sup>**

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.41	1.02
100	0.38	1.03
400	0.40	1.09
800	0.44	1.18
1600	0.52	1.29
3000	0.55	1.19
4500	0.58	1.05
6000	0.68	1.03
7500	0.83	1.08
9800	1.36	1.47
11500	2.15	1.69
13100	2.98	1.28
15000	4.98	1.16
17000	8.87	1.69
19000	15.45	2.95
22000	26.04	3.73
25000	25.03	2.77
27500	21.72	2.38
30000	21.40	3.28
32500	22.37	5.02



**Die Layout**

Fig 1. Die Layout


**Bonding Pad Position**  
(Dimensions in  $\mu\text{m}$ , Typical)

Fig 2. Bonding Pad Positions

**Critical Dimensions**

Parameter	Values
Die Thickness, $\mu\text{m}$	100
Die Width, $\mu\text{m}$	1000
Die Length, $\mu\text{m}$	550
Bond Pad Size (Ground pad), $\mu\text{m}$	75 x 75

## Assembly and Handling Procedure

### 1. Storage

Dice should be stored in a dry nitrogen purged desiccators or equivalent.

### 2. ESD

MMIC Gallium Arsenide (GaAs) filter dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.


### 3. Die Attach

The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030Hk-PT/H579/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.

### 4. Wire Bonding

Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as reasonable to minimize performance degradation due to undesirable series inductance.

## Assembly Diagram



## Recommended Wire Length, Typical

Wire	Wire Length (mm)	Wire Loop Height (mm)
All wires	1.0	0.15

Note: Use double bond wire at RF IN & RF OUT

## **Additional Detailed Technical Information**

*additional information is available on our dash board.*

\*Known Good Dice ("KGD") means that the dice are taken from PCM good wafer and visually inspected according to Mini-Circuits inspection criteria. While this is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

## **ESD Rating\*\***

Human Body Model (HBM): Class 1A (250V to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

\*\* Tested in industry standard MCLP 3x3mm 12 lead package.

## **Additional Notes**

- EXCLUSIONS**

  - A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
  - D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
  - E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
  - F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



## Typical Performance Data

FREQ.	INSERTION LOSS					GROUP DELAY				
	(dB)					(nsec)				
(MHz)	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
10	0.38	0.38	0.42	0.42	0.42	0.10	0.09	0.09	0.08	0.07
50	0.33	0.35	0.37	0.39	0.40	0.07	0.07	0.07	0.07	0.06
100	0.33	0.35	0.38	0.40	0.42	0.05	0.05	0.05	0.05	0.06
200	0.33	0.35	0.38	0.41	0.42	0.05	0.04	0.04	0.05	0.05
300	0.34	0.35	0.40	0.43	0.44	0.04	0.04	0.04	0.05	0.05
400	0.34	0.35	0.40	0.44	0.45	0.04	0.04	0.04	0.05	0.05
500	0.34	0.35	0.41	0.45	0.46	0.04	0.04	0.04	0.05	0.05
600	0.34	0.36	0.42	0.46	0.47	0.04	0.04	0.04	0.05	0.05
700	0.34	0.35	0.42	0.46	0.48	0.04	0.04	0.04	0.04	0.05
800	0.35	0.36	0.43	0.47	0.49	0.04	0.04	0.04	0.04	0.05
900	0.35	0.37	0.43	0.48	0.49	0.04	0.04	0.04	0.05	0.05
1000	0.36	0.38	0.45	0.49	0.51	0.04	0.04	0.04	0.04	0.04
1200	0.37	0.39	0.46	0.51	0.53	0.04	0.04	0.04	0.04	0.04
1400	0.37	0.40	0.48	0.53	0.55	0.04	0.04	0.04	0.04	0.04
1600	0.39	0.42	0.50	0.55	0.57	0.04	0.04	0.04	0.04	0.04
1800	0.41	0.43	0.51	0.56	0.59	0.04	0.04	0.04	0.04	0.04
2000	0.41	0.44	0.52	0.57	0.59	0.04	0.04	0.04	0.04	0.04
2500	0.41	0.44	0.53	0.59	0.61	0.04	0.04	0.04	0.04	0.04
3000	0.42	0.45	0.55	0.61	0.63	0.04	0.04	0.04	0.04	0.04
3500	0.43	0.46	0.57	0.63	0.66	0.04	0.04	0.04	0.04	0.04
4000	0.44	0.48	0.59	0.67	0.71	0.04	0.04	0.04	0.04	0.05
4500	0.46	0.50	0.62	0.72	0.76	0.04	0.04	0.04	0.04	0.04
5000	0.49	0.53	0.67	0.77	0.81	0.04	0.04	0.04	0.04	0.04
5500	0.50	0.55	0.69	0.79	0.84	0.04	0.04	0.04	0.04	0.04
6000	0.51	0.56	0.72	0.82	0.87	0.04	0.04	0.04	0.04	0.05
6500	0.53	0.57	0.74	0.86	0.91	0.05	0.05	0.04	0.04	0.05
7000	0.54	0.59	0.77	0.90	0.95	0.05	0.05	0.04	0.05	0.05
7500	0.58	0.63	0.82	0.96	1.01	0.05	0.05	0.04	0.05	0.05
8000	0.62	0.68	0.88	1.02	1.08	0.05	0.05	0.04	0.05	0.05
9000	0.78	0.84	1.06	1.22	1.29	0.05	0.05	0.05	0.05	0.05
9800	1.00	1.07	1.33	1.51	1.58	0.05	0.05	0.05	0.05	0.05
10000	1.07	1.15	1.42	1.60	1.67	0.05	0.05	0.05	0.05	0.05
10200	1.15	1.22	1.50	1.69	1.76	0.05	0.05	0.05	0.05	0.05
10400	1.23	1.30	1.60	1.79	1.86	0.05	0.05	0.05	0.05	0.05
10600	1.31	1.39	1.69	1.89	1.97	0.05	0.05	0.05	0.05	0.05
10800	1.40	1.48	1.78	1.99	2.07	0.05	0.05	0.05	0.05	0.05
11000	1.48	1.57	1.87	2.09	2.17	0.05	0.05	0.05	0.05	0.05
11200	1.57	1.66	1.96	2.19	2.27	0.05	0.05	0.05	0.05	0.05
11400	1.67	1.75	2.05	2.28	2.37	0.05	0.05	0.05	0.05	0.05
11600	1.75	1.84	2.14	2.37	2.46	0.05	0.05	0.05	0.05	0.05
11800	1.84	1.92	2.22	2.47	2.55	0.05	0.05	0.05	0.05	0.06
12000	1.94	2.02	2.32	2.57	2.66	0.05	0.05	0.05	0.05	0.05
12200	2.04	2.13	2.42	2.67	2.76	0.05	0.05	0.05	0.05	0.06
12400	2.15	2.24	2.54	2.79	2.88	0.05	0.05	0.05	0.05	0.06
12600	2.27	2.35	2.65	2.91	3.00	0.05	0.05	0.05	0.06	0.06
12800	2.38	2.46	2.78	3.04	3.13	0.06	0.06	0.05	0.06	0.06
13000	2.50	2.59	2.92	3.18	3.27	0.06	0.06	0.05	0.06	0.06
13100	2.57	2.66	2.99	3.26	3.35	0.06	0.06	0.05	0.06	0.06
13500	2.87	2.96	3.33	3.60	3.69	0.06	0.06	0.06	0.06	0.06
14000	3.32	3.43	3.82	4.10	4.20	0.06	0.06	0.05	0.06	0.06
15000	4.47	4.59	5.03	5.35	5.47	0.06	0.06	0.06	0.06	0.06
16000	5.98	6.11	6.58	6.97	7.11	0.06	0.06	0.06	0.06	0.06
17000	7.96	8.09	8.64	9.07	9.23	0.06	0.06	0.06	0.06	0.06
18000	10.61	10.76	11.43	11.92	12.07	0.05	0.05	0.05	0.05	0.05
19000	14.09	14.26	14.94	15.47	15.64	0.04	0.04	0.03	0.03	0.03
20000	18.00	18.15	18.73	19.24	19.43	0.01	0.01	0.01	0.01	0.01
21000	21.78	21.91	22.54	22.93	23.01	0.00	-0.01	-0.01	-0.02	-0.01
22000	25.13	25.22	25.51	25.63	25.63	-0.03	-0.04	-0.04	-0.03	-0.02
23000	26.93	26.93	26.73	26.67	26.67	-0.04	-0.04	-0.03	-0.04	-0.03
24000	26.62	26.58	26.38	26.07	25.98	-0.04	-0.02	-0.02	-0.02	-0.02
25000	24.98	24.94	24.88	24.67	24.63	-0.01	0.00	0.00	0.00	0.01
26000	23.09	23.13	23.28	23.29	23.26	0.02	0.02	0.01	0.02	0.02
27000	21.54	21.64	21.89	22.11	22.16	0.03	0.03	0.03	0.04	0.04
28000	20.64	20.71	20.98	21.23	21.29	0.04	0.03	0.05	0.04	0.04
29000	20.21	20.33	20.73	20.91	20.96	0.04	0.04	0.04	0.04	0.05
30000	20.27	20.36	20.99	21.15	21.04	0.04	0.04	0.02	0.04	0.05
31000	20.60	20.74	21.38	21.48	21.43	0.05	0.04	0.04	0.03	0.05
32000	21.24	21.42	21.84	22.02	22.15	0.03	0.02	0.02	0.03	0.03
32500	21.66	21.73	22.10	22.43	22.51	0.03	0.02	0.03	0.03	0.02
33000	21.85	21.96	22.35	22.69	22.78	0.02	0.03	0.01	0.02	0.03
34000	21.95	22.08	22.47	22.79	22.80	0.02	0.02	0.01	0.03	0.01
35000	21.52	21.71	22.32	22.48	22.47	0.01	0.01	0.01	0.02	0.03
36000	21.03	21.13	21.91	21.83	21.71	0.05	0.05	0.02	0.04	0.06
37000	20.89	21.08	21.39	21.40	21.42	0.04	0.01	0.03	0.03	0.03
38000	19.69	19.76	20.01	20.00	20.01	0.04	0.04	0.03	0.06	0.05
39000	17.44	17.66	18.05	18.11	18.16	0.07	0.07	0.05	0.06	0.07
40000	16.63	16.87	17.32	17.63	17.76	0.09	0.06	0.05	0.07	0.01


**Mini-Circuits®**  
 ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs &amp; shopping online see Mini-Circuits web site


 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)


IF/RF MICROWAVE COMPONENTS

## Typical Performance Data

FREQ.	INPUT RETURN LOSS					OUTPUT RETURN LOSS				
	(dB)					(dB)				
(MHz)	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
10	36.59	36.89	38.76	40.54	40.30	35.61	35.50	36.94	38.63	39.25
50	35.88	36.50	39.01	41.44	41.97	35.36	35.93	37.97	40.03	41.19
100	34.60	35.19	37.24	38.68	39.52	35.41	35.86	38.33	40.50	41.38
200	34.72	34.79	35.06	35.57	35.64	34.98	34.87	34.86	35.42	35.56
300	32.69	32.67	32.08	32.21	32.24	32.68	32.65	31.83	32.02	32.24
400	29.76	29.70	29.39	29.52	29.68	29.65	29.49	29.22	29.51	29.63
500	28.77	28.53	27.72	28.02	28.09	28.62	28.40	27.55	27.85	27.89
600	27.27	27.08	25.99	26.15	26.21	27.42	27.25	26.09	26.18	26.29
700	25.89	25.66	24.78	24.75	24.84	25.77	25.54	24.63	24.63	24.72
800	24.79	24.63	23.91	23.79	23.89	24.77	24.61	23.84	23.75	23.83
900	23.72	23.63	23.12	23.02	23.02	23.79	23.70	23.19	23.08	23.09
1000	22.72	22.60	22.28	22.15	22.16	22.68	22.56	22.23	22.13	22.13
1200	21.47	21.44	21.22	21.04	21.05	21.46	21.45	21.18	20.99	20.99
1400	20.81	20.80	20.47	20.26	20.25	20.80	20.78	20.47	20.29	20.29
1600	19.82	19.85	19.97	19.76	19.73	19.88	19.92	19.95	19.74	19.73
1800	19.41	19.48	19.75	19.61	19.58	19.44	19.51	19.79	19.64	19.60
2000	19.46	19.52	19.72	19.65	19.62	19.44	19.50	19.66	19.61	19.60
2500	20.12	20.15	20.40	20.63	20.69	20.11	20.15	20.37	20.59	20.63
3000	21.95	21.87	21.41	21.62	21.63	21.85	21.78	21.32	21.52	21.51
3500	22.11	22.11	21.92	21.77	21.69	21.70	21.73	21.55	21.40	21.32
4000	22.09	22.06	21.77	21.41	21.33	21.87	21.81	21.57	21.25	21.15
4500	21.45	21.36	21.00	20.13	19.97	21.03	20.98	20.76	19.97	19.83
5000	20.03	20.04	20.00	19.29	19.18	19.88	19.90	19.92	19.24	19.16
5500	19.74	19.81	20.03	19.92	19.85	19.62	19.68	19.98	19.91	19.86
6000	20.75	20.84	21.13	21.52	21.63	20.68	20.78	21.18	21.69	21.86
6500	22.63	22.75	23.17	23.89	24.22	22.60	22.72	23.30	24.27	24.66
7000	25.83	26.08	27.49	27.74	27.64	25.46	25.70	27.40	28.10	28.13
7500	30.80	30.85	31.94	31.08	30.39	30.24	30.49	32.38	32.07	31.57
8000	32.16	32.14	32.96	30.51	29.16	31.74	31.93	33.18	30.58	29.15
9000	20.59	20.74	21.34	20.85	20.46	20.70	20.84	21.29	20.77	20.32
9800	15.87	15.86	15.50	15.72	15.77	16.04	16.00	15.48	15.61	15.66
10000	14.97	14.95	14.56	14.73	14.81	15.11	15.08	14.56	14.64	14.71
10200	14.29	14.28	13.84	13.95	14.04	14.49	14.43	13.87	13.93	14.03
10400	13.65	13.61	13.22	13.34	13.44	13.87	13.81	13.29	13.38	13.48
10600	13.15	13.11	12.86	12.87	12.95	13.36	13.31	12.91	12.93	13.00
10800	12.80	12.76	12.58	12.54	12.58	12.98	12.94	12.59	12.57	12.60
11000	12.45	12.44	12.48	12.37	12.38	12.60	12.58	12.44	12.36	12.38
11200	12.29	12.30	12.38	12.29	12.29	12.49	12.49	12.44	12.36	12.37
11400	12.16	12.18	12.48	12.41	12.44	12.32	12.35	12.54	12.50	12.53
11600	12.22	12.26	12.65	12.68	12.72	12.48	12.53	12.80	12.78	12.80
11800	12.34	12.41	12.95	12.98	13.06	12.60	12.68	13.16	13.19	13.23
12000	12.46	12.59	13.25	13.33	13.42	12.81	12.93	13.59	13.64	13.69
12200	12.77	12.95	13.77	13.94	14.12	13.00	13.18	14.07	14.20	14.28
12400	13.07	13.25	14.12	14.46	14.71	13.35	13.55	14.67	14.89	15.00
12600	13.51	13.71	14.68	15.12	15.44	13.75	13.97	15.18	15.61	15.75
12800	14.25	14.41	15.13	15.72	16.10	14.45	14.66	15.85	16.52	16.72
13000	14.93	15.10	15.84	16.32	16.69	15.13	15.30	16.43	17.36	17.62
13100	15.17	15.31	15.97	16.48	16.86	15.57	15.76	16.77	17.81	18.12
13500	16.28	16.40	16.64	17.29	17.76	16.90	17.03	17.70	18.65	18.91
14000	16.67	16.78	16.98	17.67	18.07	18.19	18.27	18.46	19.23	19.62
15000	17.01	17.08	17.54	18.18	18.58	17.84	17.92	18.07	19.16	19.57
16000	17.36	17.54	18.59	19.08	18.96	17.02	17.20	18.44	18.26	17.99
17000	14.97	15.09	15.33	15.31	15.16	14.70	14.79	15.07	14.97	14.94
18000	10.53	10.55	10.51	10.42	10.38	10.83	10.84	10.51	10.65	10.74
19000	7.15	7.21	7.43	7.43	7.45	7.28	7.33	7.36	7.44	7.48
20000	5.44	5.53	5.84	6.08	6.15	5.29	5.38	5.74	5.87	5.90
21000	4.65	4.75	5.18	5.57	5.70	4.72	4.81	5.13	5.44	5.55
22000	4.80	4.89	5.32	5.79	6.00	4.93	5.02	5.21	5.69	5.92
23000	5.05	5.17	5.66	6.19	6.46	5.19	5.28	5.60	6.08	6.28
24000	5.41	5.54	6.08	6.70	7.01	5.31	5.45	6.10	6.47	6.57
25000	5.88	6.01	6.52	7.09	7.34	5.78	5.91	6.58	6.94	7.07
26000	6.77	6.88	7.38	7.62	7.71	7.01	7.11	7.50	7.88	8.06
27000	8.14	8.26	8.68	8.56	8.48	8.50	8.59	8.79	9.04	9.11
28000	9.32	9.46	9.82	9.91	9.73	8.74	8.90	9.61	9.46	9.31
29000	8.14	8.30	9.02	9.05	8.72	7.94	8.02	8.44	8.49	8.54
30000	6.52	6.61	7.24	7.51	7.35	6.75	6.77	6.59	7.07	7.36
31000	5.05	5.16	5.58	6.17	6.21	4.84	4.91	4.98	5.43	5.61
32000	3.77	3.89	4.45	5.01	5.07	3.41	3.53	3.98	4.20	4.23
32500	3.19	3.33	4.01	4.39	4.39	2.99	3.11	3.66	3.78	3.76
33000	2.92	3.04	3.69	3.94	3.94	2.77	2.87	3.35	3.47	3.51
34000	2.55	2.65	3.28	3.39	3.37	2.86	2.92	3.18	3.40	3.50
35000	2.47	2.54	3.07	3.14	3.18	3.03	3.07	3.15	3.49	3.68
36000	2.70	2.79	3.17	3.50	3.71	3.19	3.29	3.38	3.89	4.13
37000	3.11	3.24	3.82	4.42	4.74	3.35	3.50	4.19	4.57	4.63
38000	4.39	4.57	5.54	6.27	6.52	4.77	4.97	6.11	6.57	6.63
39000	7.12	7.33	8.36	9.14	9.49	7.68	7.86	8.66	9.59	10.18
40000	10.31	10.53	9.49	8.95	8.58	8.44	8.54	8.97	8.81	8.53


**Mini-Circuits®**

ISO 9001 ISO 14001 AS 9100 CERTIFIED









P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs &amp; shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



## Typical Performance Curves



**Environmental Specifications****ENV80**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	