

# Coaxial Bandpass Filter

## ZABP-59-S+

50Ω 30 to 88 MHz



Generic photo used for illustration purposes only  
CASE STYLE: UU1842

### The Big Deal

- Broader bandwidth
- High rejection
- Wide stopband
- Connectorized package

### Product Overview

ZABP-59-S+ is a 50Ω bandpass filter with a rugged connectorized package covering the passband of 30 to 88 MHz. The bandpass filter offers good matching within the passband and provides high rejection. This filter has miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across lots and consistent performance across temperature.

### Key Features

Feature	Advantages
High rejection	ZABP-59-S+ has sharper transition and rejects spurious signals in the stopband.
Good VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Bandpass Filter

# ZABP-59-S+

50Ω 30 to 88 MHz



Generic photo used for illustration purposes only

CASE STYLE: UU1842

Connectors Model  
SMA-MF ZABP-59-S+


## Features

- Broader bandwidth
- Low insertion loss
- High rejection
- Wide stopband
- Connectorized package


## Applications

- Telecommunication and broadband networks
- Air traffic control communication
- Private and Public land mobile
- Transmitters/ Receivers
- Test equipment

## Functional Schematic



## Typical Frequency Response



## Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	59	-	MHz
	Insertion Loss	F1-F2	30-88	1.0	2.5	dB
	VSWR	F1-F2	30-88	1.3	1.9	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 16	50	57	dB
	VSWR	DC-F4	DC - 22	20	30	:1
Stop Band, Upper	Insertion Loss	F5-F6	115-140	20	25	dB
		F6-F7	140-600	40	48	dB
	F7-F8	600-1100	30	38	dB	
	F8-F9	1100-3000	-	45	dB	
	VSWR	F9-F10	3000-4000	-	30	dB
		F5-F10	115-4000	-	10	:1

## Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.25 W max.





Permanent damage may occur if any of these limits are exceeded.

## Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1.0	74.08	13931.97	30	60.69
16.0	61.92	286.71	32	44.85
22.0	33.18	80.92	34	33.88
22.2	31.56	77.12	36	31.31
23.8	19.77	42.69	38	28.74
26.6	3.41	3.78	40	26.20
30.0	0.67	1.22	45	20.68
59.0	0.51	1.20	50	17.65
88.0	1.00	1.07	55	15.90
91.0	1.17	1.02	58	15.23
93.0	1.36	1.15	59	15.06
99.0	3.45	2.50	60	14.90
112.0	20.20	13.96	65	14.44
115.0	24.88	16.03	68	14.38
119.0	31.55	18.07	70	14.43
140.0	54.19	23.48	74	14.73
600.0	66.08	33.82	78	15.32
1100.0	70.56	18.91	80	15.75
3000.0	59.68	4.00	85	17.45
4000.0	44.88	7.40	88	19.15

## +RoHS Compliant

The + suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



## Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Coaxial Connections

PORT - 1	SMA-MALE
PORT - 2	SMA-FEMALE

## Outline Drawing



## Outline Dimensions ( $\frac{\text{inch}}{\text{mm}}$ )

A	B	C	D	E
2.300	2.250	.750	2.175	2.125
58.42	57.15	19.05	55.25	53.98
F	G	H	J	wt.
.125	.125	.312	1.125	grams
3.18	3.18	7.93	28.58	124

Note: Please refer to case style drawing for details

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



*Typical Performance Data*


FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1.0	74.12	74.08	74.65	0.00	0.00	0.00	0.01	0.00	0.01
5.0	64.78	64.86	64.85	0.00	0.00	0.00	0.03	0.03	0.03
7.0	69.18	69.02	68.92	0.01	0.01	0.01	0.05	0.06	0.07
9.0	75.57	75.20	74.88	0.01	0.01	0.01	0.09	0.11	0.12
11.0	61.75	61.78	61.77	0.02	0.02	0.02	0.15	0.17	0.19
15.0	58.77	58.78	58.78	0.04	0.05	0.05	0.28	0.33	0.35
16.0	62.03	61.92	62.05	0.06	0.06	0.07	0.32	0.37	0.40
18.0	78.58	76.80	76.87	0.08	0.09	0.09	0.41	0.47	0.50
20.0	54.23	54.07	53.91	0.12	0.13	0.14	0.50	0.56	0.61
22.0	33.29	33.18	33.12	0.20	0.21	0.23	0.61	0.68	0.72
22.4	30.08	29.99	29.93	0.22	0.24	0.26	0.64	0.70	0.75
23.0	25.55	25.46	25.42	0.27	0.29	0.31	0.69	0.76	0.81
23.6	21.25	21.17	21.13	0.34	0.37	0.39	0.77	0.83	0.89
23.8	19.86	19.77	19.74	0.38	0.41	0.43	0.80	0.87	0.92
25.0	11.84	11.76	11.74	0.86	0.91	0.96	1.27	1.35	1.42
26.0	6.01	5.96	5.96	2.36	2.47	2.55	2.76	2.89	2.99
26.6	3.43	3.41	3.43	4.54	4.70	4.83	4.95	5.12	5.27
28.0	0.98	1.01	1.06	15.52	15.83	16.07	16.70	17.13	17.50
29.0	0.70	0.75	0.80	21.89	21.56	21.46	26.89	26.83	27.12
30.0	0.63	0.67	0.71	20.26	20.00	19.89	22.06	21.92	21.94
35.0	0.43	0.47	0.50	29.68	30.01	29.95	30.58	30.88	30.90
40.0	0.43	0.46	0.49	20.99	20.82	20.67	21.34	21.13	20.98
45.0	0.41	0.45	0.48	22.39	21.99	21.71	21.64	21.17	20.87
50.0	0.41	0.45	0.49	24.81	24.07	23.62	22.95	22.21	21.74
55.0	0.44	0.48	0.51	22.94	22.52	22.24	22.18	21.62	21.22
59.0	0.46	0.51	0.54	21.12	20.94	20.79	21.15	20.81	20.54
65.0	0.51	0.55	0.59	20.49	20.48	20.43	20.97	20.83	20.71
70.0	0.54	0.59	0.63	22.26	22.35	22.34	22.88	22.87	22.83
75.0	0.59	0.64	0.68	27.77	28.09	28.03	28.50	28.72	28.78
80.0	0.67	0.73	0.78	41.23	43.59	40.22	41.07	44.22	42.29
85.0	0.81	0.88	0.93	28.26	28.35	28.34	28.81	28.96	28.96
88.0	0.92	1.00	1.05	29.31	29.58	29.76	29.17	29.47	29.75
90.0	1.02	1.10	1.16	37.65	38.51	38.59	30.09	30.20	30.46
98.0	2.66	2.84	2.98	9.14	9.00	8.90	8.46	8.30	8.18
100.0	3.98	4.21	4.40	6.09	6.02	5.98	5.60	5.50	5.43
105.0	9.57	9.91	10.17	2.37	2.43	2.47	2.08	2.10	2.11
110.0	16.76	17.16	17.45	1.33	1.41	1.47	1.10	1.15	1.18
112.0	19.79	20.20	20.50	1.16	1.25	1.30	0.94	0.99	1.03
113.0	21.32	21.74	22.05	1.09	1.18	1.24	0.88	0.93	0.97
115.0	24.45	24.88	25.20	1.00	1.09	1.14	0.79	0.84	0.88
118.0	29.35	29.82	30.16	0.90	0.99	1.04	0.70	0.75	0.78
119.0	31.07	31.55	31.90	0.88	0.96	1.01	0.67	0.72	0.76
120.0	32.84	33.34	33.70	0.86	0.94	0.99	0.65	0.70	0.73
130.0	57.70	58.06	58.04	0.74	0.81	0.85	0.51	0.55	0.58
140.0	53.93	54.19	54.41	0.68	0.74	0.77	0.42	0.46	0.49
600.0	66.18	66.08	66.15	0.40	0.51	0.57	0.11	0.16	0.17
850.0	48.53	48.21	47.79	0.54	0.69	0.77	0.18	0.23	0.25
870.0	38.02	39.37	40.55	0.64	0.76	0.84	0.31	0.33	0.33
1100.0	70.01	70.56	71.01	0.74	0.92	1.04	0.18	0.24	0.27
1500.0	75.36	77.24	75.36	1.97	2.33	2.55	0.09	0.18	0.21
1750.0	76.80	76.97	76.42	6.17	5.88	5.61	0.00	0.09	0.13
2000.0	70.07	69.45	69.25	2.59	2.85	3.03	0.09	0.00	0.05
2250.0	63.68	63.24	62.78	2.28	2.63	2.88	0.14	0.04	0.00
2500.0	60.62	60.30	59.97	3.39	3.92	4.25	0.12	0.03	0.01
2750.0	58.21	57.95	57.68	5.60	5.68	5.70	0.05	0.04	0.08
3000.0	62.01	59.68	57.66	4.77	4.44	4.26	0.06	0.15	0.20
3200.0	53.38	51.67	51.15	2.56	2.66	2.75	0.15	0.25	0.31
3500.0	54.50	52.92	51.70	2.64	2.90	3.03	0.29	0.41	0.48
3750.0	52.34	50.86	50.01	2.86	2.83	2.82	0.33	0.49	0.57
4000.0	45.97	44.88	44.26	2.12	2.36	2.51	0.38	0.56	0.67

## Typical Performance Data


FREQ.  (MHz)	GROUP DELAY		
	(ns)		
	@-40°C	@+25°C	@+85°C
30.0	60.97	60.69	60.53
31.0	51.31	51.14	51.05
32.0	44.96	44.85	44.80
33.0	40.00	39.94	39.89
34.0	33.92	33.88	33.86
35.0	32.64	32.60	32.58
36.0	31.35	31.31	31.29
37.0	30.06	30.02	30.01
38.0	28.76	28.74	28.72
39.0	27.48	27.46	27.44
40.0	26.21	26.20	26.18
41.0	24.96	24.94	24.93
42.0	23.71	23.69	23.69
43.0	22.56	22.54	22.54
44.0	21.56	21.54	21.54
45.0	20.69	20.68	20.68
46.0	19.93	19.92	19.92
47.0	19.26	19.25	19.25
48.0	18.66	18.65	18.65
49.0	18.13	18.13	18.13
50.0	17.65	17.65	17.65
51.0	17.23	17.23	17.23
52.0	16.84	16.84	16.85
53.0	16.50	16.50	16.50
54.0	16.18	16.19	16.19
55.0	15.90	15.90	15.92
56.0	15.65	15.66	15.66
57.0	15.42	15.43	15.44
58.0	15.22	15.23	15.24
59.0	15.05	15.06	15.07
60.0	14.89	14.90	14.92
61.0	14.75	14.77	14.79
62.0	14.64	14.66	14.68
63.0	14.54	14.56	14.58
64.0	14.47	14.49	14.51
65.0	14.42	14.44	14.46
66.0	14.38	14.40	14.43
67.0	14.36	14.38	14.41
68.0	14.35	14.38	14.41
69.0	14.37	14.40	14.43
70.0	14.40	14.43	14.46
71.0	14.45	14.48	14.51
72.0	14.51	14.55	14.58
73.0	14.60	14.64	14.67
74.0	14.69	14.73	14.77
75.0	14.81	14.85	14.89
76.0	14.94	14.99	15.03
77.0	15.09	15.14	15.19
78.0	15.27	15.32	15.37
79.0	15.46	15.52	15.57
80.0	15.69	15.75	15.80
81.0	15.94	16.00	16.06
82.0	16.23	16.30	16.36
88.0	19.02	19.15	19.25
84.0	16.92	17.01	17.08
85.0	17.35	17.45	17.53
86.0	17.84	17.94	18.03
87.0	18.39	18.51	18.60
88.0	19.02	19.15	19.25

## Typical Performance Curves


**INSERTION LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm




**INSERTION LOSS vs. TEMPERATURE (Zoomed)**  
INPUT POWER = 0 dBm




**INPUT RETURN LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm



**OUTPUT RETURN LOSS vs. TEMPERATURE**  
INPUT POWER = 0 dBm




**GROUP DELAY vs. TEMPERATURE**  
INPUT POWER = 0 dBm



## Outline Dimensions

UU1842



CASE#	A	B	C	D	E	F	G	H	J	WT.GRAMS
UU1842	2.300 (58.42)	2.250 (57.15)	0.750 (19.05)	2.175 (55.25)	2.125 (53.98)	0.125 (3.18)	0.125 (3.18)	0.312 (7.93)	1.125 (28.58)	124

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

- Case material: Aluminum alloy.
- Case finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I