

Coaxial

Power Splitter/Combiner

ZAPD-2-252-75+

2 Way-0° 75Ω 5 to 2500 MHz

Maximum Ratings


| | |
|-----------------------------|----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature | -55°C to 100°C |
| Power Input (as a splitter) | 0.5W max. |
| Internal Dissipation | 0.04W max. |

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

| | |
|----------|---|
| SUM PORT | S |
| PORT 1 | 1 |
| PORT 2 | 2 |

Outline Drawing



Outline Dimensions (inch/mm)

| A | B | C | D | E | F | G |
|-------|-------|-------|-------|------|-------|-------|
| 2.00 | 2.00 | 0.75 | 1.00 | 0.25 | 1.500 | 0.125 |
| 50.80 | 50.80 | 19.05 | 25.40 | 6.35 | 38.10 | 3.18 |

| H | J | K | L | wt |
|------|-------|-------|-------|-------|
| 0.39 | 1.00 | 0.50 | 1.00 | grams |
| 9.91 | 25.40 | 12.70 | 25.40 | 170.0 |

Features

- wideband, 5 to 2500 MHz, useable from 0.5 to 3000 MHz
- low insertion loss, 0.6 dB typ.
- excellent amplitude unbalance, 0.1 dB typ.
- excellent phase unbalance, 0.5 deg. typ.
- rugged shielded case

Applications

- VHF/UHF
- PCS
- GPS
- cellular
- instrumentation
- Cable TV



Generic photo used for illustration purposes only

CASE STYLE: F14

| Connectors | Model |
|------------|----------------|
| BNC | ZAPD-2-252-75+ |

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications




| FREQ. RANGE (MHz) | ISOLATION (dB) | | | | | INSERTION LOSS (dB) ABOVE 3.0 dB | | | | | | PHASE UNBALANCE (Degrees) | | | AMPLITUDE UNBALANCE (dB) | | | VSWR (:1) | | | | |
|-------------------|----------------|------|------|------|------|----------------------------------|------|------|------|------|------|---------------------------|------|------|--------------------------|------|------|-----------|------|------|------|---|
| | L | | M | | U | L | | M | | U | | L | M | U | L | M | U | S | | OUT | | |
| | Typ. | Min. | Typ. | Min. | Typ. | Typ. | Max. | Typ. | Max. | Typ. | Max. | Max. | Max. | Max. | Max. | Max. | Max. | Typ. | Max. | Typ. | Max. | |
| 5-2500 | 20 | 12 | 26 | 16 | 23 | 14 | 0.4 | 0.8 | 0.6 | 1.7 | 1.1 | 2.7 | 2 | 3 | 5 | 0.2 | 0.4 | 0.4 | 1.2 | — | 1.3 | — |

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]

Typical Performance Data

| Frequency (MHz) | Total Loss ¹ (dB) | | Amplitude Unbalance (dB) | Isolation (dB) | Phase Unbalance (deg.) | VSWR S | VSWR 1 | VSWR 2 |
|-----------------|------------------------------|------|--------------------------|----------------|------------------------|--------|--------|--------|
| | S-1 | S-2 | | | | | | |
| 5.00 | 3.46 | 3.37 | 0.09 | 19.17 | 0.05 | 1.05 | 1.55 | 1.57 |
| 200.00 | 3.52 | 3.43 | 0.08 | 22.55 | 0.02 | 1.14 | 1.40 | 1.41 |
| 400.00 | 3.56 | 3.47 | 0.09 | 25.11 | 0.04 | 1.24 | 1.35 | 1.34 |
| 500.00 | 3.59 | 3.51 | 0.08 | 27.13 | 0.08 | 1.26 | 1.33 | 1.32 |
| 600.00 | 3.62 | 3.54 | 0.08 | 29.81 | 0.01 | 1.24 | 1.30 | 1.31 |
| 800.00 | 3.68 | 3.56 | 0.11 | 34.89 | 0.14 | 1.15 | 1.26 | 1.27 |
| 1000.00 | 3.72 | 3.62 | 0.10 | 30.53 | 0.17 | 1.12 | 1.22 | 1.24 |
| 1200.00 | 3.83 | 3.74 | 0.09 | 27.67 | 0.40 | 1.15 | 1.20 | 1.22 |
| 1400.00 | 3.98 | 3.92 | 0.07 | 26.62 | 0.34 | 1.20 | 1.18 | 1.20 |
| 1600.00 | 4.09 | 4.03 | 0.07 | 25.10 | 0.44 | 1.24 | 1.16 | 1.18 |
| 1800.00 | 4.10 | 4.04 | 0.06 | 23.97 | 0.66 | 1.27 | 1.17 | 1.19 |
| 2000.00 | 4.08 | 4.01 | 0.07 | 22.66 | 0.97 | 1.26 | 1.17 | 1.17 |
| 2200.00 | 4.13 | 4.03 | 0.10 | 21.10 | 1.41 | 1.20 | 1.14 | 1.11 |
| 2400.00 | 4.34 | 4.28 | 0.06 | 19.66 | 1.69 | 1.16 | 1.11 | 1.06 |
| 2500.00 | 4.45 | 4.39 | 0.06 | 19.22 | 1.55 | 1.16 | 1.15 | 1.09 |

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



2 Way-0° Power Splitter/Combiner

ZAPD-2-252-75+






Typical Performance Data

| FREQUENCY (MHz) | TOTAL LOSS ¹ | | AMPLITUDE UNBALANCE (dB) | ISOLATION (dB) 1-2 | PHASE UNBALANCE (deg.) | FREQUENCY (MHz) | VSWR | | |
|--------------------|-------------------------|------|--------------------------------|--------------------------|------------------------------|--------------------|------|------|------|
| | (dB) | | | | | | (:1) | | |
| | S-1 | S-2 | | | | | S | 1 | 2 |
| 2.0 | 3.57 | 3.47 | 0.09 | 15.63 | 0.08 | 2.0 | 1.10 | 1.82 | 1.84 |
| 3.0 | 3.50 | 3.41 | 0.09 | 17.20 | 0.07 | 3.0 | 1.07 | 1.68 | 1.69 |
| 4.0 | 3.47 | 3.39 | 0.09 | 18.34 | 0.06 | 4.0 | 1.06 | 1.60 | 1.61 |
| 5.0 | 3.46 | 3.37 | 0.09 | 19.17 | 0.05 | 5.0 | 1.05 | 1.55 | 1.57 |
| 6.0 | 3.45 | 3.36 | 0.09 | 19.78 | 0.03 | 6.0 | 1.04 | 1.52 | 1.54 |
| 7.0 | 3.44 | 3.36 | 0.08 | 20.27 | 0.04 | 7.0 | 1.03 | 1.50 | 1.52 |
| 8.0 | 3.44 | 3.35 | 0.09 | 20.63 | 0.04 | 8.0 | 1.03 | 1.49 | 1.50 |
| 9.0 | 3.44 | 3.35 | 0.08 | 20.92 | 0.04 | 9.0 | 1.02 | 1.48 | 1.49 |
| 10.0 | 3.44 | 3.35 | 0.09 | 21.15 | 0.03 | 10.0 | 1.02 | 1.47 | 1.48 |
| 20.0 | 3.44 | 3.35 | 0.08 | 21.87 | 0.01 | 20.0 | 1.01 | 1.44 | 1.46 |
| 30.0 | 3.44 | 3.36 | 0.08 | 21.92 | 0.00 | 30.0 | 1.02 | 1.44 | 1.45 |
| 40.0 | 3.45 | 3.37 | 0.09 | 21.94 | 0.01 | 40.0 | 1.02 | 1.44 | 1.45 |
| 50.0 | 3.46 | 3.37 | 0.08 | 21.95 | 0.02 | 50.0 | 1.03 | 1.44 | 1.45 |
| 60.0 | 3.46 | 3.38 | 0.08 | 21.94 | 0.01 | 60.0 | 1.04 | 1.43 | 1.45 |
| 70.0 | 3.47 | 3.38 | 0.08 | 21.94 | 0.02 | 70.0 | 1.04 | 1.43 | 1.44 |
| 80.0 | 3.47 | 3.39 | 0.08 | 21.95 | 0.01 | 80.0 | 1.05 | 1.43 | 1.44 |
| 90.0 | 3.47 | 3.39 | 0.08 | 21.97 | 0.01 | 90.0 | 1.06 | 1.43 | 1.44 |
| 100.0 | 3.48 | 3.40 | 0.08 | 22.00 | 0.02 | 100.0 | 1.07 | 1.43 | 1.44 |
| 150.0 | 3.50 | 3.42 | 0.08 | 22.24 | 0.00 | 150.0 | 1.10 | 1.41 | 1.42 |
| 200.0 | 3.52 | 3.43 | 0.08 | 22.55 | 0.02 | 200.0 | 1.14 | 1.40 | 1.41 |
| 250.0 | 3.53 | 3.44 | 0.08 | 23.03 | 0.02 | 250.0 | 1.18 | 1.38 | 1.39 |
| 300.0 | 3.54 | 3.46 | 0.09 | 23.60 | 0.02 | 300.0 | 1.21 | 1.38 | 1.37 |
| 350.0 | 3.55 | 3.47 | 0.08 | 24.35 | 0.02 | 350.0 | 1.23 | 1.36 | 1.36 |
| 400.0 | 3.56 | 3.47 | 0.09 | 25.11 | 0.04 | 400.0 | 1.24 | 1.35 | 1.34 |
| 450.0 | 3.57 | 3.48 | 0.09 | 26.12 | 0.04 | 450.0 | 1.25 | 1.34 | 1.33 |
| 500.0 | 3.59 | 3.51 | 0.08 | 27.13 | 0.08 | 500.0 | 1.26 | 1.33 | 1.32 |
| 550.0 | 3.61 | 3.51 | 0.10 | 28.64 | 0.01 | 550.0 | 1.25 | 1.31 | 1.32 |
| 600.0 | 3.62 | 3.54 | 0.08 | 29.81 | 0.01 | 600.0 | 1.24 | 1.30 | 1.31 |
| 650.0 | 3.64 | 3.54 | 0.09 | 31.78 | 0.12 | 650.0 | 1.21 | 1.29 | 1.30 |
| 700.0 | 3.65 | 3.55 | 0.10 | 33.04 | 0.03 | 700.0 | 1.19 | 1.28 | 1.29 |
| 750.0 | 3.65 | 3.58 | 0.08 | 34.53 | 0.09 | 750.0 | 1.17 | 1.26 | 1.28 |
| 800.0 | 3.68 | 3.56 | 0.11 | 34.89 | 0.14 | 800.0 | 1.15 | 1.26 | 1.27 |
| 850.0 | 3.68 | 3.59 | 0.09 | 34.57 | 0.01 | 850.0 | 1.14 | 1.24 | 1.27 |
| 900.0 | 3.69 | 3.59 | 0.10 | 33.05 | 0.21 | 900.0 | 1.13 | 1.24 | 1.26 |
| 950.0 | 3.71 | 3.61 | 0.10 | 32.95 | 0.11 | 950.0 | 1.12 | 1.23 | 1.26 |
| 1000.0 | 3.72 | 3.62 | 0.10 | 30.53 | 0.17 | 1000.0 | 1.12 | 1.22 | 1.24 |
| 1100.0 | 3.77 | 3.66 | 0.11 | 28.78 | 0.26 | 1100.0 | 1.13 | 1.21 | 1.23 |
| 1200.0 | 3.83 | 3.74 | 0.09 | 27.67 | 0.40 | 1200.0 | 1.15 | 1.20 | 1.22 |
| 1300.0 | 3.91 | 3.83 | 0.07 | 27.00 | 0.40 | 1300.0 | 1.17 | 1.19 | 1.21 |
| 1375.0 | 3.97 | 3.89 | 0.08 | 26.43 | 0.38 | 1375.0 | 1.19 | 1.19 | 1.20 |
| 1400.0 | 3.98 | 3.92 | 0.07 | 26.62 | 0.34 | 1400.0 | 1.20 | 1.18 | 1.20 |
| 1500.0 | 4.04 | 3.98 | 0.07 | 25.96 | 0.33 | 1500.0 | 1.22 | 1.17 | 1.18 |
| 1600.0 | 4.09 | 4.03 | 0.07 | 25.10 | 0.44 | 1600.0 | 1.24 | 1.16 | 1.18 |
| 1700.0 | 4.12 | 4.05 | 0.07 | 24.68 | 0.56 | 1700.0 | 1.26 | 1.16 | 1.18 |
| 1800.0 | 4.10 | 4.04 | 0.06 | 23.97 | 0.66 | 1800.0 | 1.27 | 1.17 | 1.19 |
| 1900.0 | 4.08 | 4.02 | 0.06 | 23.19 | 0.81 | 1900.0 | 1.28 | 1.17 | 1.19 |
| 2000.0 | 4.08 | 4.01 | 0.07 | 22.66 | 0.97 | 2000.0 | 1.26 | 1.17 | 1.17 |
| 2100.0 | 4.09 | 4.00 | 0.10 | 22.15 | 1.15 | 2100.0 | 1.24 | 1.16 | 1.15 |
| 2200.0 | 4.13 | 4.03 | 0.10 | 21.10 | 1.41 | 2200.0 | 1.20 | 1.14 | 1.11 |
| 2300.0 | 4.23 | 4.14 | 0.09 | 20.19 | 1.67 | 2300.0 | 1.18 | 1.12 | 1.08 |
| 2400.0 | 4.34 | 4.28 | 0.06 | 19.66 | 1.69 | 2400.0 | 1.16 | 1.11 | 1.06 |
| 2500.0 | 4.45 | 4.39 | 0.06 | 19.22 | 1.55 | 2500.0 | 1.16 | 1.15 | 1.09 |
| 2600.0 | 4.54 | 4.44 | 0.10 | 18.50 | 1.69 | 2600.0 | 1.18 | 1.21 | 1.14 |
| 2700.0 | 4.59 | 4.42 | 0.17 | 18.15 | 1.95 | 2700.0 | 1.22 | 1.29 | 1.22 |
| 2750.0 | 4.63 | 4.50 | 0.13 | 17.71 | 3.14 | 2750.0 | 1.25 | 1.37 | 1.26 |
| 2800.0 | 4.61 | 4.40 | 0.21 | 18.25 | 2.36 | 2800.0 | 1.26 | 1.38 | 1.30 |
| 2900.0 | 4.70 | 4.42 | 0.28 | 18.41 | 2.89 | 2900.0 | 1.31 | 1.48 | 1.37 |
| 3000.0 | 4.86 | 4.52 | 0.34 | 18.87 | 3.45 | 3000.0 | 1.36 | 1.57 | 1.44 |


¹Total Loss = Insertion Loss + 3dB Splitter Loss



Typical Performance Curves



Outline Dimensions



| CASE # | A | B | C | D | E | F | G | H | J | K | L | WT. GRAM |
|--------|-----------------|-----------------|----------------|-----------------|---------------|------------------|----------------|---------------|-----------------|----------------|-----------------|----------|
| F14 | 2.00 (50.80) | 2.00 (50.80) | .75 (19.05) | 1.00 (25.40) | .25 (6.35) | 1.500 (38.10) | .125 (3.18) | .39 (9.91) | 1.00 (25.40) | .50 (12.70) | 1.00 (25.40) | 170.0 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------------|--|--------------------------------------|
| Operating Temperature | -55° to 100°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Barometric Pressure | 100,000 Feet | MIL-STD-202, Method 105, Condition D |
| Humidity | 90% RH, 65°C Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103 |
| Thermal Shock | -65° to 125°C, 5 cycles | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18) | MIL-STD-202, Method 213, Condition I |