

# DC Pass Power Splitter/Combiner

## ZB4PD-222-75+

4 Way-0° 75Ω 950 to 2200 MHz



Generic photo used for illustration purposes only

BNC version shown  
CASE STYLE: UU188

Connectors Model  
BNC ZB4PD-222-75+  
F-TYPE ZB4PD-222-75-F

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	1W max.
DC Current (each port)	0.5A max.
Permanent damage may occur if any of these limits are exceeded.	

### Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

### Outline Drawing



### Outline Dimensions (inch/mm)

A	B	C	D	E	F
3.50	2.13	.88	.150	3.350	1.06
88.90	54.10	22.35	3.81	85.09	26.92
G	H	J	K	wt	
.125	1.75	.44	.89	grams	
3.18	44.45	11.18	22.61	260	

### Electrical Schematic



### Features

- wideband, 950 to 2200 MHz
- high isolation, 25 dB typ.
- rugged, shielded case
- up to 10W power input as a splitter
- DC pass from sum port to all output ports

### Applications




- satellite communications
- GPS
- CATV

### Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
<b>Frequency Range</b>		950		2200	MHz
<b>Insertion Loss</b> (above theoretical 6.0 dB)	950 - 2200	—	0.9	1.1	dB
<b>Isolation</b>	950 - 2200	20	23	—	dB
<b>Phase Unbalance</b>	950 - 2200	—	2.7	7.0	Degree
<b>Amplitude Unbalance</b>	950 - 2200	—	0.3	0.7	dB
<b>VSWR (Port S)</b>	950 - 2200	—	1.27	1.65	:1
<b>VSWR (Port 1-4)</b>	950 - 2200	—	1.24	1.6	:1

### Typical Performance Data

Freq. (MHz)	Total Loss <sup>1</sup> (dB)				Amp. Unb. (dB)	Isolation (dB)			Phase Unb. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	2-3	3-4						
800.00	6.33	6.34	6.34	6.34	0.01	21.64	21.93	21.64	0.41	1.32	1.10	1.10	1.09	1.09
900.00	6.41	6.42	6.43	6.41	0.01	28.07	23.89	28.07	0.40	1.43	1.06	1.05	1.06	1.06
1000.00	6.40	6.42	6.42	6.40	0.02	34.44	25.95	34.44	0.38	1.39	1.14	1.14	1.15	1.15
1100.00	6.33	6.35	6.36	6.33	0.03	40.89	27.73	40.89	0.41	1.22	1.20	1.21	1.21	1.21
1200.00	6.30	6.33	6.33	6.30	0.03	32.43	28.85	32.43	0.42	1.01	1.23	1.25	1.24	1.25
1300.00	6.35	6.38	6.39	6.35	0.04	28.24	29.29	28.24	0.51	1.20	1.26	1.28	1.28	1.28
1400.00	6.45	6.49	6.49	6.44	0.05	27.17	29.29	27.17	0.57	1.39	1.29	1.32	1.31	1.30
1500.00	6.51	6.54	6.55	6.49	0.06	28.46	29.35	28.46	0.58	1.46	1.31	1.34	1.32	1.31
1600.00	6.48	6.51	6.51	6.46	0.06	31.02	29.84	31.02	0.61	1.40	1.29	1.31	1.30	1.28
1700.00	6.42	6.46	6.44	6.39	0.06	28.57	31.13	28.57	0.62	1.26	1.23	1.24	1.24	1.20
1800.00	6.42	6.45	6.44	6.39	0.06	24.07	33.71	24.07	0.61	1.20	1.13	1.14	1.13	1.11
1900.00	6.47	6.51	6.49	6.44	0.06	21.24	37.62	21.24	0.66	1.28	1.06	1.04	1.04	1.07
2000.00	6.51	6.56	6.55	6.49	0.07	20.01	37.32	20.01	0.81	1.35	1.13	1.11	1.13	1.15
2100.00	6.57	6.70	6.61	6.51	0.19	19.76	34.75	19.76	2.07	1.36	1.25	1.23	1.24	1.24
2200.00	6.58	6.54	6.49	6.52	0.10	21.25	27.54	21.25	1.09	1.31	1.33	1.30	1.30	1.30



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/WCLStore/terms.jsp](http://www.minicircuits.com/WCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A  
M151107  
ZB4PD-222-75+  
ED-13815A  
HY/CP/AM  
200819  
Page 2 of 2

# 4 Way-0° Power Splitter/Combiner

# ZB4PD-222-75+

## Typical Performance Data

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)				AMP UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (Deg)	FREQ. (MHz)	VSWR (:1)				
	S1	S2	S3	S4		1-2	2-3	3-4			S	1	2	3	4
800.0	6.33	6.34	6.34	6.34	0.01	21.64	21.93	21.64	0.41	800.0	1.32	1.10	1.10	1.09	1.09
850.0	6.38	6.39	6.39	6.39	0.01	24.79	22.88	24.79	0.38	850.0	1.39	1.05	1.05	1.05	1.05
900.0	6.41	6.42	6.43	6.41	0.01	28.07	23.89	28.07	0.40	900.0	1.43	1.06	1.05	1.06	1.06
950.0	6.42	6.43	6.43	6.42	0.02	31.16	24.94	31.16	0.39	950.0	1.43	1.10	1.10	1.10	1.10
1000.0	6.40	6.42	6.42	6.40	0.02	34.44	25.95	34.44	0.38	1000.0	1.39	1.14	1.14	1.15	1.15
1050.0	6.37	6.39	6.39	6.37	0.02	38.47	26.91	38.47	0.40	1050.0	1.32	1.18	1.18	1.18	1.19
1100.0	6.33	6.35	6.36	6.33	0.03	40.89	27.73	40.89	0.41	1100.0	1.22	1.20	1.21	1.21	1.21
1150.0	6.31	6.33	6.34	6.30	0.03	36.39	28.42	36.39	0.44	1150.0	1.12	1.22	1.23	1.23	1.23
1200.0	6.30	6.33	6.33	6.30	0.03	32.43	28.85	32.43	0.42	1200.0	1.01	1.23	1.25	1.24	1.25
1250.0	6.31	6.35	6.34	6.31	0.03	29.82	29.13	29.82	0.46	1250.0	1.09	1.25	1.27	1.26	1.26
1300.0	6.35	6.38	6.39	6.35	0.04	28.24	29.29	28.24	0.51	1300.0	1.20	1.26	1.28	1.28	1.28
1350.0	6.40	6.44	6.45	6.40	0.05	27.44	29.33	27.44	0.53	1350.0	1.30	1.28	1.30	1.29	1.29
1400.0	6.45	6.49	6.49	6.44	0.05	27.17	29.29	27.17	0.57	1400.0	1.39	1.29	1.32	1.31	1.30
1450.0	6.49	6.52	6.53	6.47	0.05	27.56	29.33	27.56	0.54	1450.0	1.44	1.30	1.33	1.32	1.31
1500.0	6.51	6.54	6.55	6.49	0.06	28.46	29.35	28.46	0.58	1500.0	1.46	1.31	1.34	1.32	1.31
1550.0	6.50	6.54	6.54	6.48	0.06	29.79	29.52	29.79	0.59	1550.0	1.44	1.30	1.33	1.32	1.30
1600.0	6.48	6.51	6.51	6.46	0.06	31.02	29.84	31.02	0.61	1600.0	1.40	1.29	1.31	1.30	1.28
1650.0	6.45	6.48	6.48	6.42	0.06	30.79	30.40	30.79	0.66	1650.0	1.33	1.27	1.28	1.28	1.24
1700.0	6.42	6.46	6.44	6.39	0.06	28.57	31.13	28.57	0.62	1700.0	1.26	1.23	1.24	1.24	1.20
1750.0	6.41	6.45	6.43	6.38	0.06	26.08	32.21	26.08	0.64	1750.0	1.21	1.18	1.19	1.19	1.15
1800.0	6.42	6.45	6.44	6.39	0.06	24.07	33.71	24.07	0.61	1800.0	1.20	1.13	1.14	1.13	1.11
1850.0	6.44	6.47	6.46	6.41	0.06	22.46	35.62	22.46	0.66	1850.0	1.23	1.08	1.08	1.07	1.07
1900.0	6.47	6.51	6.49	6.44	0.06	21.24	37.62	21.24	0.66	1900.0	1.28	1.06	1.04	1.04	1.07
1950.0	6.49	6.54	6.53	6.48	0.06	20.47	38.53	20.47	0.68	1950.0	1.32	1.08	1.06	1.08	1.10
2000.0	6.51	6.56	6.55	6.49	0.07	20.01	37.32	20.01	0.81	2000.0	1.35	1.13	1.11	1.13	1.15
2050.0	6.52	6.58	6.57	6.49	0.09	19.83	35.20	19.83	1.04	2050.0	1.37	1.19	1.17	1.18	1.20
2100.0	6.57	6.70	6.61	6.51	0.19	19.76	34.75	19.76	2.07	2100.0	1.36	1.25	1.23	1.24	1.24
2200.0	6.58	6.54	6.49	6.52	0.10	21.25	27.54	21.25	1.09	2200.0	1.31	1.33	1.30	1.30	1.30






<sup>1</sup> Total Loss = Insertion Loss + 6dB Splitter Loss



# 4 Way-0° Power Splitter/Combiner

ZB4PD-222-75+

## Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)




IF/RF MICROWAVE COMPONENTS

REV. X1  
 ZB4PD-222-75+  
 2/1/2012  
 Page 1 of 1

## Outline Dimensions

UU188



CASE#	A	B	C	D	E	F	G	H	J	K	WT. GRAMS
UU188	3.50 (88.90)	2.13 (54.10)	.88 (22.35)	.150 (3.81)	3.350 (85.09)	1.06 (26.92)	.125 (3.18)	1.75 (44.45)	.44 (11.18)	.89 (22.61)	260

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

1. Case material: Aluminum alloy.
2. Case finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	0° to 70° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Life (HTOL)	1000 hours at max operating temperature	MIL-STD-202, Method 108, Condition D
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215