

Suspended Substrate Stripline Filters and Multiplexers

50Ω DC to 26 GHz

The Big Deal

- Low insertion loss
- Ultra-wide passband width
- Fast roll-off with wide stopband
- Good power handling and temperature stability
- Passband up to 26 GHz
- Stopband up to 26.5 GHz can extend to 40 GHz



Product Overview

Mini-Circuits' Suspended Substrate Stripline filters offer low insertion loss by implementing printed circuit board suspended between two parallel ground planes, providing high Q. Low insertion loss combined with wide stopband makes them an excellent choice for wideband instruments and systems like ECM, ECCM, ELINT and ultra-broadband receivers.

Low pass, high pass, band pass, band stop, diplexer and multiplexer designs can be realized with this technology. Advanced filter design and construction can achieve stopband width greater than 6x the center frequency, and temperature stability will be better than other printed circuit realizations because the fields are mainly in the air rather than in a dielectric. The inside walls of the housing hold the circuit and prevent movement that could be caused by vibration or mechanical shock, making these designs excellent candidates for harsh operating environments.

Suspended substrate stripline filters can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitters
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide, spur-free stop band results in better receiver sensitivity
High power handling	Well suited for transmitter applications
Excellent temperature stability	Ensures minimal variation in electrical performance across temperature

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Suspended substrate stripline Band Pass Filter

ZBSS-3G-S+

50Ω 2000 to 4000 MHz



Generic photo used for illustration purposes only
CASE STYLE: VY3280

Connectors Model
SMA - F ZBSS-3G-S+


Features

- Wide fractional bandwidth design of 66.7%
- 1dB typ. Insertion loss at Center frequency
- Sharp roll-off
- High rejection floor of 90dB typ.
- Stop band up to 25 GHz
- Connectorized package


Applications

- Satellite communications
- Radiolocation
- Radio Navigation
- Military and defense
- Electronic warfare receiver

Functional Schematic



Typical Frequency Response



Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	Fc	3000	-	1.0	-	dB
	Insertion Loss	F1-F2	2000 - 4000	-	1.5	2.5	dB
	VSWR	F1-F2	2000 - 4000	-	1.4	-	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 1100	60	90	-	dB
		F3-F4	1100 - 1300	40	60	-	dB
		F4-F5	1300 - 1450	20	35	-	dB
Stop Band, Upper	Insertion Loss	F6-F7	5300 - 6000	20	35	-	dB
		F7-F8	6000 - 7600	40	55	-	dB
		F8-F9	7600 - 25000	60	90	-	dB

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10W max. @ 25°C





Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
10	109.84	737.91	2000	1.97
100	119.48	352.82	2100	1.68
600	99.94	837.60	2200	1.51
1100	91.63	123.69	2300	1.38
1300	61.39	66.40	2400	1.28
1450	42.16	39.46	2500	1.21
1600	21.35	17.36	2600	1.15
1750	2.59	1.28	2700	1.10
2000	1.38	1.27	2800	1.07
2500	0.99	1.11	2900	1.04
3000	1.00	1.26	3000	1.01
3500	1.02	1.06	3100	0.98
4000	1.24	1.13	3200	0.97
4400	3.70	2.70	3300	0.96
4850	20.07	15.26	3400	0.96
5300	34.42	19.77	3500	0.96
6000	52.89	22.96	3600	0.96
7600	79.41	28.53	3700	0.96
15000	98.50	34.33	3800	0.98
25000	91.61	5.63	4000	1.03

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

PORT - 1	SMA FEMALE
PORT - 2	SMA FEMALE

Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F
2.70	.60	.60	1.920	.380	.110
68.7	15.2	15.2	48.77	9.65	2.80
G	H	J	K	Wt.	
.11	.39	.30	.30	grams	
2.8	9.9	7.6	7.7	120	

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Suspended substrate stripline

Band Pass Filter

ZBSS-3G-S+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	110.39	109.84	101.74	0.02	0.02	0.02	0.01	0.01	0.01
50	89.28	92.29	95.69	0.02	0.02	0.02	0.02	0.02	0.01
100	113.80	119.48	111.73	0.05	0.05	0.05	0.03	0.02	0.02
150	116.37	117.74	118.31	0.04	0.04	0.03	0.01	0.01	0.01
200	116.20	113.19	116.76	0.06	0.04	0.04	0.03	0.06	0.06
250	123.91	111.37	120.25	0.03	0.01	0.01	0.06	0.09	0.10
300	103.67	103.17	103.50	0.04	0.02	0.02	0.12	0.17	0.17
350	104.10	106.46	105.29	0.03	0.00	0.00	0.17	0.21	0.22
400	114.37	107.70	118.48	0.03	0.01	0.00	0.24	0.29	0.31
500	107.67	115.36	110.57	0.01	0.01	0.02	0.37	0.42	0.45
600	100.08	99.94	97.95	0.01	0.02	0.02	0.46	0.52	0.56
700	103.27	103.78	106.54	0.01	0.04	0.05	0.49	0.56	0.59
800	103.33	105.41	103.65	0.02	0.05	0.06	0.50	0.56	0.59
900	93.02	94.21	95.71	0.04	0.08	0.09	0.47	0.53	0.56
1000	91.91	93.30	92.52	0.06	0.10	0.12	0.44	0.51	0.54
1100	91.18	91.63	90.68	0.10	0.14	0.16	0.45	0.53	0.57
1200	74.00	73.69	73.53	0.15	0.19	0.22	0.51	0.60	0.64
1300	61.76	61.39	61.22	0.20	0.26	0.29	0.64	0.75	0.80
1450	42.55	42.16	42.00	0.36	0.44	0.48	1.00	1.13	1.22
1500	35.88	35.47	35.30	0.44	0.54	0.59	1.10	1.25	1.34
1550	29.05	28.61	28.44	0.61	0.73	0.79	1.28	1.44	1.54
1600	21.82	21.35	21.18	0.84	1.00	1.09	1.41	1.61	1.73
1650	13.94	13.47	13.32	1.56	1.84	2.01	2.00	2.32	2.50
1750	2.41	2.59	2.74	17.17	18.33	18.60	20.52	22.60	22.64
2000	1.21	1.38	1.47	18.54	18.56	18.77	17.34	17.26	17.35
2200	0.96	1.10	1.18	36.92	35.35	34.57	34.92	35.29	35.76
2400	0.89	1.03	1.10	22.34	22.57	22.63	20.56	20.58	20.67
2600	0.84	0.97	1.04	27.49	27.37	27.37	24.28	24.25	24.40
2800	0.81	0.94	1.02	24.85	24.61	24.79	26.56	26.53	26.61
3000	0.87	1.00	1.07	18.64	18.75	18.80	20.78	20.82	20.87
3200	0.91	1.04	1.11	17.18	17.46	17.53	18.47	18.63	18.72
3400	0.87	1.01	1.08	22.79	23.23	23.53	22.05	22.29	22.42
3600	0.90	1.04	1.12	30.79	30.85	30.25	30.58	30.61	30.55
3800	0.97	1.13	1.21	25.03	25.55	25.30	32.29	33.82	34.34
4000	1.08	1.24	1.33	23.81	24.11	24.01	29.41	29.92	29.93
4400	3.25	3.70	3.88	7.07	6.77	6.82	6.26	5.99	5.97
4600	9.88	10.53	10.71	2.06	2.13	2.20	1.58	1.63	1.67
4850	19.45	20.07	20.19	1.00	1.14	1.21	0.61	0.70	0.74
5150	29.42	29.98	30.07	0.73	0.89	0.96	0.37	0.46	0.49
5300	33.89	34.42	34.49	0.72	0.88	0.96	0.29	0.38	0.41
5500	39.60	40.11	40.18	0.73	0.88	0.97	0.22	0.32	0.35
6000	52.36	52.89	52.99	0.62	0.76	0.80	0.15	0.25	0.26
6500	63.06	63.42	63.50	0.46	0.58	0.62	0.13	0.23	0.24
7000	72.17	72.58	72.57	0.39	0.51	0.55	0.12	0.20	0.22
7600	79.36	79.41	79.57	0.47	0.61	0.66	0.09	0.18	0.20
8000	87.17	85.52	89.31	0.48	0.63	0.66	0.09	0.18	0.21
9000	106.47	93.30	93.73	0.27	0.40	0.44	0.07	0.17	0.19
10000	100.82	93.86	94.41	0.34	0.49	0.54	0.06	0.18	0.19
11000	101.37	88.02	93.40	0.44	0.59	0.63	0.06	0.19	0.20
12000	90.23	93.94	91.78	0.31	0.46	0.50	0.09	0.22	0.23
13000	105.91	95.07	94.96	0.41	0.58	0.63	0.05	0.17	0.19
14000	89.11	90.03	90.48	0.48	0.67	0.71	0.01	0.13	0.15
15000	96.96	98.50	94.36	0.32	0.51	0.54	0.01	0.15	0.16
16000	95.09	94.34	92.04	0.48	0.72	0.79	0.03	0.19	0.21
17000	94.32	97.20	99.02	0.57	0.78	0.83	0.02	0.19	0.21
18000	93.30	97.74	96.07	0.40	0.60	0.67	0.02	0.20	0.22
19000	88.73	100.53	89.25	0.89	1.25	1.37	0.03	0.21	0.23
20000	88.95	107.31	85.06	0.98	1.30	1.39	0.06	0.24	0.27
22000	94.25	90.37	102.65	2.08	2.41	2.54	0.11	0.32	0.35
25000	91.65	91.61	89.74	2.77	3.12	3.20	0.37	0.55	0.56

Suspended substrate stripline Band Pass Filter

ZBSS-3G-S+





Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
2000	1.98	1.97	1.96
2050	1.82	1.81	1.80
2100	1.69	1.68	1.68
2150	1.59	1.58	1.58
2200	1.51	1.51	1.50
2250	1.44	1.44	1.44
2300	1.39	1.38	1.38
2350	1.33	1.33	1.33
2400	1.29	1.28	1.28
2450	1.24	1.24	1.24
2500	1.21	1.21	1.21
2550	1.18	1.18	1.18
2600	1.15	1.15	1.15
2650	1.13	1.13	1.13
2700	1.11	1.10	1.10
2750	1.09	1.08	1.08
2800	1.07	1.07	1.07
2850	1.05	1.05	1.05
2900	1.04	1.04	1.04
2950	1.02	1.02	1.02
3000	1.01	1.01	1.01
3050	1.00	1.00	1.00
3100	0.98	0.98	0.99
3150	0.98	0.98	0.98
3200	0.97	0.97	0.97
3250	0.96	0.96	0.96
3300	0.96	0.96	0.96
3350	0.96	0.96	0.96
3400	0.95	0.96	0.96
3450	0.95	0.96	0.96
3500	0.95	0.96	0.96
3550	0.96	0.96	0.96
3600	0.96	0.96	0.96
3650	0.96	0.96	0.96
3700	0.96	0.96	0.96
3750	0.97	0.97	0.97
3800	0.97	0.98	0.98
3850	0.98	0.98	0.98
3900	0.99	1.00	1.00
3950	1.00	1.01	1.01
4000	1.02	1.03	1.03

Suspended substrate stripline Band Pass Filter


ZBSS-3G-S+

Typical Performance Curves



Outline Dimensions

VY3280



CASE#	A	B	C	D	E	F
VY3280	2.70 (68.7)	.60 (15.2)	.60 (15.2)	1.920 (48.77)	.380 (9.65)	.110 (2.80)

CASE#	G	H	J	K	WT. GRAMS
VY3280	.11 (2.8)	.39 (9.9)	.30 (7.6)	.30 (7.7)	120

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .100$; 3 Pl. $\pm .015$

Notes:

1. Case material: Brass.
2. Case Finish: Powder coated over silver plating.
3. Refer to the individual model data sheet for the type of connectors available.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A