



COAXIAL

# Wideband Bias-Tee

## ZBT-K44-FT+

50Ω 10 MHz to 40 GHz 2.92mm Male to 2.92mm Female

### KEY FEATURES

- Wideband Millimeter Wave , 10 MHz to 40 GHz
- Low Insertion Loss, 1.0 dB typ.
- Excellent Return Loss, 15 dB typ.
- Excellent Isolation, 35 dB typ.




Generic photo used for illustration purposes only

### PRODUCT OVERVIEW

Mini-Circuits' ZBT-K44-FT+ is an ultra-wideband coaxial bias-tee covering frequencies from 10 MHz to 40 GHz with low insertion loss, excellent return loss, and high DC to RF isolation over its entire frequency range. This model is capable of handling up to +30 dBm (1W) RF input power and DC input current up to 250mA, and is ideal for applications such as biasing amplifiers, laser diodes, active antennas and more.

### FUNCTIONAL DIAGRAM



### ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Unit
Frequency Range		0.01		40	GHz
Insertion Loss	0.01-20	-	0.5	1.2	dB
	20-40	-	1.0	2.0	
Input Return Loss	0.01-20	-	18	9.5	dB
	20-40	-	15	9.5	
Output Return Loss	0.01-20	-	18	9.5	dB
	20-40	-	15	9.5	
Isolation <sup>1</sup>	0.01-40	-	35	-	dB
DC Resistance, DC to RF and DC port		-	2.5	-	Ohm


1. Isolation (RF+DC port to DC port) is tested with a 50Ohm SMA connector at the DC input port.

### ABSOLUTE MAXIMUM RATINGS<sup>2</sup>

Parameter	Ratings
Operating Case Temperature	-40 °C to +85 °C
Storage Temperature	-55 °C to +100 °C
RF Power	30 dBm max.
Input Current	SEE CHART
Voltage at DC Port	25V max.

2. Permanent damage may occur if any of these limits are exceeded.

### CURRENT DERATING







COAXIAL

# Wideband Bias-Tee

## ZBT-K44-FT+

50Ω 10 MHz to 40 GHz 2.92mm Male to 2.92mm Female

### TYPICAL PERFORMANCE GRAPHS





COAXIAL

# Wideband Bias-Tee


# ZBT-K44-FT+

50Ω    10 MHz to 40 GHz    2.92mm Male to 2.92mm Female

## CONNECTOR SPECIFICATIONS

Description	RF PORT	RF & DC PORT	DC PORT
Connector Type	2.92mm-Female	2.92mm-Male	Filtered Feedthrough

## CASE STYLE DRAWING



Weight: 35 grams  
Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.03; 3 Pl. ±.015 inches

## PRODUCT MARKING\*: ZBT-K44-FT+

\*Marking may contain other features or characters for internal lot control.

## ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	Y3206-1
RoHs Status	Compliant
Environmental Ratings	ENV135

### NOTES



- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)




*Typical Performance Data*

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	
		INPUT	OUTPUT
0.05	0.28	21.0	21.2
0.1	0.12	26.3	26.6
0.5	0.11	43.5	36.6
0.8	0.13	36.5	31.9
1.0	0.16	32.2	29.5
2.0	0.28	27.5	25.3
3.0	0.41	22.7	21.0
4.0	0.52	20.1	18.6
5.0	0.54	19.2	17.9
6.0	0.52	19.5	18.0
7.0	0.49	21.4	18.9
8.0	0.47	25.2	20.8
9.0	0.46	31.1	24.1
10.0	0.47	30.6	30.0
11.0	0.50	24.1	32.1
12.0	0.56	19.9	24.4
13.0	0.64	17.4	20.9
14.0	0.71	16.3	19.3
15.0	0.76	16.0	19.4
16.0	0.73	17.2	21.4
17.0	0.69	20.6	27.6
18.0	0.68	24.5	32.5
19.0	0.70	28.0	27.7
20.0	0.74	24.5	23.0
21.0	0.78	21.2	21.2
22.0	0.81	20.9	21.0
23.0	0.84	19.8	20.0
24.0	0.86	19.4	21.0
25.0	0.88	19.4	23.9
26.0	0.90	19.3	26.4
27.0	0.92	20.0	30.2
28.0	0.94	20.0	29.7
29.0	1.00	16.8	22.7
30.0	1.11	13.0	17.5
31.0	1.18	12.4	15.5
32.0	1.17	13.0	14.8
33.0	1.11	15.2	15.5
34.0	1.08	17.2	17.6
35.0	1.17	15.2	16.3
36.0	1.25	13.3	13.5
37.0	1.25	13.9	12.5
38.0	1.21	14.6	12.6
39.0	1.19	15.5	13.6
40.0	1.14	17.6	16.5

## Typical Performance Curves





Weight: 35 grams

Dimensions are in inches [mm]. Tolerances: 2 Pl.  $\pm$ .03; 3 Pl.  $\pm$ .015 inches

Notes:

Case material: Brass alloy 360.  
 Case Finish:  
 For RoHS Case Styles: Gold Plating.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-40° to +85° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-40° C to +85°C, 100 cycles	Transition time = 5 mins, Dwell time = 30 mins
Vibration	Random Vibration (Non-operating)	MIL-STD-810F Method 514.5 Procedure I, Category 24, Figure 513C-17
Mechanical Shock	Non-operation	MIL-STD 810F Method 516.5 Procedure 1, Table 516.5-II