

Coaxial

Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω DC to 6 GHz



The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions

Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency.

All our coaxial-ceramic resonator filters are built with rugged construction. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bandpass Filter

50Ω

403 to 430 MHz

ZCBP6-416R5-S+



Features

- Low insertion loss, 1.1dB typ.
- High rejection, 70dB typ.
- Connectorized package

Generic photo used for illustration purposes only
CASE STYLE: CC1764

Applications

- Public safety communication
- Medical radio communication service

Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	—	416.5	—	MHz
	Insertion Loss	F1-F2	403 - 430	—	1.11	1.7	dB
	VSWR	F1-F2	403 - 430	—	1.23	1.67	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 320	65	80	—	dB
		F3-F4	320 - 382	20	27	—	dB
Stop Band, Upper	Insertion Loss	F5-F6	451 - 520	20	28	—	dB
		F6-F7	520 - 800	55	73	—	dB


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	20W at 25°C


Permanent damage may occur if any of these limits are exceeded.

*Passband rating

Functional Schematic




Typical Frequency Response



Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nSec)
0.5	113.14	10528.35	403.0	34.90
10.5	99.30	6363.29	404.0	33.55
100.5	106.80	1670.36	405.0	32.47
150.5	98.24	883.61	406.0	31.56
320.0	82.56	163.95	407.0	30.82
380.0	31.19	45.89	408.0	30.21
382.0	27.98	39.86	409.0	29.70
395.0	3.12	2.47	410.0	29.29
403.0	1.05	1.08	411.0	28.96
410.0	0.93	1.19	412.0	28.69
416.5	0.90	1.20	413.0	28.47
420.0	0.92	1.23	414.0	28.31
430.0	1.07	1.08	415.0	28.17
436.0	3.53	3.21	416.5	28.07
451.0	28.10	67.81	417.0	28.05
455.0	33.00	85.86	418.0	28.07
520.0	98.12	156.55	420.0	28.30
600.0	76.28	149.40	425.0	30.31
700.0	76.56	125.39	428.0	33.08
800.0	76.62	109.67	430.0	36.34


ZCBP6-416R5-S+




ZCBP6-416R5-S+



ZCBP6-416R5-S+



ZCBP6-416R5-S+




Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Connections

PORt - 1	SMA-FEMALE
PORt - 2	SMA-FEMALE

Outline Drawing**Outline Dimensions (inch)**

A	B	C	D	E
2.000	2.000	.750	.938	.125
50.80	50.80	19.05	23.83	3.18

F	G	H	J	Wt.
1.750	.125	.375	.750	grams
44.45	3.18	9.53	19.05	116

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Band Pass Filter

ZCBP6-416R5-S+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
	0.5	95.01	113.14	94.75	0.00	0.00	0.00	0.01	0.01
10.5	96.82	99.30	105.04	0.01	0.00	0.00	0.01	0.01	0.01
20.5	107.49	110.77	102.44	0.01	0.00	0.00	0.01	0.01	0.01
30.5	97.93	105.90	96.57	0.01	0.00	0.00	0.01	0.01	0.01
50.5	96.94	104.27	116.33	0.01	0.01	0.01	0.01	0.01	0.01
100.5	105.77	106.80	99.14	0.01	0.01	0.01	0.01	0.01	0.02
120.5	109.59	102.63	96.56	0.01	0.01	0.02	0.01	0.01	0.02
150.5	99.43	98.24	98.30	0.01	0.02	0.03	0.02	0.03	0.03
200.0	98.69	96.60	95.07	0.02	0.04	0.05	0.03	0.04	0.05
210.0	96.61	96.33	96.46	0.02	0.04	0.05	0.03	0.04	0.05
220.0	95.16	97.07	95.98	0.03	0.05	0.05	0.04	0.05	0.06
230.0	89.78	103.33	93.86	0.03	0.05	0.06	0.04	0.05	0.06
240.0	89.67	92.60	93.15	0.03	0.05	0.06	0.04	0.06	0.07
250.0	90.54	92.97	96.28	0.04	0.06	0.07	0.05	0.06	0.07
260.0	90.43	91.58	89.15	0.05	0.06	0.07	0.06	0.07	0.08
270.0	91.28	92.54	91.36	0.05	0.07	0.08	0.06	0.08	0.09
280.0	89.33	88.69	88.89	0.06	0.07	0.08	0.07	0.08	0.09
300.0	84.33	87.68	89.28	0.07	0.09	0.10	0.08	0.09	0.11
320.0	81.66	82.56	82.24	0.08	0.11	0.12	0.09	0.11	0.13
350.0	64.06	64.15	64.12	0.12	0.15	0.17	0.13	0.15	0.17
360.0	55.34	55.35	55.35	0.15	0.18	0.20	0.16	0.18	0.20
370.0	44.78	44.71	44.66	0.20	0.24	0.26	0.21	0.23	0.26
380.0	31.38	31.19	31.13	0.33	0.38	0.42	0.31	0.35	0.39
382.0	28.18	27.98	27.91	0.37	0.44	0.48	0.36	0.40	0.44
386.0	21.05	20.80	20.70	0.56	0.64	0.70	0.51	0.58	0.63
395.0	3.15	3.12	3.13	6.81	7.45	7.97	6.27	6.84	7.28
400.0	1.09	1.20	1.29	28.68	28.75	29.16	26.52	27.63	28.71
403.0	0.94	1.05	1.14	31.16	28.54	27.05	33.77	30.39	28.57
405.0	0.90	1.01	1.10	24.42	23.32	22.29	24.83	23.76	22.72
408.0	0.86	0.96	1.05	20.90	20.70	20.01	21.50	21.39	20.69
410.0	0.83	0.93	1.01	21.17	21.34	20.82	22.29	22.67	22.15
416.5	0.80	0.90	0.97	21.42	20.93	20.87	22.41	21.86	21.92
418.0	0.81	0.91	0.98	20.37	19.88	19.67	20.81	20.27	20.13
420.0	0.81	0.92	1.00	20.17	19.77	19.37	20.21	19.77	19.41
425.0	0.82	0.92	1.00	33.66	34.12	31.18	29.44	29.09	27.91
430.0	0.94	1.07	1.15	28.40	28.02	28.52	27.15	26.95	27.58
436.0	3.22	3.53	3.58	5.75	5.60	5.83	5.66	5.50	5.73
440.0	9.97	10.37	10.35	1.28	1.31	1.39	1.26	1.28	1.37
446.0	20.61	20.95	20.92	0.36	0.40	0.43	0.36	0.40	0.43
450.0	26.47	26.77	26.75	0.23	0.27	0.30	0.24	0.27	0.30
454.0	31.56	31.84	31.83	0.18	0.21	0.23	0.19	0.22	0.24
459.0	37.13	37.39	37.38	0.14	0.17	0.19	0.15	0.18	0.20
500.0	70.21	70.38	70.29	0.08	0.11	0.13	0.10	0.12	0.13
510.0	80.17	80.55	79.98	0.08	0.11	0.13	0.09	0.12	0.13
520.0	91.94	98.12	92.23	0.08	0.11	0.13	0.10	0.12	0.14
540.0	80.28	81.08	80.27	0.08	0.11	0.13	0.10	0.12	0.14
560.0	76.91	77.21	78.38	0.08	0.12	0.14	0.10	0.12	0.14
580.0	76.45	77.16	77.03	0.08	0.12	0.14	0.10	0.13	0.15
600.0	75.60	76.28	76.46	0.08	0.12	0.14	0.11	0.13	0.15
620.0	76.23	77.15	76.85	0.09	0.12	0.14	0.11	0.13	0.15
640.0	76.05	77.20	76.25	0.09	0.13	0.15	0.11	0.14	0.16
660.0	74.97	76.43	76.54	0.10	0.13	0.15	0.12	0.14	0.16
680.0	75.60	75.68	77.77	0.10	0.13	0.16	0.12	0.15	0.17
700.0	75.74	76.56	76.32	0.11	0.14	0.16	0.13	0.15	0.17
720.0	75.29	75.70	76.30	0.11	0.14	0.16	0.13	0.15	0.18
740.0	75.63	76.52	76.21	0.11	0.15	0.17	0.13	0.16	0.18
760.0	75.13	75.45	75.31	0.11	0.15	0.17	0.14	0.16	0.18
770.0	75.16	75.49	76.34	0.12	0.15	0.17	0.14	0.16	0.19
780.0	75.09	75.50	76.26	0.12	0.15	0.18	0.14	0.17	0.19
800.0	75.29	76.62	76.18	0.12	0.16	0.18	0.14	0.17	0.19



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. OR

ZCBP6-416R5-S+

210927

Page 1 of 2






Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(ns)		
	@-40°C	@+25°C	@+85°C
397.0	46.94	46.62	46.42
398.0	45.78	45.32	45.04
399.0	43.83	43.30	42.97
400.0	41.44	40.92	40.60
401.0	39.04	38.60	38.31
402.0	36.93	36.57	36.33
403.0	35.19	34.90	34.71
404.0	33.78	33.55	33.39
405.0	32.65	32.47	32.32
406.0	31.71	31.56	31.43
407.0	30.95	30.82	30.70
408.0	30.31	30.21	30.10
409.0	29.78	29.70	29.60
410.0	29.35	29.29	29.20
411.0	29.00	28.96	28.88
412.0	28.72	28.69	28.62
413.0	28.50	28.47	28.41
414.0	28.33	28.31	28.25
415.0	28.19	28.17	28.12
416.5	28.08	28.07	28.01
417.0	28.07	28.05	28.00
418.0	28.08	28.07	28.01
419.0	28.15	28.15	28.09
420.0	28.29	28.30	28.23
421.0	28.51	28.54	28.46
422.0	28.80	28.84	28.76
423.0	29.18	29.24	29.16
424.0	29.65	29.72	29.64
425.0	30.21	30.31	30.23
426.0	30.91	31.03	30.94
427.0	31.79	31.93	31.84
428.0	32.90	33.08	32.97
429.0	34.33	34.55	34.42
430.0	36.09	36.34	36.16
431.0	38.09	38.34	38.13
432.0	40.09	40.29	40.06
433.0	41.74	41.85	41.63
434.0	42.75	42.74	42.54
435.0	42.94	42.79	42.64
436.0	42.25	41.97	41.86
437.0	40.68	40.28	40.24

Coaxial Band Pass Filter

ZCBP6-416R5-S+

Typical Performance Curves




Case Style

CC

Outline Dimensions

CC1764



CASE#	A	B	C	D	E	F	G	H	J	WT. GRAMS
CC1764	2.000 (50.80)	2.000 (50.80)	0.750 (19.05)	0.938 (23.83)	0.125 (3.18)	1.750 (44.45)	0.125 (3.18)	0.375 (9.53)	0.750 (19.05)	116

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet