

Coaxial Low Noise Amplifier

ZEL-1217LN+


50Ω 1200 to 1700 MHz

Features

- very low noise figure, 1.6 dB max.
- wideband, 1200 to 1700 MHz
- rugged, shielded case

Applications

- GPS
- mar sat
- communication systems



Generic photo used for illustration purposes only

Case Style: EEE132

Connectors	Model
SMA	ZEL-1217LN+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		1200		1700	MHz
Noise Figure	1200-1700	—	—	1.6	dB
Gain	1200-1700	20	—	—	dB
Gain Flatness	1200-1700	—	—	±1.0	dB
Output Power at 1dB compression	1200-1700	—	+8	—	dBm
Output third order intercept point	1200-1700	—	+25	—	dBm
Input VSWR	1200-1700	—	—	2.5	:1
Output VSWR	1200-1700	—	—	2.5	:1
DC Supply Voltage		—	15	—	V
Supply Current		—	—	70	mA

Noise Figure specified at room temperature, increases to 2 dB typical at +85°C

Open load is not recommended, potentially can cause damage.
With no load derate max input power by 20 dB

Outline Drawing



Maximum Ratings

Parameter	Ratings
Operating Temperature	-54°C to 85°C
Storage Temperature	-55°C to 100°C
DC Voltage	17V
Input RF Power (no damage)	+13 dBm

Permanent damage may occur if any of these limits are exceeded.

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	wt
.90	.90	.675	.245	.45	1.34	.09	1.152	.09	.712	.22	.106	.05	grams
22.86	22.86	17.15	6.22	11.43	34.04	2.29	29.26	2.29	18.08	5.59	2.69	1.27	50.0

Notes






- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
M175652
ZEL-1217LN+
200512
Page 1 of 2

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR (:1)		NOISE FIGURE (dB)	POUT at 1 dB COMPR. (dBm)
	12V	15V	16V	12V	15V	16V	IN	OUT		
1200.00	29.28	30.36	30.62	9.70	9.00	9.20	1.97	1.40	1.30	11.67
1236.60	29.06	30.12	30.37	10.50	9.80	9.70	1.97	1.35	1.20	11.72
1287.00	28.74	29.77	30.00	10.40	10.40	10.10	2.01	1.33	1.11	11.81
1339.60	28.41	29.42	29.65	11.40	11.10	11.20	2.08	1.32	1.08	11.74
1392.30	28.23	29.21	29.45	11.50	11.20	11.30	2.12	1.32	1.09	11.83
1443.60	28.23	29.21	29.42	11.80	11.60	11.70	2.12	1.35	1.14	12.05
1507.70	28.31	29.24	29.44	11.50	11.90	11.70	2.08	1.37	1.22	12.07
1571.80	28.53	29.41	29.61	11.30	11.30	11.50	2.00	1.41	1.32	12.47
1635.90	29.13	29.91	30.07	10.10	10.10	10.10	1.86	1.44	1.43	12.79
1700.00	30.01	30.62	30.77	8.10	8.80	8.70	1.63	1.57	1.49	13.13



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Noise Amplifier

ZEL-1217LN+

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR IN (:1) 15V	VSWR OUT (:1) 15V	NOISE FIGURE (dB) 15V	Pout at 1dB Comp. (dBm) 15V
	12V	15V	16V	12V	15V	16V				
1200.0	29.28	30.36	30.62	9.70	9.00	9.20	1.97	1.40	1.30	11.67
1236.6	29.06	30.12	30.37	10.50	9.80	9.70	1.97	1.35	1.20	11.72
1287.0	28.74	29.77	30.00	10.40	10.40	10.10	2.01	1.33	1.11	11.81
1339.6	28.41	29.42	29.65	11.40	11.10	11.20	2.08	1.32	1.08	11.74
1392.3	28.23	29.21	29.45	11.50	11.20	11.30	2.12	1.32	1.09	11.83
1443.6	28.23	29.21	29.42	11.80	11.60	11.70	2.12	1.35	1.14	12.05
1507.7	28.31	29.24	29.44	11.50	11.90	11.70	2.08	1.37	1.22	12.07
1571.8	28.53	29.41	29.61	11.30	11.30	11.50	2.00	1.41	1.32	12.47
1635.9	29.13	29.91	30.07	10.10	10.10	10.10	1.86	1.44	1.43	12.79
1700.0	30.01	30.62	30.77	8.10	8.80	8.70	1.63	1.57	1.49	13.13



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine  Provides ACTUAL Data Instantly at minicircuits.com

IF/RF MICROWAVE COMPONENTS






For detailed performance specs & shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

Low Noise Amplifier

Typical Performance Curves

ZEL-1217LN+




For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine www.minicircuits.com Provides ACTUAL Data Instantly at minicircuits.com

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.sp.

Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L
EEE132	.90 (22.86)	.90 (22.86)	.675 (17.15)	.245 (6.22)	.45 (11.43)	1.34 (34.04)	.09 (2.29)	1.152 (29.26)	.09 (2.29)	.712 (18.08)	.22 (5.59)

CASE #	M	N	WT. GRAM
EEE132	.106 (2.69)	.05 (1.27)	50.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-54° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C