

Coaxial Slope Equalizer

ZEQ-3-222N+

50Ω 950 to 2150 MHz

The Big Deal

- Good matching
- Minimal deviation in the attenuation slope ± 0.4 dB
- Connectorized package



Generic photo used for illustration purposes only
CASE STYLE: H795-4

Product Overview

ZEQ-3-222N+ is a 50Ω coaxial slope Equalizer. This model offers excellent performance in the “L band” frequency range of 950-2150 MHz with minimal deviation in the attenuation slope.

Key Features

Feature	Advantages
Minimal deviation in the attenuation slope, ± 0.4 dB	Provide low signal distortion over the passband. Can used in satellite system.
Good matching in the passband	Good 50Ω matching between input and output.
Connectorized package	This connectorized package is easy to interface with other devices and well suits for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Slope Equalizer

50Ω 950 to 2150 MHz

ZEQ-3-222N+



Generic photo used for illustration purposes only
CASE STYLE: H795-4

Connectors	Model
N-M/F	ZEQ-3-222N+

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Input power	+20 dBm

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

Input	(N Male)
Output	(N Female)

Features

- Good matching in passband
- Minimal deviation in the attenuation slope ± 0.4 dB
- Connectorized package


Applications

- Loss compensation
- Satellite L band applications

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch mm)

A	B	C	D	E
1.25	1.25	0.94	0.63	0.47
31.75	31.75	23.88	16.00	11.94
F	G	H	wt	
1.00	0.13	0.13	grams	
25.40	3.18	3.18	91	

Note: Please refer to case style drawing for details

Typical Frequency Response




Electrical Specifications at 25°C

Parameter	Condition	Min.	Typ.	Max.	Units
Frequency Range	-	950	-	2150	MHz
Insertion Loss	950 MHz	4.5	-	5.9	dB
	1500 MHz	1.9	-	3.3	
VSWR	2150 MHz	0.3	-	1.7	:1
	950-2150 MHz	-	1.1	1.6	

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR
950.0	5.33	1.18
1000.0	5.09	1.19
1100.0	4.59	1.20
1200.0	4.10	1.21
1250.0	3.86	1.22
1300.0	3.62	1.22
1400.0	3.17	1.22
1500.0	2.73	1.22
1600.0	2.33	1.20
1750.0	1.78	1.17
1850.0	1.47	1.15
1900.0	1.32	1.13
2000.0	1.07	1.11
2100.0	0.85	1.08
2150.0	0.76	1.06

Simplified Functional Schematic





Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
ECO-005139
ZEQ-3-222N+
EDU1185_1
URJ
201201
Page 2 of 3



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Slope Equalizer

ZEQ-3-222N+

Typical Performance Data


FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
950	5.30	5.33	5.34	21.24	21.63	21.56	24.51	24.71	24.69
960	5.25	5.28	5.29	21.18	21.56	21.50	24.52	24.72	24.70
970	5.20	5.23	5.24	21.12	21.48	21.44	24.53	24.75	24.70
980	5.15	5.18	5.19	21.08	21.41	21.39	24.53	24.77	24.71
990	5.10	5.13	5.14	21.03	21.34	21.34	24.53	24.79	24.71
1000	5.06	5.09	5.09	20.98	21.28	21.28	24.52	24.82	24.71
1010	5.01	5.03	5.04	20.92	21.21	21.22	24.52	24.84	24.72
1020	4.96	4.99	4.99	20.87	21.14	21.16	24.52	24.87	24.74
1030	4.91	4.94	4.94	20.84	21.08	21.11	24.53	24.90	24.77
1040	4.86	4.89	4.89	20.82	21.02	21.06	24.54	24.94	24.80
1050	4.81	4.84	4.85	20.80	20.96	21.02	24.55	24.98	24.83
1060	4.76	4.79	4.80	20.78	20.90	20.97	24.54	25.01	24.84
1070	4.71	4.74	4.75	20.76	20.84	20.92	24.52	25.05	24.85
1080	4.66	4.69	4.70	20.73	20.79	20.87	24.51	25.09	24.86
1090	4.61	4.64	4.65	20.71	20.73	20.83	24.52	25.13	24.88
1100	4.56	4.59	4.60	20.69	20.68	20.78	24.54	25.18	24.93
1150	4.31	4.34	4.35	20.62	20.45	20.61	24.66	25.41	25.08
1200	4.07	4.10	4.11	20.52	20.27	20.49	25.03	25.67	25.29
1250	3.83	3.86	3.87	20.32	20.13	20.39	25.54	25.92	25.50
1300	3.59	3.62	3.63	20.09	20.04	20.34	26.07	26.18	25.72
1350	3.35	3.39	3.40	19.94	20.01	20.36	26.49	26.39	25.98
1400	3.13	3.17	3.17	19.87	20.03	20.39	26.74	26.55	26.27
1450	2.91	2.95	2.95	19.97	20.10	20.45	26.72	26.63	26.40
1500	2.69	2.73	2.74	20.20	20.24	20.56	26.71	26.65	26.53
1550	2.48	2.53	2.53	20.47	20.43	20.69	26.79	26.60	26.67
1600	2.28	2.33	2.33	20.78	20.70	20.91	26.61	26.50	26.56
1650	2.09	2.14	2.14	21.10	21.04	21.15	26.46	26.37	26.46
1700	1.91	1.96	1.96	21.49	21.45	21.51	26.45	26.23	26.41
1750	1.74	1.78	1.79	21.96	21.94	21.91	26.33	26.11	26.17
1800	1.57	1.62	1.63	22.53	22.53	22.40	26.32	26.05	26.03
1820	1.51	1.56	1.57	22.75	22.79	22.61	26.33	26.02	25.98
1830	1.48	1.53	1.54	22.88	22.92	22.74	26.36	26.02	25.99
1840	1.45	1.50	1.51	23.01	23.06	22.88	26.38	26.02	26.00
1850	1.42	1.47	1.48	23.16	23.21	23.02	26.37	26.02	25.98
1900	1.27	1.32	1.34	23.73	24.01	23.69	26.32	26.09	25.93
1910	1.25	1.30	1.31	23.87	24.17	23.85	26.33	26.11	25.95
1920	1.22	1.27	1.28	24.02	24.35	24.04	26.32	26.13	25.97
1930	1.19	1.24	1.25	24.18	24.53	24.23	26.31	26.16	25.98
1940	1.17	1.22	1.23	24.33	24.73	24.42	26.29	26.19	25.99
1950	1.14	1.19	1.20	24.45	24.92	24.59	26.29	26.23	26.00
1960	1.12	1.17	1.18	24.58	25.13	24.75	26.30	26.28	26.04
1970	1.09	1.14	1.15	24.70	25.33	24.93	26.33	26.33	26.08
1980	1.06	1.11	1.13	24.85	25.54	25.12	26.34	26.38	26.12
1990	1.04	1.09	1.10	25.02	25.75	25.34	26.37	26.43	26.15
2000	1.02	1.07	1.08	25.23	25.98	25.59	26.38	26.48	26.19
2010	0.99	1.04	1.06	25.44	26.21	25.84	26.41	26.55	26.23
2020	0.97	1.02	1.03	25.65	26.44	26.07	26.46	26.61	26.31
2030	0.95	1.00	1.01	25.84	26.69	26.31	26.51	26.69	26.39
2040	0.92	0.98	0.99	26.01	26.95	26.54	26.57	26.78	26.47
2050	0.90	0.95	0.97	26.20	27.21	26.77	26.62	26.87	26.55
2060	0.88	0.93	0.95	26.42	27.48	27.03	26.66	26.96	26.60
2070	0.86	0.91	0.93	26.70	27.75	27.32	26.71	27.05	26.65
2080	0.84	0.89	0.91	27.03	28.03	27.64	26.77	27.14	26.73
2090	0.82	0.87	0.89	27.34	28.32	27.96	26.87	27.25	26.85
2100	0.80	0.85	0.87	27.63	28.63	28.29	26.97	27.36	26.99
2110	0.78	0.83	0.85	27.89	28.94	28.60	27.07	27.48	27.14
2120	0.76	0.81	0.83	28.14	29.26	28.90	27.15	27.62	27.27
2130	0.74	0.79	0.81	28.42	29.60	29.21	27.22	27.76	27.36
2140	0.72	0.77	0.79	28.80	29.94	29.56	27.28	27.89	27.43
2150	0.70	0.76	0.77	29.21	30.29	29.95	27.39	28.04	27.53

Typical Performance Curves



Outline Dimensions

H795-4



CASE#	A	B	C	D	E	F	G	H	WT.GRAMS
H795-4	1.25 (31.75)	1.25 (31.75)	.94 (23.88)	.63 (16.00)	.47 (11.94)	1.000 (25.40)	.125 (3.18)	.125 (3.18)	91

Dimensions are in inches (mm). Tolerances: 2PL. $\pm .03$; 3PL. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I