

# Power Splitter/Combiner

## ZFSC-4-175W+

4 Way-0° 75Ω 5 to 1000 MHz



Generic photo used for illustration purposes only

### Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.5W max.
Permanent damage may occur if any of these limits are exceeded.	

### Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

### Features

- wideband, 5 to 1000MHz
- high isolation, 36 dB typ.

### Applications

- VHF/UHF
- cellular
- transmitters/receivers
- communication systems

CASE STYLE: G15

Connectors Model  
 BNC ZFSC-4-175W+  
 BRACKET(OPTION "B")

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 6.0 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L	M	U	L	M	U
	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.
5-1000	34	22	36	22	27	20	0.5	0.8	0.5	1.2	0.9	1.9	1	3	5	0.2	0.2	0.5


L = low range [ $f_L$  to  $10 f_L$ ] M = mid range [ $10 f_L$  to  $f_U/2$ ] U = upper range [ $f_U/2$  to  $f_U$ ]

### Typical Performance Data

Freq. (MHz)	Total Loss <sup>1</sup> (dB)				Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	1-4	3-4						
5.00	6.50	6.50	6.50	6.50	0.01	30.86	34.90	29.99	0.08	1.05	1.25	1.25	1.25	1.25
50.00	6.51	6.50	6.50	6.50	0.02	42.15	36.85	44.00	0.08	1.04	1.31	1.36	1.36	1.35
110.00	6.56	6.55	6.55	6.55	0.01	38.96	35.85	39.79	0.09	1.09	1.41	1.39	1.41	1.41
200.00	6.59	6.58	6.57	6.58	0.02	35.94	35.13	36.69	0.16	1.17	1.43	1.38	1.39	1.40
290.00	6.62	6.60	6.61	6.60	0.02	34.18	35.08	34.85	0.29	1.26	1.41	1.36	1.38	1.38
350.00	6.64	6.63	6.62	6.63	0.02	33.19	35.41	33.65	0.36	1.29	1.37	1.33	1.37	1.35
440.00	6.72	6.69	6.67	6.68	0.05	31.61	36.45	31.58	0.41	1.33	1.34	1.31	1.33	1.34
500.00	6.76	6.72	6.71	6.72	0.05	30.34	37.40	29.92	0.45	1.30	1.30	1.26	1.31	1.31
570.00	6.79	6.75	6.74	6.74	0.05	28.79	38.31	28.13	0.42	1.27	1.28	1.25	1.28	1.30
605.00	6.78	6.76	6.75	6.74	0.04	28.03	38.33	27.29	0.51	1.26	1.27	1.24	1.28	1.30
710.00	6.87	6.83	6.82	6.82	0.06	26.38	35.74	25.41	0.64	1.17	1.28	1.26	1.28	1.28
815.00	7.00	6.95	6.94	6.93	0.07	25.73	32.14	24.55	0.76	1.06	1.32	1.31	1.30	1.31
850.00	7.03	6.98	6.98	6.96	0.07	25.76	31.10	24.52	0.91	1.10	1.35	1.31	1.31	1.31
910.00	7.12	7.09	7.07	7.06	0.06	26.28	29.65	24.81	0.94	1.14	1.40	1.35	1.35	1.37
1000.00	7.29	7.25	7.24	7.21	0.08	28.14	28.09	25.90	1.10	1.23	1.46	1.36	1.39	1.40




1. Total Loss = Insertion Loss + 6dB splitter loss.

### Outline Drawing



### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	.61	--	.80
31.75	31.75	19.05	16.00	9.65	15.49	--	20.32
J	K	L	M	N	P	Q	wt
.80	.76	.125	1.688	2.18	.75	.07	grams
20.32	19.30	3.18	42.88	55.37	19.05	1.78	85.0



### electrical schematic



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/WCLStore/terms.jsp](http://www.minicircuits.com/WCLStore/terms.jsp)



# 4 Way-0° Power Splitter/Combiner

# ZFSC-4-175W+

## Typical Performance Data

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	1-3	3-4			S	1	2	3	4
5.0	6.50	6.50	6.50	6.50	0.01	30.86	34.90	29.99	0.08	5.0	1.05	1.25	1.25	1.25	1.25
9.0	6.48	6.48	6.47	6.47	0.01	35.66	36.80	35.11	0.07	9.0	1.02	1.23	1.24	1.24	1.23
13.0	6.47	6.47	6.47	6.47	0.01	38.75	37.41	38.85	0.09	13.0	1.01	1.23	1.24	1.24	1.24
17.0	6.48	6.48	6.47	6.47	0.01	40.77	37.53	41.68	0.06	17.0	1.00	1.24	1.26	1.25	1.25
21.0	6.48	6.48	6.48	6.48	0.01	42.04	37.63	43.82	0.03	21.0	1.01	1.25	1.28	1.27	1.27
25.0	6.49	6.49	6.48	6.47	0.01	42.58	37.55	45.21	0.08	25.0	1.02	1.26	1.30	1.29	1.29
30.0	6.49	6.50	6.48	6.48	0.02	43.05	37.46	45.80	0.03	30.0	1.02	1.27	1.31	1.31	1.31
35.0	6.50	6.50	6.50	6.48	0.02	42.99	37.29	45.79	0.03	35.0	1.03	1.28	1.33	1.32	1.32
40.0	6.50	6.50	6.49	6.49	0.01	42.87	37.19	45.44	0.12	40.0	1.03	1.29	1.34	1.33	1.33
45.0	6.51	6.50	6.50	6.50	0.01	42.56	36.95	44.52	0.08	45.0	1.04	1.30	1.35	1.34	1.34
50.0	6.51	6.50	6.50	6.50	0.02	42.15	36.85	44.00	0.08	50.0	1.04	1.31	1.36	1.36	1.35
80.0	6.52	6.52	6.52	6.53	0.01	40.44	36.18	41.49	0.09	80.0	1.07	1.36	1.38	1.39	1.39
110.0	6.56	6.55	6.55	6.55	0.01	38.96	35.85	39.79	0.09	110.0	1.09	1.41	1.39	1.41	1.41
140.0	6.57	6.56	6.55	6.55	0.02	37.69	35.57	38.53	0.06	140.0	1.12	1.43	1.39	1.40	1.41
170.0	6.59	6.59	6.57	6.57	0.02	36.72	35.38	37.50	0.18	170.0	1.15	1.44	1.39	1.40	1.40
200.0	6.59	6.58	6.57	6.58	0.02	35.94	35.13	36.69	0.16	200.0	1.17	1.43	1.38	1.39	1.40
230.0	6.63	6.63	6.61	6.62	0.02	35.31	35.12	36.13	0.23	230.0	1.20	1.43	1.37	1.39	1.39
260.0	6.62	6.62	6.59	6.60	0.02	34.71	35.04	35.44	0.16	260.0	1.23	1.42	1.37	1.39	1.38
290.0	6.62	6.60	6.61	6.60	0.02	34.18	35.08	34.85	0.29	290.0	1.26	1.41	1.36	1.38	1.38
320.0	6.69	6.67	6.66	6.67	0.03	33.69	35.25	34.33	0.28	320.0	1.28	1.39	1.35	1.37	1.37
350.0	6.64	6.63	6.62	6.63	0.02	33.19	35.41	33.65	0.36	350.0	1.29	1.37	1.33	1.37	1.35
380.0	6.69	6.68	6.66	6.67	0.03	32.73	35.69	33.05	0.29	380.0	1.31	1.36	1.33	1.36	1.35
410.0	6.71	6.68	6.67	6.68	0.03	32.20	36.00	32.33	0.39	410.0	1.34	1.35	1.32	1.34	1.35
440.0	6.72	6.69	6.67	6.68	0.05	31.61	36.45	31.58	0.41	440.0	1.33	1.34	1.31	1.33	1.34
470.0	6.74	6.72	6.70	6.70	0.04	30.98	36.89	30.72	0.37	470.0	1.30	1.32	1.28	1.32	1.32
500.0	6.76	6.72	6.71	6.72	0.05	30.34	37.40	29.92	0.45	500.0	1.30	1.30	1.26	1.31	1.31
535.0	6.76	6.73	6.72	6.73	0.05	29.53	37.93	29.00	0.50	535.0	1.30	1.29	1.26	1.29	1.31
570.0	6.79	6.75	6.74	6.74	0.05	28.79	38.31	28.13	0.42	570.0	1.27	1.28	1.25	1.28	1.30
605.0	6.78	6.76	6.75	6.74	0.04	28.03	38.33	27.29	0.51	605.0	1.26	1.27	1.24	1.28	1.30
640.0	6.81	6.78	6.76	6.77	0.05	27.42	37.79	26.56	0.57	640.0	1.26	1.27	1.26	1.29	1.31
675.0	6.84	6.81	6.78	6.79	0.06	26.84	36.94	25.92	0.69	675.0	1.21	1.28	1.27	1.28	1.30
710.0	6.87	6.83	6.82	6.82	0.06	26.38	35.74	25.41	0.64	710.0	1.17	1.28	1.26	1.28	1.28
745.0	6.90	6.87	6.86	6.85	0.05	26.00	34.54	24.96	0.70	745.0	1.17	1.28	1.28	1.30	1.29
780.0	6.94	6.89	6.88	6.88	0.06	25.82	33.33	24.74	0.66	780.0	1.11	1.30	1.31	1.31	1.30
815.0	7.00	6.95	6.94	6.93	0.07	25.73	32.14	24.55	0.76	815.0	1.06	1.32	1.31	1.30	1.31
850.0	7.03	6.98	6.98	6.96	0.07	25.76	31.10	24.52	0.91	850.0	1.10	1.35	1.31	1.31	1.31
880.0	7.09	7.05	7.04	7.03	0.07	26.01	30.42	24.69	0.92	880.0	1.10	1.37	1.33	1.34	1.34
910.0	7.12	7.09	7.07	7.06	0.06	26.28	29.65	24.81	0.94	910.0	1.14	1.40	1.35	1.35	1.37
940.0	7.19	7.14	7.14	7.11	0.08	26.78	29.06	25.14	1.03	940.0	1.21	1.43	1.35	1.34	1.38
970.0	7.23	7.19	7.19	7.15	0.08	27.41	28.54	25.53	1.12	970.0	1.24	1.45	1.34	1.36	1.38
1000.0	7.29	7.25	7.24	7.21	0.08	28.14	28.09	25.90	1.10	1000.0	1.23	1.46	1.36	1.39	1.40






<sup>1</sup> Total Loss = Insertion Loss+ 6dB Splitter Loss



# 4 Way-0° Power Splitter/Combiner

# ZFSC-4-175W+

## Typical Performance Curves



REV. X2  
ZFSC-4-175W+  
100627  
Page 1 of 1




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see [minicircuits.com](http://minicircuits.com)

### Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L
G15	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	.61 (15.49)	--	.80 (20.32)	.80 (20.32)	.76 (19.30)	.125 (3.18)

CASE #	M	N	P	Q	WT. GRAM
G15	1.688 (42.88)	2.18 (55.37)	.75 (19.05)	.07 (1.78)	85.0

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

#### Notes:

- Case material: Aluminum alloy.
- Case finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number.
- For Bracket version, option "B" dimension "K" changes from .76 to .90 inches when connectors are type TNC.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I