

Coaxial Low Noise Amplifier

ZFL-500HLN+

50Ω 10 to 500 MHz

Features

- low noise, 3.8 dB typ.
- high IP3, +30 dBm typ.

Applications

- VHF/UHF
- small signal amplifier
- communications system



Generic photo used for illustration purposes only

CASE STYLE: Y460

Connectors Model
SMA ZFL-500HLN+
BRACKET (OPTION "B")

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Low Noise Amplifier Electrical Specifications

MODEL NO.	FREQUENCY (MHz)		NOISE FIGURE (dB)	GAIN (dB)		MAXIMUM POWER (dBm)		INTERCEPT POINT (dBm)	VSWR (:1) Typ.		DC POWER	
	f_L	f_U		Flatness Max.	Total Range	Output (1 dB Compr.)	Input (no damage)		IP3 Typ.	In	Out	Volt (V) Nom.
ZFL-500HLN+	10	500	3.8	Min.	±0.4	+16	+15	+30	2.0	2.0	15	110

m = mid range [2 fL to fU/2]

Open load is not recommended, potentially can cause damage.
 With no load derate max input power by 20 dB

Maximum Ratings

Operating Temperature -20°C to 71°C

Storage Temperature -55°C to 100°C



DC Voltage +17V Max.

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing

STANDARD

OPTION "B"



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.25	1.25	.75	.63	.36	1.000	1.000	.125	.125	.46	2.18	1.688	.06	.750	.50	.80	.45	.29	grams
31.75	31.75	19.05	16.00	9.14	25.40	25.40	3.18	3.18	11.68	55.37	42.88	1.52	19.05	12.70	20.32	11.43	7.37	38

Notes






- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
 M151107
 ZFL-500HLN+
 151005
 Page 1 of 2

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR (:1)		NOISE FIGURE (dB)	POUT at 1 dB COMPR. (dBm)
	12V	15V	16V	12V	15V	16V	IN	OUT		
10.00	20.50	20.97	21.05	16.70	16.20	16.30	1.24	1.17	3.83	16.78
19.30	20.37	20.82	20.92	17.10	17.00	16.00	1.12	1.13	3.84	17.09
46.50	20.21	20.68	20.76	17.50	15.30	15.90	1.05	1.11	3.83	17.14
111.80	20.31	20.78	20.87	16.20	15.20	16.50	1.02	1.11	3.89	17.19
198.50	20.22	20.66	20.77	15.60	16.20	15.30	1.02	1.06	3.88	17.17
248.70	20.35	20.82	20.90	15.80	15.10	14.90	1.04	1.07	3.92	17.13
311.50	20.22	20.69	20.77	15.80	15.20	15.00	1.07	1.06	3.95	16.97
374.40	20.46	20.96	21.03	14.30	15.10	14.20	1.10	1.10	3.96	16.95
437.20	20.32	20.79	20.90	14.20	13.90	13.60	1.13	1.17	3.97	16.91
500.00	20.36	20.87	20.96	13.80	13.20	12.30	1.17	1.25	3.97	16.91



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Low Noise Amplifier

ZFL-500HLN+

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR IN (:1) 15V	VSWR OUT (:1) 15V	NOISE FIGURE (dB) 15V	Pout at 1dB Comp. (dBm) 15V
	12V	15V	16V	12V	15V	16V				
10.0	20.50	20.97	21.05	16.70	16.20	16.30	1.24	1.17	3.83	16.78
19.3	20.37	20.82	20.92	17.10	17.00	16.00	1.12	1.13	3.84	17.09
46.5	20.21	20.68	20.76	17.50	15.30	15.90	1.05	1.11	3.83	17.14
111.8	20.31	20.78	20.87	16.20	15.20	16.50	1.02	1.11	3.89	17.19
198.5	20.22	20.66	20.77	15.60	16.20	15.30	1.02	1.06	3.88	17.17
248.7	20.35	20.82	20.90	15.80	15.10	14.90	1.04	1.07	3.92	17.13
311.5	20.22	20.69	20.77	15.80	15.20	15.00	1.07	1.06	3.95	16.97
374.4	20.46	20.96	21.03	14.30	15.10	14.20	1.10	1.10	3.96	16.95
437.2	20.32	20.79	20.90	14.20	13.90	13.60	1.13	1.17	3.97	16.91
500.0	20.36	20.87	20.96	13.80	13.20	12.30	1.17	1.25	3.97	16.91

REV. X1
ZFL-500HLN+
060913
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Low Noise Amplifier

ZFL-500HLN+

Typical Performance Curves



REV. X1
ZFL-500HLN+
060913
Page 1 of 1




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
Y460	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.0)	.36 (9.15)	1.000 (25.4)	1.000 (25.4)	.125 (3.2)	.125 (3.2)	.46 (11.7)	2.18 (55.4)	1.688 (42.9)	.06 (1.5)

CASE#	P	Q	R	S	T	WT. GRAMS
Y460	.750 (19.0)	.50 (12.7)	.80 (20.3)	.45 (11.4)	.29 (7.4)	38

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 71° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C