

DC Pass, Coaxial

# Power Splitter/Combiner ZFSC-2-1WDC-S+

2 Way-0° 50Ω 1 to 750 MHz

## The Big Deal

- Wideband, 1 to 750 MHz
- Low insertion loss, 0.4 dB
- Low unbalance, 0.1 dB, 0.5°
- High isolation, 28 dB
- DC Passing up to 30mA



CASE STYLE: K18

## Product Overview

Mini-Circuits' ZFSC-2-1WDC-S+ is a 2-way 0° splitter/combiner supporting applications from 1 to 750 MHz such as VHF/UHF communications. This model is capable of handling up to 1W RF input power and passing up to 30mA DC current (15mA per port) from input to output. It provides very low insertion loss of just 0.4 dB, low phase and amplitude unbalance of 0.5° and 0.1 dB, respectively, and outstanding isolation of 28 dB. The ZFSC-2-1WDC-S+ comes housed in a rugged aluminum alloy case measuring 1.25 x 1.25 x 0.75" with SMA connectors at all ports.

## Key Features

Feature	Advantages
Wideband, 1 to 750 MHz	This model supports bandwidth requirements for VHF/UHF communications.
Low insertion loss, 0.4 dB	Efficient transmission of signal power from input to output.
Low unbalance: <ul style="list-style-type: none"><li>• 0.1 dB amplitude unbalance</li><li>• 0.5° phase unbalance</li></ul>	Produces nearly equal output signals, ideal for parallel path and multichannel systems.
High isolation, 28 dB	Minimizes interference between ports.
DC Passing, 30mA (15mA each port)	Supports applications where DC power is needed through the RF line.

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# DC Pass, Coaxial Power Splitter/Combiner

## ZFSC-2-1WDC-S+

2 Way-0° 50Ω 1 to 750 MHz

### Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.125W max.
DC Current	30mA (15mA per port)

Permanent damage may occur if any of these limits are exceeded.

### Coaxial Connections

SUM PORT	3
PORT 1	1
PORT 2	2

### Outline Drawing




### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H						
1.25	1.25	.75	.63	.38	1.00	.125	1.000						
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40						
J	K	L	M	N	P	Q	wt						
-	-	.125	1.688	2.18	.75	.07	grams						
-	-	3.18	42.88	55.37	19.05	1.78	70.0						

For option B with N-type connectors, dimension "C" increases to 0.94 inches.

### Electrical Schematic



### Features

- low insertion loss, 0.4 dB typ.
- high isolation, 28 dB typ.
- excellent amplitude unbalance, 0.1 dB typ.
- excellent phase unbalance, 0.5 deg. typ.
- very good return loss, VSWR, 1.15:1 typ.
- rugged shielded case

### Applications

- VHF/UHF
- federal & defense communication



Generic photo used for illustration purposes only  
CASE STYLE: K18

Connectors	Model
SMA	ZFSC-2-1WDC-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




### Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		1		750	MHz
Insertion Loss Above 3.0 dB	1-10	--	0.2	0.5	
	10-375	--	0.4	0.8	dB
Isolation	10-375	20	28	--	dB
	375-750	20	25	--	
Phase Unbalance (±)	1-10	--	0.1	2.0	Degree
	10-375	--	0.4	4.0	
Amplitude Unbalance (±)	1-10	--	0.01	0.15	dB
	10-375	--	0.01	0.15	
VSWR (Port S)	1-750	--	1.29	--	:1
VSWR (Port 1-2)	1-750	--	1.22	--	:1

### Typical Performance Data

Frequency (MHz)	Total Loss <sup>2</sup> (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
1	3.21	3.21	0.00	30.82	0.05	1.02	1.09	1.09
5	3.15	3.15	0.00	40.21	0.02	1.01	1.05	1.05
10	3.16	3.15	0.00	40.07	0.02	1.01	1.04	1.04
45	3.19	3.19	0.00	37.20	0.01	1.03	1.05	1.05
100	3.23	3.23	0.00	34.10	0.03	1.06	1.06	1.06
160	3.27	3.26	0.00	32.11	0.06	1.09	1.07	1.07
215	3.30	3.29	0.01	30.39	0.07	1.12	1.08	1.08
265	3.33	3.33	0.01	28.99	0.08	1.15	1.10	1.10
320	3.37	3.36	0.01	27.82	0.09	1.18	1.11	1.11
375	3.42	3.41	0.01	26.82	0.11	1.21	1.13	1.13
415	3.45	3.44	0.01	26.19	0.11	1.23	1.14	1.15
450	3.48	3.47	0.01	25.72	0.11	1.26	1.15	1.16
525	3.55	3.53	0.02	24.93	0.11	1.30	1.18	1.19
600	3.63	3.61	0.02	24.45	0.12	1.35	1.20	1.22
750	3.79	3.76	0.03	24.37	0.07	1.43	1.26	1.28

2. Total Loss = Insertion Loss + 3dB splitter theoretical loss.



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/WCLStore/terms.jsp](http://www.minicircuits.com/WCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR  
ECO-004653  
ZFSC-2-1WDC-S+  
AG/CP/AM  
201020  
Page 2 of 2

# 2 Way-0° Power Splitter/Combiner

# ZFSC-2-1WDC-S+

## Typical Performance Data






FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)		AMP. UNBAL. (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. (Deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
0.3	3.57	3.58	0.01	19.46	0.01	0.3	1.08	1.17	1.17
0.6	3.28	3.28	0.00	26.36	0.05	0.6	1.01	1.11	1.11
0.9	3.22	3.23	0.00	29.86	0.03	0.9	1.02	1.09	1.09
1	3.21	3.21	0.00	30.82	0.05	1	1.02	1.09	1.09
3	3.15	3.15	0.00	38.70	0.00	3	1.02	1.05	1.05
5	3.15	3.15	0.00	40.21	0.02	5	1.01	1.05	1.05
7	3.15	3.15	0.00	40.42	0.02	7	1.01	1.05	1.05
10	3.16	3.15	0.00	40.07	0.02	10	1.01	1.04	1.04
15	3.16	3.16	0.00	39.34	0.00	15	1.01	1.04	1.04
30	3.18	3.18	0.00	38.29	0.03	30	1.02	1.05	1.05
45	3.19	3.19	0.00	37.20	0.01	45	1.03	1.05	1.05
65	3.21	3.20	0.00	36.19	0.02	65	1.04	1.05	1.05
80	3.22	3.21	0.00	35.70	0.03	80	1.05	1.05	1.05
100	3.23	3.23	0.00	34.10	0.03	100	1.06	1.06	1.06
110	3.23	3.23	0.00	33.60	0.03	110	1.06	1.06	1.06
135	3.25	3.25	0.00	33.27	0.04	135	1.08	1.06	1.06
160	3.27	3.26	0.00	32.11	0.06	160	1.09	1.07	1.07
185	3.28	3.28	0.00	31.32	0.05	185	1.10	1.07	1.07
215	3.30	3.29	0.01	30.39	0.07	215	1.12	1.08	1.08
240	3.32	3.31	0.01	29.64	0.07	240	1.13	1.09	1.09
265	3.33	3.33	0.01	28.99	0.08	265	1.15	1.10	1.10
295	3.36	3.35	0.01	28.31	0.08	295	1.16	1.10	1.11
320	3.37	3.36	0.01	27.82	0.09	320	1.18	1.11	1.11
345	3.40	3.39	0.01	27.37	0.08	345	1.19	1.12	1.12
375	3.42	3.41	0.01	26.82	0.11	375	1.21	1.13	1.13
380	3.42	3.41	0.01	26.75	0.11	380	1.21	1.13	1.14
415	3.45	3.44	0.01	26.19	0.11	415	1.23	1.14	1.15
450	3.48	3.47	0.01	25.72	0.11	450	1.26	1.15	1.16
490	3.52	3.50	0.02	25.27	0.11	490	1.28	1.17	1.18
525	3.55	3.53	0.02	24.93	0.11	525	1.30	1.18	1.19
565	3.59	3.57	0.02	24.63	0.11	565	1.33	1.19	1.21
600	3.63	3.61	0.02	24.45	0.12	600	1.35	1.20	1.22
635	3.67	3.64	0.02	24.28	0.12	635	1.37	1.22	1.24
675	3.71	3.68	0.02	24.20	0.11	675	1.39	1.23	1.25
710	3.75	3.72	0.03	24.24	0.09	710	1.41	1.24	1.27
750	3.79	3.76	0.03	24.37	0.07	750	1.43	1.26	1.28
760	3.80	3.77	0.03	24.42	0.06	760	1.43	1.26	1.29
820	3.87	3.84	0.03	24.96	0.02	820	1.46	1.28	1.31
880	3.95	3.91	0.03	25.97	0.04	880	1.47	1.30	1.33
940	4.02	3.98	0.04	27.93	0.15	940	1.48	1.31	1.34
1000	4.10	4.07	0.03	31.41	0.30	1000	1.47	1.32	1.35

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss


# 2 Way-0° Power Splitter/Combiner

# ZFSC-2-1WDC-S+

## Typical Performance Curves



### Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
K18	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	--	--	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT. GRAMS
K18	.75 (19.05)	.07 (1.78)	70.0

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

#### Notes:

- Case material: Aluminum alloy.
- Case finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number.
- For port marking 1, 2, and 3 see specifications data sheet.
- For bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.
- Refer to the individual model data sheet for the type of connectors available.

**Mini-Circuits®**

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I