



COAXIAL

High Power Amplifier


ZHL-1-2W+ ZHL-1-2WX+

Mini-Circuits

50Ω 2W 5 to 500 MHz

FEATURES

- Wideband, 5 to 500 MHz
- High Power Output, +33 dBm min.
- High Gain, +29 dB min.
- High IP3, +44 dBm typ.
- Good matching VSWR, 1.5:1



Generic photo used for illustration purposes only

Case Style: T35

APPLICATIONS

- VHF/UHF
- Instrumentation
- Laboratory

| Connectors | Model No |
|------------|--------------------|
| BNC | ZHL-1-2W+ (shown) |
| BNC | ZHL-1-2WX+ (shown) |
| SMA | ZHL-1-2W-S+ |
| SMA | ZHL-1-2WX-S+ |
| N-TYPE | ZHL-1-2W-N+ |
| N-TYPE | ZHL-1-2WX-N+ |

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter | Condition (MHz) | ZHL-1-2W+ ZHL-1-2WX+ [▲] | | | Units |
|------------------------------------|-----------------|--------------------------------------|------|------|-------|
| | | Min. | Typ. | Max. | |
| Frequency Range | | 5 | — | 500 | MHz |
| Gain | 5-500 | 29 | — | — | dB |
| Gain Flatness | 5-500 | — | — | ±1.0 | dB |
| Output Power at 1dB compression | 5-500 | +33 | — | — | dBm |
| Noise Figure | 5-500 | — | 7.0 | — | dB |
| Output third order intercept point | 5-500 | — | +44 | — | dBm |
| Input VSWR | 5-500 | — | 1.5 | — | :1 |
| Output VSWR | 5-500 | — | 1.5 | — | :1 |
| DC Supply Voltage | | — | 24 | — | V |
| Supply Current | | — | — | 0.9 | A |

Open load is not recommended, potentially can cause damage.
With no load derate max. input power by 20 dB.

[▲] Heat sink not included. Alternative heat sinking and heat removal must be provided by the user to limit maximum base-plate temperature to 85°C, in order to ensure proper performance. For reference, this requires thermal resistance of user's external heat sink to be 1.0°C/W max.

ABSOLUTE MAXIMUM RATINGS

| Parameter | Ratings |
|----------------------------|-----------------|
| Operating Temperature | -20°C to +65°C |
| Storage Temperature | -55°C to +100°C |
| DC Voltage | +25V |
| Input RF Power (no damage) | +10 dBm |

Permanent damage may occur if any of these limits are exceeded.

REV. F
ECO-017840
ZHL-1-2W+
MCL NY
230516





COAXIAL


High Power Amplifier

ZHL-1-2W+ ZHL-1-2WX+


Mini-Circuits

50Ω 2W 5 to 500 MHz

OUTLINE DRAWING FOR MODELS WITH HEATSINK



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



OUTLINE DIMENSIONS (Inch mm)

| A | B | C | D | E | F | G | H | J | K | L | M | N | P | Q | R | S | T | wt |
|--------|-------|-------|------|--------|------|-------|------|-------|------|-------|-------|-------|------|------|--------|-------|--------|--------|
| 4.75 | 2.00 | 2.37 | .19 | 4.375 | .23 | 1.540 | .144 | .58 | .34 | .50 | 1.50 | 1.00 | .13 | .38 | 4.00 | 1.50 | 5.0 | grams* |
| 120.65 | 50.80 | 60.20 | 4.83 | 111.13 | 5.84 | 39.12 | 3.66 | 14.73 | 8.64 | 12.70 | 38.10 | 25.40 | 3.30 | 9.65 | 101.60 | 38.10 | 127.00 | 700 |

*300 grams without heatsink



COAXIAL

High Power Amplifier






ZHL-1-2W+ ZHL-1-2WX+

Mini-Circuits

50Ω 2W 5 to 500 MHz

TYPICAL PERFORMANCE DATA/CURVES

| FREQUENCY (MHz) | GAIN (dB) | | | DIRECTIVITY (dB) | | | VSWR (:1) | | NOISE FIGURE (dB) | P _{OUT} at 1 dB COMPR. (dBm) |
|-----------------|-----------|-------|-------|------------------|-------|-------|-----------|------|-------------------|---------------------------------------|
| | 23V | 24V | 24.5V | 23V | 24V | 24.5V | IN | OUT | | |
| 5.00 | 32.84 | 32.87 | 32.92 | 25.30 | 26.00 | 26.10 | 1.12 | 1.51 | | 34.98 |
| 11.30 | 32.45 | 32.47 | 32.50 | 25.90 | 26.70 | 26.00 | 1.10 | 1.49 | 6.11 | 35.08 |
| 33.40 | 32.41 | 32.42 | 32.45 | 25.80 | 23.80 | 24.30 | 1.16 | 1.49 | 6.06 | 35.42 |
| 98.80 | 33.72 | 33.78 | 33.83 | 24.90 | 25.40 | 22.60 | 1.28 | 1.43 | 5.63 | 35.07 |
| 195.40 | 34.00 | 34.10 | 34.19 | 21.90 | 21.60 | 22.50 | 1.41 | 1.18 | 5.82 | 34.36 |
| 246.20 | 33.64 | 33.73 | 33.84 | 20.00 | 19.90 | 19.50 | 1.45 | 1.11 | 5.95 | 34.34 |
| 309.60 | 33.47 | 33.57 | 33.67 | 17.10 | 17.70 | 18.00 | 1.48 | 1.19 | 6.09 | 35.54 |
| 373.10 | 33.77 | 33.89 | 34.02 | 15.90 | 16.10 | 17.60 | 1.51 | 1.29 | 6.45 | 34.85 |
| 436.50 | 33.15 | 33.35 | 33.54 | 17.60 | 17.20 | 17.60 | 1.56 | 1.37 | 6.98 | 34.71 |
| 500.00 | 32.49 | 32.80 | 33.14 | 22.50 | 20.60 | 20.80 | 1.59 | 1.57 | 7.28 | 33.90 |



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Amplifier

ZHL-1-2W+

Typical Performance Data

| FREQUENCY (MHz) | GAIN (dB) | | | DIRECTIVITY (dB) | | | VSWR IN (:1) | VSWR OUT (:1) | NOISE FIGURE (dB) | Pout at 1dB Comp. (dBm) |
|--------------------|--------------|-------|-------|---------------------|-------|-------|--------------------|---------------------|-------------------------|-------------------------------|
| | 23V | 24V | 24.5V | 23V | 24V | 24.5V | 24V | 24V | 24V | 24V |
| 5.0 | 32.84 | 32.87 | 32.92 | 25.30 | 26.00 | 26.10 | 1.25 | 1.33 | | 34.98 |
| 11.3 | 32.45 | 32.47 | 32.50 | 25.90 | 26.70 | 26.00 | 1.07 | 1.32 | 6.11 | 35.08 |
| 33.4 | 32.41 | 32.42 | 32.45 | 25.80 | 23.80 | 24.30 | 1.16 | 1.32 | 6.06 | 35.42 |
| 98.8 | 33.72 | 33.78 | 33.83 | 24.90 | 25.40 | 22.60 | 1.58 | 1.33 | 5.63 | 35.07 |
| 195.4 | 34.00 | 34.10 | 34.19 | 21.90 | 21.60 | 22.50 | 1.77 | 1.22 | 5.82 | 34.36 |
| 246.2 | 33.64 | 33.73 | 33.84 | 20.00 | 19.90 | 19.50 | 1.86 | 1.24 | 5.95 | 34.34 |
| 309.6 | 33.47 | 33.57 | 33.67 | 17.10 | 17.70 | 18.00 | 1.82 | 1.76 | 6.09 | 35.54 |
| 373.1 | 33.77 | 33.89 | 34.02 | 15.90 | 16.10 | 17.60 | 1.46 | 1.95 | 6.45 | 34.85 |
| 436.5 | 33.15 | 33.35 | 33.54 | 17.60 | 17.20 | 17.60 | 1.15 | 1.54 | 6.98 | 34.71 |
| 500.0 | 32.49 | 32.80 | 33.14 | 22.50 | 20.60 | 20.80 | 1.83 | 1.81 | 7.28 | 33.90 |



ISO 9001 ISO 14001 AS 9100 CERTIFIED






P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

IF/RF MICROWAVE COMPONENTS


For detailed performance specs & shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.


Typical Performance Curves



Outline Dimensions



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



| CASE# | A | B | C | D | E | F | G | H | J | K | L | M | N |
|-------|------------------|-----------------|-----------------|---------------|-------------------|---------------|------------------|----------------|----------------|---------------|----------------|-----------------|-----------------|
| T35 | 4.75 (120.65) | 2.00 (50.80) | 2.37 (60.20) | .19 (4.83) | 4.375 (111.13) | .23 (5.84) | 1.540 (39.12) | .144 (3.66) | .58 (14.73) | .34 (8.64) | .50 (12.70) | 1.50 (38.10) | 1.00 (25.40) |

| CASE# | P | Q | R | S | T | WT. GRAMS | WT. WITHOUT HEATSINK GRAMS |
|-------|---------------|---------------|------------------|-----------------|------------------|-----------|----------------------------|
| T35 | .13 (3.30) | .38 (9.65) | 4.00 (101.60) | 1.50 (38.10) | 5.00 (127.00) | 700.0 | 300.0 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish, mounting bracket finish, and baseplate finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Heat sink finish: Black anodize if supplied with heat sink..



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|---------------------------|---------------------------------------|--|
| Operating Temperature | -20° to 65° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Stabilization Bake | (non-operating) 125°C, 24 hours | - - - |
| Burn-in at Elevated Temp. | (DC on) 160 hours at 85° C | MIL-STD-202, Method 108 |
| Thermal Shock | -55° to 100°C, 5 cycles | MIL-STD-202, Method 107, Condition A, except 100°C |