



COAXIAL High Power Amplifier

ZHL-1000-3W+ ZHL-1000-3WX+

50Ω 3W 500 to 1000 MHz

FEATURES

- High Power, 3 Watt
- Wideband, 500 to 1000 MHz
- High Power Output, +35dBm Min.
- High IP3, +45 dBm typ.
- High Gain, 43 dB typ.
- Protected by US Patent, 6,943,629

APPLICATIONS

- VHF
- Cellular
- Instrumentation
- Laboratory



Generic photo used for illustration purposes only

| | | |
|-------------------|--------------|----------------------------|
| Model No. | ZHL-1000-3W+ | ZHL-1000-3WX+ [▲] |
| Case Style | DDD131 | |
| Connectors | SMA | |

+RoHS Compliant
The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS

| Parameter | Min. | Typ. | Max. | Units |
|------------------------------------|------|------|------|-------|
| Frequency Range | 500 | — | 1000 | MHz |
| Gain | 38 | — | — | dB |
| Gain Flatness ¹ | — | — | ±1.0 | dB |
| Output Power at 1dB compression | +35 | +37 | — | dBm |
| Noise Figure | — | 3.5 | — | dB |
| Output third order intercept point | — | +45 | — | dBm |
| Input VSWR | — | 2.0 | — | :1 |
| Output VSWR | — | 2.5 | — | :1 |
| DC Supply Voltage | — | 24 | — | V |
| Supply Current | — | — | 2.25 | A |

1. 1.5 dB over temperature range -20°C to +65°C.

[▲] Heat sink not included. Alternative heat sinking and heat removal must be provided by the user to limit maximum base-plate temperature to 75°C, in order to ensure proper performance. For reference, this requires thermal resistance of user's external heat sink to be 0.8°C/W max.

ABSOLUTE MAXIMUM RATINGS

| Parameter | Ratings |
|----------------------------|-----------------|
| Operating Temperature | -20°C to +65°C |
| Storage Temperature | -55°C to +100°C |
| Base Plate Temperature | +75°C |
| DC Voltage | +25V |
| Input RF Power (no damage) | 0 dBm |

Permanent damage may occur if any of these limits are exceeded.





COAXIAL


High Power Amplifier

ZHL-1000-3W+ ZHL-1000-3WX+


Mini-Circuits

50Ω 3W 500 to 1000 MHz

OUTLINE DRAWING



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



OUTLINE DIMENSIONS (Inch mm)

| A | B | C | D | E | F | G | H | J | K | L | M | N | P | Q | R | S | T | wt |
|--------|-------|-------|------|--------|------|-------|------|-------|-------|-------|-------|-------|------|-------|--------|-------|--------|--------|
| 7.00 | 3.25 | 3.13 | .25 | 6.500 | .38 | 2.500 | .156 | .88 | .43 | .62 | 1.00 | 2.63 | .125 | .50 | 6.00 | 2.23 | 8.35 | grams* |
| 177.80 | 82.55 | 79.50 | 6.35 | 165.10 | 9.65 | 63.50 | 3.96 | 22.35 | 10.92 | 15.75 | 25.40 | 66.80 | 3.18 | 12.70 | 152.40 | 56.64 | 212.09 | 1780 |

*510 grams without heatsink











COAXIAL High Power Amplifier

ZHL-1000-3W+ ZHL-1000-3WX+

50Ω 3W 500 to 1000 MHz

TYPICAL PERFORMANCE DATA AND CHARTS

| FREQUENCY (MHz) | GAIN (dB) | | | DIRECTIVITY (dB) | VSWR (:1) | | NOISE FIGURE (dB) | P _{OUT} at 1 dB COMPR. (dBm) | IP ₃ (dBm) |
|-----------------|-----------|-------|-------|------------------|-----------|------|-------------------|---------------------------------------|-----------------------|
| | 23V | 24V | 24.5V | | 24V | IN | | | |
| 500.00 | 43.44 | 43.51 | 43.57 | 33.21 | 1.64 | 1.22 | 3.60 | 37.59 | 47.32 |
| 550.00 | 43.44 | 43.53 | 43.60 | 39.42 | 1.53 | 1.32 | 3.63 | 37.59 | 47.36 |
| 600.00 | 43.64 | 43.73 | 43.81 | 35.50 | 1.30 | 1.52 | 3.63 | 37.77 | 47.29 |
| 650.00 | 43.49 | 43.57 | 43.66 | 34.29 | 1.21 | 1.63 | 3.57 | 37.75 | 46.09 |
| 700.00 | 43.86 | 43.93 | 44.01 | 34.55 | 1.30 | 1.74 | 3.61 | 37.08 | 45.12 |
| 750.00 | 44.17 | 44.23 | 44.31 | 44.04 | 1.34 | 1.77 | 3.53 | 36.75 | 44.66 |
| 800.00 | 44.48 | 44.54 | 44.62 | 38.17 | 1.31 | 1.77 | 3.46 | 36.78 | 44.74 |
| 850.00 | 44.65 | 44.70 | 44.77 | 52.63 | 1.30 | 1.77 | 3.50 | 36.31 | 45.06 |
| 900.00 | 44.73 | 44.78 | 44.84 | 45.00 | 1.34 | 1.81 | 3.53 | 36.72 | 44.83 |
| 950.00 | 44.86 | 44.91 | 44.98 | 53.07 | 1.33 | 1.86 | 3.53 | 36.50 | 44.91 |
| 1000.00 | 44.89 | 44.95 | 45.04 | 42.88 | 1.19 | 1.88 | 3.55 | 36.24 | 44.26 |



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Coaxial High Power Amplifier

ZHL-1000-3W+

Typical Performance Data

| FREQ. (MHz) | GAIN (dB) | | | DIRECTIVITY 24V | VSWR (:1) | | NOISE FIGURE (dB) 24V | POUT @ 1 dB COMPRESSION (dBm) 24V | OUTPUT IP3 (dBm) 24V |
|----------------|--------------|-------|-------|--------------------|-----------|------------|--------------------------------|--|----------------------------|
| | 23V | 24V | 25V | | IN 24V | OUT 24V | | | |
| 300 | 44.10 | 44.04 | 44.00 | 32.58 | 1.53 | 4.24 | 3.60 | 31.60 | 47.04 |
| 350 | 44.45 | 44.42 | 44.40 | 37.32 | 1.57 | 2.78 | 3.61 | 33.99 | 48.36 |
| 400 | 44.12 | 44.13 | 44.13 | 33.32 | 1.66 | 1.90 | 3.71 | 35.86 | 47.83 |
| 450 | 43.69 | 43.74 | 43.77 | 37.94 | 1.70 | 1.39 | 3.64 | 37.36 | 47.62 |
| 500 | 43.44 | 43.51 | 43.57 | 33.21 | 1.64 | 1.22 | 3.60 | 37.59 | 47.32 |
| 550 | 43.44 | 43.53 | 43.60 | 39.42 | 1.53 | 1.32 | 3.63 | 37.59 | 47.36 |
| 600 | 43.64 | 43.73 | 43.81 | 35.50 | 1.30 | 1.52 | 3.63 | 37.77 | 47.29 |
| 650 | 43.49 | 43.57 | 43.66 | 34.29 | 1.21 | 1.63 | 3.57 | 37.75 | 46.09 |
| 700 | 43.86 | 43.93 | 44.01 | 34.55 | 1.30 | 1.74 | 3.61 | 37.08 | 45.12 |
| 750 | 44.17 | 44.23 | 44.31 | 44.04 | 1.34 | 1.77 | 3.53 | 36.75 | 44.66 |
| 800 | 44.48 | 44.54 | 44.62 | 38.17 | 1.31 | 1.77 | 3.46 | 36.78 | 44.74 |
| 850 | 44.65 | 44.70 | 44.77 | 52.63 | 1.30 | 1.77 | 3.50 | 36.31 | 45.06 |
| 900 | 44.73 | 44.78 | 44.84 | 45.00 | 1.34 | 1.81 | 3.53 | 36.72 | 44.83 |
| 950 | 44.86 | 44.91 | 44.98 | 53.07 | 1.33 | 1.86 | 3.53 | 36.50 | 44.91 |
| 1000 | 44.89 | 44.95 | 45.04 | 42.88 | 1.19 | 1.88 | 3.55 | 36.24 | 44.26 |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site









The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS


REV. OR
ZHL-1000-3W+
11/9/2018
Page 1 of 1

Typical Performance Curves




Outline Dimensions

DDD131



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



| CASE# | A | B | C | D | E | F | G | H | J | K | L | M | N |
|--------|------------------|-----------------|-----------------|---------------|-------------------|---------------|------------------|----------------|----------------|----------------|----------------|-----------------|-----------------|
| DDD131 | 7.00 (177.80) | 3.25 (82.55) | 3.13 (79.50) | .25 (6.35) | 6.500 (165.10) | .38 (9.65) | 2.500 (63.50) | .156 (3.96) | .88 (22.35) | .43 (10.92) | .62 (15.75) | 1.00 (25.40) | 2.63 (66.68) |

| CASE# | P | Q | R | S | T | WT. GRAMS | WT. WITHOUT HEATSINK GRAMS |
|--------|----------------|----------------|------------------|-----------------|------------------|-----------|----------------------------|
| DDD131 | .125 (3.18) | .50 (12.70) | 6.00 (152.40) | 2.23 (56.64) | 8.35 (212.09) | 1780 | 510 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heatsink finish: Black anodize if supplied with heatsink.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|---------------------------|---------------------------------------|--|
| Operating Temperature | -20° to 65° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Stabilization Bake | (non-operating) 125°C, 24 hours | - - - |
| Burn-in at Elevated Temp. | (DC on) 160 hours at 85° C | MIL-STD-202, Method 108 |
| Thermal Shock | -55° to 100°C, 5 cycles | MIL-STD-202, Method 107, Condition A, except 100°C |