


Suspended Substrate Stripline Filters and Multiplexers

50Ω DC to 26 GHz

The Big Deal

- Low insertion loss
- Ultra-wide passband width
- Fast roll-off with wide stopband
- Good power handling and temperature stability
- Passband up to 26 GHz
- Stopband up to 26.5 GHz can extend to 40 GHz



Product Overview

Mini-Circuits' Suspended Substrate Stripline filters offer low insertion loss by implementing printed circuit board suspended between two parallel ground planes, providing high Q. Low insertion loss combined with wide stopband makes them an excellent choice for wideband instruments and systems like ECM, ECCM, ELINT and ultra-broadband receivers.

Low pass, high pass, band pass, band stop, diplexer and multiplexer designs can be realized with this technology. Advanced filter design and construction can achieve stopband width greater than 6x the center frequency, and temperature stability will be better than other printed circuit realizations because the fields are mainly in the air rather than in a dielectric. The inside walls of the housing hold the circuit and prevent movement that could be caused by vibration or mechanical shock, making these designs excellent candidates for harsh operating environments.

Suspended substrate stripline filters can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitters
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide, spur-free stop band results in better receiver sensitivity
High power handling	Well suited for transmitter applications
Excellent temperature stability	Ensures minimal variation in electrical performance across temperature

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Suspended substrate stripline High Pass Filter

ZHSS-8G-S+

50Ω 8000 to 24000 MHz



Generic photo used for illustration purposes only

CASE STYLE: RP2464

Connectors	Model
SMA-M	ZHSS-8G-S+

Features

- Wider passband
- Low insertion loss
- Sharp rejection
- Connectorized package

Applications

- Satellite communications
- Transmitter / Receiver
- X-band Radar
- KU-band Satellites

Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Stop Band	Rejection Loss	DC-F1	DC-4000	60	85	-	dB
		F1-F2	4000-5300	40	50	-	dB
		F2-F3	5300-5800	20	30	-	dB
Pass Band	VSWR	DC-F3	DC-5800	-	20	-	:1
	Insertion Loss	F4-F5	8000-24000	-	1	2	dB
	VSWR	F4-F5	8000-24000	-	2	-	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	3 W @ 25°C

Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	99.20	19157.23
100	90.65	6188.96
1000	101.93	629.55
2500	91.16	205.38
4000	88.11	119.10
5300	76.20	85.04
5800	55.95	68.97
6000	48.29	60.82
6450	30.19	36.74
6650	21.37	23.94
6900	9.62	8.08
7050	3.93	2.80
7500	1.04	1.14
8000	0.94	1.51
9000	0.91	1.71
10000	0.67	1.53
12500	0.42	1.21
15000	0.76	1.80
20000	0.64	1.53
24000	0.71	1.68

Functional Schematic







Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.C
ECO-008564
ZHSS-8G-S+
EDU2657/1
URJ
210629
Page 2 of 3

Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Male

Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F	G	H	J	K	Wt.
Max	Max	Max	-	-	-	-	-	-	-	-
.70	.50	.50	.25	.25	.43	.350	.25	.170	.065	grams
17.78	12.70	12.70	6.35	6.35	10.92	8.89	6.35	4.32	1.65	30

Note: Please refer to case style drawing for details

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Suspended substrate stripline High Pass Filter





ZHSS-8G-S+

Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
10	99.20	0.00	0.00	8000	0.41
50	82.83	0.00	0.00	8250	0.38
150	99.74	0.00	0.00	8500	0.36
250	93.14	0.01	0.01	8750	0.34
750	103.44	0.02	0.02	9000	0.32
1250	105.10	0.04	0.04	9250	0.31
1500	105.67	0.05	0.05	9500	0.30
1750	101.96	0.06	0.06	9750	0.29
2000	96.68	0.06	0.07	10000	0.28
2250	94.84	0.08	0.08	10250	0.27
2500	91.16	0.08	0.09	10500	0.26
2750	90.53	0.09	0.10	10750	0.25
3000	89.85	0.11	0.11	11000	0.25
3250	90.05	0.12	0.12	11250	0.24
3500	88.20	0.13	0.13	11500	0.24
3750	88.19	0.14	0.14	11750	0.23
4000	88.11	0.15	0.15	12000	0.23
4250	86.76	0.15	0.16	12250	0.22
4500	90.82	0.16	0.16	12500	0.22
4750	89.56	0.18	0.17	12750	0.22
5000	92.78	0.18	0.18	13000	0.21
5250	78.24	0.20	0.20	13250	0.21
5300	76.20	0.20	0.20	13500	0.21
5500	67.53	0.22	0.22	13750	0.21
5750	57.93	0.25	0.24	14000	0.21
5800	55.95	0.25	0.25	14250	0.21
6000	48.29	0.29	0.28	14500	0.21
6250	38.44	0.36	0.36	14750	0.20
6450	30.19	0.47	0.46	15000	0.20
6500	28.04	0.52	0.51	15250	0.20
6650	21.37	0.73	0.69	15500	0.20
6700	19.06	0.84	0.79	15750	0.20
6900	9.62	2.16	1.96	16000	0.20
7000	5.48	4.42	3.98	16250	0.20
7050	3.93	6.48	5.80	16500	0.19
7100	2.82	9.41	8.31	16750	0.19
7500	1.04	23.72	28.64	17000	0.19
7750	0.92	17.97	18.78	17250	0.19
8000	0.94	13.81	14.09	17500	0.18
9000	0.91	11.65	11.67	17750	0.18
10000	0.67	13.63	13.62	18000	0.18
11000	0.44	22.80	22.14	18250	0.18
12000	0.41	25.84	22.87	18500	0.18
13000	0.44	17.68	17.39	18750	0.18
14000	0.56	13.05	13.05	19000	0.19
15000	0.76	10.90	10.56	19250	0.19
16000	0.69	12.46	11.83	19500	0.19
17000	0.41	27.14	23.22	19750	0.19
18000	0.60	12.81	12.76	20000	0.19
19000	0.88	9.93	9.86	20250	0.19
20000	0.64	13.64	13.40	20500	0.19
20500	0.48	21.27	20.70	20750	0.18
21000	0.47	24.71	22.56	21000	0.18
21500	0.62	14.67	14.02	21500	0.17
22000	0.83	11.06	10.74	22000	0.18
22500	0.96	9.76	9.54	22500	0.18
23000	0.96	9.58	9.51	23000	0.19
23500	0.86	10.28	10.43	23500	0.20
23750	0.79	11.01	11.28	23750	0.20
24000	0.71	11.95	12.41	24000	0.20




Typical Performance Curves



Outline Dimensions

RP2464



CASE#	A	B	C	D	E	F	G	H	J	K	WT. GRAMS
	(Max)	(Max)	(Max)								
RP2464	.70 (17.8)	.50 (12.7)	.50 (12.7)	.25 (6.4)	.25 (6.4)	.43 (10.9)	.350 (8.89)	.25 (6.4)	.170 (4.32)	.065 (1.65)	30

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .10$; 3 Pl. $\pm .015$

Notes:

1. Case material: Brass.
2. Case finish: Powder coated over silver plating
3. Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A