SUSPENDED SUBSTRATE STRIPLINE COAXIAL

High Pass Filter

ZHSS-V26G+

50Ω 26 to 50 GHz 2.4mm Female

KEY FEATURES

- Insertion Loss, 1.3 dB Typ.
- High Rejection, 80 dB Typ.
- Wide Passband up to 50 GHz




Generic photo used for illustration purposes only

APPLICATIONS

- 5G Applications
- Satellite Communication
- Military Radar

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' Suspended Substrate Stripline filters offer low insertion loss combined with wide stopband, good power handling & temperature stability, small form factor with rugged build ideal for harsh operating environments making them an excellent choice for wideband instruments and systems like ECM, ECCM, ELINT and ultrabroadband receivers. Low pass, high pass, band pass, diplexer and multiplexer designs can be realized with this technology with passband, stopband up to 50GHz and stopband width greater than 6x cutoff frequency.

ELECTRICAL SPECIFICATIONS AT +25°C


Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Pass Band	Insertion Loss	F4-F5	26 - 45	—	1.3	2.5	dB
		F5-F6	45 - 50	—	1.5	—	
	Return Loss	F4-F6	26 - 50	—	9.5	—	dB
Stop Band	Rejection	DC-F1	DC - 16	60	80	—	dB
		F1-F2	16 - 18	40	60	—	
		F2-F3	18 - 20	20	40	—	

ABSOLUTE MAXIMUM RATINGS[1]

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Input Power[2]	1 W @ 25°C

1. Permanent damage may occur if any of these limits are exceeded.
2. Power rating applies only to signals within the passband.

TYPICAL FREQUENCY RESPONSE




REV. A
ECO-030019
EDU5243
ZHSS-V26G+
MCINU
260630


High Pass Filter


ZHSS-V26G+


50Ω 26 to 50 GHz 2.4mm Female

TYPICAL PERFORMANCE GRAPHS









High Pass Filter

ZHSS-V26G+


50Ω 26 to 50 GHz 2.4mm Female

CONNECTOR DESCRIPTION

Function	Connector
RF1[3]	2.4mm Female
RF2[3]	2.4mm Female

3. This filter is bi-directional, RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

CASE STYLE DRAWING



Unit Weight: 21 grams.
Dimensions are in inches [mm]. Tolerances: 2 Pl. ± 0.06 [1.5]; 3 Pl. ± 0.015 [0.38].

PRODUCT MARKING*: ZHSS-V26G+

*Marking may contain other features or characters for internal lot control.

High Pass Filter

ZHSS-V26G+

50Ω 26 to 50 GHz 2.4mm Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	BCB3876
RoHs Status	Compliant
Environmental Ratings	ENV001

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Suspended substrate stripline

Coaxial High Pass Filter

ZHSS-V26G+


Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss
(MHz)	(dB)	(dB)	(dB)
10	79.44	0.00	0.00
20	95.46	0.00	0.00
40	92.15	0.00	0.00
100	99.62	0.00	0.00
150	115.83	0.00	0.00
200	103.60	0.00	0.00
250	98.47	0.00	0.00
400	95.44	0.00	0.00
500	95.60	0.00	0.00
800	102.62	0.00	0.00
900	95.71	0.00	0.00
1000	93.44	0.00	0.00
1500	95.19	0.00	0.00
2000	101.72	0.01	0.01
2500	92.08	0.02	0.02
3000	103.68	0.03	0.03
3500	100.53	0.04	0.05
4000	110.16	0.05	0.06
4500	108.45	0.07	0.08
5000	97.23	0.10	0.10
5500	97.96	0.12	0.13
6000	104.65	0.14	0.15
6500	97.45	0.17	0.18
6700	99.00	0.18	0.19
7000	110.71	0.20	0.20
8000	104.81	0.26	0.26
9000	103.98	0.33	0.32
10000	100.08	0.41	0.40
14000	110.61	0.68	0.70
16000	83.98	0.64	0.66
18000	64.06	0.36	0.37
20000	42.47	0.23	0.25
22000	16.32	1.46	1.23
24000	1.59	15.31	13.94
26000	1.13	21.58	19.55
28000	1.11	15.28	17.28
30000	0.98	23.22	22.57
31000	1.07	15.65	17.03
32000	1.06	14.26	14.52
33000	1.02	15.63	14.78
34000	0.95	20.67	17.38
35000	0.92	31.07	21.89
36000	1.01	21.34	21.90
37000	1.10	17.05	18.05
40000	1.10	14.72	14.58
41000	1.03	18.65	18.11
41500	1.00	22.80	21.97
42000	1.01	25.59	26.68
42100	1.01	25.26	26.83
43000	1.08	17.79	18.72
43700	1.15	15.28	15.59
45000	1.13	15.71	15.69
45500	1.08	17.51	17.49
46000	1.03	20.26	20.60
46500	0.99	23.51	25.80
47000	0.99	25.07	38.86
47500	1.00	23.74	34.01
48000	1.04	22.81	26.93
49000	1.10	23.93	23.58
50000	1.12	33.76	24.06


FREQ.	Group Delay
(MHz)	(ns)
26000	0.23
26500	0.22
27000	0.21
27500	0.20
28000	0.20
28500	0.19
29000	0.19
29500	0.19
30000	0.18
30100	0.18
30200	0.18
30400	0.18
30600	0.18
30800	0.18
31000	0.17
31200	0.17
31400	0.17
31600	0.17
31800	0.17
32000	0.17
32200	0.17
32400	0.17
32600	0.17
32800	0.17
33000	0.17
34000	0.16
34500	0.16
35000	0.16
35500	0.16
36000	0.16
36500	0.16
37000	0.15
37500	0.15
38000	0.15
38500	0.15
39000	0.15
39500	0.15
40000	0.15
40500	0.15
41000	0.15
41500	0.15
42000	0.15
42500	0.15
43000	0.15
43500	0.15
44000	0.15
44500	0.14
45000	0.15
45500	0.15
45800	0.15
46000	0.15
46200	0.15
46400	0.15
46600	0.15
46800	0.15
47000	0.15
47500	0.15
48000	0.15
49000	0.15
50000	0.15

Typical Performance Curves


INSERTION LOSS
INPUT POWER = 0 dBm




INPUT RETURN LOSS
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS
INPUT POWER = 0 dBm




GROUP DELAY
INPUT POWER = 0 dBm



Case Style BCB

Outline Dimensions BCB3876



Dimensions are in inches [mm]. Tolerances: 2 Pl. ± 0.06 [1.5]; 3 Pl. ± 0.015 [0.38].

Notes:

1. Case material: Brass.
2. Case Finish: Powder coating.
3. Unit Weight: 21 grams.
4. Refer to the individual model data sheet for the type of connectors available.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Mini-Circuits

Environmental Specifications ENV001

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet

This document and its contents are the property of Mini-Circuits.