

Coaxial Amplifier

50Ω Low Power 20 to 6000 MHz

ZJL-6G+



Generic photo used for illustration purposes only

CASE STYLE: BW459
 Connectors Model
 SMA ZJL-6G+

+RoHS Compliant
 The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Features

- ultra wideband, 20 to 6000 MHz
- compact rugged case, 1.07"x 0.61" (including mounting bracket)
- protected by US Patent, 6,943,629

Applications

- communications systems
- radar
- instrumentation
- laboratory use

Amplifier Electrical Specifications

| MODEL NO. | FREQUENCY (MHz) | | GAIN (dB) | | | MAXIMUM POWER (dBm) | | | DYNAMIC RANGE | | VSWR (:1) Typ. | | DC POWER | |
|-----------|-----------------|-------|-----------|------|----------------------------|----------------------|-----|-------------------|---------------|----------------|----------------|-----|---------------|-------------------|
| | f_L | f_U | Typ. | Min. | Flatness ¹ Typ. | Output (1 dB Compr.) | | Input (no damage) | NF (dB) Typ. | IP3 (dBm) Typ. | In | Out | Volt (V) Nom. | Current (mA) Max. |
| ZJL-6G+ | 20 | 6000 | 13 | 10 | ±1.6 | +9 | +10 | +15 | 4.5 | +24 | 1.5 | 1.4 | 12 | 50 |

1. Flatness specified to 0.75 fU, dynamic range at 2 GHz.

Open load is not recommended, potentially can cause damage.
 With no load derate max input power by 20 dB

L= low range (f_L to $f_U/2$)

U= upper range ($f_U/2$ to f_U)

Maximum Ratings


Operating Temperature -40°C to 75°C

Storage Temperature -55°C to 100°C

DC Voltage +13V Max.

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



Outline Dimensions (inch/mm)

| A | B | C | D | E | F | G | H | J | K | L | M | N | P | wt |
|-------|-------|-------|------|------|------|------|------|-------|-------|------|------|-------|------|-------|
| 1.00 | .75 | .61 | .38 | .29 | .25 | .26 | .35 | .65 | .688 | .156 | .13 | 1.07 | .140 | grams |
| 25.40 | 19.05 | 15.49 | 9.65 | 7.37 | 6.35 | 6.60 | 8.89 | 16.51 | 17.48 | 3.96 | 3.30 | 27.18 | 3.56 | 25 |

Notes






- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
 M151107
 ZJL-6G+
 200430
 Page 1 of 2

| FREQUENCY (MHz) | GAIN (dB) | | | DIRECTIVITY (dB) | | | VSWR (:1) | | NOISE FIGURE (dB) | POUT at 1 dB COMPR. (dBm) |
|-----------------|-----------|-------|-------|------------------|------|------|-----------|------|-------------------|---------------------------|
| | 9V | 12V | 13V | 9V | 12V | 13V | IN | OUT | | |
| 20.00 | 14.03 | 14.80 | 14.90 | 4.98 | 4.94 | 4.94 | 1.40 | 1.72 | 4.36 | 13.17 |
| 470.00 | 14.06 | 14.84 | 14.94 | 4.90 | 4.82 | 4.83 | 1.37 | 1.64 | 4.20 | 13.31 |
| 920.00 | 13.68 | 14.39 | 14.48 | 5.42 | 5.37 | 5.39 | 1.33 | 1.56 | 4.30 | 13.35 |
| 1370.00 | 13.71 | 14.38 | 14.46 | 5.08 | 4.99 | 4.98 | 1.29 | 1.47 | 4.13 | 13.34 |
| 1820.00 | 13.57 | 14.28 | 14.37 | 5.10 | 4.83 | 4.78 | 1.21 | 1.36 | 4.16 | 13.26 |
| 2120.00 | 13.42 | 14.10 | 14.19 | 5.19 | 4.96 | 4.89 | 1.17 | 1.29 | 4.21 | 13.21 |
| 2570.00 | 12.98 | 13.62 | 13.69 | 5.84 | 5.55 | 5.48 | 1.16 | 1.24 | 4.35 | 13.20 |
| 3020.00 | 12.65 | 13.16 | 13.21 | 6.20 | 6.09 | 6.05 | 1.19 | 1.27 | 4.33 | 13.24 |
| 3470.00 | 12.32 | 12.81 | 12.86 | 6.55 | 6.36 | 6.33 | 1.23 | 1.34 | 4.47 | 13.52 |
| 3920.00 | 11.78 | 12.19 | 12.21 | 7.55 | 7.40 | 7.40 | 1.26 | 1.40 | 4.41 | 13.51 |
| 4220.00 | 11.74 | 12.15 | 12.18 | 7.62 | 7.49 | 7.46 | 1.26 | 1.42 | 4.45 | 13.61 |
| 4820.00 | 11.50 | 11.82 | 11.81 | 8.38 | 8.29 | 8.30 | 1.25 | 1.47 | 4.80 | 13.21 |
| 5120.00 | 11.58 | 11.88 | 11.86 | 9.05 | 8.98 | 8.95 | 1.18 | 1.53 | 4.88 | 12.80 |
| 5570.00 | 10.90 | 11.14 | 11.12 | 9.40 | 9.27 | 9.30 | 1.20 | 1.42 | 4.96 | 12.39 |
| 6000.00 | 10.48 | 10.71 | 10.69 | 9.76 | 9.64 | 9.67 | 1.28 | 1.40 | 5.03 | 12.04 |



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Amplifier

ZJL-6G+

Typical Performance Data

| FREQUENCY (MHz) | GAIN (dB) 12V | DIRECTIVITY (dB) 12V | VSWR IN (:1) 12V | VSWR OUT (:1) 12V | NOISE FIGURE (dB) 12V | Pout at 1dB Comp. (dBm) 12V |
|--------------------|---------------------|----------------------------|---------------------------|-------------------------|--------------------------------|--------------------------------------|
| 20.0 | 14.80 | 4.94 | 1.40 | 1.72 | 4.36 | 13.17 |
| 470.0 | 14.84 | 4.82 | 1.37 | 1.64 | 4.20 | 13.31 |
| 920.0 | 14.39 | 5.37 | 1.33 | 1.56 | 4.30 | 13.35 |
| 1370.0 | 14.38 | 4.99 | 1.29 | 1.47 | 4.13 | 13.34 |
| 1820.0 | 14.28 | 4.83 | 1.21 | 1.36 | 4.16 | 13.26 |
| 2120.0 | 14.10 | 4.96 | 1.17 | 1.29 | 4.21 | 13.21 |
| 2570.0 | 13.62 | 5.55 | 1.16 | 1.24 | 4.35 | 13.20 |
| 3020.0 | 13.16 | 6.09 | 1.19 | 1.27 | 4.33 | 13.24 |
| 3470.0 | 12.81 | 6.36 | 1.23 | 1.34 | 4.47 | 13.52 |
| 3920.0 | 12.19 | 7.40 | 1.26 | 1.40 | 4.41 | 13.51 |
| 4220.0 | 12.15 | 7.49 | 1.26 | 1.42 | 4.45 | 13.61 |
| 4820.0 | 11.82 | 8.29 | 1.25 | 1.47 | 4.80 | 13.21 |
| 5120.0 | 11.88 | 8.98 | 1.18 | 1.53 | 4.88 | 12.80 |
| 5570.0 | 11.14 | 9.27 | 1.20 | 1.42 | 4.96 | 12.39 |
| 6000.0 | 10.71 | 9.64 | 1.28 | 1.40 | 5.03 | 12.04 |

REV. X1
ZJL-6G+
060917
Page 1 of 1








IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Typical Performance Curves



Outline Dimensions



| CASE# | A | B | C | D | E | F | G | H | J | K | L | M | N |
|-------|-----------------|----------------|----------------|---------------|---------------|---------------|---------------|---------------|----------------|-----------------|----------------|---------------|-----------------|
| BW459 | 1.00 (25.40) | .75 (19.05) | .61 (15.49) | .38 (9.65) | .29 (7.37) | .25 (6.35) | .26 (6.60) | .35 (8.89) | .65 (16.51) | .688 (17.48) | .156 (3.96) | .13 (3.30) | 1.07 (27.18) |

| CASE# | P | WT. GRAMS |
|-------|----------------|-----------|
| BW459 | .140 (3.56) | 25 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:

For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|---------------------------|---------------------------------------|--|
| Operating Temperature | -40° to 75°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Stabilization Bake | (non-operating) 125°C, 24 hours | - - - |
| Burn-in at Elevated Temp. | (DC on) 160 hours at 85° C | MIL-STD-202, Method 108 |
| Thermal Shock | -55° to 100°C, 5 cycles | MIL-STD-202, Method 107, Condition A, except 100°C |