

Coaxial

Pulse Amplifier

ZPUL-30P+

50Ω Non-Inverting 0.0025 to 700 MHz

The Big Deal

- Wideband, 2.5 kHz - 700 MHz
- High gain, 35 dB typ. with excellent flatness, ± 0.6 dB typ.
- Can handle wide pulses width (15 μ s typ.) with excellent rise/fall time (1.1 ns typ.)
- Delay time, 1.5 ns typ.
- Protected by US Patent, 6,943,629



CASE STYLE: S32

Product Overview

Mini-Circuits ZPUL-30P+ utilizes high power LDMOS transistor output stage. Class A operation accept any kind of modulation. The frequency range is so wide (280,000:1) that the amplifier may handle long pulses, 15 μ sec typ. with very short rise and fall duration 1.1 nsec. typ. Of course it may work as a ordinary RF amplifier within its very wide frequency range.

Key Features

Feature	Advantages
Current stabilization circuits.	The design utilizes a patented technology to set and maintain the constant current consumption.
Rugged Design	Extreme load mismatch such as open/short at output are tolerated without damaging the amplifier.
Range of Protections	Reverse polarity protection.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Pulse Amplifier

ZPUL-30P+

50Ω Non-Inverting 0.0025 to 700 MHz

Features

- wide bandwidth 2.5 kHz to 700 MHz, useable to 1000 MHz
- excellent flatness, ± 0.6 dB typ.
- can handle wide pulse width & (15 μ s typ.) with excellent rise/fall time (1.1 ns typ.)
- delay time, 1.5 ns typ.
- protected by US Patent, 6,943,629

Applications

- computers
- digital communication
- medical test set-ups



CASE STYLE: S32
Connectors Model
BNC ZPUL-30P+

Pulse Amplifier Electrical Specifications

Parameter	ZPUL-30P+			Units
	Min.	Typ.	Max.	
Frequency Range	0.0025		700	MHz
Gain	29	35	—	dB
Gain Flatness	—	—	± 1.0	dB
Output Power at 1dB compression	+22***	—	—	dBm
Output Third Order Intercept Point (OIP3)	—	+34	—	dBm
Noise Figure**	—	7.7	—	dB
Rise/Fall Time	—	—	1.5	ns
Pulse Width*	6	15	—	μ s
Input VSWR ¹	—	2.0	—	:1
Output VSWR	—	2.0	—	:1
DC Supply Voltage	—	24	—	V
Supply Current	—	—	400	mA

* Pulse width for less than 10% droop.

** Noise Figure tested above 10 MHz.

Open load is not recommended, potentially can cause damage.

With no load derate max input power by 20 dB

*** For 500-700 MHz, +20.5 dBm

Maximum Ratings

Operating Temperature -20°C to 65°C

Storage Temperature -55°C to 100°C

DC Voltage +24.5V Max.

Input Power (no damage) +10 dBm

Permanent damage may occur if any of these limits are exceeded.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
M173321
ZPUL-30P+
190319
Page 2 of 4



Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt
3.75	2.00	1.80	.19	3.375	.19	1.625	.144	.50	.40	.50	1.30	.10	.38	3.00	.30	2.60	.80	grams
95.25	50.80	45.72	4.83	85.73	4.83	41.28	3.66	12.70	10.16	12.70	33.02	2.54	9.65	76.20	7.62	66.04	20.32	220.0

typical amplifier response to a pulse input



Notes







- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data/Curves

ZPUL-30P+

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		NOISE FIGURE (dB)	POUT at 1 dB COMPR. (dBm)	OUTPUT IP3 (dBm)
	24V	24V	IN	OUT	24V		24V
0.0025	35.64	31.23	1.33	1.23	--	--	--
0.010	35.11	25.86	1.06	1.06	--	--	--
0.050	34.95	28.03	1.02	1.05	--	--	--
0.100	35.03	22.39	1.02	1.09	--	--	--
0.200	35.15	28.86	1.02	1.13	--	--	--
1	35.17	27.99	1.02	1.15	--	--	--
2	35.14	27.59	1.03	1.15	--	--	36.59
10	34.65	47.00	1.03	1.17	8.04	24.48	37.03
50	34.60	45.74	1.06	1.19	7.74	25.54	37.88
100	35.10	51.26	1.08	1.23	7.77	25.51	37.96
200	35.54	44.55	1.08	1.31	7.76	25.04	37.42
300	35.51	39.14	1.08	1.35	7.74	24.46	36.36
400	35.34	49.01	1.09	1.31	7.77	23.98	36.81
500	35.13	40.32	1.12	1.22	7.79	23.78	36.25
600	35.03	40.83	1.16	1.20	7.81	23.70	35.27
700	35.06	58.56	1.23	1.44	7.86	22.70	33.86



Notes







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. Page 2 of 2
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 24V	DIRECTIVITY (dB) 24V	VSWR IN (:1) 24V	VSWR OUT (:1) 24V	NOISE FIGURE (dB) 24V	Pout @ 1dB COMPRESSION (dBm) 24V	OUTPUT IP3 (dBm) 24V
0.0025	35.64	31.23	1.33	1.23	--	--	--
0.009	35.14	40.80	1.08	1.08	--	--	--
0.01	35.11	25.86	1.06	1.06	--	--	--
0.05	34.95	28.03	1.02	1.05	--	--	--
0.10	35.03	22.39	1.02	1.09	--	--	--
0.20	35.15	28.86	1.02	1.13	--	--	--
0.30	35.15	32.49	1.02	1.14	--	--	--
0.40	35.18	30.75	1.02	1.15	--	--	--
0.50	35.15	31.06	1.02	1.14	--	--	--
1	35.17	27.99	1.02	1.15	--	--	--
2	35.14	27.59	1.03	1.15	--	--	36.59
4	35.08	26.65	1.03	1.16	--	--	36.61
6	34.93	37.04	1.03	1.17	--	--	36.69
8	34.79	30.64	1.03	1.18	--	--	36.92
10	34.65	47.00	1.03	1.17	8.04	24.48	37.03
20	34.43	42.29	1.04	1.17	7.77	25.14	37.52
30	34.45	45.35	1.05	1.17	7.75	25.45	37.75
40	34.51	42.40	1.05	1.18	7.72	25.52	37.80
50	34.60	45.74	1.06	1.19	7.74	25.54	37.88
60	34.69	55.53	1.06	1.20	7.72	25.52	37.95
70	34.80	45.73	1.07	1.21	7.73	25.48	37.88
80	34.91	44.53	1.07	1.21	7.74	25.50	37.83
90	35.00	41.67	1.08	1.22	7.75	25.51	37.79
100	35.10	51.26	1.08	1.23	7.77	25.51	37.96
125	35.29	52.57	1.08	1.25	7.76	25.46	37.87
150	35.42	49.03	1.08	1.27	7.75	25.24	37.70
175	35.49	46.24	1.08	1.29	7.75	25.15	37.69
200	35.54	44.55	1.08	1.31	7.76	25.04	37.42
225	35.55	48.98	1.08	1.33	7.74	24.86	37.20
250	35.54	49.12	1.08	1.34	7.75	24.72	37.14
275	35.53	41.22	1.08	1.35	7.74	24.72	36.41
300	35.51	39.14	1.08	1.35	7.74	24.46	36.36
325	35.49	48.63	1.09	1.35	7.74	24.36	36.28
350	35.49	43.23	1.09	1.34	7.74	24.30	36.60
375	35.38	47.26	1.09	1.33	7.76	24.18	36.64
400	35.34	49.01	1.09	1.31	7.77	23.98	36.81
425	35.29	52.57	1.10	1.29	7.78	23.97	36.66
450	35.24	47.17	1.10	1.27	7.79	23.99	36.62
475	35.19	41.83	1.11	1.24	7.79	23.83	36.51
500	35.13	40.32	1.12	1.22	7.79	23.78	36.25
525	35.08	45.33	1.13	1.21	7.79	23.85	36.02
550	35.05	43.39	1.14	1.20	7.81	23.71	35.89
575	35.02	40.87	1.15	1.19	7.82	23.68	35.66
600	35.03	40.83	1.16	1.20	7.81	23.70	35.27
625	35.04	51.70	1.18	1.21	7.82	23.61	35.08
650	35.07	37.16	1.19	1.25	7.82	23.41	34.82
675	35.08	52.84	1.21	1.32	7.85	23.27	34.38
700	35.06	58.56	1.23	1.44	7.86	22.70	33.86


Typical Performance Curves



Outline Dimensions



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
S32	3.75 (95.25)	2.00 (50.80)	1.80 (45.72)	.19 (4.83)	3.375 (85.73)	.19 (4.83)	1.625 (41.28)	.144 (3.66)	.50 (12.70)	.40 (10.16)	.50 (12.70)	1.30 (33.02)	.10 (2.54)

CASE#	P	Q	R	S	T	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
S32	.38 (9.65)	3.00 (76.20)	.30 (7.62)	2.60 (66.04)	.80 (20.32)	220.0	150.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 65° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C