

Coaxial Low Noise Amplifier

ZQL-900LN+

50Ω 824 to 849 MHz

Features

- Very low noise figure, 1.3 dB max.
- High IP3, +35 dBm typ.
- Rugged, shielded case

Applications

- UHF
- Communications systems
- Cellular



Generic photo used for illustration purposes only

Case Style: CW686	
Connectors	Model
SMA	ZQL-900LN+


+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

Parameter	Condition (MHz)	Min.	Typ.	Max.	Units
Frequency Range		824		849	MHz
Noise Figure	824-849	—	—	1.3	dB
Gain	824-849	15	—	—	dB
Gain Flatness	824-849	—	—	±0.5	dB
Output Power at 1dB compression	824-849	—	+21	—	dBm
Output third order intercept point	824-849	—	+35	—	dBm
Input VSWR	824-849	—	1.2	—	:1
Output VSWR	824-849	—	1.1	—	:1
DC Supply Voltage	824-849	—	15	—	V
Supply Current	824-849	—	—	160	mA

Open load is not recommended, potentially can cause damage.
With no load derate max input power by 20 dB

Outline Drawing



Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 70°C
Storage Temperature	-55°C to 100°C
DC Voltage	17V
Input RF Power (no damage)	+10 dBm

Permanent damage may occur if any of these limits are exceeded.

Outline Dimensions (inch/mm)






A	B	C	D	E	F	G	H	J	K	L	M	N	P	wt
1.77	2.42	.55	.13	.12	2.165	1.535	.126	.22	.28	.51	.61	.39	0.22	grams
44.96	61.47	13.97	3.30	3.05	55.0	39.0	3.20	5.59	7.11	12.95	15.49	9.91	5.59	71.0

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		NOISE FIGURE (dB)	POUT at 1 dB COMPR. (dBm)
	15V	15V	IN	OUT	15V	15V
824.00	16.93	6.75	1.09	1.15	0.96	23.01
826.00	16.90	6.79	1.09	1.15	0.96	22.97
828.00	16.86	6.80	1.09	1.15	0.96	22.97
830.00	16.83	6.82	1.09	1.16	0.96	23.01
832.00	16.80	6.83	1.09	1.16	0.99	22.99
835.00	16.75	6.88	1.09	1.16	0.99	23.05
837.00	16.71	6.91	1.09	1.16	0.99	23.05
839.00	16.68	6.93	1.10	1.16	0.97	23.01
841.00	16.64	6.97	1.10	1.16	0.99	23.07
843.00	16.60	7.01	1.10	1.16	1.00	23.09
845.00	16.57	7.03	1.10	1.16	1.00	23.03
847.00	16.53	7.03	1.10	1.16	0.99	23.14
849.00	16.50	7.04	1.10	1.16	1.01	23.13



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Noise Amplifier

ZQL-900LN+

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 15V	DIRECTIVITY (dB) 15V	VSWR IN (:1) 15V	VSWR OUT (:1) 15V	NOISE FIGURE (dB) 15V	Pout at 1dB Comp. (dBm) 15V
800.0	17.28	6.50	1.14	1.17	0.82	22.93
811.1	17.11	6.59	1.13	1.17	0.82	22.86
822.2	16.93	6.77	1.12	1.17	0.83	22.89
833.3	16.73	6.91	1.12	1.17	0.85	23.00
844.4	16.53	7.10	1.12	1.17	0.87	22.91
855.6	16.31	7.29	1.12	1.16	0.85	22.98
866.7	16.09	7.52	1.11	1.16	0.89	22.87
877.8	15.90	7.70	1.11	1.15	0.88	22.99
888.9	15.71	7.88	1.11	1.15	0.90	22.94
900.0	15.52	8.15	1.11	1.14	0.90	23.00

REV. X1
ZQL-900LN+
060917
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Low Noise Amplifier

ZQL-900LN+

Typical Performance Curves



REV. X1
ZQL-900LN+
060917
Page 1 of 1




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
CW686	1.77 (44.96)	2.42 (61.47)	.55 (13.97)	.13 (3.30)	.12 (3.05)	2.165 (54.99)	1.535 (38.99)	.126 (3.20)	.22 (5.59)	.28 (7.11)	.51 (12.95)	.61 (15.49)	.39 (9.91)

CASE#	P	Q	WT. GRAMS
CW686	.22 (5.59)	-- --	71

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 70° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 85°C, 5 cycles	MIL-STD-202, Method 107, Condition A