

3 Way-0° Power Splitter/Combiner

ZSC-3-2+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)			
	S-1	S-2	S-3		1-2	2-3	1-3			S	1	2	3
0.01	5.08	5.05	5.05	0.03	39.98	45.28	45.16	0.66	0.01	2.19	2.06	2.06	2.11
0.02	4.92	4.90	4.91	0.02	45.61	50.79	50.33	0.20	0.02	1.53	1.46	1.46	1.48
0.03	4.88	4.87	4.87	0.01	49.13	54.35	53.54	0.11	0.03	1.35	1.30	1.30	1.31
0.04	4.87	4.86	4.86	0.01	51.55	56.72	55.87	0.07	0.04	1.27	1.23	1.23	1.24
0.05	4.86	4.85	4.85	0.01	53.25	58.54	57.54	0.04	0.05	1.23	1.19	1.19	1.19
0.06	4.86	4.85	4.85	0.01	54.63	59.76	58.82	0.02	0.06	1.20	1.16	1.16	1.17
0.07	4.86	4.85	4.85	0.01	55.65	60.61	59.88	0.01	0.07	1.19	1.14	1.14	1.15
0.08	4.86	4.85	4.85	0.01	56.50	61.15	60.78	0.00	0.08	1.17	1.13	1.13	1.14
0.09	4.86	4.85	4.85	0.01	57.08	61.63	61.22	0.01	0.09	1.17	1.13	1.13	1.13
0.10	4.86	4.85	4.85	0.01	57.61	61.74	61.58	0.01	0.10	1.16	1.12	1.12	1.12
1.00	4.85	4.85	4.85	0.01	53.52	53.82	53.61	0.02	1.00	1.12	1.08	1.08	1.09
1.90	4.86	4.85	4.86	0.01	48.74	48.96	48.74	0.02	1.90	1.12	1.08	1.08	1.08
2.80	4.87	4.86	4.86	0.00	45.79	46.05	45.85	0.03	2.80	1.12	1.07	1.07	1.08
3.70	4.88	4.88	4.88	0.00	43.77	44.01	43.84	0.03	3.70	1.12	1.07	1.07	1.07
4.60	4.89	4.89	4.89	0.00	42.19	42.45	42.31	0.03	4.60	1.12	1.07	1.07	1.07
5.50	4.90	4.90	4.90	0.00	40.94	41.19	41.05	0.04	5.50	1.12	1.06	1.06	1.07
6.40	4.91	4.91	4.91	0.00	39.85	40.14	40.01	0.04	6.40	1.13	1.06	1.06	1.06
7.30	4.92	4.92	4.92	0.00	38.93	39.21	39.10	0.05	7.30	1.13	1.05	1.05	1.06
8.20	4.93	4.92	4.93	0.00	38.13	38.40	38.30	0.06	8.20	1.13	1.05	1.05	1.05
9.10	4.94	4.93	4.94	0.00	37.40	37.69	37.59	0.06	9.10	1.14	1.04	1.04	1.05
10.00	4.94	4.94	4.95	0.00	36.74	37.02	36.94	0.06	10.00	1.14	1.04	1.04	1.05
11.00	4.95	4.95	4.96	0.01	36.08	36.36	36.29	0.07	11.00	1.15	1.03	1.04	1.04
12.00	4.96	4.96	4.97	0.01	35.48	35.76	35.70	0.09	12.00	1.15	1.03	1.03	1.04
13.00	4.97	4.97	4.98	0.01	34.93	35.21	35.17	0.09	13.00	1.16	1.02	1.03	1.04
14.00	4.98	4.98	4.99	0.01	34.43	34.71	34.68	0.10	14.00	1.17	1.02	1.03	1.04
15.00	4.98	4.99	5.00	0.01	33.96	34.24	34.22	0.11	15.00	1.17	1.02	1.03	1.04
16.00	4.99	5.00	5.00	0.01	33.52	33.80	33.81	0.12	16.00	1.18	1.03	1.04	1.04
17.00	5.00	5.01	5.02	0.02	33.12	33.40	33.40	0.13	17.00	1.19	1.03	1.04	1.05
18.00	5.01	5.01	5.03	0.02	32.75	33.02	33.05	0.14	18.00	1.19	1.04	1.05	1.05
19.00	5.01	5.02	5.04	0.02	32.40	32.67	32.70	0.15	19.00	1.20	1.05	1.05	1.06
20.00	5.02	5.03	5.05	0.03	32.07	32.32	32.38	0.16	20.00	1.21	1.06	1.06	1.07
21.00	5.03	5.04	5.06	0.03	31.75	32.00	32.08	0.17	21.00	1.22	1.07	1.07	1.08
22.00	5.04	5.05	5.07	0.03	31.46	31.70	31.79	0.18	22.00	1.23	1.08	1.08	1.09
23.00	5.05	5.06	5.08	0.03	31.17	31.41	31.53	0.19	23.00	1.24	1.09	1.09	1.10
24.00	5.05	5.07	5.09	0.04	30.90	31.14	31.27	0.21	24.00	1.25	1.10	1.11	1.11
25.00	5.06	5.08	5.10	0.04	30.64	30.87	31.02	0.22	25.00	1.26	1.11	1.12	1.12
26.00	5.07	5.09	5.12	0.05	30.40	30.62	30.79	0.24	26.00	1.28	1.12	1.13	1.13
27.00	5.08	5.10	5.13	0.05	30.16	30.36	30.57	0.24	27.00	1.29	1.13	1.14	1.14
28.00	5.09	5.12	5.14	0.05	29.93	30.13	30.34	0.25	28.00	1.31	1.15	1.15	1.16
29.00	5.10	5.13	5.16	0.06	29.70	29.88	30.13	0.26	29.00	1.33	1.16	1.17	1.17
30.00	5.11	5.14	5.17	0.06	29.48	29.65	29.91	0.27	30.00	1.34	1.18	1.18	1.18

¹ Total Loss = Insertion Loss + 4.8dB Splitter Loss

REV. X2
ZSC-3-2+
100713
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



3 Way-0° Power Splitter/Combiner

ZSC-3-2+

Typical Performance Curves



REV. X2
ZSC-3-2+
100713
Page 1 of 1

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Case Style

P

P25
P26

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
P25	2.25	1.38	1.24	.50	.150	3.100	.138	1.238	3.25	.10	.78	1.47	--
	(57.15)	(35.05)	(31.50)		(3.81)	(78.74)		(31.45)	(82.55)		(19.81)	(37.34)	--
P26	1.50	1.13	1.00	(12.70)	.155	2.345	(3.51)	.987	2.50	(2.54)	.50	1.00	--
	(38.10)	(28.70)	(25.40)		(3.94)	(59.56)		(25.07)	(63.50)		(12.70)	(25.40)	--

CASE#	P	Q	R	S	WT. GRAMS
P25	.38	1.00	--	.150	110.0
	(9.65)	(25.40)	--		
P26	.31	.81	--	(3.81)	60.0
	(7.87)	(20.57)	--		

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
 - For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
 - For Non-RoHS Case Styles: Yellow hexavalent chrome based conversion coating.

Due to transition from non-RoHS to RoHS, models will be supplied with either case style finish until the non-RoHS case inventory is depleted.
- Mounting bracket available on request. For bracket mounted on connector end add suffix B to part number and add \$5.00 to unit cost. For bracket mounted on the rear, add suffix BR to part number and add \$1.50 to unit cost.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I