

Coaxial Switch

50Ω SP4T Pin Diode, Reflective TTL Driver 10 to 2500 MHz

ZSDR-425+



Generic photo used for illustration purposes only

CASE STYLE: GGG126

Connectors	Model
SMA	ZSDR-425+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power	L(+20 dBm), M(+28 dBm), U(+30 dBm)
Supply V	+6V max.
Permanent damage may occur if any of these limits are exceeded.	

Coaxial/Pin Connections

RF IN	RF-IN
RF OUT 1	RF-1
RF OUT 2	RF-2
RF OUT 3	RF-3
RF OUT 4	RF-4
TTL-1	TTL-1
TTL-2	TTL-2
+5V	+5V

Features

- wideband, 10 to 2500 MHz
- high isolation, 40 dB typ.

Applications

- test set-ups
- antenna switching
- satellite communication

Electrical Specifications (T_{AMB}=25°C)


MODEL NO.	FREQ. (MHz)		INSERTION LOSS (dB)				IN-OUT ISOLATION (dB)							
			Low band lw		Upper band U		L		M		U			
	f _L	f _U	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
ZSDR-425(+)	10	2500	1.1	1.7	1.5	2.5	60	40	40	30	35	22		

L=low range(f_L to 10 f_L)

M=mid range(10 f_L to f_U/2)
lw=low band (f_L to f_U/2)

U=upper range (f_U/2 to f_U)

Outline Drawing



Outline Dimensions (Inch/mm)

A	B	C	D	E	F	G	H	J	K
2.25	1.38	1.24	.50	.150	3.100	.138	1.238	.30	.12
57.15	35.05	31.50	12.70	3.81	78.74	3.51	31.45	7.62	3.05
L	M	N	P	Q	R	S	T	wt	
.80	.69	--	.60	1.200	.52	.82	.150	grams	
20.32	17.53	--	15.24	30.48	13.21	20.83	3.81	80.0	


Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Control Logic






	TTL LOGIC	
	TTL-1	TTL-2
RF-1	1	0
RF-2	1	1
RF-3	0	1
RF-4	0	0

REV. C
M151107
ZSDR-425+
WP/CP/AM
151007

Typical Performance Data

FREQ. (MHz)	ON (TTL LOW @ 0V) IN-OUT		INSERTION LOSS (dB) AMP. UNBAL.				OFF (TTL HIGH @ 5V) IN-OUT		ISOLATION (dB) DELTA		VSWR OUT (RF 1) ON OFF	
	\bar{x}	σ	\bar{x}	σ	\bar{x}	σ	\bar{x}	σ	\bar{x}	\bar{x}	\bar{x}	
	10.00	1.22	0.16	0.18	0.15	74.41	4.10	9.64	5.24	1.35	1.40	27.25
20.00	1.06	0.12	0.15	0.12	70.64	2.69	8.25	4.56	1.19	1.22	27.08	
50.00	0.97	0.09	0.13	0.09	61.72	2.10	8.97	7.88	1.11	1.13	27.42	
100.00	0.94	0.09	0.12	0.09	56.09	1.46	6.48	2.94	1.10	1.11	26.82	
200.00	0.90	0.08	0.12	0.08	49.80	1.51	6.32	3.03	1.13	1.12	26.58	
408.40	1.01	0.07	0.11	0.07	45.66	1.36	5.61	1.32	1.21	1.18	26.03	
500.00	1.06	0.08	0.12	0.09	44.93	1.43	5.49	1.62	1.25	1.20	24.98	
669.85	1.10	0.07	0.12	0.07	44.06	1.59	5.94	1.86	1.30	1.24	24.36	
856.60	1.30	0.07	0.13	0.08	43.15	1.93	6.13	2.01	1.35	1.25	22.45	
1000.00	1.39	0.05	0.11	0.07	44.52	3.69	8.35	2.97	1.37	1.24	20.59	
1118.05	1.48	0.05	0.13	0.07	42.72	2.91	8.56	3.40	1.37	1.23	19.44	
1250.00	1.37	0.06	0.13	0.06	42.75	2.61	10.05	4.95	1.36	1.22	19.15	
1391.95	1.51	0.09	0.16	0.07	44.07	3.21	10.73	3.71	1.34	1.20	18.57	
1578.70	1.47	0.05	0.15	0.05	40.41	2.62	9.61	3.27	1.31	1.16	17.15	
1777.90	1.52	0.05	0.17	0.05	37.07	2.87	9.43	3.26	1.30	1.14	16.04	
2002.00	1.66	0.12	0.20	0.08	34.27	3.55	9.08	1.82	1.30	1.16	13.88	
2176.30	1.81	0.09	0.20	0.08	30.64	3.24	7.16	1.46	1.30	1.21	12.25	
2363.05	1.82	0.07	0.19	0.04	26.86	2.95	5.63	1.07	1.28	1.28	9.41	
2437.75	2.08	0.14	0.24	0.05	25.66	2.78	5.42	1.03	1.29	1.30	7.81	
2500.00	2.14	0.16	0.25	0.05	25.03	2.28	5.15	1.27	1.30	1.31	7.10	



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Switch SP4T , 50W

ZSDR-425+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS TTL Low @ 0V (dB) IN-OUT , "ON"	ISOLATION TTL High @ 5V (dB) IN-OUT , "OFF"	VSWR		
			IN	(:1) OUT , "ON"	OUT , "OFF"
10.00	1.22	74.41	1.35	1.40	27.25
20.00	1.06	70.64	1.19	1.22	27.08
50.00	0.97	61.72	1.11	1.13	27.42
100.00	0.94	56.09	1.10	1.11	26.82
200.00	0.90	49.80	1.13	1.12	26.58
408.40	1.01	45.66	1.21	1.18	26.03
500.00	1.06	44.93	1.25	1.20	24.98
669.85	1.10	44.06	1.30	1.24	24.36
856.60	1.30	43.15	1.35	1.25	22.45
1000.00	1.39	44.52	1.37	1.24	20.59
1118.05	1.48	42.72	1.37	1.23	19.44
1250.00	1.37	42.75	1.36	1.22	19.15
1391.95	1.51	44.07	1.34	1.20	18.57
1578.70	1.47	40.41	1.31	1.16	17.15
1777.90	1.52	37.07	1.30	1.14	16.04
2002.00	1.66	34.27	1.30	1.16	13.88
2176.30	1.81	30.64	1.30	1.21	12.25
2363.05	1.82	26.86	1.28	1.28	9.41
2437.75	2.08	25.66	1.29	1.30	7.81
2500.00	2.14	25.03	1.30	1.31	7.10



ISO 9001 ISO 14001 AS 9100 CERTIFIED

For detailed performance specs & shopping online see web site


P.O. Box 350166, Brooklyn, New York 11235-0008 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

RF/MICROWAVE COMPONENTS


Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCISHome/terms.jsp.

Typical Performance Curves


In-Out Insertion Loss, "ON"



In-Out Isolation, "OFF"



VSWR



ISO 9001 ISO 14001 AS 9100 CERTIFIED


P.O. Box 350166, Brooklyn, New York 11235-0008 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

RF/MICROWAVE COMPONENTS

For detailed performance specs & shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCIShowTerms.jsp.

Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GGG126	2.25 (57.15)	1.38 (35.05)	1.24 (31.50)	.50 (12.70)	.150 (3.81)	3.100 (78.74)	.138 (3.51)	1.238 (31.45)	3.25 (82.55)	.12 (3.05)	.80 (20.32)	.69 (17.53)	--

CASE #.	P	Q	R	S	T	WT, GRAM
GGG126	.60 (15.24)	1.200 (30.48)	.52 (13.21)	.82 (20.83)	.150 (3.81)	80.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I