



RACK-MOUNTED

Adapter Patch Panel

ZT-182

Mini-Circuits

50Ω DC to 11 GHz N-Type Female

THE BIG DEAL

- Convenient panel-mounted design
- Excellent VSWR
- Flat frequency response


APPLICATIONS

- Production test set-ups
- Simplification of cable runs
- Interconnection of RF cables & equipment
- Cellular base-station testing

PRODUCT OVERVIEW

Mini-Circuits panel-mounted structures provide clean, organized management of cable runs and connections in complex, high-volume test setups. Multiple connector adapters, power splitters, directional couplers and other essential RF components and test accessories can be integrated efficiently within the test system. Custom configurations are available upon request.

ZT-182 integrates 48 precision N-Type connector adapters (female to female) on to a 4U panel.



Generic photo used for illustration purposes only

Model No.	ZT-182
Case Style	YF2075
Connectors	N-Type Female

RoHS Compliant

See our website for RoHS Compliance methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Unit
Frequency	-	DC	-	11	GHz
Insertion Loss	DC - 6	-	0.1	-	dB
Return Loss	DC - 6	-	35	-	dB
	6 - 11	-	30	-	

MECHANICAL & ENVIRONMENTAL SPECIFICATIONS

Dimensions	19" (W) x 4U (H)				
Case Style	YF2075				
Case Material	Aluminum (with protective coating to prevent corrosion)				
RF Connectors	Face	Connector	Quantity	Port Labels	
	Front	N-Type Female	48	01-48	
	Rear	N-Type Female	48	01-48	
Panel Marking	Front Panel		Rear Panel		
	<ul style="list-style-type: none"> • ZT-182 • N-Type Patch Panel 		<ul style="list-style-type: none"> • CE / EAC / UKCA • Serial number / date code / model name 		
Panel Items	<ul style="list-style-type: none"> • Carry handles 				
Temperature	Operating: 0 to +50 °C				

REV. A
ECO-015207
ZT-182
MCL NY
220926





RACK-MOUNTED



Adapter Patch Panel

ZT-182

Mini-Circuits

50Ω DC to 11 GHz N-Type Female

TYPICAL PERFORMANCE CURVES





RACK-MOUNTED


Adapter Patch Panel

ZT-182

Mini-Circuits

50Ω DC to 11 GHz N-Type Female


OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch/mm)

A	B	C	D	E	F	G	H	J	K	L	weight
6.97	19.00	0.75	0.13	17	4.000	18.28	1.06	1.62	1.42	1.47	grams
177.0	482.6	19.1	3.3	431.8	101.60	464.31	26.9	41.1	36.1	37.3	3400





RACK-MOUNTED

Adapter Patch Panel

ZT-182

Mini-Circuits

50Ω DC to 11 GHz N-Type Female

ORDERING INFORMATION


To learn more, click here: [ZT-182](#)

Model	Description
ZT-182	48 x N-Type Female to Female Adapter Patch Panel

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html





CASE #	A	B	C	D	E	F	G	H	J	K	L	WT, GRAMS
YF2075	6.97	19.00	.75	.13	17.00	4.000	18.280	1.06	1.62	1.42	1.47	3400
	(177.0)	(482.6)	(19.0)	(3.3)	(431.8)	(101.60)	(464.31)	(26.9)	(41.1)	(36.1)	(37.3)	

Dimensions are in inches (mm). Tolerances: 1 Pl. ± 1 ; 2 Pl. ± 03 ; 3 Pl. ± 015

Notes:

1. Case material: Aluminum alloy.
2. Finish: Clear chemical conversion coating



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



Environmental Specifications **ENV55**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3