



RACK-MOUNTED

# Splitter / Combiner Rack

ZT-402

50 Ω 30-2000 MHz 2 x 8-Way SMA Female

## THE BIG DEAL

- Rack-mounted RF splitter / combiner system
- 2 x 8-way splitters in 1U rack space
- All connectors on the front panel
- Wide band




Front View

Generic photo used for illustration purposes only

## APPLICATIONS

- Production test setups
- Military VHF / UHF radio testing
- GNSS (GPS, Galileo, GLONASS) signal distribution
- Test instrumentation time synchronization

## FUNCTIONAL BLOCK DIAGRAM



## PRODUCT OVERVIEW

Mini-Circuits' rack-mounted test solutions enable convenient integration of any combination of passive or active RF and microwave components within complex production test environments. A wide range of standard configurations are supplied from stock, with custom configurations available upon request.

ZT-402 integrates 2 x 8-way splitter / combiners into a compact rack-mounted chassis requiring only 1U of rack space. Each splitter covers an exceptionally wide bandwidth of 30-2000 MHz with high isolation, ideally suited for applications in the VHF, UHF and L bands.

The system is configured with all SMA RF connectors on the front for easy access within a rack-mounted test environment.

## ELECTRICAL SPECIFICATIONS AT +25°C (EACH SPLITTER)

Parameter	Conditions	Min	Typ	Max	Units
Frequency	Above theoretical 9 dB loss, 30 – 500 MHz	30		2000	MHz
Insertion Loss	Above theoretical 9 dB loss, 500 – 2000 MHz		3.0	4.0	dB
	30 – 500 MHz		5.0	7.0	
Isolation	500 – 2000 MHz	20	25		dB
	Sum ports, 30 – 500 MHz	18	20		
Return Loss	Sum ports, 500 – 2000 MHz		11		dB
	Ports 1-8, 30 – 500 MHz		8		
	Ports 1-8, 500 – 2000 MHz		22		
	As a splitter into load with 2:1 max VSWR		17		
Input Power	As a splitter into load with 2:1 max VSWR			+28	dBm

REV. A  
ECO-022135  
ZTM-402  
MCL NY  
240618





RACK-MOUNTED




# Splitter / Combiner Rack

ZT-402

Mini-Circuits

50  $\Omega$  30-2000 MHz 2 x 8-Way SMA Female

## TYPICAL PERFORMANCE GRAPHS





RACK-MOUNTED

# Splitter / Combiner Rack

# ZT-402

Mini-Circuits

50 Ω 30-2000 MHz 2 x 8-Way SMA Female

### ABSOLUTE MAXIMUM RATINGS


Parameter	Conditions	Limits	Units
Temperature	Operating	0 to +50	°C
	Storage	-20 to +60	

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

### CONNECTIONS

Port	Function
A & B	SMA female
A1-8 & B1-8	SMA female

### CASE STYLE DRAWING



Weight: 1860 grams.

Dimensions are in inches (mm). Tolerances: 2 Pl.±.03 inch; 3 Pl.±.015 inch.

### PRODUCT MARKING\*

Product Marking: ZT-402

Product Frequency: 30-2000 MHz

Unit ID Label: Serial number and other identification marks

\*Marking may contain other features or characters for internal lot control





RACK-MOUNTED


# Splitter / Combiner Rack

ZT-402


Mini-Circuits

50 Ω 30-2000 MHz 2 x 8-Way SMA Female

DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE [CLICK HERE](#)

Case Style	AAS3583	
Environmental Rating	ENV55	
Regulatory Compliance	<p>Refer to our website for compliance methodologies and qualifications</p> 	<p><a href="http://www.minicircuits.com/quality/environmental_introduction.html">www.minicircuits.com/quality/environmental_introduction.html</a></p>

Contact Us: [testsolutions@minicircuits.com](mailto:testsolutions@minicircuits.com)


Included Accessories	Part Number	Description
	HT-4-SMA	SMA connector wrench (4" length)

- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



## Outline Dimensions

AAS3583



### Notes:

1. Case material: Aluminum (with protective coating to prevent corrosion).
2. Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$  inch; 3 Pl.  $\pm .015$  inch.
3. Weight: 1860 grams.
4. Marking may contain other features or characters for internal lot control.

 **Mini-Circuits**<sup>®</sup>  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
 minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



Environmental Specifications **ENV55**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3