RACK-MOUNTED


Adapter Patch Panel

ZT-412

50Ω DC to 18 GHz Rack-Mount 18 x SMA Female to Female

KEY FEATURES

- Rack-mounted connector patch panel
- 18 x SMA adapters in 1U rack space
- Excellent return loss
- Flat frequency response



Generic photo used for illustration purposes only

APPLICATIONS

- Production test setups
- Quantum computing
- · Simplification of cable runs
- Interconnection of RF cables & equipment

PRODUCT OVERVIEW


Mini-Circuits panel-mounted structures provide clean, organized management of cable runs and connections in complex, high volume test setups. Multiple connector adapters, power splitters, directional couplers and other essential RF components and test accessories can be integrated efficiently within the test system. Custom configurations are available upon request.


ZT-412 integrates 18 wideband adapters on to a compact panel requiring only 1U of rack space, with SMA female connectors on the front and rear.

ELECTRICAL SPECIFICATIONS AT +25°C (EACH ADAPTER)

Parameter	Conditions	Min.	Тур.	Max.	Units
Frequency Range		DC		18	GHz
Insertion Loss			0.1		dB
Return Loss		23			dB

TYPICAL PERFORMANCE GRAPHS








RACK-MOUNTED


Adapter Patch Panel


ZT-412

50Ω DC to 18 GHz Rack-Mount 18 x SMA Female to Female

CASE STYLE DRAWING







PRODUCT MARKING*

Product Marking: ZT-412 Product Frequency: DC-18 GHz

Unit ID Label: Serial number and other identification marks

*Marking may contain other features or characters for internal lot control



RACK-MOUNTED

Adapter Patch Panel

ZT-412

50Ω DC to 18 GHz Rack-Mount 18 x SMA Female to Female

ABSOLUTE MAXIMUM RATINGS

Parameter	Conditions	Limits	Units
Temperature -	Operating	perating 0 to +50	
	Storage	-20 to +60	

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

CONNECTIONS

Port	Connector
01-18 (front & rear)	SMA female

DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE CLICK HERE

Case Style	99-01-3633	
Environmental Rating	ENV55	
Regulatory Compliance	Refer to our website for compliance methodologies and qualifications	www.minicircuits.com/quality/environmental_introduction.html

Contact Us: testsolutions@minicircuits.com

	HT-4-SMA	SMA connector wrench (4" length)
- 1		

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Environmental Specifications

ENV55

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-20° to 60° C Ambient Environment	Individual Model Data Sheet
Operating and Storage Humidity	5% to 85% RH (non-condensing)	Ambient
Bench Handling Test	Bench Top Tip 45° & Drop	MIL-PRF-28800F
Transit Drop Test	Free Fall Drop, 20 cm (7.9 inches)	MIL-PRF-28800F Class 3

This document and its contents are the property of Mini-Circuits