

# Cavity Bandpass Filters

## ZVBP Model Series

50Ω 24.25 to 43.5 GHz



### The Big Deal

- Very low insertion loss with excellent power handling
- Sharp roll-off with wide stopband
- Passbands from 24.25 to 43.5 GHz covering 5G bands\*.
- Stopbands up to 57 GHz

### Product Overview

Mini-Circuits' cavity filters are designed by implementing resonant structures with very high Q and are ideal for narrow-band, high-selectivity applications. These designs can provide bandwidths as narrow as 3% with very high selectivity and excellent low noise floor. Low insertion loss combined with excellent power handling makes them well-suited for transmitter and receiver front end. Advanced filter design and construction enables stopband width greater than 3x the center frequency.

### Key Features

Feature	Advantages
5G bands	Use in various 5G applications, covering n257, n258, n259, n260, and n261 bands.
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitter
Sharp roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide spur free band results in better receiver sensitivity
High power handling	Well suited for transmitter application
Protective assembly	Prevents accidental de-tuning of precisely tuned resonant circuit

\*High frequency models operating above 40 GHz are available with 2.4mm connectors.



[www.minicircuits.com](http://www.minicircuits.com)

P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Page 1 of 3

Cavity

# Bandpass Filter

50Ω 37000 to 40000 MHz

ZVBP-38500-K+

## Features

- Low insertion loss, 2.0 dB typical
- Good return loss, 21 dB typical
- High rejection
- Broad stopband performance up to 31 GHz
- Sharp roll-off
- Also available with 2.4mm connectors (model ZVBP-38500-V+)

## Applications

- 5G band n260



Generic photo used for illustration purposes only

CASE STYLE: UH3129


Connectors	Model
2.92mm-F	ZVBP-38500-K+

## Electrical Specifications<sup>1</sup> at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
<b>Pass Band</b>	Center Frequency	-	-	38500	-	MHz
	Insertion Loss	F1-F2	37000 - 40000	2.1	4.0	dB
	Return Loss	F1-F2	37000 - 40000	15	27	dB
<b>Stop Band, Lower</b>	Insertion Loss	DC-F3	DC - 36500	80	127	-
	Return Loss	DC-F3	DC - 36500	-	0.21	-
<b>Stop Band, Upper</b>	Insertion Loss	F4-F5	40500 - 55000	80	116	-
	Return Loss	F4-F5	40500 - 55000	-	0.68	-

1.Data measured after calibrating using 2.92mm cal kit.

## Simplified Functional Schematic



## Typical Frequency Response







Maximum Ratings	
Operating Temperature	-30°C to 70°C
Storage Temperature	-30°C to 70°C
RF Power Input	2.5 W

Permanent damage may occur if any of these limits are exceeded.

## Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
10	84.6	0.01	37000	3.53
200	118.6	0.03	37150	2.89
2000	138.1	0.12	37300	2.55
10000	133.1	0.15	37450	2.29
20000	128.9	0.27	37600	2.16
30000	122.5	0.09	37750	2.07
36500	95.2	0.78	37900	1.98
36750	41.1	1.28	38050	1.94
37000	3.0	20.77	38200	1.89
37500	1.9	44.45	38350	1.86
38000	1.7	25.34	38500	1.85
38500	1.6	26.23	38650	1.85
39000	1.7	28.89	38800	1.86
39500	2.0	27.47	38950	1.91
40000	3.7	22.20	39100	1.94
40250	48.2	1.15	39250	2.02
40500	87.0	0.68	39400	2.13
45000	117.8	0.02	39550	2.28
50000	132.7	0.45	39700	2.53
55000	125.0	0.99	40000	4.24




### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

**Coaxial Connections**

<u>PORT 1</u>	2.92mm-FEMALE
<u>PORT 2</u>	2.92mm-FEMALE

**Outline Drawing**

Weight: 85 grams  $\pm$  5 grams ;  
 Dimensions are in inches [mm]. Tolerances: 2 Pl. $\pm$ .03; 3 Pl.  $\pm$  .015

**Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# Cavity Band Pass Filter

**ZVBP-38500-K+**

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@-30°C	@+25°C	@+70°C	@-30°C	@+25°C	@+70°C	@-30°C	@+25°C	@+70°C
	100	109.33	106.70	113.34	0.01	0.02	0.03	0.01	0.02
200	111.51	111.92	117.64	0.02	0.03	0.04	0.02	0.03	0.04
300	109.87	108.08	102.34	0.04	0.05	0.06	0.03	0.05	0.06
400	109.78	111.11	107.24	0.04	0.06	0.07	0.04	0.05	0.07
500	110.39	122.41	113.80	0.04	0.06	0.07	0.04	0.06	0.07
600	103.50	109.65	103.63	0.04	0.07	0.08	0.04	0.06	0.08
800	108.59	109.10	117.85	0.05	0.07	0.09	0.04	0.07	0.09
1000	106.08	104.60	109.23	0.05	0.08	0.10	0.04	0.07	0.10
1200	104.31	103.64	117.27	0.04	0.08	0.10	0.03	0.07	0.10
1500	119.17	105.63	103.44	0.04	0.08	0.10	0.03	0.07	0.10
2000	109.12	122.65	116.05	0.03	0.07	0.10	0.02	0.07	0.10
2500	107.09	106.81	105.59	0.01	0.06	0.10	0.00	0.06	0.10
3000	103.85	113.18	106.05	0.00	0.06	0.09	0.01	0.05	0.09
3500	112.48	108.15	103.72	0.01	0.05	0.08	0.02	0.04	0.09
4000	107.80	113.24	110.50	0.02	0.04	0.08	0.04	0.03	0.08
4500	110.26	109.47	111.74	0.03	0.04	0.08	0.05	0.03	0.08
5000	110.21	115.59	117.71	0.03	0.04	0.09	0.05	0.03	0.09
5500	111.60	114.47	105.92	0.03	0.05	0.10	0.05	0.04	0.10
6000	114.98	109.39	115.90	0.02	0.06	0.11	0.04	0.05	0.12
6500	114.99	103.14	108.58	0.01	0.08	0.13	0.02	0.07	0.14
7000	108.32	108.88	106.06	0.02	0.10	0.15	0.00	0.10	0.17
8000	105.62	110.12	122.43	0.05	0.15	0.21	0.03	0.14	0.22
10000	103.83	118.84	104.68	0.03	0.14	0.21	0.02	0.14	0.23
15000	102.03	114.62	106.15	0.12	0.02	0.11	0.20	0.04	0.10
20000	114.42	113.00	104.65	0.03	0.25	0.37	0.07	0.29	0.44
25000	112.30	103.28	106.48	0.30	0.06	0.09	0.36	0.08	0.13
30000	101.09	92.05	96.67	0.15	0.42	0.58	0.15	0.43	0.65
35000	107.51	96.00	91.68	0.26	0.08	0.28	0.39	0.01	0.32
36500	87.38	86.21	81.59	0.78	1.20	1.49	0.48	0.88	1.15
36800	37.70	30.78	23.99	1.32	2.15	3.10	0.56	1.35	2.13
36840	29.22	21.77	14.57	1.78	2.99	5.11	0.86	1.91	3.61
36900	15.16	8.31	5.28	3.70	9.24	25.31	2.30	6.28	14.41
37000	3.11	3.21	3.32	22.47	27.14	29.00	20.95	30.43	28.44
37300	1.65	2.08	2.38	21.76	22.18	22.76	24.37	24.19	21.62
37600	1.33	1.77	2.07	27.63	28.20	30.22	20.67	21.08	21.48
37900	1.22	1.66	1.97	20.03	20.42	21.62	21.76	21.36	24.83
38200	1.11	1.55	1.87	23.66	23.85	23.11	29.61	28.82	24.11
38500	1.08	1.52	1.84	31.88	31.63	29.32	33.08	30.31	26.94
39000	1.13	1.59	1.92	23.09	22.13	22.72	21.60	20.41	21.35
39500	1.31	1.83	2.20	31.55	24.72	23.70	22.47	20.59	21.51
40000	2.32	3.24	4.10	25.28	18.88	21.01	28.67	19.29	19.31
40120	4.45	9.27	17.67	16.60	9.99	6.68	11.51	4.91	2.39
40160	8.78	18.30	27.98	8.89	5.63	3.84	4.26	1.98	1.39
40200	18.03	28.60	37.38	4.73	3.28	2.55	1.45	1.11	0.98
40500	75.38	80.06	83.42	0.08	0.37	0.54	0.44	0.02	0.26
41000	96.41	89.37	91.78	0.34	0.02	0.29	0.44	0.05	0.32
41500	87.27	101.83	89.11	0.24	0.11	0.38	0.20	0.11	0.48
42100	96.28	95.92	96.09	0.04	0.28	0.52	0.03	0.30	0.66
42550	99.61	85.01	89.64	0.08	0.39	0.61	0.12	0.41	0.77
43000	85.51	90.18	94.74	0.19	0.48	0.69	0.14	0.47	0.84
43600	88.90	97.94	104.41	0.23	0.53	0.76	0.18	0.58	0.92
44050	89.20	98.53	94.22	0.24	0.57	0.80	0.19	0.59	0.91
44500	105.41	94.41	90.66	0.22	0.58	0.82	0.20	0.60	0.87
45550	88.60	93.33	94.36	0.07	0.46	0.65	0.10	0.48	0.67
46000	91.53	90.74	91.56	0.02	0.40	0.58	0.02	0.41	0.59
47200	105.01	98.98	102.80	0.31	0.11	0.29	0.49	0.11	0.25
48100	86.48	87.31	90.74	0.56	0.06	0.18	0.72	0.16	0.03
49000	92.03	90.57	87.90	0.71	0.19	0.08	0.83	0.32	0.01
51100	97.61	100.19	86.14	0.43	0.03	0.35	0.54	0.01	0.41
55000	88.71	88.99	86.74	1.21	0.60	0.34	0.96	0.18	0.14



minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. A

ZVBP-38500-K+

230621

Page 1 of 2






*Typical Performance Data*

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-30°C	@+25°C	@+70°C
37000	5.02	4.40	3.93
37050	4.15	3.75	3.49
37100	3.61	3.37	3.19
37150	3.28	3.11	2.98
37200	3.04	2.92	2.82
37250	2.86	2.76	2.68
37300	2.72	2.64	2.57
37350	2.60	2.54	2.48
37400	2.51	2.45	2.41
37450	2.43	2.38	2.34
37500	2.36	2.31	2.28
37550	2.30	2.26	2.23
37600	2.24	2.21	2.18
37650	2.19	2.16	2.14
37700	2.15	2.12	2.10
37750	2.11	2.09	2.07
37800	2.08	2.05	2.04
37850	2.04	2.02	2.01
37900	2.01	2.00	1.98
38000	1.97	1.96	1.95
38100	1.94	1.93	1.92
38200	1.91	1.90	1.89
38300	1.88	1.87	1.87
38400	1.86	1.86	1.86
38500	1.86	1.86	1.86
38600	1.85	1.85	1.85
38700	1.85	1.85	1.85
38800	1.85	1.86	1.86
38900	1.87	1.88	1.89
39000	1.89	1.90	1.91
39100	1.92	1.93	1.95
39150	1.93	1.95	1.97
39200	1.95	1.97	1.99
39300	2.00	2.03	2.05
39400	2.06	2.09	2.12
39500	2.14	2.18	2.22
39600	2.25	2.30	2.36
39700	2.40	2.47	2.54
39800	2.59	2.70	2.81
39900	2.91	3.10	3.32
40000	3.52	3.96	4.51

# Cavity Band Pass Filter

ZVBP-38500-K+

## Typical Performance Curves




# Case Style

**UH**

## Outline Dimensions

**UH3129**



**Weight: 85 grams  $\pm$  5 grams;**

**Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm$  .03; 3 Pl.  $\pm$  .015**

### Notes:

1. Case material: H62 Copper Alloy
2. Case Finish: Black Painting

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
[minicircuits.com](http://minicircuits.com)

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



RF/IF MICROWAVE COMPONENTS



## Environmental Specifications ENV77T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-30° to 70°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-30° to 70° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles +100°C	MIL-STD-202, Method 107, Condition A-3, except +100°C