

# Cavity Bandpass Filters

50Ω DC to 40 GHz

## The Big Deal

- Very low insertion loss with excellent power handling
- Very fast roll-off with wide stopband
- Passbands up to 36 GHz
- Stopbands up to 40 GHz



## Product Overview

Mini-Circuits' cavity filters are designed by implementing resonant structures with very high Q and are ideal for narrow-band, high-selectivity applications. These designs can provide bandwidths as narrow as 1% with very high selectivity and excellent low noise floor. Low insertion loss combined with excellent power handling makes them well-suited for transmitter and receiver front end. Advanced filter design and construction enables stopband width greater than 3x the center frequency.

Mini-Circuits' cavity filters feature a special protective assembly to prevent accidental de-tuning that would otherwise require expensive replacement or return to factory for re-tuning. Custom integrated assembly with LNA and bias tees results in greatly simplifying system integration. Precise machining allows realization of cavity filters with small form factors for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

## Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitter
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide spur free band results in better receiver sensitivity
High power handling	Well suited for transmitter application
Protective assembly	Prevents accidental de-tuning of precisely tuned resonant circuit

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Bandpass Filter

50Ω 4750 to 4870 MHz

## ZVBP-4810-S+



Generic photo used for illustration purposes only

CASE STYLE: ME1656

Connectors Model  
SMA-F ZVBP-4810-S+

### Features

- Low insertion loss, 0.7 dB typical
- Good VSWR, 1.3:1 typical
- High rejection
- Fast roll-off
- Connectorized package

### Applications

- Fixed-Satellite
- Radio astronomy
- Defence systems

### Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	-	-	4810	-	MHz	
	Insertion Loss	F1-F2	4750-4870	-	0.7	1.5	dB
	VSWR	F1-F2	4750-4870	-	1.3	1.5	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 4600	20	31	-	dB
	VSWR	DC-F3	DC - 4600	-	20	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	5020-8250	20	31	-	dB
	VSWR	F4-F5	5020-8250	-	20	-	:1

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10 W max.

Permanent damage may occur if any of these limits are exceeded.

### Functional Schematic



### Typical Frequency Response







### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
510	90.70	157.93	4750	6.28
1010	97.97	193.02	4755	5.94
4420	54.36	102.19	4760	5.70
4600	32.77	82.73	4765	5.52
4615	30.11	78.97	4770	5.40
4660	20.40	52.65	4775	5.31
4700	8.58	13.81	4780	5.24
4718	3.16	3.96	4785	5.18
4750	0.67	1.16	4790	5.11
4810	0.63	1.23	4795	5.06
4870	0.69	1.22	4800	5.00
4910	3.56	4.12	4805	4.97
4935	11.65	17.57	4810	4.94
4965	20.48	34.75	4820	4.96
5010	30.50	51.10	4830	5.04
5020	32.36	54.29	4840	5.16
5800	85.95	115.81	4850	5.30
6500	102.48	144.77	4860	5.48
7500	101.36	144.77	4865	5.62
8250	114.23	108.58	4870	5.82

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Coaxial Connections

PORT - 1	SMA-FEMALE
PORT - 2	SMA-FEMALE

## Outline Drawing



## Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K
4.40	1.14	0.91	4.096	3.80	0.800	4.60	0.57	0.10	0.118
111.66	29.03	23.01	104.04	96.42	20.32	116.74	14.50	2.54	3.00
L	M	N	P	Q	R	S	T		Wt.
0.57	0.20	0.30	0.65	3.72	3.30	1.10	1.40		grams
14.53	5.00	7.62	16.51	94.39	83.82	28.02	35.64		160

Note: Please refer to case style drawing for details

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



Typical Performance Data

FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	84.11	84.08	91.22	0.00	0.01	0.01	0.00	0.00	0.00
110	111.27	95.61	98.95	0.03	0.03	0.03	0.02	0.02	0.03
210	104.15	99.88	99.51	0.08	0.08	0.07	0.08	0.08	0.08
310	98.96	91.32	96.79	0.11	0.12	0.11	0.11	0.12	0.11
410	100.04	97.22	96.24	0.11	0.13	0.13	0.11	0.13	0.13
510	117.26	114.97	99.30	0.11	0.14	0.14	0.12	0.13	0.14
610	106.71	95.93	97.17	0.11	0.13	0.14	0.12	0.14	0.15
710	102.75	101.40	101.49	0.10	0.13	0.13	0.10	0.13	0.14
810	99.97	110.00	104.51	0.09	0.12	0.12	0.09	0.11	0.13
910	108.91	104.41	103.59	0.08	0.11	0.12	0.07	0.09	0.11
1010	103.81	105.64	98.64	0.07	0.10	0.11	0.06	0.09	0.11
1210	104.77	99.85	101.28	0.05	0.08	0.10	0.04	0.07	0.10
1410	107.57	119.91	104.99	0.03	0.07	0.09	0.01	0.05	0.08
1610	109.57	100.91	101.45	0.02	0.07	0.09	0.01	0.05	0.08
2010	106.83	104.86	97.71	0.01	0.07	0.10	0.01	0.05	0.09
2510	110.22	102.17	102.60	0.03	0.11	0.14	0.01	0.07	0.13
3510	95.05	92.08	91.29	0.09	0.17	0.21	0.06	0.13	0.20
3810	84.88	83.94	86.85	0.10	0.18	0.22	0.09	0.15	0.21
4010	77.81	78.16	78.66	0.10	0.18	0.22	0.08	0.14	0.20
4310	62.66	62.60	62.58	0.10	0.18	0.21	0.10	0.16	0.21
4510	45.71	45.54	45.41	0.10	0.18	0.21	0.10	0.15	0.20
4600	33.65	33.37	33.12	0.12	0.20	0.23	0.12	0.17	0.22
4615	31.11	30.81	30.53	0.13	0.21	0.24	0.13	0.19	0.24
4665	20.84	20.40	19.97	0.23	0.31	0.35	0.22	0.28	0.34
4690	14.18	13.61	13.07	0.45	0.58	0.65	0.45	0.55	0.64
4710	7.97	7.33	6.74	1.27	1.57	1.84	1.24	1.53	1.81
4720	4.88	4.31	3.82	2.53	3.14	3.72	2.48	3.07	3.65
4725	3.52	3.04	2.65	3.67	4.55	5.40	3.59	4.46	5.29
4750	0.54	0.61	0.66	21.96	30.28	31.30	21.17	26.78	27.55
4800	0.42	0.53	0.59	28.82	30.57	29.76	24.48	24.55	23.72
4810	0.43	0.53	0.60	23.57	24.73	24.05	22.02	22.56	21.75
4825	0.44	0.54	0.60	21.55	22.31	22.27	21.16	21.73	21.43
4500	46.84	46.64	46.52	0.10	0.18	0.21	0.10	0.15	0.21
4800	0.42	0.53	0.59	28.82	30.57	29.76	24.48	24.55	23.72
4870	0.48	0.57	0.64	21.24	24.18	24.79	21.90	25.26	26.35
4900	0.71	1.04	1.26	15.58	12.11	10.74	15.50	12.15	10.79
4910	1.63	2.26	2.70	7.60	6.17	5.46	7.55	6.16	5.48
4920	3.72	4.60	5.23	3.58	3.07	2.77	3.55	3.05	2.79
4940	10.02	10.88	11.58	0.99	1.02	1.02	0.95	0.98	1.01
4950	13.21	13.98	14.64	0.64	0.72	0.77	0.60	0.67	0.75
4960	16.19	16.87	17.49	0.47	0.57	0.63	0.43	0.52	0.61
4970	18.94	19.55	20.13	0.37	0.49	0.55	0.34	0.43	0.52
5000	26.06	26.53	27.01	0.25	0.37	0.43	0.23	0.32	0.41
5020	30.08	30.47	30.92	0.22	0.33	0.39	0.19	0.28	0.37
5050	35.31	35.63	36.02	0.19	0.30	0.36	0.16	0.24	0.33
5100	42.56	42.80	43.12	0.15	0.26	0.32	0.13	0.21	0.30
5250	58.07	58.17	58.35	0.11	0.22	0.27	0.10	0.18	0.25
6000	93.80	95.96	88.30	0.04	0.15	0.19	0.05	0.13	0.19
6250	95.62	104.29	97.76	0.03	0.14	0.17	0.05	0.12	0.18
6500	99.96	102.31	96.22	0.02	0.13	0.16	0.04	0.11	0.17
6750	107.10	103.91	99.03	0.01	0.12	0.15	0.04	0.11	0.17
7000	104.34	104.21	106.53	0.01	0.11	0.15	0.04	0.11	0.17
7250	105.21	117.60	102.68	0.01	0.11	0.14	0.04	0.11	0.17
7500	105.38	101.50	109.20	0.01	0.11	0.14	0.04	0.11	0.18
7750	100.41	95.11	97.11	0.02	0.12	0.15	0.04	0.12	0.19
8000	105.97	98.61	98.44	0.02	0.12	0.16	0.04	0.13	0.20
8050	96.17	100.84	101.16	0.02	0.12	0.16	0.03	0.12	0.20
8100	102.57	97.15	108.50	0.03	0.13	0.16	0.04	0.13	0.21
8150	103.02	106.41	96.02	0.03	0.13	0.16	0.03	0.12	0.20
8250	94.94	106.30	100.21	0.03	0.13	0.17	0.04	0.13	0.21



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site







The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS


## Typical Performance Data

FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
4750	7.12	6.87	6.65
4752	6.92	6.67	6.47
4754	6.73	6.48	6.30
4756	6.54	6.31	6.15
4758	6.37	6.16	6.01
4760	6.22	6.02	5.88
4762	6.08	5.89	5.78
4764	5.95	5.78	5.68
4766	5.84	5.69	5.60
4768	5.74	5.60	5.52
4770	5.66	5.53	5.46
4774	5.51	5.41	5.36
4778	5.40	5.32	5.28
4782	5.32	5.24	5.21
4786	5.24	5.18	5.15
4790	5.18	5.13	5.10
4794	5.13	5.08	5.06
4798	5.08	5.04	5.02
4802	5.03	5.00	4.98
4806	5.00	4.97	4.95
4810	4.96	4.94	4.93
4814	4.94	4.92	4.91
4818	4.92	4.91	4.91
4822	4.92	4.91	4.91
4826	4.92	4.92	4.92
4830	4.94	4.94	4.95
4834	4.96	4.96	4.98
4838	5.00	5.00	5.02
4842	5.04	5.04	5.06
4846	5.08	5.09	5.11
4850	5.13	5.14	5.17
4854	5.18	5.20	5.23
4858	5.24	5.27	5.31
4862	5.31	5.35	5.40
4866	5.39	5.45	5.51
4868	5.43	5.51	5.57
4870	5.49	5.58	5.65


## Typical Performance Curves



## Typical Performance Curves



### Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	P
ME1656	4.40 (111.66)	1.14 (29.03)	0.91 (23.01)	4.096 (104.04)	3.80 (96.42)	0.800 (20.32)	4.60 (116.74)	0.57 (14.50)	0.10 (2.54)	0.118 (3.00)	0.57 (14.53)	0.20 (5.00)	0.30 (7.62)	0.65 (16.51)

CASE #.	Q	R	S	T	WT, GRAM
ME1656	3.72 (94.39)	3.30 (83.82)	1.10 (28.02)	1.40 (35.64)	160

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

#### Notes:

1. Case material: Aluminum alloy.
2. Case finish: Powder coated.
3. Refer to the individual model data sheet for the type of connectors available.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215