

Cavity Bandpass Filters

50Ω DC to 40 GHz



The Big Deal

- Very low insertion loss with excellent power handling
- Very fast roll-off with wide stopband
- Passbands up to 36 GHz
- Stopbands up to 40 GHz

Product Overview

Mini-Circuits' cavity filters are designed by implementing resonant structures with very high Q and are ideal for narrow-band, high-selectivity applications. These designs can provide bandwidths as narrow as 1% with very high selectivity and excellent low noise floor. Low insertion loss combined with excellent power handling makes them well-suited for transmitter and receiver front end. Advanced filter design and construction enables stopband width greater than 3x the center frequency.

Mini-Circuits' cavity filters feature a special protective assembly to prevent accidental de-tuning that would otherwise require expensive replacement or return to factory for re-tuning. Custom integrated assembly with LNA and bias tees results in greatly simplifying system integration. Precise machining allows realization of cavity filters with small form factors for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitter
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide spur free band results in better receiver sensitivity
High power handling	Well suited for transmitter application
Protective assembly	Prevents accidental de-tuning of precisely tuned resonant circuit

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bandpass Filter

ZVBP-8250-S+

50Ω 8025 to 8475 MHz



Generic photo used for illustration purposes only

CASE STYLE: PN2113

Connectors	Model
SMA-F/M	ZVBP-8250-S+

Features

- Low insertion loss, 1.0 dB typical
- High rejection
- Fast roll-off
- Connectorized package
- Small size

Applications

- Satellite
- Radar

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit	
Pass Band	Center Frequency	-	-	8250	-	MHz	
	Insertion Loss	F1-F2	8025-8475	-	1.0	1.5	dB
	VSWR	F1-F2	8025-8475	-	1.5	1.7	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 7650	20	28	-	dB
	VSWR	DC-F3	DC - 7650	-	40	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	8925-11000	20	28	-	dB
	VSWR	F4-F5	8925-11000	-	40	-	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10 W max.

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
100	91.71	347.44	8025	2.22
500	105.19	108.58	8050	1.98
3000	101.78	124.09	8075	1.86
7000	58.19	64.35	8100	1.78
7650	29.90	57.91	8125	1.75
7770	20.80	44.55	8150	1.71
7940	3.18	3.63	8175	1.67
7950	2.42	2.81	8200	1.63
8000	0.85	1.05	8225	1.60
8025	0.81	1.26	8250	1.57
8250	0.71	1.31	8260	1.57
8475	0.76	1.18	8275	1.57
8500	0.79	1.02	8300	1.58
8570	2.45	2.84	8325	1.60
8580	3.07	3.50	8350	1.63
8780	20.10	41.37	8375	1.65
8925	28.85	66.82	8400	1.68
9300	43.24	75.53	8425	1.72
9800	54.20	96.51	8450	1.79
11000	64.38	96.51	8475	1.90

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

PORT - 1	SMA-FEMALE
PORT - 2	SMA-MALE

Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F	G	H
2.72	.83	.85	2.09	.16	.61	.08	.41
69.00	21.00	21.50	53.00	4.00	15.50	2.00	10.50
J	K	L	M	N	Wt.		
.30	.472	2.401	.150	.18	grams		
7.50	12.00	61.00	3.81	4.50	56		

Note: Please refer to case style drawing for details.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp









Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	69.12	76.87	74.50	0.03	0.04	0.03	0.02	0.03	0.03
40	100.37	104.26	100.59	0.03	0.03	0.03	0.01	0.02	0.02
450	100.19	105.17	118.86	0.13	0.15	0.14	0.08	0.10	0.11
1450	110.58	116.80	104.88	0.14	0.18	0.19	0.09	0.14	0.15
3900	105.62	98.50	105.37	0.00	0.12	0.20	0.01	0.11	0.20
4600	93.21	94.65	95.89	0.01	0.15	0.25	0.02	0.10	0.19
5025	93.47	93.71	92.35	0.03	0.17	0.27	0.01	0.12	0.22
5850	81.83	82.34	82.00	0.09	0.23	0.31	0.01	0.15	0.24
6725	65.49	65.76	65.77	0.15	0.27	0.31	0.03	0.17	0.24
7375	44.47	44.62	44.70	0.13	0.23	0.24	0.07	0.19	0.22
7650	29.92	29.90	29.81	0.21	0.30	0.30	0.11	0.22	0.23
7780	20.11	19.92	19.61	0.30	0.39	0.41	0.25	0.37	0.40
7830	15.43	15.12	14.67	0.51	0.61	0.65	0.42	0.56	0.61
7910	6.71	6.18	5.54	1.93	2.25	2.70	1.86	2.24	2.71
7945	3.24	2.79	2.34	4.73	5.63	7.06	4.64	5.64	7.14
7960	2.16	1.82	1.55	7.12	8.55	10.89	7.01	8.60	11.10
7980	1.26	1.10	1.03	12.31	15.16	20.42	12.07	15.29	21.59
7990	1.02	0.94	0.94	16.42	20.99	28.19	15.87	21.14	34.44
8000	0.87	0.85	0.90	23.16	32.25	23.53	21.06	30.90	24.05
8010	0.79	0.81	0.90	42.09	25.66	19.05	25.48	25.10	19.11
8020	0.76	0.81	0.91	24.87	20.23	16.64	22.33	20.02	16.58
8025	0.76	0.81	0.92	21.96	18.72	15.87	20.52	18.56	15.78
8075	0.75	0.82	0.91	15.42	15.36	15.02	15.22	15.31	14.80
8095	0.71	0.77	0.85	16.24	16.73	16.95	16.04	16.61	16.51
8105	0.69	0.75	0.82	17.10	17.89	18.47	16.87	17.74	17.82
8110	0.68	0.74	0.81	17.63	18.60	19.39	17.38	18.40	18.58
8120	0.65	0.71	0.79	18.85	20.25	21.60	18.58	19.96	20.32
8140	0.61	0.68	0.75	22.73	25.66	29.45	22.37	24.60	24.39
8160	0.58	0.66	0.74	31.72	41.39	30.85	28.66	28.38	24.43
8165	0.58	0.66	0.75	35.77	36.40	27.86	30.04	27.63	23.51
8195	0.58	0.67	0.77	25.48	22.56	19.86	24.46	21.18	18.75
8230	0.60	0.70	0.80	19.32	18.18	16.63	19.02	17.61	16.22
8250	0.61	0.71	0.81	18.01	17.42	16.18	17.98	17.08	15.96
8320	0.60	0.67	0.75	19.18	20.69	20.38	19.72	21.05	20.75
8325	0.59	0.67	0.75	19.62	21.38	21.17	20.23	21.90	21.69
8350	0.58	0.66	0.74	22.14	25.57	26.52	24.21	30.02	30.24
8360	0.58	0.66	0.74	23.06	26.60	28.06	26.32	39.20	36.04
8365	0.58	0.66	0.74	23.48	26.72	28.12	27.24	51.39	35.66
8380	0.58	0.67	0.76	24.15	25.23	25.74	28.36	30.76	27.90
8395	0.59	0.69	0.78	23.35	22.67	22.66	26.36	24.85	23.28
8400	0.60	0.70	0.79	22.86	21.87	21.78	25.51	23.58	22.16
8460	0.66	0.76	0.85	20.42	19.40	19.72	20.70	19.53	19.31
8475	0.68	0.76	0.85	22.24	21.58	22.47	22.25	21.47	21.72
8490	0.70	0.77	0.87	26.10	26.95	30.33	26.11	26.53	28.66
8495	0.71	0.78	0.87	28.04	30.75	38.50	28.43	30.01	34.63
8500	0.72	0.79	0.89	30.25	38.42	38.53	31.62	35.50	38.67
8530	0.93	1.04	1.24	17.13	15.87	14.07	17.57	15.92	14.29
8570	2.07	2.45	2.96	7.14	6.39	5.69	7.30	6.42	5.72
8595	3.59	4.19	4.89	4.06	3.67	3.34	4.15	3.66	3.31
8680	11.22	12.05	12.87	0.76	0.87	0.94	0.77	0.83	0.88
8750	17.15	17.91	18.65	0.32	0.48	0.58	0.31	0.43	0.51
8790	20.08	20.81	21.50	0.25	0.41	0.50	0.19	0.32	0.40
8925	28.29	28.85	29.41	0.09	0.26	0.36	0.05	0.19	0.26
8975	30.80	31.31	31.81	0.11	0.27	0.35	0.03	0.17	0.25
9100	36.20	36.59	37.02	0.03	0.20	0.29	0.02	0.11	0.18
9300	42.98	43.24	43.53	0.08	0.23	0.27	0.03	0.12	0.18
9625	51.00	51.03	51.18	0.03	0.18	0.24	0.10	0.06	0.14
9800	54.18	54.20	54.26	0.02	0.18	0.23	0.10	0.07	0.15
10400	61.34	61.45	61.31	0.02	0.18	0.22	0.08	0.11	0.20
11000	64.46	64.38	64.32	0.04	0.18	0.21	0.06	0.16	0.29


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
8025	2.30	2.22	2.13
8035	2.18	2.11	2.03
8040	2.13	2.06	1.99
8050	2.04	1.98	1.93
8060	1.97	1.92	1.88
8070	1.91	1.88	1.84
8075	1.89	1.86	1.83
8080	1.87	1.84	1.81
8090	1.83	1.81	1.79
8100	1.80	1.78	1.77
8110	1.78	1.77	1.76
8120	1.77	1.75	1.74
8130	1.75	1.74	1.73
8140	1.74	1.73	1.72
8150	1.73	1.71	1.70
8155	1.72	1.70	1.69
8160	1.71	1.70	1.68
8165	1.70	1.69	1.68
8170	1.70	1.68	1.67
8175	1.69	1.67	1.66
8180	1.68	1.67	1.65
8185	1.67	1.66	1.64
8190	1.67	1.65	1.63
8195	1.66	1.64	1.62
8200	1.65	1.63	1.62
8205	1.64	1.63	1.61
8210	1.64	1.62	1.60
8215	1.63	1.61	1.59
8220	1.63	1.61	1.59
8225	1.62	1.60	1.58
8230	1.61	1.59	1.58
8235	1.61	1.59	1.57
8240	1.60	1.58	1.57
8245	1.60	1.58	1.56
8250	1.59	1.57	1.56
8255	1.59	1.57	1.56
8260	1.59	1.57	1.56
8265	1.58	1.57	1.56
8270	1.58	1.57	1.56
8280	1.58	1.57	1.57
8290	1.58	1.58	1.57
8300	1.59	1.58	1.58
8310	1.59	1.59	1.59
8320	1.60	1.60	1.60
8330	1.61	1.61	1.61
8340	1.62	1.62	1.62
8350	1.63	1.63	1.63
8360	1.64	1.64	1.64
8370	1.65	1.65	1.65
8380	1.66	1.66	1.66
8390	1.67	1.67	1.67
8400	1.68	1.68	1.68
8410	1.69	1.69	1.69
8420	1.71	1.71	1.71
8430	1.73	1.73	1.74
8440	1.75	1.75	1.77
8450	1.78	1.79	1.81
8460	1.81	1.83	1.85
8470	1.86	1.88	1.91
8475	1.88	1.90	1.94

Typical Performance Curves




Typical Performance Curves



Outline Dimensions

PN2113



CASE#	A	B	C	D	E	F	G	H
PN2113	2.72 (69.00)	.83 (21.00)	.85 (21.50)	2.09 (53.00)	.16 (4.00)	.61 (15.50)	.08 (2.00)	.41 (10.50)

CASE#	J	K	L	M	N	WT. GRAMS
PN2113	.30 (7.50)	.472 (12.00)	2.401 (61.00)	.150 (3.81)	.18 (4.50)	56

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish: Powder coated.
3. Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A