



CAVITY COAXIAL

# Bandpass Filter

ZVBP-K27G+

50Ω 24 to 30 GHz 2.92mm Female

## KEY FEATURES

- Low Insertion Loss, 0.4dB Typ.
- Good Return Loss, 14dB Typ.
- High Rejection, 70dB Typ.
- Power Handling: 2.5W
- Stopband Up to 50GHz

## APPLICATIONS

- 5G Millimeter Wave Communicatios.
- Telecommunication.


## PRODUCT OVERVIEW

Mini-Circuits' cavity filters are designed by implementing resonant structures with very high Q and are ideal for narrow-band, high-selectivity applications. These designs can provide bandwidths as narrow as 3% with very high selectivity and excellent low noise floor. Low insertion loss combined with excellent power handling makes them well-suited for transmitter and receiver front end. Advanced filter design and construction enables stopband width greater than 3x the center frequency.



Generic photo used for illustration purposes only

## FUNCTIONAL DIAGRAM



## ELECTRICAL SPECIFICATIONS<sup>1,2</sup> AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency	Fc	—	—	27	—	GHz
	1dB Bandwidth	—	—	6	—	—	GHz
	Insertion Loss	Fc	27	—	0.4	0.8	dB
	Return Loss	F1-F2	24 - 30	—	14	—	dB
Stop Band, Lower	Rejection	DC-F3	DC - 9	60	77	—	dB
		F3-F4	9 - 17	45	54	—	dB
Stop Band, Upper	Rejection	F5-F6	37 - 45	45	55	—	dB
		F6-F7	45 - 50	60	68	—	dB

1. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

2. Data measured after calibrating using 2.92mm cal kit.

## ABSOLUTE MAXIMUM RATINGS<sup>3,4</sup>


Parameter	Ratings
Operating Temperature	-30°C to +70°C
Storage Temperature	-30°C to +70°C
Input Power <sup>5</sup>	2.5W at 25°C

3. Permanent damage may occur if any of these limits are exceeded.

4. Input and output ports are DC short to ground.

5. Power rating applies only to signals within the passband.





## TYPICAL FREQUENCY RESPONSE AT +25°C





# Bandpass Filter

### TYPICAL PERFORMANCE GRAPHS





CAVITY COAXIAL

# Bandpass Filter

## ZVBP-K27G+


Mini-Circuits

50Ω 24 to 30 GHz 2.92mm Female

### CONNECTOR DESCRIPTION

Function	Marking on Unit	Connector
RF1 <sup>1</sup>	1	2.92mm Female
RF2 <sup>1</sup>	2	2.92mm Female

### CASE STYLE DRAWING



Unit Weight: 35 Grams.  
Dimensions are in inches (mm). Tolerances: 2 Pl. + .100; 3 Pl. + .015

### PRODUCT MARKING\*: ZVBP-K27G+

\*Marking may contain other features or characters for internal lot control.





CAVITY COAXIAL

# Bandpass Filter

ZVBP-K27G+

50Ω 24 to 30 GHz 2.92mm Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	ZL3532
RoHS Status	Compliant
Environmental Ratings	ENV001

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)








## Typical Performance Data

FREQ.  (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-30°C	@+25°C	@+70°C	@-30°C	@+25°C	@+70°C	@-30°C	@+25°C	@+70°C
100	104.17	98.10	106.54	0.01	0.00	0.01	0.00	0.02	0.03
200	95.06	97.46	111.34	0.00	0.01	0.02	0.02	0.03	0.04
400	96.77	94.35	99.89	0.01	0.02	0.03	0.03	0.04	0.06
800	93.95	89.64	98.33	0.01	0.03	0.04	0.04	0.06	0.08
1000	92.49	101.59	91.44	0.01	0.03	0.04	0.03	0.06	0.08
1500	91.42	94.36	91.34	0.01	0.03	0.05	0.02	0.05	0.08
2000	96.59	91.29	89.94	0.01	0.03	0.05	0.02	0.05	0.08
2400	85.57	88.41	88.41	0.00	0.03	0.05	0.01	0.05	0.08
3000	86.82	92.18	86.33	0.01	0.02	0.04	0.01	0.04	0.07
3500	88.38	86.44	88.82	0.02	0.01	0.03	0.03	0.02	0.05
4500	83.47	86.16	85.76	0.08	0.04	0.02	0.06	0.01	0.03
5500	84.37	83.21	83.80	0.10	0.06	0.04	0.07	0.01	0.03
9000	76.90	77.86	77.76	0.08	0.13	0.17	0.11	0.18	0.23
9500	75.80	76.22	76.66	0.09	0.15	0.18	0.11	0.19	0.24
11000	73.39	73.47	73.51	0.07	0.14	0.17	0.06	0.14	0.19
12000	70.69	70.12	70.62	0.02	0.09	0.12	0.02	0.07	0.12
13000	67.58	67.44	67.70	0.04	0.03	0.06	0.12	0.02	0.04
14500	63.05	62.99	62.73	0.09	0.02	0.01	0.20	0.10	0.03
15000	61.07	61.38	61.31	0.09	0.02	0.02	0.19	0.10	0.02
16000	57.77	57.69	57.79	0.05	0.03	0.07	0.14	0.04	0.04
17000	53.79	53.73	53.70	0.03	0.11	0.16	0.03	0.07	0.16
18500	46.93	46.89	46.86	0.13	0.23	0.28	0.15	0.26	0.37
20000	38.25	38.25	38.18	0.18	0.28	0.33	0.25	0.38	0.47
22000	22.03	22.08	21.91	0.08	0.19	0.22	0.03	0.16	0.22
22500	16.42	16.45	16.23	0.11	0.21	0.25	0.01	0.12	0.19
23000	9.83	9.78	9.54	0.46	0.60	0.68	0.28	0.44	0.57
23500	3.03	2.94	2.84	3.16	3.55	3.86	2.93	3.32	3.68
24000	0.22	0.33	0.40	19.31	21.63	22.43	17.30	18.51	19.13
25500	0.13	0.27	0.34	21.33	21.00	22.06	24.46	23.54	25.09
26000	0.18	0.31	0.38	16.85	17.19	17.53	16.40	16.93	17.16
26500	0.15	0.28	0.37	18.57	19.91	19.27	17.78	19.17	18.60
27000	0.12	0.26	0.34	30.40	32.63	30.65	29.76	31.05	30.07
28500	0.14	0.28	0.37	23.67	27.15	26.73	22.56	25.70	25.29
29000	0.20	0.36	0.44	20.06	19.85	19.93	19.34	19.13	19.15
29500	0.28	0.41	0.48	15.41	16.54	17.13	15.04	16.21	16.78
30000	0.37	0.60	0.79	16.87	14.77	13.27	17.34	14.98	13.47
30400	3.33	3.76	4.24	3.33	3.23	2.93	3.29	3.18	2.92
31000	12.22	12.59	13.07	0.23	0.37	0.38	0.15	0.32	0.39
32000	24.33	24.66	25.03	0.19	0.05	0.01	0.20	0.01	0.10
33000	33.34	33.64	34.07	0.17	0.03	0.06	0.17	0.02	0.16
33500	37.20	37.43	37.86	0.11	0.02	0.12	0.08	0.08	0.23
34000	40.56	40.85	41.30	0.04	0.08	0.19	0.01	0.14	0.30
34500	43.78	44.02	44.48	0.03	0.16	0.26	0.02	0.15	0.32
35000	46.82	46.77	47.19	0.11	0.25	0.35	0.10	0.22	0.38
35500	49.34	49.62	49.91	0.22	0.35	0.44	0.17	0.33	0.46
36000	51.85	51.89	51.96	0.30	0.42	0.51	0.18	0.35	0.48
36500	53.92	53.92	54.57	0.36	0.48	0.57	0.20	0.36	0.49
37000	56.33	56.16	56.28	0.40	0.53	0.61	0.21	0.36	0.52
37500	57.60	58.60	57.69	0.40	0.55	0.62	0.25	0.42	0.59
38000	59.40	59.66	59.05	0.39	0.54	0.61	0.24	0.46	0.58
38500	60.77	61.62	60.79	0.39	0.54	0.61	0.19	0.40	0.54
39000	62.40	62.06	62.09	0.34	0.51	0.58	0.17	0.40	0.53
39500	63.04	62.44	64.97	0.30	0.48	0.53	0.17	0.43	0.52
40000	65.78	65.71	63.99	0.25	0.44	0.48	0.13	0.41	0.49
40500	66.23	66.03	66.00	0.20	0.39	0.43	0.02	0.30	0.40
41000	67.06	66.67	67.62	0.08	0.28	0.31	0.05	0.22	0.30
41500	67.43	68.47	67.33	0.00	0.20	0.22	0.11	0.20	0.24
42000	68.55	72.64	72.70	0.08	0.10	0.13	0.21	0.10	0.15
45000	74.46	72.58	86.28	0.33	0.16	0.06	0.58	0.40	0.20
50000	75.79	81.00	71.58	0.08	0.27	0.42	0.36	0.53	0.73

## Typical Performance Data


FREQ.  (MHz)	GROUP DELAY		
	(nsec)		
	@-30°C	@+25°C	@+70°C
24000	0.42	0.42	0.41
24200	0.38	0.37	0.37
24310	0.36	0.36	0.35
24400	0.35	0.34	0.34
24600	0.33	0.33	0.33
24500	0.34	0.33	0.33
24650	0.33	0.32	0.32
24900	0.32	0.31	0.31
25230	0.31	0.31	0.31
25500	0.30	0.30	0.30
25670	0.29	0.29	0.29
25750	0.29	0.29	0.29
25910	0.29	0.29	0.29
26000	0.29	0.29	0.29
26210	0.29	0.29	0.29
26440	0.28	0.28	0.28
26660	0.29	0.29	0.29
27000	0.29	0.29	0.29
27250	0.29	0.28	0.29
27410	0.29	0.28	0.29
27430	0.29	0.28	0.29
27680	0.29	0.29	0.29
28080	0.29	0.29	0.29
28300	0.30	0.30	0.30
28400	0.30	0.30	0.30
28510	0.30	0.30	0.30
28610	0.31	0.31	0.31
28990	0.32	0.32	0.32
29010	0.32	0.32	0.32
29020	0.32	0.32	0.32
29030	0.32	0.32	0.32
29040	0.32	0.32	0.32
29050	0.32	0.32	0.32
29060	0.32	0.32	0.32
29070	0.32	0.32	0.32
29610	0.36	0.37	0.37
29650	0.37	0.38	0.38
29700	0.38	0.39	0.39
29800	0.41	0.41	0.42
29900	0.43	0.44	0.45
30000	0.46	0.46	0.47

## Typical Performance Curves



## Outline Dimensions

ZL3532



Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm$  .100; 3 Pl.  $\pm$  .015

### Notes:

1. Case material: Brass.
2. Case Finish: Powder coated.
3. Unit Weight: 35 Grams.
4. Refer to the individual model data sheet for the type of connectors available.

 **Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
 minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet