

Coaxial Directional Coupler

50Ω 5 to 1200 MHz

ZX30-9-4-S+



Generic photo used for illustration purposes only

CASE STYLE: FL905

Connectors Model
SMA ZX30-9-4-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	1
OUTPUT	2
COUPLED	3

Features

- very flat coupling
- very broad, multi-octave
- all welded construction
- protected by U.S. Patents 6,140,887 & 6,784,521 & 6,790,049

Applications


- VHF/UHF
- communications receivers & transmitters
- cellular
- instrumentation

Directional Coupler Electrical Specifications (T_{AMB} = 25°C)

FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT, W		
	Nom.	Typ. Flatness	L		M		U		L		M		U			Typ.	L	MU
f _L -f _U			Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Max.	
5-1200	8.9±0.5	±0.1	1.1	1.4	1.1	1.4	1.3	1.8	21	19	20	15	16	12	1.2	0.5	1.0	

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]
1. Mainline loss includes theoretical power loss at coupled port.

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.74	.90	.54	.50	.04	.16	.29
18.80	22.86	13.72	12.70	1.02	4.06	7.37
H	J	K	L	M	N	wt
.37	--	.122	.496	.106	.122	grams
9.40	--	3.10	12.60	2.69	3.10	20.0


Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
5.00	1.07	8.84	21.39	19.47	31.15	19.43
50.00	1.05	8.84	21.49	20.10	33.43	20.04
100.00	1.06	8.86	21.35	20.20	32.64	19.97
200.00	1.08	8.88	20.91	20.25	30.27	19.49
400.00	1.12	8.88	19.77	19.93	26.11	17.56
600.00	1.18	8.86	18.46	19.22	23.13	15.39
800.00	1.27	8.85	17.21	18.44	20.89	13.50
1000.00	1.38	8.86	16.07	17.66	19.30	11.99
1100.00	1.46	8.87	15.50	17.40	18.78	11.37
1200.00	1.54	8.88	14.90	17.03	18.14	10.77


ZX30-9-4-S+ MAINLINE LOSS




ZX30-9-4-S+ COUPLING & DIRECTIVITY



ZX30-9-4-S+ RETURN LOSS



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TERMINATION THAT ROUTES DC FROM RF PORTS TO GROUND.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp



Directional Coupler

ZX30-9-4+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
5.0	1.07	8.82	21.34	19.53	31.41	19.58
10.0	1.05	8.82	21.49	19.84	33.08	19.96
15.0	1.05	8.81	21.51	19.94	33.46	20.00
20.0	1.05	8.82	21.48	19.99	33.60	20.04
50.0	1.06	8.84	21.37	20.07	33.68	20.10
80.0	1.07	8.87	21.24	20.19	33.31	20.11
100.0	1.08	8.84	21.17	20.23	33.06	20.15
125.0	1.07	8.85	21.05	20.27	32.81	20.05
150.0	1.07	8.87	20.91	20.28	32.63	19.93
200.0	1.09	8.88	20.63	20.38	31.52	19.63
250.0	1.09	8.89	20.31	20.51	30.51	19.19
275.0	1.10	8.88	20.15	20.49	30.22	18.97
300.0	1.10	8.88	19.95	20.45	29.95	18.73
325.0	1.09	8.88	19.77	20.47	29.59	18.49
350.0	1.10	8.88	19.57	20.43	29.09	18.19
375.0	1.10	8.89	19.37	20.43	28.57	17.85
400.0	1.10	8.89	19.17	20.44	28.10	17.57
450.0	1.11	8.89	18.76	20.30	27.23	16.98
475.0	1.13	8.91	18.54	20.30	26.62	16.66
500.0	1.13	8.89	18.36	20.29	26.08	16.36
525.0	1.13	8.89	18.13	20.23	25.70	16.05
550.0	1.15	8.89	17.95	20.10	25.45	15.75
575.0	1.15	8.91	17.71	19.95	25.12	15.47
600.0	1.17	8.90	17.51	19.85	24.66	15.17
625.0	1.17	8.90	17.30	19.80	24.21	14.89
650.0	1.18	8.94	17.11	19.73	23.86	14.61
675.0	1.19	8.90	16.91	19.60	23.56	14.38
700.0	1.19	8.86	16.72	19.39	23.20	14.07
725.0	1.19	8.93	16.53	19.23	22.78	13.81
750.0	1.22	8.97	16.34	19.11	22.35	13.54
775.0	1.24	8.92	16.15	18.99	21.99	13.32
800.0	1.23	8.88	15.96	18.86	21.72	13.08
825.0	1.23	8.95	15.80	18.66	21.45	12.86
850.0	1.25	9.02	15.61	18.44	21.13	12.61
875.0	1.29	8.96	15.44	18.28	20.73	12.38
900.0	1.28	8.91	15.30	18.19	20.38	12.17
925.0	1.28	8.98	15.11	18.06	20.10	11.97
950.0	1.30	9.00	14.96	17.90	19.92	11.76
975.0	1.32	9.02	14.81	17.65	19.63	11.55
1000.0	1.35	8.99	14.67	17.43	19.23	11.35

REV. X1
 ZX30-9-4+
 060718
 Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661







The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Directional Coupler

ZX30-9-4+

Typical Performance Curves



REV. X1
ZX30-9-4+
060718
Page 1 of 1




IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
FL905	.74 (18.80)	.90 (22.86)	.54 (13.72)	.50 (12.70)	.04 (1.02)	.16 (4.06)	.29 (7.37)	.37 (9.40)	- -	.122 (3.10)	.496 (12.60)	.106 (2.69)	.122 (3.10)	20.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$.

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I