



COAXIAL

Low Noise Amplifier


ZX60-06183P+

Mini-Circuits

50Ω 6 to 18 GHz Positive Gain Slope SMA Female

KEY FEATURES

- Wideband, 6 to 18 GHz
- High gain, 24 dB typ.
- Low noise figure, 1.7 dB typ at 15 GHz.
- Voltage regulated internally and reverse voltage protected
- Excellent directivity, 30 dB typ.




Generic photo used for illustration purposes only

APPLICATIONS

- Microwave point to point radios
- Military EW and radar
- Satellite Systems

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' ZX60-06183P+ is a wideband, low noise, connectorized amplifier, providing a unique combination of low noise figure and high gain over a very wide frequency range. It supports a wide range of applications and many systems where high performance over wideband is needed. This design operates on a single +5V supply and comes in a rugged, compact unibody case (0.74 x 0.75 x 0.46") with SMA connectors, making it an excellent candidate for tough operating conditions and crowded system layouts.

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Units
Frequency Range		6		18	GHz
Noise Figure	6-8	—	1.6	—	dB
	8-13	—	1.6	—	
	13-17	—	1.6	—	
	17-18	—	1.8	—	
Gain	6-8	—	24	—	dB
	8-13	—	24	—	
	13-17	—	25	—	
	17-18	—	27	—	
Input Return Loss	6-8	—	8	—	dB
	8-13	—	13	—	
	13-17	—	11	—	
	17-18	—	6	—	
Output Return Loss	6-8	—	9	—	dB
	8-13	—	17	—	
	13-17	—	12	—	
	17-18	—	10	—	
Output Power at 1dB Compression (P1dB) ¹	6-8	—	+8.0	—	dBm
	8-13	—	+6.5	—	
	13-17	—	+8.0	—	
	17-18	—	+9.0	—	
Output Third Order Intercept Point (OIP3) ²	6-8	—	+19	—	dBm
	8-13	—	+16.5	—	
	13-17	—	18.5	—	
	17-18	—	+21.0	—	
Device Operating Voltage (V _{DD})	—	+4.75	+5.0	+10	V
Device Operating Current (I _{DD})	—	—	56	75	mA

1. Current increases at P1dB

2. OIP3 measured with 0 dBm tones and 1 MHz spacing.

REV. A
 ECO-020150
 ZX60-06183P+
 MCL NY
 231206





COAXIAL

Low Noise Amplifier


ZX60-06183P+

Mini-Circuits


50Ω 6 to 18 GHz Positive Gain Slope SMA Female

TYPICAL PERFORMANCE GRAPHS


GAIN




DIRECTIVITY




RETURN LOSS




OUTPUT POWER AT 1dB COMPRESSION



NOISE FIGURE



OUTPUT IP3





COAXIAL

Low Noise Amplifier

ZX60-06183P+

Mini-Circuits


50Ω 6 to 18 GHz Positive Gain Slope SMA Female

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Total Power Dissipation	0.9 W
Input Power (CW), Vd=5V	+13 dBm
DC Voltage ³	+10.5 V

3. See max voltage derating chart below.
Permanent damage may occur if any of these limits are exceeded.

Max Voltage Derating



DETERMINING MAXIMUM THERMAL RESISTANCE OF USERS' EXTERNAL HEAT SINK

MAXIMUM THERMAL RESISTANCE	$= \frac{\text{MAXIMUM OPERATING CASE TEMP} - \text{MAXIMUM USER AMBIENT TEMP}}{\text{POWER DISSIPATION}}$
Example:	MAXIMUM OPERATING CASE TEMP = +50 °C (CHECK MAXIMUM RATINGS TABLE FOR THIS VALUE) MAXIMUM USER AMBIENT TEMP = +30 °C (USER DEFINED) POWER DISSIPATION = 10 WATTS (CHECK MAXIMUM RATINGS TABLE FOR THIS VALUE) THEN MAXIMUM ALLOWABLE THERMAL RESISTANCE = 2 °C/W





COAXIAL


Low Noise Amplifier

ZX60-06183P+

Mini-Circuits

50Ω 6 to 18 GHz Positive Gain Slope SMA Female

CASE STYLE DRAWING



Weight: 23.0 grams

Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.03; 3 Pl. ±.015 Inches

NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminal. See Application Note [AN-40-010](#)

OUTLINE DIMENSIONS (Inches/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	wt
.74	.75	.46	1.18	.04	.17	.45	.59	.33	.21	.22	.14	1.00	.37	.18	.106	grams
18.80	19.1	11.68	30.0	1.02	4.32	11.4	14.99	8.38	5.33	5.59	3.56	25.40	9.40	4.57	2.69	23.0





COAXIAL

Low Noise Amplifier

ZX60-06183P+

Mini-Circuits

50Ω 6 to 18 GHz Positive Gain Slope SMA Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD.

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
RoHS Status	Compliant
Environmental Ratings	ENV23T10

ORDERING INFORMATION

Model No. Link	ZX60-06183P+
Case Style	GC957
Connector	IN SMA/Female / OUT SMA/Female

- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)







Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5V, Id = 51mA @ Temperature = +25°C

FREQUENCY (GHz)	GAIN (dB)	ACTIVE DIRECTIVITY (dB)	RETURN LOSS (dB)		STABILITY		Pout @ 1 dB COMPRESSION (dBm)	NOISE FIGURE (dB)	OIP3 (dBm)
			IN	OUT	K	Measure			
5.0	24.3	41	7.6	6.8	38	0.9	9.1	1.5	21.1
5.5	24.2	39	7.4	7.2	30	1.0	9.2	1.5	21.6
6.0	24.0	37	7.2	7.7	23	1.0	9.1	1.5	21.6
6.5	24.0	35	7.1	8.1	20	1.0	8.6	1.6	20.1
7.0	24.1	34	7.5	8.7	18	1.0	8.2	1.6	18.9
7.5	24.3	33	8.2	9.3	17	1.0	7.7	1.6	18.1
8.0	24.6	33	9.2	10.2	19	1.0	7.2	1.6	17.3
8.5	24.8	32	10.7	11.3	17	1.0	6.8	1.6	16.4
9.0	25.0	32	12.4	13.3	17	1.0	6.5	1.5	16.5
9.5	25.1	32	14.2	15.9	20	1.0	6.5	1.5	16.4
10.0	25.1	34	15.6	20.1	24	1.0	6.5	1.5	16.4
10.5	25.0	36	16.2	25.8	30	1.0	6.6	1.5	16.8
11.0	25.0	39	16.3	34.5	45	1.0	6.7	1.5	16.8
11.5	25.1	42	15.6	28.5	63	1.0	6.9	1.5	17.1
12.0	25.2	45	14.4	26.5	90	1.0	6.9	1.5	17.4
12.5	25.1	45	13.4	28.7	90	1.0	7.2	1.5	17.7
13.0	25.1	41	12.5	36.4	54	1.1	7.4	1.5	18.2
13.5	25.1	39	11.8	34.8	40	1.1	7.3	1.5	18.0
14.0	25.3	36	11.1	24.8	31	1.1	7.1	1.6	17.9
14.5	25.4	33	10.5	19.2	19	1.1	7.0	1.6	17.7
15.0	25.6	31	10.2	15.8	15	1.1	7.2	1.7	17.6
15.5	25.9	29	10.7	13.9	12	1.0	7.6	1.7	18.0
16.0	26.3	27	12.3	12.8	10	1.0	8.2	1.7	18.8
16.5	26.6	26	16.3	12.8	9	1.0	8.9	1.7	19.6
17.0	26.8	25	21.5	13.6	8	1.0	9.4	1.7	20.4
17.5	26.8	26	11.7	12.9	9	1.0	9.5	1.8	20.6
18.0	26.5	27	6.0	8.9	7	1.1	9.1	1.9	20.4
18.5	25.5	25	3.1	5.7	3	1.1	8.5	2.0	20.3
19.0	23.4	26	2.2	4.8	3	1.1	8.1	2.1	19.7

Typical Performance Curves




Case Style

GC

Outline Dimensions

GC957



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GC957	.74 (18.80)	.75 (19.15)	.46 (11.61)	1.18 (30.07)	.04 (1.02)	.17 (4.32)	.45 (11.40)	.59 (14.86)	.33 (8.31)	.21 (5.44)	.22 (5.59)	.14 (3.56)	1.00 (25.4)

CASE #.	P	Q	R	WT GRAMS
GC957	.37 (9.40)	.18 (4.57)	.106 (2.69)	23.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits[®]

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C