

Connectorized Amplifier

ZX60-2531MA+

50Ω 0.5 to 2.5 GHz

Features

- From 2.8V to 5V operation
- High directivity, 27 dB typ.
- Wide bandwidth, 0.5 to 2.5 GHz
- Low noise figure, 2.9 dB typ.
- Output power, up to 19 dBm typ.
- Protected by US patent 6,790,049

Applications

- Buffer amplifier
- Cellular
- PCN
- Lab
- Instrumentation
- Test equipment



CASE STYLE: GA955

Connectors	Model
SMA	ZX60-2531MA-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at T_{AMB} = 25°C

MODEL NO.	FREQ. (GHz) f _L - f _U	DC VOLTAGE @ Pin V+ (V)	GAIN over frequency in GHz Typ (dB)						MAXIMUM POWER (dBm) Output (1 dB Comp.) Typ. f _L f _U		DYNAMIC RANGE			VSWR (:1) Typ.		ACTIVE DIRECTIVITY (dB) Isolation-Gain Typ.	DC OPERATING CURRENT @ Pin V+ (mA)	
			0.5	1.0	1.5	2.0	2.5	Min.at 2 GHz	NF (dB) Typ.	IP3 (dBm) Typ.		1.5-2.5 GHz In Out		Typ.	Typ.		Max.	
			1GHz	1GHz	2GHz	1GHz	2GHz											
ZX60-2531MA+	0.5-2.5	5.0	37	41.5	41	39	37	33	19	17	2.9	24	26	1.3	1.5	24	102	130
		2.8	34	37	36	34	32	-	10	11	3.1	19	22	1.3	1.7	27		

Maximum Ratings

Operating Temperature -40°C to 80°C case

Storage Temperature -55°C to 100°C

DC Voltage 7V

Input Power (no damage) -15dBm


Power Dissipation 500mW

Permanent damage may occur if any of these limits are exceeded.



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note AN-40-10.

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	wt.
1.20	.75	.46	1.18	.04	.17	.45	.59	.33	.21	.22	.18	1.00	.50	.35	.18	.106	grams
30.48	19.05	11.68	29.97	1.02	4.32	11.43	14.99	8.38	5.33	5.59	4.57	25.40	12.70	8.89	4.57	2.69	35.0

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
M160331
EDU2488
ZX60-2531MA+
URJ
170217
Page 1 of 3

Typical Performance Data at 25°C

ZX60-2531MA+

V+ = 5.0V

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR IN (:1)	VSWR OUT (:1)	POWER OUT @1dB COMPRESSION (dBm)	IP3 (dBm)	NF (dB)
500	37.09	31.59	3.16	1.56	18.92	29.29	3.33
550	38.42	22.68	2.86	1.45	19.20	28.38	3.32
600	39.30	29.15	2.68	1.35	19.30	27.14	3.21
650	39.90	29.32	2.51	1.28	19.15	26.15	3.15
700	40.33	34.45	2.35	1.21	19.37	26.06	3.12
800	40.82	26.29	2.09	1.16	19.42	25.05	2.97
900	41.16	21.34	1.91	1.17	19.30	25.05	2.86
1000	41.40	24.62	1.74	1.20	19.26	24.2	2.83
1100	41.54	21.79	1.62	1.23	18.85	23.91	2.80
1300	41.45	24.15	1.41	1.26	18.71	24.05	2.95
1400	41.23	18.27	1.33	1.26	18.68	24.1	2.91
1500	40.90	26.12	1.26	1.24	18.78	24.84	2.96
1600	40.50	25.94	1.21	1.25	18.22	24.6	2.89
1800	39.58	20.03	1.11	1.24	18.08	25.59	2.83
2000	38.63	25.40	1.06	1.27	18.01	26.45	2.82
2200	37.74	18.99	1.02	1.34	17.75	27.02	2.75
2300	37.33	20.40	1.01	1.38	17.45	27.33	2.78
2400	36.91	22.75	1.01	1.42	17.26	27.48	2.81
2450	36.71	19.32	1.02	1.44	17.23	27.58	2.80
2500	36.49	20.04	1.03	1.46	16.89	27.7	2.80

V+ = 2.8V

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR IN (:1)	VSWR OUT (:1)	POWER OUT @1dB COMPRESSION (dBm)	IP3 (dBm)	NF (dB)
500	33.69	34.22	3.12	1.69	9.56	18.92	3.40
550	34.84	35.99	2.80	1.62	9.82	18.92	3.40
600	35.60	33.95	2.55	1.58	10.22	19.41	3.34
650	36.11	28.51	2.34	1.57	10.33	19.44	3.31
700	36.47	27.92	2.18	1.57	10.39	19.16	3.27
800	36.85	32.24	1.93	1.60	10.84	19.28	3.21
900	37.04	25.11	1.75	1.66	10.56	19.38	3.08
1000	37.09	38.47	1.62	1.71	10.69	19.16	3.10
1100	37.03	26.40	1.51	1.74	10.74	19.58	3.08
1300	36.63	22.41	1.34	1.77	10.62	20.23	3.14
1400	36.31	25.06	1.28	1.76	10.88	20.59	3.13
1500	35.93	23.14	1.22	1.73	10.66	20.85	3.18
1600	35.51	23.16	1.17	1.71	10.92	21.34	3.14
1800	34.61	22.26	1.11	1.66	10.98	21.41	3.15
2000	33.69	21.48	1.07	1.62	11.23	21.47	3.16
2200	32.80	23.99	1.07	1.61	11.15	21.61	3.17
2300	32.37	23.35	1.07	1.61	11.14	21.6	3.17
2400	31.93	27.38	1.08	1.61	11.09	21.69	3.19
2450	31.71	26.86	1.08	1.61	11.20	21.87	3.23
2500	31.49	24.91	1.09	1.62	11.18	22.03	3.24







Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Curves at 25 °C

ZX60-2531MA+



Notes







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

FREQ. (MHz)	GAIN		DIRECTIVITY		VSWR IN		VSWR OUT		POWER OUT @ 1dB COMPRESSION		IP3		NF	
	(dB)		(dB)		(:1)		(:1)		(dBm)		(dBm)		(dB)	
	2.8V	5V	2.8V	5V	2.8V	5V	2.8V	5V	2.8V	5V	2.8V	5V	2.8V	5V
500	33.69	37.09	34.22	31.59	3.12	3.16	1.69	1.56	9.56	18.92	18.92	29.29	3.40	3.33
550	34.84	38.42	35.99	22.68	2.80	2.86	1.62	1.45	9.82	19.20	18.92	28.38	3.40	3.32
600	35.60	39.30	33.95	29.15	2.55	2.68	1.58	1.35	10.22	19.30	19.41	27.14	3.34	3.21
650	36.11	39.90	28.51	29.32	2.34	2.51	1.57	1.28	10.33	19.15	19.44	26.15	3.31	3.15
700	36.47	40.33	27.92	34.45	2.18	2.35	1.57	1.21	10.39	19.37	19.16	26.06	3.27	3.12
800	36.85	40.82	32.24	26.29	1.93	2.09	1.60	1.16	10.84	19.42	19.28	25.05	3.21	2.97
900	37.04	41.16	25.11	21.34	1.75	1.91	1.66	1.17	10.56	19.30	19.38	25.05	3.08	2.86
1000	37.09	41.40	38.47	24.62	1.62	1.74	1.71	1.20	10.69	19.26	19.16	24.2	3.10	2.83
1100	37.03	41.54	26.40	21.79	1.51	1.62	1.74	1.23	10.74	18.85	19.58	23.91	3.08	2.80
1300	36.63	41.45	22.41	24.15	1.34	1.41	1.77	1.26	10.62	18.71	20.23	24.05	3.14	2.95
1400	36.31	41.23	25.06	18.27	1.28	1.33	1.76	1.26	10.88	18.68	20.59	24.1	3.13	2.91
1500	35.93	40.90	23.14	26.12	1.22	1.26	1.73	1.24	10.66	18.78	20.85	24.84	3.18	2.96
1600	35.51	40.50	23.16	25.94	1.17	1.21	1.71	1.25	10.92	18.22	21.34	24.6	3.14	2.89
1800	34.61	39.58	22.26	20.03	1.11	1.11	1.66	1.24	10.98	18.08	21.41	25.59	3.15	2.83
2000	33.69	38.63	21.48	25.40	1.07	1.06	1.62	1.27	11.23	18.01	21.47	26.45	3.16	2.82
2200	32.80	37.74	23.99	18.99	1.07	1.02	1.61	1.34	11.15	17.75	21.61	27.02	3.17	2.75
2300	32.37	37.33	23.35	20.40	1.07	1.01	1.61	1.38	11.14	17.45	21.6	27.33	3.17	2.78
2400	31.93	36.91	27.38	22.75	1.08	1.01	1.61	1.42	11.09	17.26	21.69	27.48	3.19	2.81
2450	31.71	36.71	26.86	19.32	1.08	1.02	1.61	1.44	11.20	17.23	21.87	27.58	3.23	2.80
2500	31.49	36.49	24.91	20.04	1.09	1.03	1.62	1.46	11.18	16.89	22.03	27.7	3.24	2.80

Typical Performance Curves




Case Style

GA

Outline Dimensions

GA955



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GA955	1.20 (30.48)	.75 (19.05)	.46 (11.61)	1.18 (29.97)	.04 (1.02)	.17 (4.27)	.45 (11.35)	.58 (14.81)	.33 (8.46)	.21 (5.44)	.22 (5.59)	.14 (3.56)	1.000 (25.4)

CASE #.	P	Q	R	S	WT GRAMS
GA955	.500 (12.70)	.35 (8.89)	.18 (4.57)	.106 (2.69)	35.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C