

Amplifier

ZX60-3800LN-S+

50Ω 3300 to 3800 MHz

Features

- Low noise figure 0.9 typ.
- +18 dBm typ. output power at 1 dB compression
- High active directivity, 17 dB typ.
- Good IP3, 35 dBm typ.
- Reverse voltage connection protected
- Protected by US patent 6,790,049

Applications

- Low noise amplifier RF front end
- Low noise pre-amp
- Buffer amplifier
- WiMAX
- SAB / SAP
- Lab
- Test equipment



CASE STYLE: GA955

Connectors	Model
SMA	ZX60-3800LN-S+

+RoHS Compliant
 The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at T_{AMB} = 25°C

MODEL NO.	FREQ. (MHz)	GAIN (dB)				MAXIMUM POWER (dBm)	DYNAMIC RANGE			VSWR (:1) Typ.		ACTIVE DIRECTIVITY (dB) Isolation-Gain	DC VOLTAGE @ Pin V+ (V)	DC OPERATING CURRENT @ Pin V+ (mA)		
		Flatness					Output (1 dB Comp.)	NF (dB)	IP3 (dBm)	In	Out			Typ.	Typ.	Max.
		Typ.	Min.	Typ.	Max.											
ZX60-3800LN-S+	3300-3600	24	20	±0.1	±0.4	18.0	0.9	2.0	36	1.5	1.3	17	5	85	110	
	3600-3800	23	19	±0.6	±1.0	18.0	1.0	2.0	35	1.2	1.4	17	5	85	110	


Maximum Ratings

Operating Temperature	-40°C to 80°C case
Storage Temperature	-55°C to 100°C
DC Voltage	6.5V
Input Power(no Damage)	1dBm

Permanent damage may occur if any of these limits are exceeded.

! NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note [AN-40-10](#).

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	wt. grams
1.20	.75	.46	1.18	.04	.17	.45	.59	.33	.21	.22	.14	1.00	.50	.35	.18	.106	35.0
30.48	19.05	11.68	29.97	1.02	4.32	11.43	14.99	8.38	5.33	5.59	3.56	25.40	12.70	8.89	4.57	2.69	







Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data & Curves at 25°C ZX60-3800LN-S+

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR IN (:1)	VSWR OUT (:1)	POWER OUT @ 1dB COMPRESSION (dBm)	IP3 (dBm)	NF (dB)
3300	23.71	16.42	1.48	1.15	17.92	38.44	0.91
3320	23.72	17.60	1.46	1.18	17.95	37.89	0.89
3340	23.71	17.44	1.44	1.20	17.94	37.41	0.90
3360	23.64	17.17	1.42	1.22	17.95	37.38	0.91
3380	23.63	16.51	1.40	1.24	17.92	37.21	0.91
3400	23.60	16.36	1.38	1.25	17.91	37.08	0.90
3420	23.63	16.52	1.36	1.27	17.99	36.90	0.90
3440	23.67	16.80	1.34	1.28	18.01	36.72	0.90
3460	23.70	16.14	1.32	1.29	17.98	36.66	0.91
3480	23.67	15.40	1.31	1.30	18.08	36.60	0.92
3500	23.60	15.69	1.29	1.31	18.09	36.42	0.89
3520	23.64	15.28	1.27	1.31	18.26	36.40	0.92
3540	23.70	15.95	1.25	1.31	18.16	36.36	0.91
3560	23.76	14.39	1.23	1.32	18.15	36.41	0.92
3580	23.67	14.26	1.21	1.32	18.32	36.25	0.93
3600	23.51	14.96	1.20	1.32	18.30	36.36	0.93
3650	23.57	14.83	1.20	1.31	18.35	36.53	0.98
3700	23.18	14.84	1.22	1.29	18.35	36.71	0.98
3750	23.00	15.11	1.25	1.27	18.24	36.66	0.99
3800	22.52	15.71	1.29	1.24	18.30	36.85	1.01



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Noise Amplifier

ZX60-3800LN-S+

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 5V	DIRECTIVITY (dB) 5V	VSWR IN (:1) 5V	VSWR OUT (:1) 5V	Output IP3 (dBm) 5V	NOISE FIGURE (dB) 5V	Pout at 1dB Comp. (dBm) 5V
3300	23.71	16.42	1.48	1.15	38.44	0.91	17.92
3320	23.72	17.60	1.46	1.18	37.89	0.89	17.95
3340	23.71	17.44	1.44	1.20	37.41	0.90	17.94
3360	23.64	17.17	1.42	1.22	37.38	0.91	17.95
3380	23.63	16.51	1.40	1.24	37.21	0.91	17.92
3400	23.60	16.36	1.38	1.25	37.08	0.90	17.91
3420	23.63	16.52	1.36	1.27	36.90	0.90	17.99
3440	23.67	16.80	1.34	1.28	36.72	0.90	18.01
3460	23.70	16.14	1.32	1.29	36.66	0.91	17.98
3480	23.67	15.40	1.31	1.30	36.60	0.92	18.08
3500	23.60	15.69	1.29	1.31	36.42	0.89	18.09
3520	23.64	15.28	1.27	1.31	36.40	0.92	18.26
3540	23.70	15.95	1.25	1.31	36.36	0.91	18.16
3560	23.76	14.39	1.23	1.32	36.41	0.92	18.15
3580	23.67	14.26	1.21	1.32	36.25	0.93	18.32
3600	23.51	14.96	1.20	1.32	36.36	0.93	18.30
3650	23.57	14.83	1.20	1.31	36.53	0.98	18.35
3700	23.18	14.84	1.22	1.29	36.71	0.98	18.35
3750	23.00	15.11	1.25	1.27	36.66	0.99	18.24
3800	22.52	15.71	1.29	1.24	36.85	1.01	18.30



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0033 (718) 934-4500 Fax (718) 332-4666 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

IR/RF MICROWAVE COMPONENTS







For detailed performance specs & shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp.

Low Noise Amplifier

Typical Performance Curves

ZX60-3800LN-S+



For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0033 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine www.minicircuits.com Provides ACTUAL Data Instantly at minicircuits.com


Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchase of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

Case Style

GA

Outline Dimensions

GA955



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GA955	1.20 (30.48)	.75 (19.05)	.46 (11.61)	1.18 (29.97)	.04 (1.02)	.17 (4.27)	.45 (11.35)	.58 (14.81)	.33 (8.46)	.21 (5.44)	.22 (5.59)	.14 (3.56)	1.000 (25.4)

CASE #.	P	Q	R	S	WT GRAMS
GA955	.500 (12.70)	.35 (8.89)	.18 (4.57)	.106 (2.69)	35.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 50° C Ambient Environment	Individual Model Data Sheet
Operating Temperature	-40° to 80° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C Case	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C