

# Coaxial Bandpass Filter

## ZX75BP-1940-S+

50Ω 1710 to 2170 MHz

### The Big Deal

- Fast roll-off on the upper sideband
- Good Matching and low loss in the pass band
- Connectorized package



Generic photo used for illustration purposes only  
CASE STYLE: KE1467

### Product Overview

ZX75BP-1940-S+ is a wideband bandpass filter in a rugged connectorized package covering 1710 to 2170 MHz. This is designed for asymmetric rejection applications such as super-heterodyne receivers. By having asymmetric band, faster roll-off at upper side band is achieved in a comparatively smaller package and lower pass band insertion loss. It has repeatable performance across lots and consistent performance across temperature

### Key Features

| Feature                                 | Advantages                                                                                                              |
|-----------------------------------------|-------------------------------------------------------------------------------------------------------------------------|
| Fast roll-off on the upper side band    | Wide bandwidth filter with fast-roll off on the upper side band, which increases selectivity on the adjacent channel.   |
| Good matching and low loss in pass band | This filter has good matching and low loss in the pass band                                                             |
| Connectorized package                   | Connectorized package is easy to interface with other devices and well suited for test setups.                          |
| High power handling                     | This model uses high Q capacitors and high current handling inductors which is well suited for high power applications. |

#### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Coaxial Bandpass Filter

50Ω 1710 to 2170 MHz

## ZX75BP-1940-S+



Generic photo used for illustration purposes only

|                    |                |
|--------------------|----------------|
| CASE STYLE: KE1467 |                |
| Connectors         | Model          |
| SMA-MF             | ZX75BP-1940-S+ |


### Features

- Fast roll-off on the upper side band
- Good matching in the pass band
- Connectorized package


### Applications

- Defense systems
- Cable TV relay
- DECT, GSM and IMT
- Mobile satellite
- Private and public land mobile
- PCS Broadband

### Functional Schematic



### Typical Frequency Response



### Electrical Specifications at 25°C

| Parameter        | F#               | Frequency (MHz) | Min.      | Typ. | Max. | Unit |
|------------------|------------------|-----------------|-----------|------|------|------|
| Pass Band        | Center Frequency | -               | -         | 1940 | -    | MHz  |
|                  | Insertion Loss   | F1-F2           | 1710-2170 | 0.7  | 2.0  | dB   |
|                  | VSWR             | F1-F2           | 1710-2170 | -    | 1.2  | 1.78 |
| Stop Band, Lower | Insertion Loss   | DC-F3           | DC - 150  | 20   | 30   | dB   |
|                  | VSWR             | DC-F3           | DC - 150  | -    | 20   | -    |
| Stop Band, Upper | Insertion Loss   | F4-F5           | 2800-4000 | 20   | 31   | dB   |
|                  | VSWR             | F4-F5           | 2800-4000 | -    | 20   | -    |

#### Maximum Ratings

|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power Input        | 8 W max.       |





Permanent damage may occur if any of these limits are exceeded.

### Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) | Frequency (MHz) | Group Delay (nsec) |
|-----------------|---------------------|-----------|-----------------|--------------------|
| 5               | 59.48               | 1737.18   | 1710            | 1.06               |
| 40              | 41.47               | 1737.18   | 1730            | 1.05               |
| 150             | 30.00               | 579.06    | 1750            | 1.04               |
| 400             | 21.49               | 133.63    | 1780            | 1.03               |
| 750             | 15.61               | 49.64     | 1800            | 1.02               |
| 1250            | 7.24                | 13.70     | 1830            | 1.02               |
| 1450            | 3.00                | 4.78      | 1850            | 1.02               |
| 1530            | 1.63                | 2.89      | 1870            | 1.03               |
| 1710            | 0.40                | 1.14      | 1890            | 1.03               |
| 1940            | 0.45                | 1.15      | 1900            | 1.04               |
| 2170            | 0.60                | 1.08      | 1920            | 1.05               |
| 2280            | 1.52                | 2.08      | 1940            | 1.06               |
| 2340            | 3.67                | 4.36      | 1960            | 1.07               |
| 2400            | 7.26                | 9.43      | 1980            | 1.08               |
| 2500            | 14.13               | 22.87     | 2000            | 1.10               |
| 2600            | 20.58               | 34.75     | 2030            | 1.13               |
| 2800            | 31.78               | 46.96     | 2050            | 1.15               |
| 3000            | 41.55               | 51.10     | 2100            | 1.21               |
| 3500            | 58.35               | 56.04     | 2140            | 1.29               |
| 4000            | 60.06               | 56.04     | 2170            | 1.37               |

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



#### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



## Coaxial Connections

|        |            |
|--------|------------|
| INPUT  | SMA-MALE   |
| OUTPUT | SMA-FEMALE |

## Outline Drawing



## Outline Dimensions (inch/mm)

| A     | B     | C     | D     | E    | F     | G    |
|-------|-------|-------|-------|------|-------|------|
| .74   | .75   | .46   | 1.18  | .04  | .362  | .21  |
| 18.80 | 19.05 | 11.68 | 29.97 | 1.02 | 9.19  | 5.33 |
| H     | J     | K     | L     | M    | Wt.   |      |
| .362  | 1.00  | .37   | .18   | .11  | grams |      |
| 9.19  | 25.40 | 9.40  | 4.57  | 2.79 | 24.4  |      |

Note: Please refer to case style drawing for details

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

*Typical Performance Data*







| FREQ.<br><br>(MHz) | INSERTION LOSS |        |        | INPUT RETURN LOSS |        |        | OUTPUT RETURN LOSS |        |        |
|--------------------|----------------|--------|--------|-------------------|--------|--------|--------------------|--------|--------|
|                    | (dB)           |        |        | (dB)              |        |        | (dB)               |        |        |
|                    | @-40°C         | @+25°C | @+85°C | @-40°C            | @+25°C | @+85°C | @-40°C             | @+25°C | @+85°C |
| 5                  | 59.57          | 59.48  | 59.49  | 0.00              | 0.00   | 0.00   | 0.00               | 0.00   | 0.00   |
| 10                 | 53.58          | 53.53  | 53.54  | 0.00              | 0.00   | 0.00   | 0.00               | 0.00   | 0.00   |
| 20                 | 47.50          | 47.51  | 47.47  | 0.00              | 0.00   | 0.00   | 0.00               | 0.00   | 0.00   |
| 45                 | 40.47          | 40.47  | 40.42  | 0.00              | 0.01   | 0.00   | 0.00               | 0.00   | 0.00   |
| 90                 | 34.52          | 34.43  | 34.37  | 0.00              | 0.01   | 0.01   | 0.00               | 0.01   | 0.01   |
| 150                | 30.14          | 30.00  | 29.89  | 0.01              | 0.03   | 0.03   | 0.00               | 0.01   | 0.01   |
| 260                | 25.24          | 25.24  | 25.16  | 0.04              | 0.06   | 0.07   | 0.02               | 0.03   | 0.04   |
| 470                | 19.98          | 20.07  | 20.15  | 0.13              | 0.16   | 0.17   | 0.05               | 0.07   | 0.08   |
| 510                | 19.26          | 19.35  | 19.42  | 0.16              | 0.19   | 0.19   | 0.06               | 0.09   | 0.09   |
| 590                | 17.93          | 18.01  | 18.07  | 0.20              | 0.24   | 0.24   | 0.09               | 0.11   | 0.12   |
| 720                | 15.98          | 16.04  | 16.10  | 0.28              | 0.33   | 0.33   | 0.14               | 0.17   | 0.18   |
| 850                | 14.10          | 14.15  | 14.21  | 0.38              | 0.43   | 0.43   | 0.22               | 0.25   | 0.26   |
| 990                | 11.93          | 12.00  | 12.03  | 0.53              | 0.58   | 0.58   | 0.35               | 0.39   | 0.40   |
| 1090               | 10.24          | 10.32  | 10.32  | 0.69              | 0.74   | 0.75   | 0.52               | 0.56   | 0.57   |
| 1210               | 7.98           | 8.06   | 8.02   | 1.02              | 1.08   | 1.12   | 0.88               | 0.93   | 0.95   |
| 1300               | 6.14           | 6.19   | 6.14   | 1.51              | 1.59   | 1.65   | 1.40               | 1.45   | 1.50   |
| 1400               | 4.01           | 4.03   | 3.98   | 2.59              | 2.71   | 2.82   | 2.51               | 2.61   | 2.70   |
| 1450               | 2.98           | 3.00   | 2.96   | 3.52              | 3.69   | 3.83   | 3.47               | 3.61   | 3.73   |
| 1500               | 2.06           | 2.09   | 2.07   | 4.90              | 5.11   | 5.31   | 4.88               | 5.06   | 5.22   |
| 1580               | 0.97           | 1.02   | 1.04   | 8.46              | 8.84   | 9.12   | 8.50               | 8.84   | 9.09   |
| 1610               | 0.71           | 0.77   | 0.79   | 10.42             | 10.90  | 11.23  | 10.50              | 10.94  | 11.23  |
| 1710               | 0.31           | 0.40   | 0.45   | 22.81             | 23.93  | 24.40  | 22.83              | 23.96  | 24.70  |
| 1740               | 0.29           | 0.39   | 0.44   | 33.55             | 36.34  | 36.35  | 31.09              | 33.37  | 36.47  |
| 1770               | 0.30           | 0.39   | 0.44   | 32.70             | 32.83  | 32.73  | 29.66              | 30.46  | 31.38  |
| 1800               | 0.31           | 0.41   | 0.46   | 25.38             | 25.84  | 26.24  | 24.61              | 25.24  | 25.75  |
| 1840               | 0.33           | 0.43   | 0.48   | 21.96             | 22.61  | 23.19  | 21.78              | 22.49  | 23.00  |
| 1890               | 0.35           | 0.44   | 0.49   | 20.95             | 21.77  | 22.56  | 21.10              | 21.98  | 22.65  |
| 1910               | 0.35           | 0.44   | 0.50   | 21.13             | 22.06  | 22.97  | 21.42              | 22.41  | 23.21  |
| 1940               | 0.35           | 0.45   | 0.51   | 21.84             | 23.03  | 24.15  | 22.45              | 23.76  | 24.86  |
| 1980               | 0.36           | 0.46   | 0.52   | 23.50             | 25.22  | 26.80  | 24.45              | 26.59  | 28.49  |
| 2020               | 0.36           | 0.47   | 0.53   | 25.48             | 27.77  | 29.47  | 26.53              | 29.51  | 32.11  |
| 2060               | 0.38           | 0.49   | 0.56   | 26.49             | 28.26  | 28.81  | 26.62              | 28.34  | 29.01  |
| 2090               | 0.39           | 0.52   | 0.59   | 26.56             | 27.65  | 27.61  | 25.80              | 26.62  | 26.63  |
| 2130               | 0.42           | 0.55   | 0.63   | 27.33             | 28.08  | 27.53  | 25.55              | 25.88  | 25.37  |
| 2170               | 0.46           | 0.60   | 0.69   | 28.32             | 28.05  | 26.73  | 25.92              | 25.26  | 24.00  |
| 2210               | 0.54           | 0.71   | 0.82   | 20.84             | 20.08  | 19.33  | 20.36              | 19.31  | 18.38  |
| 2230               | 0.64           | 0.83   | 0.95   | 16.86             | 16.26  | 15.73  | 16.65              | 15.82  | 15.15  |
| 2280               | 1.25           | 1.52   | 1.70   | 9.40              | 9.08   | 8.82   | 9.23               | 8.81   | 8.51   |
| 2300               | 1.74           | 2.05   | 2.27   | 7.25              | 7.02   | 6.83   | 7.06               | 6.77   | 6.55   |
| 2330               | 2.82           | 3.20   | 3.46   | 4.79              | 4.67   | 4.57   | 4.58               | 4.43   | 4.31   |
| 2350               | 3.77           | 4.19   | 4.49   | 3.60              | 3.54   | 3.49   | 3.39               | 3.30   | 3.23   |
| 2390               | 6.11           | 6.60   | 6.93   | 2.06              | 2.09   | 2.10   | 1.85               | 1.85   | 1.85   |
| 2410               | 7.42           | 7.93   | 8.26   | 1.59              | 1.64   | 1.67   | 1.38               | 1.41   | 1.43   |
| 2470               | 11.55          | 12.08  | 12.42  | 0.83              | 0.93   | 0.98   | 0.63               | 0.71   | 0.74   |
| 2530               | 15.61          | 16.13  | 16.48  | 0.54              | 0.64   | 0.71   | 0.34               | 0.42   | 0.47   |
| 2590               | 19.45          | 19.97  | 20.31  | 0.41              | 0.52   | 0.58   | 0.22               | 0.30   | 0.34   |
| 2600               | 20.07          | 20.58  | 20.92  | 0.40              | 0.50   | 0.56   | 0.21               | 0.29   | 0.33   |
| 2670               | 24.23          | 24.72  | 25.07  | 0.33              | 0.43   | 0.50   | 0.15               | 0.23   | 0.27   |
| 2770               | 29.75          | 30.22  | 30.56  | 0.28              | 0.38   | 0.45   | 0.11               | 0.19   | 0.22   |
| 2800               | 31.32          | 31.78  | 32.13  | 0.27              | 0.37   | 0.44   | 0.11               | 0.19   | 0.22   |
| 2960               | 39.22          | 39.67  | 40.02  | 0.24              | 0.35   | 0.40   | 0.09               | 0.16   | 0.19   |
| 3080               | 44.75          | 45.12  | 45.48  | 0.22              | 0.33   | 0.39   | 0.08               | 0.15   | 0.18   |
| 3220               | 50.63          | 50.90  | 51.14  | 0.21              | 0.32   | 0.38   | 0.07               | 0.15   | 0.17   |
| 3400               | 56.52          | 56.56  | 56.66  | 0.20              | 0.32   | 0.37   | 0.08               | 0.15   | 0.18   |
| 3605               | 59.69          | 59.63  | 59.48  | 0.20              | 0.31   | 0.37   | 0.08               | 0.15   | 0.19   |
| 3705               | 60.16          | 60.12  | 59.73  | 0.20              | 0.31   | 0.37   | 0.08               | 0.16   | 0.19   |
| 3785               | 60.27          | 59.95  | 59.60  | 0.19              | 0.31   | 0.37   | 0.09               | 0.16   | 0.19   |
| 3805               | 60.29          | 60.02  | 59.69  | 0.19              | 0.31   | 0.37   | 0.09               | 0.16   | 0.19   |
| 3965               | 60.12          | 59.76  | 59.54  | 0.19              | 0.31   | 0.37   | 0.09               | 0.17   | 0.20   |
| 4000               | 60.20          | 60.06  | 59.68  | 0.19              | 0.31   | 0.38   | 0.09               | 0.17   | 0.21   |




## Typical Performance Data

| FREQ.<br><br>(MHz) | GROUP DELAY |        |        |
|--------------------|-------------|--------|--------|
|                    | (nsec)      |        |        |
|                    | @-40°C      | @+25°C | @+85°C |
| 1710               | 1.07        | 1.06   | 1.05   |
| 1720               | 1.06        | 1.05   | 1.04   |
| 1730               | 1.06        | 1.05   | 1.04   |
| 1740               | 1.06        | 1.04   | 1.04   |
| 1750               | 1.05        | 1.04   | 1.03   |
| 1760               | 1.05        | 1.04   | 1.03   |
| 1770               | 1.04        | 1.03   | 1.03   |
| 1780               | 1.04        | 1.03   | 1.02   |
| 1790               | 1.04        | 1.03   | 1.02   |
| 1800               | 1.03        | 1.02   | 1.02   |
| 1810               | 1.03        | 1.02   | 1.02   |
| 1820               | 1.03        | 1.02   | 1.02   |
| 1830               | 1.03        | 1.02   | 1.02   |
| 1840               | 1.03        | 1.02   | 1.02   |
| 1850               | 1.03        | 1.02   | 1.02   |
| 1860               | 1.03        | 1.02   | 1.02   |
| 1870               | 1.03        | 1.03   | 1.02   |
| 1880               | 1.04        | 1.03   | 1.03   |
| 1890               | 1.04        | 1.03   | 1.03   |
| 1900               | 1.04        | 1.04   | 1.03   |
| 1910               | 1.05        | 1.04   | 1.04   |
| 1920               | 1.05        | 1.05   | 1.04   |
| 1930               | 1.06        | 1.05   | 1.05   |
| 1940               | 1.06        | 1.06   | 1.05   |
| 1950               | 1.07        | 1.06   | 1.06   |
| 1960               | 1.08        | 1.07   | 1.07   |
| 1970               | 1.08        | 1.08   | 1.08   |
| 1980               | 1.09        | 1.08   | 1.08   |
| 1990               | 1.10        | 1.09   | 1.09   |
| 2000               | 1.11        | 1.10   | 1.10   |
| 2010               | 1.11        | 1.11   | 1.11   |
| 2020               | 1.12        | 1.12   | 1.12   |
| 2030               | 1.13        | 1.13   | 1.13   |
| 2040               | 1.14        | 1.14   | 1.14   |
| 2050               | 1.15        | 1.15   | 1.15   |
| 2060               | 1.16        | 1.16   | 1.16   |
| 2070               | 1.18        | 1.17   | 1.17   |
| 2080               | 1.19        | 1.19   | 1.18   |
| 2090               | 1.20        | 1.20   | 1.20   |
| 2100               | 1.22        | 1.21   | 1.21   |
| 2110               | 1.23        | 1.23   | 1.23   |
| 2120               | 1.25        | 1.25   | 1.25   |
| 2130               | 1.27        | 1.27   | 1.27   |
| 2140               | 1.29        | 1.29   | 1.29   |
| 2150               | 1.31        | 1.32   | 1.32   |
| 2160               | 1.34        | 1.34   | 1.35   |
| 2170               | 1.37        | 1.37   | 1.38   |

## Typical Performance Curves



## Typical Performance Curves



### Outline Dimensions



| CASE #. | A              | B              | C              | D               | E             | F              | G             | H              | J               | K             | L             | M             |
|---------|----------------|----------------|----------------|-----------------|---------------|----------------|---------------|----------------|-----------------|---------------|---------------|---------------|
| KE1467  | .74<br>(18.80) | .75<br>(19.05) | .46<br>(11.68) | 1.18<br>(29.97) | .04<br>(1.02) | .362<br>(9.19) | .21<br>(5.33) | .362<br>(9.19) | 1.00<br>(25.40) | .37<br>(9.40) | .18<br>(4.57) | .11<br>(2.79) |

| CASE #. | WT. GRAM |
|---------|----------|
| KE1467  | 24.4     |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

Tolerance on hole size and interaxes dimensions to be  $\pm .005$ .

#### Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                                               | Reference/Spec                                        |
|----------------------------|---------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                                    | Individual Model Data Sheet                           |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                                                   | Individual Model Data Sheet                           |
| Humidity                   | 90 to 95% RH, 40°C, 96 hours;<br>Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103, Condition B                  |
| Thermal Shock              | -55° to 100°C, 100 cycles                                                                               | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                     | MIL-STD-202, Method 204, Condition D                  |
| Mechanical Shock           | 50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)                                          | MIL-STD-202, Method 213, Condition A                  |