



LUMPED LC COAXIAL

Bandpass Filter

ZX75BP-400-S+

50Ω 292 to 490 MHz SMA-Male to SMA-Female

KEY FEATURES

- Insertion Loss, 3dB Max.
- Pass Band Return Loss, 11dB Typ.
- Stop Band Rejection, 30dB Typ.

APPLICATIONS

- Aircraft Communication
- Navigation


PRODUCT OVERVIEW

ZX75BP-400-S+ is a 50Ω bandpass filter in a connectorized package covering 292 to 490MHz. This offers good matching within the passband and high rejection in stopband.



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM



ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency	Fc	—	—	391	—	MHz
	Insertion Loss	F1-F2	292 - 490	—	—	3	dB
	Return Loss	F1-F2	292 - 490	8.1	11.4	—	dB
Stop Band, Lower	Rejection	DC-F3	DC - 200	35	—	—	dB
		F3-F4	200 - 230	20	—	—	dB
Stop Band, Upper	Rejection	F5-F6	620 - 700	20	—	—	dB
		F6-F7	700 - 2000	35	—	—	dB
		F7-F8	2000 - 4000	—	30	—	dB


1. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

ABSOLUTE MAXIMUM RATINGS²

Parameter	Ratings
Operating Temperature	-40°C to + 85°C
Storage Temperature	-55°C to + 100°C
Input Power ³	0.5W at 25°C

2. Permanent damage may occur if any of these limits are exceeded.
 3. Power rating applies only to signals within the passband.

TYPICAL FREQUENCY RESPONSE AT +25°C





LUMPED LC COAXIAL





Bandpass Filter

ZX75BP-400-S+

Mini-Circuits

50Ω 292 to 490 MHz SMA-Male to SMA-Female

TYPICAL PERFORMANCE GRAPHS





LUMPED LC COAXIAL

Bandpass Filter

ZX75BP-400-S+


Mini-Circuits

50Ω 292 to 490 MHz SMA-Male to SMA-Female

CONNECTOR DESCRIPTION

Function	Marking on Unit	Connector
RF1 ¹	1	SMA Male
RF2 ¹	2	SMA Female

CASE STYLE DRAWING



Weight: 24.4 gram

Dimensions are in inches (mm). Tolerances: 2PI. ± .03; 3PI. ± .015

Tolerance on hole size and interaxes dimensions to be ± .005.

PRODUCT MARKING*: ZX75BP-400-S+

*Marking may contain other features or characters for internal lot control.



LUMPED LC COAXIAL

Bandpass Filter

ZX75BP-400-S+

Mini-Circuits

50Ω 292 to 490 MHz SMA-Male to SMA-Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	KE1467
RoHS Status	Compliant
Environmental Ratings	ENV46

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html








Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	108.99	102.18	112.02	0.00	0.00	0.00	0.00	0.00	0.00
20	94.40	100.89	102.67	0.00	0.00	0.00	0.00	0.00	0.00
30	104.61	95.43	98.06	0.00	0.00	0.00	0.00	0.00	0.00
40	104.19	96.30	94.52	0.00	0.00	0.01	0.00	0.00	0.00
50	94.28	104.75	95.81	0.01	0.01	0.01	0.00	0.01	0.01
60	108.41	104.21	96.92	0.01	0.01	0.01	0.00	0.01	0.01
70	98.69	95.61	95.29	0.01	0.01	0.01	0.00	0.01	0.01
80	98.92	99.26	109.46	0.01	0.02	0.02	0.01	0.01	0.01
100	98.72	94.56	102.64	0.02	0.02	0.02	0.01	0.02	0.02
110	86.11	84.66	88.36	0.02	0.03	0.03	0.01	0.02	0.03
120	80.36	78.96	78.54	0.02	0.03	0.04	0.01	0.03	0.03
130	73.41	73.05	72.95	0.03	0.04	0.04	0.02	0.03	0.04
140	67.96	67.77	67.83	0.03	0.05	0.05	0.02	0.04	0.05
150	62.93	62.90	62.53	0.04	0.06	0.06	0.03	0.05	0.06
160	58.35	58.29	58.08	0.05	0.07	0.08	0.04	0.06	0.07
170	54.02	53.84	53.66	0.06	0.08	0.09	0.05	0.07	0.08
180	49.72	49.55	49.34	0.07	0.10	0.11	0.06	0.09	0.10
190	45.47	45.29	45.03	0.09	0.12	0.14	0.08	0.11	0.13
200	41.19	41.01	40.74	0.12	0.15	0.17	0.10	0.13	0.16
210	36.85	36.65	36.40	0.15	0.19	0.22	0.13	0.17	0.20
220	32.36	32.17	31.90	0.20	0.25	0.28	0.19	0.23	0.27
230	27.68	27.49	27.22	0.28	0.34	0.38	0.26	0.32	0.36
244	20.62	20.43	20.15	0.50	0.59	0.66	0.49	0.58	0.65
262	10.51	10.36	10.13	1.65	1.90	2.13	1.72	1.98	2.22
272	5.24	5.24	5.16	4.57	5.14	5.68	4.89	5.56	6.18
280	2.71	2.86	2.96	10.75	11.63	12.39	12.36	13.94	15.34
292	1.66	1.90	2.06	17.61	16.44	15.80	20.02	18.02	16.87
320	1.20	1.39	1.52	35.02	35.96	36.11	19.89	19.07	18.45
350	1.18	1.35	1.48	14.41	14.15	14.04	14.16	13.95	13.80
391	1.03	1.20	1.32	18.25	17.86	17.64	21.97	22.30	22.50
400	1.06	1.23	1.35	17.25	16.78	16.64	19.77	19.64	19.83
430	1.22	1.43	1.56	14.10	13.61	13.52	14.16	13.72	13.68
450	1.29	1.50	1.66	15.04	14.54	14.33	14.30	13.86	13.69
470	1.40	1.63	1.81	15.88	15.54	15.16	15.18	14.96	14.76
490	1.74	2.03	2.27	13.24	12.87	12.36	15.11	14.95	14.52
510	3.14	3.61	4.03	7.10	6.84	6.53	8.50	8.23	7.87
520	4.88	5.45	5.94	4.37	4.28	4.16	5.13	5.05	4.91
540	10.27	10.86	11.35	1.69	1.78	1.82	1.92	2.01	2.07
570	18.82	19.31	19.69	0.72	0.81	0.88	0.76	0.87	0.94
620	29.98	30.33	30.59	0.38	0.45	0.51	0.37	0.46	0.52
650	35.16	35.44	35.66	0.30	0.37	0.42	0.29	0.38	0.43
700	42.02	42.23	42.39	0.23	0.30	0.35	0.22	0.30	0.36
750	47.39	47.49	47.62	0.19	0.26	0.31	0.18	0.26	0.31
800	51.62	51.72	51.75	0.17	0.24	0.29	0.16	0.24	0.29
900	58.26	58.21	58.28	0.14	0.22	0.27	0.14	0.22	0.27
1000	63.66	63.50	63.71	0.13	0.22	0.27	0.13	0.22	0.27
1100	69.25	68.94	69.20	0.13	0.22	0.28	0.12	0.22	0.27
1200	77.28	75.61	75.45	0.14	0.23	0.30	0.12	0.23	0.28
1300	89.24	86.57	83.27	0.14	0.24	0.31	0.13	0.23	0.30
1400	92.50	101.74	92.81	0.15	0.25	0.32	0.13	0.24	0.31
1600	97.25	86.56	83.06	0.17	0.28	0.35	0.15	0.27	0.34
1800	73.80	72.09	70.95	0.19	0.30	0.37	0.17	0.29	0.36
2000	64.63	63.90	63.12	0.21	0.32	0.39	0.18	0.31	0.39
2200	59.00	58.51	58.15	0.23	0.34	0.41	0.20	0.33	0.41
2400	54.74	54.43	54.13	0.24	0.36	0.43	0.22	0.35	0.43
2600	51.23	50.99	50.82	0.26	0.37	0.44	0.23	0.36	0.44
2800	48.20	48.08	47.93	0.27	0.38	0.46	0.24	0.37	0.45
3000	45.57	45.40	45.35	0.28	0.39	0.47	0.24	0.38	0.46
3500	38.85	38.78	38.80	0.31	0.44	0.54	0.25	0.38	0.47
4000	33.63	33.28	33.04	0.33	0.49	0.61	0.22	0.37	0.47


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
292	10.16	9.98	9.82
296	9.48	9.31	9.16
300	8.80	8.66	8.53
304	8.21	8.10	8.00
308	7.74	7.65	7.57
312	7.36	7.29	7.23
316	7.05	7.00	6.95
320	6.79	6.75	6.71
324	6.56	6.52	6.49
328	6.35	6.32	6.29
332	6.16	6.13	6.10
336	5.98	5.95	5.93
340	5.82	5.80	5.77
344	5.68	5.66	5.64
348	5.55	5.53	5.52
352	5.45	5.43	5.42
356	5.36	5.35	5.34
360	5.30	5.28	5.27
364	5.24	5.23	5.22
368	5.20	5.19	5.18
372	5.16	5.16	5.15
376	5.13	5.13	5.13
380	5.10	5.11	5.10
384	5.08	5.08	5.08
388	5.05	5.06	5.06
391	5.03	5.04	5.04
396	5.00	5.01	5.01
400	4.97	4.98	4.99
406	4.94	4.94	4.95
412	4.91	4.91	4.92
418	4.89	4.90	4.91
424	4.89	4.90	4.91
430	4.91	4.92	4.93
436	4.96	4.96	4.98
442	5.02	5.03	5.05
448	5.11	5.13	5.15
454	5.22	5.24	5.26
460	5.35	5.38	5.41
470	5.63	5.67	5.71
480	6.02	6.07	6.12
490	6.53	6.58	6.61

Typical Performance Curves



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M
KE1467	.74 (18.80)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.362 (9.19)	.21 (5.33)	.362 (9.19)	1.00 (25.40)	.37 (9.40)	.18 (4.57)	.11 (2.79)

CASE #.	WT. GRAM
KE1467	24.4

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A