



WIDEBAND

Medium Power Amplifier ZX60-83MP-S+

50Ω 0.4 to 8 GHz SMA Female

THE BIG DEAL

- Wideband, 400 MHz to 8 GHz
- P1dB, +27dBm Typ.
- Excellent OIP3, +40 dBm Typ.
- 3.2dB Typ Noise Figure
- Reverse Polarity Protection



Generic photo used for illustration purposes only

Model No.	ZX60-83MP-S+
Case Style	GC957
Connectors	SMA Female

APPLICATIONS

- Sub- 6GHz 5G Infrastructure
- WiFi6E, IoT & ISM Applications
- Test & Measurement Equipment
- R&D Lab, Production, and OTA Test Systems

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

PRODUCT OVERVIEW

Mini-Circuits' ZX60-83MP-S+ is a medium power amplifier offering industry-leading performance over its full frequency range from 400 MHz to 8 GHz. This design operates on a single +8V supply @ 144 mA and comes in a rugged, compact unibody case (0.74" x 0.75" x 0.46") with integrated SMA female connectors, making it an excellent candidate for tough operating conditions and crowded system layouts.

KEY FEATURES

Feature	Advantages
Wideband: 0.4 to 8 GHz	Ideal for a wide range of transmitter applications including military, commercial wireless, and instrumentation.
Flat gain	Ideal for broadband or multi-band applications. Just one, cost-efficient model required for multiple frequency usage.
High OIP3, +38 dBm typ.	Provides enhanced linearity over a broad frequency range.
High gain, 20 dB typ.	Reduces the number of gain stages, lowering component count and overall system cost.
Rugged unibody construction	Mini-Circuits' unibody construction integrates the RF connectors into the case body, providing high reliability and excellent survivability in critical applications.

REV. OR
ECO-016347
ZX60-83MP-S+
MM/CP/AM
230201





WIDEBAND

Medium Power Amplifier **ZX60-83MP-S+**

Mini-Circuits

50Ω 0.4 to 8 GHz SMA Female

ELECTRICAL SPECIFICATIONS AT 25°C, Z₀ =50Ω AND +8V, UNLESS NOTED OTHERWISE

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		0.4		8	GHz
Gain	0.4		21.5		dB
	1.0		21.4		
	2.0		20.7		
	4.0		19.5		
	6.0		18.5		
	8.0		16.5		
Gain Flatness	0.4-4.0		±1.0		dB
	0.4-8.0		±2.5		
Input Return Loss	0.4		13.5		dB
	1.0		14.5		
	2.0		13.5		
	4.0		12.5		
	6.0		9.7		
	8.0		5.4		
Output Return Loss	0.4		10.0		dB
	1.0		12.5		
	2.0		13.2		
	4.0		16.2		
	6.0		13.2		
	8.0		11.3		
Output Power at 1dB Compression	0.4		27.0		dBm
	1.0		27.5		
	2.0		27.5		
	4.0		27.2		
	6.0		25.5		
	8.0		24.2		
Output IP3	0.4		40.0		dBm
	2.0		37.7		
	4.0		40.0		
	8.0		34.3		
Noise Figure	0.4		3.3		dB
	2.0		3.2		
	4.0		2.8		
	8.0		3.2		
Device Operating Voltage (V _{DD})	—	7.7	8.0	8.3	V
Device Operating Current (I _{DD})	—	—	144	175	mA

ABSOLUTE MAXIMUM RATINGS¹

Parameter	Ratings
Operating Temperature (Baseplate)	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Total Power Dissipation	1.4 W
Input Power	+22 dBm (5 minutes max.) +17 dBm (continuous)
DC Voltage V _{DD} ²	+8.8V

1. Permanent damage may occur if any of these limits are exceeded.

Electrical maximum ratings are not intended for continuous normal operation.

2. This module includes reverse voltage protection, however it does not include over voltage protection or internal voltage regulation. Caution must be used to not exceed the maximum rated voltage at all times.






WIDEBAND

Medium Power Amplifier **ZX60-83MP-S+**

Mini-Circuits

50Ω 0.4 to 8 GHz SMA Female

OUTLINE DRAWING



! NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminal. See Application Note. [AN-40-010](#).

OUTLINE DIMENSIONS (Inches) mm

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	wt
.74	.75	.46	1.18	.04	.17	.45	.59	.33	.21	.22	.14	1.00	.37	.18	.106	grams
18.80	19.1	11.68	30.0	1.02	4.32	11.4	14.99	8.38	5.33	5.59	3.56	25.40	9.40	4.57	2.69	23.0





WIDEBAND

Medium Power Amplifier **ZX60-83MP-S+**

Mini-Circuits

50Ω 0.4 to 8 GHz SMA Female

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Gain (dB)	VSWR (:1)		Power Out @1 dB COMPR. (dBm)	Noise Figure (dB)	Frequency (MHz)	Output IP3 (dBm)
		IN	OUT				
400	21.60	1.51	1.87	27.04	3.24	400	39.73
500	21.63	1.46	1.79	27.44	3.28	2000	37.55
600	21.63	1.44	1.73	27.22	3.22	4000	41.65
1000	21.44	1.43	1.64	27.70	3.29	8000	35.63
2000	20.71	1.51	1.51	27.69	3.14		
3000	19.89	1.51	1.32	27.44	3.12		
4000	19.57	1.61	1.32	27.05	2.86		
5000	19.11	1.69	1.35	26.65	2.81		
6000	18.58	1.93	1.43	25.75	2.97		
6600	18.17	2.17	1.48	25.54	3.16		
7000	17.87	2.44	1.53	25.29	3.29		
7600	17.19	2.90	1.66	24.41	3.27		
8000	16.70	3.37	1.68	24.24	3.23		








WIDEBAND

Medium Power Amplifier ZX60-83MP-S+

Mini-Circuits

50Ω 0.4 to 8 GHz SMA Female

TYPICAL PERFORMANCE GRAPHS



NOTES






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 8V	VSWR (:1)		NOISE FIGURE (dB) 8V	POUT @ 1 dB COMPRESSION (dBm) 8V	FREQUENCY (MHz)	OUTPUT IP3 (dBm) 8V
		IN 8V	OUT 8V				
400	21.60	1.51	1.87	3.24	27.04	400	39.73
500	21.63	1.46	1.79	3.28	27.44	2000	37.55
600	21.63	1.44	1.73	3.22	27.22	4000	41.65
700	21.60	1.43	1.70	3.24	27.22	8000	35.63
800	21.55	1.42	1.67	3.30	27.84		
900	21.50	1.42	1.65	3.26	27.78		
1000	21.44	1.43	1.64	3.29	27.70		
1200	21.30	1.44	1.61	3.25	27.66		
1400	21.16	1.46	1.59	3.27	27.79		
1600	21.01	1.48	1.57	3.31	28.04		
1800	20.83	1.50	1.54	3.20	27.67		
2000	20.71	1.51	1.51	3.14	27.69		
2200	20.55	1.52	1.48	3.10	27.74		
2400	20.39	1.53	1.46	3.03	28.21		
2600	20.19	1.51	1.43	3.15	27.67		
2800	20.00	1.49	1.37	3.16	27.34		
3000	19.89	1.51	1.32	3.12	27.44		
3200	19.85	1.54	1.32	3.07	27.80		
3400	19.79	1.56	1.33	3.09	27.36		
3600	19.72	1.57	1.34	3.02	27.39		
3800	19.64	1.59	1.32	2.90	27.57		
4000	19.57	1.61	1.32	2.86	27.05		
4200	19.49	1.63	1.33	2.81	27.09		
4400	19.39	1.64	1.33	2.78	27.59		
4600	19.30	1.64	1.33	2.86	27.03		
4800	19.21	1.67	1.33	2.89	26.87		
5000	19.11	1.69	1.35	2.81	26.65		
5200	19.00	1.71	1.38	2.82	26.53		
5400	18.89	1.74	1.39	2.87	26.08		
5600	18.79	1.79	1.39	2.98	26.59		
5800	18.69	1.85	1.41	2.87	26.67		
6000	18.58	1.93	1.43	2.97	25.75		
6200	18.47	2.01	1.47	2.94	25.86		
6400	18.34	2.10	1.47	3.03	25.60		
6600	18.17	2.17	1.48	3.16	25.54		
6800	18.02	2.29	1.51	3.39	25.11		
7000	17.87	2.44	1.53	3.29	25.29		
7200	17.56	2.55	1.53	3.30	24.59		
7400	17.38	2.70	1.59	3.18	25.01		
7600	17.19	2.90	1.66	3.27	24.41		
7800	16.96	3.13	1.70	3.28	24.57		
8000	16.70	3.37	1.68	3.23	24.24		

Typical Performance Curves




Case Style

GC

Outline Dimensions

GC957



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GC957	.74 (18.80)	.75 (19.15)	.46 (11.61)	1.18 (30.07)	.04 (1.02)	.17 (4.32)	.45 (11.40)	.59 (14.86)	.33 (8.31)	.21 (5.44)	.22 (5.59)	.14 (3.56)	1.00 (25.4)

CASE #.	P	Q	R	WT GRAMS
GC957	.37 (9.40)	.18 (4.57)	.106 (2.69)	23.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits[®]

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C