



LUMPED LC COAXIAL

Bandpass Filter

ZX75BP-75-S+

50Ω 60 to 90 MHz SMA-Male to SMA-Female

KEY FEATURES

- Insertion Loss, 4dB Max.
- Stop Band Return Loss, 18dB Typ.
- Stop Band Rejection, 30dB Typ.

APPLICATIONS

- Military Radar
- Maritime Mobile


PRODUCT OVERVIEW

ZX75BP-75-S+ is a 50Ω bandpass filter in a connectorized package covering 60 to 90MHz. This offers good matching within the passband and high rejection in stopband.



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM



ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Units	
Passband	Center Frequency	Fc	—	75	—	MHz	
	Insertion Loss	F1-F2	—	—	4	dB	
	Return Loss	F1-F2	60 - 90	11.7	17.7	—	dB
Stop Band, Lower	Rejection	DC-F3	DC - 30	35	—	—	dB
		F3-F4	30 - 37	20	—	—	dB
Stop Band, Upper	Rejection	F5-F6	122 - 155	20	—	—	dB
		F6-F7	155 - 2000	35	—	—	dB
		F7-F8	2000 - 3500	—	30	—	dB
Maximum Deviation from Linear Phase	—	Fc ± 15	—	—	±8	deg	

1. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.


ABSOLUTE MAXIMUM RATINGS²

Parameter	Ratings
Operating Temperature	-40°C to + 85°C
Storage Temperature	-55°C to + 100°C
Input Power ³	0.1W at 25°C

2. Permanent damage may occur if any of these limits are exceeded.

3. Power rating applies only to signals within the passband.

TYPICAL FREQUENCY RESPONSE AT +25°C





LUMPED LC COAXIAL

Bandpass Filter


ZX75BP-75-S+

Mini-Circuits


50Ω 60 to 90 MHz SMA-Male to SMA-Female

TYPICAL PERFORMANCE GRAPHS


ZX75BP-75-S+
INSERTION LOSS




ZX75BP-75-S+
INSERTION LOSS (Zoomed)




ZX75BP-75-S+
RETURN LOSS



ZX75BP-75-S+
GROUP DELAY



ZX75BP-75-S+
INSERTION PHASE &
DEVIATION FROM LINEAR PHASE AT 25°C





LUMPED LC COAXIAL

Bandpass Filter

ZX75BP-75-S+

50Ω 60 to 90 MHz SMA-Male to SMA-Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	KE1467
RoHS Status	Compliant
Environmental Ratings	ENV46

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Coaxial Band Pass Filter

ZX75BP-75-S+






Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10	104.83	99.01	101.62	0.01	0.01	0.01	0.01	0.01	0.01
12	90.56	96.05	101.44	0.01	0.02	0.02	0.01	0.02	0.02
14	87.77	87.84	88.91	0.02	0.03	0.03	0.02	0.02	0.03
16	81.06	82.67	83.99	0.03	0.04	0.04	0.02	0.03	0.04
20	70.41	70.18	69.95	0.05	0.06	0.07	0.05	0.06	0.06
22	65.09	64.83	64.94	0.06	0.08	0.09	0.06	0.08	0.08
25	57.75	57.50	57.32	0.10	0.12	0.13	0.09	0.11	0.12
30	46.04	45.81	45.71	0.18	0.22	0.24	0.18	0.21	0.24
35	34.62	34.41	34.26	0.37	0.44	0.49	0.36	0.43	0.48
37	29.96	29.74	29.58	0.51	0.60	0.66	0.50	0.59	0.66
40	22.73	22.54	22.39	0.87	1.02	1.12	0.85	1.01	1.12
45	10.54	10.54	10.54	2.98	3.42	3.73	3.00	3.46	3.78
50	3.44	3.78	3.99	13.34	14.14	14.71	13.84	14.73	15.35
55	2.18	2.48	2.68	20.33	20.17	20.05	19.93	19.82	19.73
60	1.85	2.11	2.28	19.05	19.03	19.00	18.79	18.87	18.92
65	1.66	1.91	2.07	25.65	25.45	25.19	26.76	27.23	27.49
70	1.62	1.86	2.02	25.45	25.12	24.84	26.92	26.93	26.91
75	1.64	1.88	2.04	22.52	23.19	23.64	22.65	23.36	23.83
80	1.69	1.95	2.12	33.95	38.28	41.53	30.70	31.40	31.10
85	1.86	2.15	2.34	24.47	23.41	22.74	24.13	23.15	22.49
90	2.20	2.55	2.80	25.01	23.63	22.72	28.54	26.42	24.90
100	8.22	8.84	9.27	3.33	3.42	3.46	3.34	3.42	3.45
122	29.75	30.04	30.24	0.54	0.61	0.64	0.53	0.60	0.63
140	40.42	40.57	40.69	0.33	0.38	0.40	0.32	0.37	0.39
150	44.84	44.96	45.02	0.27	0.31	0.34	0.26	0.31	0.33
155	46.76	46.85	46.91	0.25	0.29	0.31	0.24	0.28	0.31
200	58.57	58.45	58.37	0.14	0.18	0.19	0.14	0.18	0.20
300	69.80	69.93	69.81	0.08	0.12	0.13	0.08	0.12	0.13
400	77.22	76.83	77.46	0.06	0.10	0.12	0.06	0.10	0.12
500	84.92	84.86	84.67	0.06	0.11	0.13	0.06	0.10	0.13
600	98.71	100.90	100.12	0.06	0.11	0.14	0.06	0.11	0.14
700	88.37	91.17	91.71	0.06	0.12	0.16	0.06	0.12	0.15
800	86.50	100.62	94.66	0.07	0.14	0.17	0.07	0.14	0.17
900	93.70	102.38	102.22	0.07	0.15	0.19	0.07	0.15	0.19
1000	88.46	82.74	83.09	0.08	0.16	0.21	0.08	0.17	0.21
1100	78.77	78.02	76.65	0.09	0.18	0.23	0.09	0.18	0.23
1200	73.44	72.98	71.93	0.10	0.20	0.25	0.10	0.19	0.24
1300	69.24	68.55	68.26	0.11	0.21	0.27	0.10	0.20	0.26
1400	65.63	65.12	65.29	0.13	0.22	0.29	0.11	0.22	0.28
1500	63.12	62.75	62.30	0.14	0.24	0.30	0.12	0.24	0.29
1600	60.42	60.07	59.75	0.15	0.25	0.32	0.13	0.25	0.31
1700	58.84	58.81	58.60	0.16	0.26	0.34	0.20	0.29	0.35
1800	56.73	56.40	56.32	0.17	0.28	0.36	0.15	0.28	0.34
1900	54.80	54.50	54.50	0.18	0.29	0.36	0.16	0.29	0.35
2000	53.13	52.91	52.74	0.20	0.30	0.38	0.17	0.30	0.36
2100	51.49	51.30	51.20	0.21	0.32	0.39	0.18	0.31	0.37
2200	50.00	49.85	49.74	0.22	0.32	0.40	0.19	0.32	0.38
2300	48.62	48.38	48.36	0.23	0.34	0.41	0.20	0.33	0.39
2400	47.22	47.08	47.03	0.24	0.35	0.43	0.20	0.34	0.40
2500	45.94	45.78	45.76	0.25	0.36	0.44	0.21	0.34	0.41
2600	44.64	44.57	44.55	0.26	0.37	0.45	0.22	0.35	0.42
2700	43.49	43.42	43.42	0.27	0.39	0.47	0.23	0.36	0.43
2800	42.44	42.35	42.32	0.29	0.42	0.50	0.24	0.37	0.44
2900	41.49	41.36	41.31	0.36	0.50	0.58	0.26	0.40	0.48
3000	40.21	40.15	40.17	0.59	0.68	0.74	0.54	0.71	0.77
3100	39.62	39.40	39.31	0.38	0.54	0.62	0.31	0.49	0.55
3200	38.56	38.45	38.31	0.55	0.87	0.92	0.49	0.85	0.88
3300	37.64	36.95	36.85	1.11	0.90	1.01	0.92	0.74	0.83
3400	35.59	35.27	35.13	0.50	0.63	0.73	0.36	0.48	0.56
3500	34.07	33.72	33.54	0.45	0.63	0.74	0.30	0.44	0.52

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
60	28.78	28.61	28.50
61	27.83	27.70	27.61
62	27.02	26.91	26.83
63	26.31	26.22	26.15
64	25.70	25.62	25.56
65	25.15	25.09	25.04
66	24.67	24.61	24.58
67	24.24	24.20	24.16
68	23.86	23.82	23.79
69	23.52	23.49	23.47
70	23.22	23.20	23.18
71	22.95	22.94	22.94
72	22.73	22.73	22.73
73	22.54	22.55	22.57
74	22.40	22.43	22.44
75	22.30	22.33	22.36
76	22.25	22.28	22.31
77	22.23	22.27	22.30
78	22.24	22.29	22.33
79	22.30	22.35	22.39
80	22.39	22.44	22.49
81	22.52	22.58	22.64
82	22.69	22.76	22.82
83	22.93	23.01	23.07
84	23.22	23.31	23.38
85	23.60	23.70	23.78
86	24.07	24.18	24.26
87	24.63	24.74	24.82
88	25.28	25.39	25.46
89	26.01	26.09	26.14
90	26.76	26.80	26.81

Typical Performance Curves



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M
KE1467	.74 (18.80)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.362 (9.19)	.21 (5.33)	.362 (9.19)	1.00 (25.40)	.37 (9.40)	.18 (4.57)	.11 (2.79)

CASE #.	WT. GRAM
KE1467	24.4

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A